

酸化銀電池

SR1120

■適用範囲

当データシートは、酸化銀電池 SR1120 に適用します。

■適用用途


- 民生機器：家電機器・AV 機器・通信機器・情報機器・事務機器・家庭用ロボット機器といった民生機器、かつ、その機能が人命及び財産の保護に直接的にかかわらない機器に使用できる製品
- 医療機器(GHTF Class A)：国際分類クラス GHTF/IMDRF で Class A で規定される医療機器で、かつ、その機能が人命及び財産の保護に直接的にかかわらない機器に使用できる製品

■適用外用途

車載機器、医療機器 B・C・D 及び当データシートの「用途の限定」に書かれている用途

*車載機器、医療機器 GHTF Class B・C の対応品については、お客様とお取引のある弊社営業窓口・代理店・商社、またはお問い合わせフォーム(<https://www.murata.com/contactform>)までお問い合わせください。

■外形寸法 (mm)



■定格


公称電圧	1.55 V
公称容量 (終止電圧 1.2 V)	60 mAh
標準放電負荷 ※公称電圧/抵抗	15 kΩ (≒0.1mA)
標準質量	0.92 g
使用温度範囲	-10 ~ +60°C
水銀使用率 0%	

■刻印




■放電特性


load : 15kΩ temperature: 23°C




■ 放電負荷特性



■ 放電温度特性



■ 負荷/温度違い放電容量



■ 用途の限定

当データシートに記載の製品は、当データシート内で個別に記載の適用用途向けに設計・製造されたものであり、高度な性能・機能・品質・管理・安全性が要求される本注意書き末尾①から⑪までの用途への適合性・性能発揮・品質等を保証するものではありませんので、当データシート記載の適用用途に従ってご使用ください。

万が一、当データシート記載の適用用途以外の用途でご使用された場合、又は以下の①から⑪までの用途でご使用された場合(別途当データシート内に用途記載があるものは除く*)には、弊社は当該使用によって生じた不測の事故その他の損害に関する一切の責任を負いかねますのでご注意ください。

- ①航空機器 ②宇宙機器 ③海底機器 ④発電所制御機器 ⑤医療機器 ⑥輸送機器
- ⑦交通用信号機器 ⑧防災/防犯機器 ⑨産業用情報処理機器 ⑩燃焼/爆発制御機器
- ⑪その他上記機器と同等の機器

当データシートに記載の適用用途以外の用途に対応した製品については、お客様とお取引のある弊社営業窓口・代理店・商社、またはお問い合わせフォーム(<https://www.murata.com/contactform>)までお問い合わせください。

*製品によっては、①から⑪までの用途向けに設計・製造される場合があります、それらは弊社カタログ、仕様書、データシート等に個別で用途を記載しております。

*記載のデータ及び数値は、参考値であり保証値ではありません。

Silver Oxide batteries

SR1120

■ Scope

This data sheet is applicable to Silver Oxide Battery Model SR1120

■ Specific Applications

- Consumer equipment: Products that can be used in consumer equipment such as home appliances, audio/visual equipment, communication equipment, information equipment, office equipment, and household robotics, and whose functions are not directly related to the protection of human life and property.
- Medical equipment (GHTF Class A): Products that can be used for medical equipment regulated by Class A of the international classification class GHTF/IMDRF and whose functions do not directly relate to the protection of human life and property


■ Unsuitable Applications

Automotive equipment, medical equipment GHTF Class B, C, D and applications listed in "Limitation of applications" in this Data sheet.

* Automotive equipment and medical equipment GHTF Class B and C, please contact our sales offices, distribution agents, or trading companies with which you make a deal, or via our web contact form.

Contact form: <https://www.murata.com/contactform>

■ Dimensions (mm)



■ Monogram




■ Specifications


Nominal Voltage	1.55 V
Nominal Capacity (1.2V cutoff)	60 mAh
Standard Discharge Load ※Nominal Voltage/Standard Load	15 kΩ (≒0.1mA)
Weigh	0.92 g
Operating Temperature	-10 ~ +60°C
No mercury added	

■ Discharge Characteristics


load : 15kΩ temperature: 23°C




■ Discharge Characteristics



■ Discharge Characteristics on Temperature



■ Discharge Capacity on Temperature and Load



■ Limitation of Applications

The products listed in the Data sheet hereinafter the product(s) is called as the "Product(s)" are designed and manufactured for applications specified in the Data sheet. (hereinafter called as the "Specific Application").

We shall not warrant anything in connection with the Products including fitness, performance, adequateness, safety, or quality, in the case of applications listed in from (1) to (11) written at the end of this precautions, which may generally require high performance, function, quality, management of production or safety. Therefore, the Product shall be applied in compliance with the specific application.

WE DISCLAIM ANY LOSS AND DAMAGES ARISING FROM OR IN CONNECTION WITH THE PRODUCTS INCLUDING BUT NOT LIMITED TO THE CASE SUCH LOSS AND DAMAGES CAUSED BY THE UNEXPECTED ACCIDENT, IN EVENT THAT (i) THE PRODUCT IS APPLIED FOR THE PURPOSE WHICH IS NOT SPECIFIED AS THE SPECIFIC APPLICATION FOR THE PRODUCT, AND/OR (ii) THE PRODUCT IS APPLIED FOR ANY FOLLOWING APPLICATION PURPOSES FROM (1) TO (11) (EXCEPT THAT SUCH APPLICATION PURPOSE IS UNAMBIGUOUSLY SPECIFIED AS SPECIFIC APPLICATION FOR THE PRODUCT IN OUR CATALOG SPECIFICATION FORMS, DATASHEETS, OR OTHER DOCUMENTS OFFICIALLY ISSUED BY US*).

- (1) Aircraft equipment (2) Aerospace equipment (3) Undersea equipment (4) Power plant control equipment (5) Medical equipment
(6) Transportation equipment (7) Traffic control equipment (8) Disaster prevention/security equipment
(9) Industrial data-processing equipment (10) Combustion/explosion control equipment
(11) Equipment with complexity and/or required reliability equivalent to the applications listed in the above.

For exploring information of the Products which will be compatible with the particular purpose other than those specified in the Data sheet, please contact our sales offices, distribution agents, or trading companies with which you make a deal, or via our web contact form.

Contact form: <https://www.murata.com/contactform>

*We may design and manufacture particular Products for applications listed in (1) to (11). Provided that, in such case we shall unambiguously specify such Specific Application in the Data sheet without any exception. Therefore, any other documents and/or performances, whether exist or non-exist, shall not be deemed as the evidence to imply that we accept the applications listed in (1) to (11).

*Data is not guaranteed and is provided for reference purposes only.