

## ● Part Numbering

### Crystal Filter

(Part Number)

<b>XD</b>	<b>C</b>	<b>A</b>	<b>F</b>	<b>21M400</b>	<b>R</b>	<b>A</b>	<b>A00</b>	<b>L2</b>
①	②	③	④	⑤	⑥	⑦	⑧	⑨

#### ① Product ID

Product ID	
<b>XD</b>	Crystal Filter

#### ② Type · Lead Style

Code	Type · Lead Style
<b>C</b>	Monolithic SMD

#### ③ Size

Code	Size
<b>A</b>	7050

#### ④ Structure

Expressed by one-digit alphabet.

#### ⑤ Nominal Center Frequency

Expressed by six-digit alphanumeric. The unit is in hertz (Hz).  
Decimal point is expressed by capital letter "M".

#### ⑥ Bandwidth

Code	Bandwidth (3dB)
<b>M</b>	6.800 to 8.199kHz
<b>P</b>	10.000 to 11.999kHz
<b>Q</b>	12.000 to 14.999kHz
<b>R</b>	15.000 to 17.999kHz

#### ⑦ Number of Pole

Code	Number of Pole
<b>A</b>	2 (1 Element)
<b>G</b>	4 (1 Element)
<b>H</b>	4 (2 Elements)

#### ⑧ Individual Specification

Code	
***	Three-digit alphanumeric express Individual Specification.

#### ⑨ Packaging (Packging quantity is expressed by one-digit number in "\*\*")

Code	Packaging
<b>L*</b>	Plastic Taping ø330mm