# Part Numbering

## CERAFIL®

(Part Number)	SF S KA 4M50 CF 00 -R1 <b>0 2 3 4 5 6 9</b>
Product ID	
Product ID	
SF	Ceramic Filters

## Oscillation/Numbers of Element

Code	Oscillation/Numbers of Element
S	2 Elements Thickness Shear mode

#### 3Structure/Size

Code	Structure/Size
К□	Chip Type

□ is expressed "A" or subsequent code, which indicates the structure/size.

#### Nominal Center Frequency

Expressed by four-digit alphanumerics. The unit is in hertz (Hz). Decimal point is expressed by capital letter "M" in case of MHz.

## Product Specification Code (1)

Code	Product Specification Code (1)
BF	Tight Bandwidth Type
CF	Standard Bandwidth Type
DF	Broad Bandwidth Type
EF	Ultra-broad Bandwidth Type

#### Product Specification Code (2)

Code	Product Specification Code (2)
00	Standard Type

## Packaging

Code	Packaging
-B0	Bulk
-R1	Embossed Taping ø=330mm

With non-standard products, two-digit alphanumerics indicating "Individual Specification" is added between "6 Product Specification Code (2)" and "Packaging".