Part Numbering

Crystal Filter

(Part Number) XD C A F 21M400 R A A00 P0

1Product ID

Product ID	
XD	Crystal Filter

${\bf 2} \mathsf{Type} \cdot \mathsf{Lead} \; \mathsf{Style}$

Code	Туре · Lead Style
С	Monolithic SMD

Size

Code	Size
Α	7050

4Structure

Expressed by one alphabetic character.

6 Nominal Center Frequency

Expressed by six-digit alphanumeric. The unit is in hertz (Hz). Decimal point is expressed by capital letter ${}^{\rm H}M{}^{\rm H}$.

6Bandwidth

Code	Bandwidth (3dB)
М	6.800 to 8.199kHz
Р	10.000 to 11.999kHz
Q	12.000 to 14.999kHz
R	15.000 to 17.999kHz
E	1.800 to 2.199kHz
Н	3.300 to 3.899kHz

Number of Poles

Code	Number of Poles
Α	2 (1 Element)
G	4 (1 Element)
н	4 (2 Elements)

8Individual Specification

Code	
***	Three-digit Alphanumerics Express Individual Specification.

Code	Packaging
P*	Plastic Taping ø330mm