Part Numbering

Ceramic Trimmer Capacitors

(Part Number) TZ Y2 R 200 A C01 R00

1Product ID

Product ID	
TZ	Trimmer Capacitors

2Series/Terminal

Code	Series/Terminal
В4	4mm Size SMD Type
W4	4mm Size SMD Type
С3	3mm Size SMD Type
Y2	2mm Size SMD Type
R1	1mm Size SMD Type

3Temperature Characteristics

Code	Temperature Characteristics
Z	NP0ppm/°C
R	N750ppm/°C
K	N1000ppm/°C
Р	N1200ppm/°C

Please refer to ratings for tolerance of temperature characteristics.

Maximum Capacitance

Expressed by three-digit alphanumerics. The unit is pico-farad (pF). The first and second figures are significant digits, and the third figure expresses the number of zeros that follow the two numbers. If there is a decimal point, it is expressed by the capital letter "R". In this case, all figures are significant digits.

5Terminal Shape

Code	Terminal Shape
Α	Top Adjustment: TZR1, TZY2, TZC3, TZW4, TZB4
В	Top Adjustment: TZB4

Please refer to dimensions for terminal details.

6Individual Specifications

Code	Individual Specifications
001	TZR1, TZW4 Standard Type
C01	TZY2 Standard Type
A01	TZC3 Standard Type
A10	TZB4 No-cover Film Standard Type
B10	TZB4 with Cover Film Standard Type

Packaging

Code	Packaging
В00	Bulk
R00	Reel (Taping ø180mm)
R01*	Reel (Taping ø330mm)

^{*} TZB4 only.