

# MURATA CMCC products application list and supported products

For Signal line - Automotive Grade -



## Signal speed

(inch/mm)

	CAN/ Flex Ray (-10Mbps)	CAN-FD (-8Mbps)		A <sup>2</sup> B <sup>®</sup> (50Mbps)	Ethernet 100Base-T1 (100Mbps)	USB 2.0 (480Mbps)	Ethernet 1000Base-T1 (1000Mbps)	LVDS <*1> (-1.5Gbps)	HDMI 1.4 (1.7Gbps)	USB 3.0 (5Gbps)	HDMI 2.0 (6Gbps)	USB 3.1 (10Gbps)
		DCMR Class2	DCMR Class3									
1.25 x 1.0mm (0504/1210)						DLM11SN 900HZ2 		DLM11SN _HZ2 Series 				
2.0 x 1.2mm (0805/2012)						DLW21SZ 900HQ2 		DLW21SZ Series 	DLW21SZ900HQ2 			
3.2 x 2.5mm (1210/3225)	DLW32SH _XK2 Series 	DLW32SH 510XK2  DLW32SH 101XK2 	<b>NEW</b> DLW32SH 101XF2 	DLW32MH 101XK2 	DLW32MH 201XK2  <b>NEW</b> DLW32MH 201YK2 150°C 		DLW32MH 101XT2 					
4.5 x 3.2mm (1812/4532)	DLW43SH Series 				DLW43MH 201XK2 							

<\*1> SerDes