

# A part number list of sample kit for Medical & Healthcare



No.	Category	Part Number	Qty.	Note
1	MEMS Resonator	<a href="#">WMRAG32K76CS1C00R0</a>	5 pcs	0.9x0.6 mm, Fo=32.768kHz ±20ppm(Initial), CL=8pF
2	Crystal Units	<a href="#">XRCGB32M000F2P10R0</a>	5 pcs	2.0x1.6mm, Fo=32MHz ±20ppm(Initial), CL=6pF
3	Crystal Units	<a href="#">XRCMD32M000FXP54R0</a>	5 pcs	1.6x1.2mm, Fo=32MHz ±35ppm(Total), CL=6pF
4	Crystal Units	<a href="#">XRCGB32M000F2P29R0</a>	5 pcs	2.0x1.6mm, Fo=32MHz ±20ppm(Initial), CL=6pF
5	Crystal Units	<a href="#">XRCGB24M000FBP12R0</a>	5 pcs	2.0x1.6mm, Fo=24MHz ±15ppm(Initial), CL=6pF
6	Crystal Units	<a href="#">XRCMD48M000F1P2AR0</a>	5 pcs	1.6x1.2mm, Fo=48MHz ±20ppm(Initial), CL=7pF
7	Crystal Units	<a href="#">XRCMD32M000FXP53R0</a>	5 pcs	1.6x1.2mm, Fo=32MHz ±30ppm(Total), CL=6pF (-40 to 85° C)
8	Crystal Units	<a href="#">XRCMD32M000FXP52R0</a>	5 pcs	1.6x1.2mm, Fo=32MHz ±30ppm(Total), CL=6pF (-30 to 85° C)
9	Crystal Units	<a href="#">XRCGB32M000F2N13R0</a>	5 pcs	2.0x1.6mm, Fo=32MHz ±20ppm(Initial), CL=10pF
10	Crystal Units	<a href="#">XRCGB32M000F2P26R0</a>	5 pcs	2.0x1.6mm, Fo=32MHz ±20ppm(Initial), CL=5pF
11	Crystal Units	<a href="#">XRCMD32M000FZQ52R0</a>	5 pcs	1.6x1.2mm, Fo=32MHz -5 to +15 ppm(Initial), CL=6pF
12	Crystal Units	<a href="#">XRCMD40M000FXQ61R0</a>	5 pcs	1.6x1.2mm, Fo=40MHz ±20ppm(Total), CL=5.8pF
13	Crystal Units	<a href="#">XRCMD48M000FXQ60R0</a>	5 pcs	1.6x1.2mm, Fo=48MHz ±20ppm(Total), CL=5.8pF
14	Crystal Units	<a href="#">XRCMD32M000F1P00R0</a>	5 pcs	1.6x1.2mm, Fo=32MHz ±10ppm(Initial), CL=6pF
15	Crystal Units	<a href="#">XRCGB16M000FXN20R0</a>	5 pcs	2.0x1.6mm, Fo=16MHz ±40ppm(Total), CL=8pF
16	Crystal Units	<a href="#">XRCGB24M000F1H23R0</a>	5 pcs	2.0x1.6mm, Fo=24MHz ±10ppm(Initial), CL=6pF (-40 to 85° C)
17	Crystal Units	<a href="#">XRCGB24M000F1H24R0</a>	5 pcs	2.0x1.6mm, Fo=24MHz ±10ppm(Initial), CL=6pF (-40 to 110° C)
18	Crystal Units	<a href="#">XRCTD32M000N1P1AR0</a>	5 pcs	1.2x1.0mm, Fo=32MHz ±10ppm(Initial), CL=6pF
19	Piezo Sound Components	<a href="#">PKLCS1212E2000-R1</a>	5 pcs	Fo=2KHz, SPL=76dB typ. 12.0×12.0×3.0 mm, SMD
20	Piezo Sound Components	<a href="#">PKLCS1212E2400-R1</a>	5 pcs	Fo=2.4KHz, SPL=80dB typ. 12.0×12.0×3.0 mm, SMD
21	Piezo Sound Components	<a href="#">PKLCS1212E4001-R1</a>	5 pcs	Fo=4KHz, SPL=84dB typ. 12.0×12.0×3.0 mm, SMD
22	Piezo Sound Components	<a href="#">PKMCS0909E4000-R1</a>	5 pcs	Fo=4KHz, SPL=72dB typ. 9.0×9.0×1.9 mm, SMD