

Type	Frequency	Part Number	Size (mm)	Appearance ^{※1}	SPL(Typ.) (dB) [±1.5Vo-p, SquareWave,10cm]
Piezoelectric Diaphragms		7BB-20-6	φ20×0.42		-
Piezoelectric Sounders (Pin Type)	2kHz	PKM17EPP-2002-B0	φ17×9.8		79
		PKM22EPPH2001-B0 ^{※2}	φ22×12		79
	4kHz	PKM13EPYH4002-B0	φ12.6×6.9		78
		PKM13EPYH4000-A0 (Taping)			
		PKHPS0013E4000-A2 (Taping)	φ12.6×9.4		83
		PKM17EPPH4001-B0 ^{※2}	φ17×8.2		79
		PKM22EPPH4001-B0 ^{※2}	φ22×8.2		87
		PKM22EPPH4005-B0			86
		PKM22EPPH4007-B0		φ22×12	
		Piezoelectric Sounders (SMD Type)	2kHz	PKMCS1818E20A0-R1	18×18×8
PKLCS1212E2000-R1(For Consumer) PKLCS1212E20A0-R1(For Automotive)					76
2.4kHz	PKLCS1212E2400-R1(For Consumer) PKLCS1212E24A0-R1(For Automotive)		12×12×3		80
	PKLCS1212E4001-R1(For Consumer) PKLCS1212E40A1-R1(For Automotive)				84
4.8kHz	PKMCS0909E4000-R1		9×9×1.9		72
	PKMCS0909E48H0-R1		9×9×3.0		75
Piezoelectric Buzzer (Pin Type)	3.6kHz	PKB24SPCH3601-B0	φ24×9.7		90 (min.) [12Vdc,10cm]

※1 Appearance is not a full scale.

※2 Another lead length is available .

Product specifications are as of June 2021. They are subject to change without notice.

Copyright © Murata Manufacturing Co., Ltd. All rights reserved. No.PSE-21GA-0054