

タイプ	周波数	品番	サイズ (mm)	外観 ^{※1}	音圧レベル(Typ) [±1.5Vo-p, 方形波, 10cm] (dB)
圧電振動板		7BB-20-6	φ20×0.42		-
圧電サウンダ (ピンタイプ)	2kHz	PKM17EPP-2002-B0	φ17×9.8		79
		PKM22EPPH2001-B0 ^{※2}	φ22×12		79
	4kHz	PKHPS0013E4000-A2 (Taping)	φ12.6×9.4		83
		PKM22EPPH4001-B0 ^{※2}	φ22×8.2		87
		PKM22EPPH4005-B0			86
		PKM22EPPH4007-B0	φ22×12		92
圧電サウンダ (表面実装)	2kHz	PKMCS1818E20A0-R1	18×18×8		100 [12Vo-p, 10cm]
		PKLCS1212E2000-R1(民生用) PKLCS1212E20A0-R1(自動車用)	12×12×3		76
	2.4kHz	PKLCS1212E2400-R1(民生用) PKLCS1212E24A0-R1(自動車用)			80
		4kHz	PKLCS1212E4001-R1(民生用) PKLCS1212E40A1-R1(自動車用)		84
	4.8kHz		PKMCS0909E4000-R1	9×9×1.9	
		PKMCS0909E48H0-R1	9×9×3.0		75
圧電ブザー (ピンタイプ)	3.6kHz	PKB24SPCH3601-B0	φ24×9.7		90 (min.) [12Vdc, 10cm]

※1 原寸大ではありません。
※2 リード長さを選択可能です。

当内容は2022年1月現在のものです。記載内容について、予告なく変更することがございます。