

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application
BLE18PK100SN1	10		0.008	6000	1608/0603	General
BLE18PK160SN1	16		0.012	5000	1608/0603	General
BLE18PS080BH1			8ohm@100MHz	0.004	1608mm (0603inch)	Bias BLE18PS080.csv
BLE18PS080SH1			8ohm@100MHz	0.004	1608mm (0603inch)	Bias BLE18PS080.csv
BLE18PS080SZ1			8ohm@100MHz	0.004	1608mm (0603inch)	Bias BLE18PS080.csv
BLE18PS080SN1	8		0.004	8000	1608/0603	General
BLE32PN260SH1			26ohm@100MHz	0.0016	3225mm(1210inch)	Bias BLE32PN260SN1.csv
BLE32PN260SZ1			26ohm@100MHz	0.0016	3225mm(1210inch)	Bias BLE32PN260SN1.csv
BLE32PN300SH1			30ohm@100MHz	0.0016	3225mm(1210inch)	Bias BLE32PN300SN1.csv
BLE32PN300SZ1			30ohm@100MHz	0.0016	3225mm(1210inch)	Bias BLE32PN300SN1.csv
BLE32PN260SN1	26		0.0016	10000	3225/1210	General
BLE32PN300SN1	30		0.0016	10000	3225/1210	General
BLE32SN120BH1				0.0006	3225mm (1210inch)	Bias BLE32SN120.csv
BLE32SN120SH1				0.0006	3225mm (1210inch)	Bias BLE32SN120.csv
BLE32SN120SZ1				0.0006	3225mm (1210inch)	Bias BLE32SN120.csv
BLE32SN120SN1				0.0006	3225mm (1210inch)	Bias BLE32SN120.csv
BLE32SN120BN1	12		0.0006	20000	3225/1210	General
BLE32SN120SN1	12		0.0006	20000	3225/1210	General
BLF02GD162GNE			3	100	0402/01005	General
BLF02JD361GNE			0.45	380	0402/01005	General
BLF02JD471GNE			0.6	330	0402/01005	General
BLF02RD331GNE			0.6	330	0402/01005	General
BLF02RD471GNE			0.9	200	0402/01005	General
BLF03JD421GNE			0.28	480	0603/0201	General
BLF03JD421GZE				0.28	0603mm (0201inch)	
BLF03RD102GNE			1	220	0603/0201	General
BLF03RD501GNE			0.36	500	0603/0201	General
BLF03RD102GZE				1	0603mm (0201inch)	
BLF03RD501GZE				0.36	0603mm (0201inch)	
BLF03VK221SNG			0.155	800	0603/0201	General
BLF03VK600SNL			0.065	1200	0603/0201	General
BLM02AX100SN1	10		0.07	750	0402/01005	General
BLM02AX121SN1	120		0.5	250	0402/01005	General
BLM02AX241SN1	240		0.9	200	0402/01005	General
BLM02AX331SN1	330		1.4	150	0402/01005	General
BLM02AX700SN1	70		0.36	300	0402/01005	General
BLM02BB101SN1	100		2	125	0402/01005	General
BLM02BC100SN1	10	95	0.5	250	0402/01005	General
BLM02BC220SN1	22	240	0.9	200	0402/01005	General
BLM02BX121SN1	120		0.5	350	0402/01005	General
BLM02BX151SN1	150		0.7	280	0402/01005	General
BLM02BX241SN1	240		1.1	240	0402/01005	General
BLM02KX100SN1	10		0.03	1500	0402/01005	General
BLM02KX180SN1	18		0.045	1200	0402/01005	General
BLM02PX100SN1	10		0.05	1100	0402/01005	General
BLM02PX220SN1	22		0.11	750	0402/01005	General
BLM02PX330SN1	33		0.2	550	0402/01005	General
BLM02PX600SN1	60		0.25	500	0402/01005	General
BLM03AG100SZ1			10ohm@100MHz	0.1	0603mm (0201inch)	Bias BLM03AG100SN1.csv
BLM03AG102SZ1			1000ohm@100MHz	2.5	0603mm (0201inch)	Bias BLM03AG102SN1.csv
BLM03AG241SZ1			240ohm@100MHz	0.8	0603mm (0201inch)	Bias BLM03AG241SN1.csv
BLM03AG700SZ1			70ohm@100MHz	0.4	0603mm (0201inch)	Bias BLM03AG700SN1.csv
BLM03AG800SZ1			80ohm@100MHz	0.4	0603mm (0201inch)	Bias BLM03AG800SN1.csv
BLM03AG100SN1	10		0.1	500	0603/0201	General
BLM03AG102SN1	1000		2.5	100	0603/0201	General
BLM03AG121SN1	120		0.5	200	0603/0201	General
BLM03AG241SN1	240		0.8	200	0603/0201	General
BLM03AG601SN1	600		1.5	100	0603/0201	General
BLM03AG700SN1	70		0.4	200	0603/0201	General
BLM03AG800SN1	80		0.4	200	0603/0201	General
BLM03AG121SZ1			120ohm@100MHz	0.5	0603mm (0201inch)	
BLM03AG601SZ1			600ohm@100MHz	1.5	0603mm (0201inch)	
BLM03AX100SZ1			10ohm@100MHz	0.05	0603mm (0201inch)	Bias BLM03AX100SN1.csv
BLM03AX102SZ1			1000ohm@100MHz	1.25	0603mm (0201inch)	Bias BLM03AX102SN1.csv
BLM03AX121SZ1			120ohm@100MHz	0.23	0603mm (0201inch)	Bias BLM03AX121SN1.csv
BLM03AX241SZ1			240ohm@100MHz	0.38	0603mm (0201inch)	Bias BLM03AX241SN1.csv
BLM03AX601SZ1			600ohm@100MHz	0.85	0603mm (0201inch)	Bias BLM03AX601SN1.csv
BLM03AX100SN1	10		0.05	1000	0603/0201	General
BLM03AX102SN1	1000		1.25	200	0603/0201	General
BLM03AX121SN1	120		0.23	450	0603/0201	General
BLM03AX241SN1	240		0.38	350	0603/0201	General
BLM03AX601SN1	600		0.85	250	0603/0201	General
BLM03AX800SN1	80		0.18	500	0603/0201	General
BLM03AX800SZ1			80ohm@100MHz	0.18	0603mm (0201inch)	
BLM03BB100SZ1			10ohm@100MHz	0.4	0603mm (0201inch)	Bias BLM03BB100SN1.csv
BLM03BB121SZ1			120ohm@100MHz	1.5	0603mm (0201inch)	Bias BLM03BB121SN1.csv
BLM03BB470SZ1			47ohm@100MHz	0.7	0603mm (0201inch)	Bias BLM03BB470SN1.csv
BLM03BB750SZ1			75ohm@100MHz	1	0603mm (0201inch)	Bias BLM03BB750SN1.csv
BLM03BB100SN1	10		0.4	300	0603/0201	General
BLM03BB121SN1	120		1.5	100	0603/0201	General
BLM03BB220SN1	22		0.5	200	0603/0201	General
BLM03BB470SN1	47		0.7	200	0603/0201	General
BLM03BB750SN1	75		1	200	0603/0201	General
BLM03BB220SZ1			22ohm@100MHz	0.5	0603mm (0201inch)	
BLM03BC330SZ1			33ohm@100MHz	0.85	0603mm (0201inch)	Bias BLM03BC330SN1.csv
BLM03BC560SZ1			56ohm@100MHz	1.05	0603mm (0201inch)	Bias BLM03BC560SN1.csv
BLM03BC800SZ1			80ohm@100MHz	1.4	0603mm (0201inch)	Bias BLM03BC800SN1.csv
BLM03BC330SN1	33		0.85	150	0603/0201	General
BLM03BC560SN1	56		1.05	100	0603/0201	General
BLM03BC800SN1	80		1.4	100	0603/0201	General
BLM03BD121SZ1			120ohm@100MHz	0.5	0603mm (0201inch)	Bias BLM03BD121SN1.csv
BLM03BD241SZ1			240ohm@100MHz	0.8	0603mm (0201inch)	Bias BLM03BD241SN1.csv
BLM03BD471SZ1			470ohm@100MHz	1.5	0603mm (0201inch)	Bias BLM03BD471SN1.csv
BLM03BD601SZ1			600ohm@100MHz	1.7	0603mm (0201inch)	Bias BLM03BD601SN1.csv
BLM03BD750SZ1			75ohm@100MHz	0.4	0603mm (0201inch)	Bias BLM03BD750SN1.csv
BLM03BD121SN1	120		0.5	250	0603/0201	General
BLM03BD241SN1	240		0.8	200	0603/0201	General

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application
BLM03BD471SN1	470		1.5	215	0603/0201	General
BLM03BD601SN1	600		1.7	200	0603/0201	General
BLM03BD750SN1	75		0.4	300	0603/0201	General
BLM03BX102SN1	1000		1.7	170	0603/0201	General
BLM03BX182SN1	1800		2.5	140	0603/0201	General
BLM03EB250SH1			25ohm@100MHz	0.26	D603mm (0201inch)	BLM03EB250SN1
BLM03EB250SZ1			25ohm@100MHz	0.26	D603mm (0201inch)	BLM03EB250SN1
BLM03EB500SH1			50ohm@100MHz	0.58	D603mm (0201inch)	BLM03EB500SN1
BLM03EB500SZ1			50ohm@100MHz	0.58	D603mm (0201inch)	BLM03EB500SN1
BLM03EB250SN1	25	105	0.26	600	0603/0201	General
BLM03EB500SN1	50	255	0.58	400	0603/0201	General
BLM03HB191SZ1			190ohm@100MHz	2	D603mm (0201inch)	BLM03HB191SN1
BLM03HB191SN1	190	1150	2	150	0603/0201	General
BLM03HB401SN1	400	1850	2.8	125	0603/0201	General
BLM03HB401SZ1			400ohm@100MHz	2.8	D603mm (0201inch)	
BLM03HD331SZ1			330ohm@100MHz	1	D603mm (0201inch)	BLM03HD331SN1
BLM03HD471SZ1			470ohm@100MHz	1.3	D603mm (0201inch)	BLM03HD471SN1
BLM03HD601SZ1			600ohm@100MHz	1.7	D603mm (0201inch)	BLM03HD601SN1
BLM03HD102FN1	1000	2300	2.4	135	0603/0201	General
BLM03HD102SN1	1000	2300	2.9	120	0603/0201	General
BLM03HD152FN1	1500	2700	3.1	120	0603/0201	General
BLM03HD182FN1	1800	3000	3.8	100	0603/0201	General
BLM03HD331SN1	330	750	1	200	0603/0201	General
BLM03HD471SN1	470	1000	1.3	175	0603/0201	General
BLM03HD601SN1	600	1500	1.7	150	0603/0201	General
BLM03HD102FZ1			1000ohm@100MHz	2.4	D603mm (0201inch)	
BLM03HD102SZ1			1000ohm@100MHz	2.9	D603mm (0201inch)	
BLM03HD152FZ1			1500ohm@100MHz	3.1	D603mm (0201inch)	
BLM03HD182FZ1			1800ohm@100MHz	3.8	D603mm (0201inch)	
BLM03HG102SH1			1000ohm@100MHz	2.6	D603mm (0201inch)	BLM03HG102SN1
BLM03HG102SZ1			1000ohm@100MHz	2.6	D603mm (0201inch)	BLM03HG102SN1
BLM03HG122SH1			1200ohm@100MHz	3.5	D603mm (0201inch)	BLM03HG122SN1
BLM03HG122SZ1			1200ohm@100MHz	3.5	D603mm (0201inch)	BLM03HG122SN1
BLM03HG601SH1			600ohm@100MHz	1.6	D603mm (0201inch)	BLM03HG601SN1
BLM03HG601SZ1			600ohm@100MHz	1.6	D603mm (0201inch)	BLM03HG601SN1
BLM03HG102SN1	1000	1800	2.6	125	0603/0201	General
BLM03HG122SN1	1200	2000	3.5	100	0603/0201	General
BLM03HG601SN1	600	1000	1.6	150	0603/0201	General
BLM03PG220SZ1			22ohm@100MHz	0.065	D603mm (0201inch)	BLM03PG220SN1
BLM03PG330SZ1			33ohm@100MHz	0.09	D603mm (0201inch)	BLM03PG330SN1
BLM03PG220SN1	22		0.065	900	0603/0201	General
BLM03PG330SN1	33		0.09	750	0603/0201	General
BLM03PX121SZ1			120ohm@100MHz	0.16	D603mm (0201inch)	BLM03PX121SN1
BLM03PX220SZ1			22ohm@100MHz	0.04	D603mm (0201inch)	BLM03PX220SN1
BLM03PX330SZ1			33ohm@100MHz	0.055	D603mm (0201inch)	BLM03PX330SN1
BLM03PX800SZ1			80ohm@100MHz	0.13	D603mm (0201inch)	BLM03PX800SN1
BLM03PX121SN1	120		0.16	900	0603/0201	General
BLM03PX220SN1	22		0.04	1800	0603/0201	General
BLM03PX330SN1	33		0.055	1500	0603/0201	General
BLM03PX800SN1	80		0.13	1000	0603/0201	General
BLM15AG100SH1			10ohm@100MHz	0.05	1005mm (0402inch)	BLM15AG100SN1
BLM15AG100SZ1			10ohm@100MHz	0.025	1005mm (0402inch)	BLM15AG100SN1
BLM15AG102SH1			1000ohm@100MHz	1	1005mm (0402inch)	BLM15AG102SN1
BLM15AG102SZ1			1000ohm@100MHz	0.65	1005mm (0402inch)	BLM15AG102SN1
BLM15AG121SH1			120ohm@100MHz	0.25	1005mm (0402inch)	BLM15AG121SN1
BLM15AG121SZ1			120ohm@100MHz	0.19	1005mm (0402inch)	BLM15AG121SN1
BLM15AG221SH1			220ohm@100MHz	0.35	1005mm (0402inch)	BLM15AG221SN1
BLM15AG221SZ1			220ohm@100MHz	0.29	1005mm (0402inch)	BLM15AG221SN1
BLM15AG601SH1			600ohm@100MHz	0.6	1005mm (0402inch)	BLM15AG601SN1
BLM15AG601SZ1			600ohm@100MHz	0.52	1005mm (0402inch)	BLM15AG601SN1
BLM15AG100SN1	10		0.025	1000	1005/0402	General
BLM15AG102SN1	1000		0.65	300	1005/0402	General
BLM15AG121SN1	120		0.19	550	1005/0402	General
BLM15AG221SN1	220		0.29	450	1005/0402	General
BLM15AG601SN1	600		0.52	300	1005/0402	General
BLM15AG700SN1	70		0.15	600	1005/0402	General
BLM15AG700SH1			70ohm@100MHz	0.15	1005mm (0402inch)	
BLM15AG700SZ1			70ohm@100MHz	0.15	1005mm (0402inch)	
BLM15AX100SZ1			10ohm@100MHz	0.015	1005mm (0402inch)	BLM15AX100SN1
BLM15AX102SZ1			1000ohm@100MHz	0.49	1005mm (0402inch)	BLM15AX102SN1
BLM15AX300SZ1			30ohm@100MHz	0.06	1005mm (0402inch)	BLM15AX300SN1
BLM15AX100SN1	10		0.015	1740	1005/0402	General
BLM15AX102SN1	1000		0.49	350	1005/0402	General
BLM15AX121SN1	120		0.13	700	1005/0402	General
BLM15AX221SN1	220		0.18	600	1005/0402	General
BLM15AX300SN1	30		0.06	1100	1005/0402	General
BLM15AX601SN1	600		0.34	500	1005/0402	General
BLM15AX700SN1	70		0.1	780	1005/0402	General
BLM15AX121SZ1			120ohm@100MHz	0.13	1005mm (0402inch)	
BLM15AX221SZ1			220ohm@100MHz	0.18	1005mm (0402inch)	
BLM15AX601SZ1			600ohm@100MHz	0.34	1005mm (0402inch)	
BLM15AX700SZ1			70ohm@100MHz	0.1	1005mm (0402inch)	
BLM15BA220SZ1			22ohm@100MHz	0.3	1005mm (0402inch)	BLM15BA220SN1
BLM15BA330SZ1			33ohm@100MHz	0.4	1005mm (0402inch)	BLM15BA330SN1
BLM15BA750SZ1			75ohm@100MHz	0.8	1005mm (0402inch)	BLM15BA750SN1
BLM15BA050SN1	5		0.1	300	1005/0402	General
BLM15BA100SN1	10		0.2	300	1005/0402	General
BLM15BA220SN1	22		0.3	300	1005/0402	General
BLM15BA330SN1	33		0.4	300	1005/0402	General
BLM15BA470SN1	47		0.6	200	1005/0402	General
BLM15BA750SN1	75		0.8	200	1005/0402	General
BLM15BA050SZ1			5ohm@100MHz	0.1	1005mm (0402inch)	
BLM15BA100SZ1			10ohm@100MHz	0.2	1005mm (0402inch)	
BLM15BA470SZ1			47ohm@100MHz	0.6	1005mm (0402inch)	
BLM15BB050SN1	5		0.08	500	1005/0402	General
BLM15BB100SN1	10		0.1	300	1005/0402	General
BLM15BB121SN1	120		0.55	300	1005/0402	General

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application
BLM15BB220SN1	22		0.2	300	1005/0402	General
BLM15BB221SN1	220		0.8	200	1005/0402	General
BLM15BB470SN1	47		0.35	300	1005/0402	General
BLM15BB750SN1	75		0.4	300	1005/0402	General
BLM15BB050SH1			5ohm@100MHz	0.08	1005mm (0402inch)	
BLM15BB050SZ1			5ohm@100MHz	0.08	1005mm (0402inch)	
BLM15BB100SH1			10ohm@100MHz	0.1	1005mm (0402inch)	
BLM15BB100SZ1			10ohm@100MHz	0.1	1005mm (0402inch)	
BLM15BB121SH1			120ohm@100MHz	0.55	1005mm (0402inch)	
BLM15BB121SZ1			120ohm@100MHz	0.55	1005mm (0402inch)	
BLM15BB220SH1			22ohm@100MHz	0.2	1005mm (0402inch)	
BLM15BB220SZ1			22ohm@100MHz	0.2	1005mm (0402inch)	
BLM15BB221SH1			220ohm@100MHz	0.8	1005mm (0402inch)	
BLM15BB221SZ1			220ohm@100MHz	0.8	1005mm (0402inch)	
BLM15BB470SH1			47ohm@100MHz	0.35	1005mm (0402inch)	
BLM15BB470SZ1			47ohm@100MHz	0.35	1005mm (0402inch)	
BLM15BB750SH1			75ohm@100MHz	0.4	1005mm (0402inch)	
BLM15BB750SZ1			75ohm@100MHz	0.4	1005mm (0402inch)	
BLM15BC121SN1	120		0.45	350	1005/0402	General
BLM15BC241SN1	240		0.7	250	1005/0402	General
BLM15BC121SZ1			120ohm@100MHz	0.45	1005mm (0402inch)	
BLM15BC241SZ1			240ohm@100MHz	0.7	1005mm (0402inch)	
BLM15BD102SH1			1000ohm@100MHz	0.9	1005mm (0402inch)	BLM15BD102SN1, G
BLM15BD102SZ1			1000ohm@100MHz	0.9	1005mm (0402inch)	BLM15BD102SN1, G
BLM15BD221SZ1			220ohm@100MHz	0.4	1005mm (0402inch)	BLM15BD221SN1, G
BLM15BD750SZ1			75ohm@100MHz	0.2	1005mm (0402inch)	BLM15BD750SN1, G
BLM15BD102SN1	1000		0.9	200	1005/0402	General
BLM15BD121SN1	120		0.3	300	1005/0402	General
BLM15BD152SN1	1500		1	190	1005/0402	General
BLM15BD182SN1	1800		1.4	100	1005/0402	General
BLM15BD221SN1	220		0.4	300	1005/0402	General
BLM15BD471SN1	470		0.6	200	1005/0402	General
BLM15BD601SN1	600		0.65	200	1005/0402	General
BLM15BD750SN1	75		0.2	300	1005/0402	General
BLM15BD121SZ1			120ohm@100MHz	0.3	1005mm (0402inch)	
BLM15BD152SZ1			1500ohm@100MHz	1	1005mm (0402inch)	
BLM15BD182SH1			1800ohm@100MHz	1.4	1005mm (0402inch)	
BLM15BD182SZ1			1800ohm@100MHz	1.4	1005mm (0402inch)	
BLM15BD471SH1			470ohm@100MHz	0.6	1005mm (0402inch)	
BLM15BD471SZ1			470ohm@100MHz	0.6	1005mm (0402inch)	
BLM15BD601SH1			600ohm@100MHz	0.65	1005mm (0402inch)	
BLM15BD601SZ1			600ohm@100MHz	0.65	1005mm (0402inch)	
BLM15BX102SZ1			1000ohm@100MHz	0.65	1005mm (0402inch)	BLM15BX102SN1, G
BLM15BX121SZ1			120ohm@100MHz	0.17	1005mm (0402inch)	BLM15BX121SN1, G
BLM15BX182SZ1			1800ohm@100MHz	0.9	1005mm (0402inch)	BLM15BX182SN1, G
BLM15BX221SZ1			220ohm@100MHz	0.27	1005mm (0402inch)	BLM15BX221SN1, G
BLM15BX601SZ1			600ohm@100MHz	0.46	1005mm (0402inch)	BLM15BX601SN1, G
BLM15BX102SN1	1000		0.65	300	1005/0402	General
BLM15BX121SN1	120		0.17	600	1005/0402	General
BLM15BX182SN1	1800		0.9	250	1005/0402	General
BLM15BX221SN1	220		0.27	450	1005/0402	General
BLM15BX471SN1	470		0.41	350	1005/0402	General
BLM15BX601SN1	600		0.46	350	1005/0402	General
BLM15BX750SN1	75		0.15	600	1005/0402	General
BLM15BX471SZ1			470ohm@100MHz	0.41	1005mm (0402inch)	
BLM15BX750SZ1			75ohm@100MHz	0.15	1005mm (0402inch)	
BLM15EG121SH1			120ohm@100MHz	0.095	1005mm (0402inch)	BLM15EG121SN1, G
BLM15EG121SZ1			120ohm@100MHz	0.095	1005mm (0402inch)	BLM15EG121SN1, G
BLM15EG221SH1			220ohm@100MHz	0.28	1005mm (0402inch)	BLM15EG221SN1, G
BLM15EG221SZ1			220ohm@100MHz	0.28	1005mm (0402inch)	BLM15EG221SN1, G
BLM15EG121SN1	120	145	0.095	1500	1005/0402	General
BLM15EG221SN1	220	270	0.28	700	1005/0402	General
BLM15EX121SN1	120	170	0.075	1800	1005/0402	General
BLM15EX221SN1	220	300	0.14	1300	1005/0402	General
BLM15EX331SN1	330	450	0.205	1100	1005/0402	General
BLM15EX471SN1	470	630	0.28	950	1005/0402	General
BLM15GA750SZ1			75ohm@100MHz	1.3	1005mm (0402inch)	BLM15GA750SN1, G
BLM15GA750SN1	75	1000	1.3	200	1005/0402	General
BLM15GG221SZ1			220ohm@100MHz	0.7	1005mm (0402inch)	BLM15GG221SN1, G
BLM15GG471SZ1			470ohm@100MHz	1.3	1005mm (0402inch)	BLM15GG471SN1, G
BLM15GG221SN1	220	600	0.7	300	1005/0402	General
BLM15GG471SN1	470	1200	1.3	200	1005/0402	General
BLM15HB121SH1			120ohm@100MHz	0.7	1005mm (0402inch)	BLM15HB121SN1, G
BLM15HB121SZ1			120ohm@100MHz	0.7	1005mm (0402inch)	BLM15HB121SN1, G
BLM15HB121SN1	120	500	0.7	300	1005/0402	General
BLM15HB221SN1	220	900	1	250	1005/0402	General
BLM15HB221SH1			220ohm@100MHz	1	1005mm (0402inch)	
BLM15HB221SZ1			220ohm@100MHz	1	1005mm (0402inch)	
BLM15HD182BH1			1800ohm@100MHz	2.2	1005mm (0402inch)	BLM15HD182SN1, G
BLM15HD182SH1			1800ohm@100MHz	2.2	1005mm (0402inch)	BLM15HD182SN1, G
BLM15HD182SZ1			1800ohm@100MHz	2.2	1005mm (0402inch)	BLM15HD182SN1, G
BLM15HD102SN1	1000	2000	1.25	250	1005/0402	General
BLM15HD182SN1	1800	2700	2.2	200	1005/0402	General
BLM15HD601SN1	600	1400	0.85	300	1005/0402	General
BLM15HD102BH1			1000ohm@100MHz	1.25	1005mm (0402inch)	
BLM15HD102SH1			1000ohm@100MHz	1.25	1005mm (0402inch)	
BLM15HD102SZ1			1000ohm@100MHz	1.25	1005mm (0402inch)	
BLM15HD601BH1			600ohm@100MHz	0.85	1005mm (0402inch)	
BLM15HD601SH1			600ohm@100MHz	0.85	1005mm (0402inch)	
BLM15HD601SZ1			600ohm@100MHz	0.85	1005mm (0402inch)	
BLM15HG102BH1			1000ohm@100MHz	1.1	1005mm (0402inch)	BLM15HG102SN1, G
BLM15HG102SH1			1000ohm@100MHz	1.1	1005mm (0402inch)	BLM15HG102SN1, G
BLM15HG102SZ1			1000ohm@100MHz	1.1	1005mm (0402inch)	BLM15HG102SN1, G
BLM15HG601BH1			600ohm@100MHz	0.7	1005mm (0402inch)	BLM15HG601SN1, G
BLM15HG601SH1			600ohm@100MHz	0.7	1005mm (0402inch)	BLM15HG601SN1, G
BLM15HG601SZ1			600ohm@100MHz	0.7	1005mm (0402inch)	BLM15HG601SN1, G
BLM15HG102SN1	1000	1400	1.1	250	1005/0402	General
BLM15HG601SN1	600	1000	0.7	300	1005/0402	General

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application
BLM15KD121SN1	120		0.07	1500	1005/0402	General
BLM15KD200SN1	20		0.011	3800	1005/0402	General
BLM15KD300SN1	30		0.0125	3100	1005/0402	General
BLM15PD121SZ1			120ohm@100MHz	0.09	1005mm (0402inch)	BLM15PD121SN1.c
BLM15PD300SZ1			30ohm@100MHz	0.035	1005mm (0402inch)	Bias BLM15PD300.c
BLM15PD600SZ1			60ohm@100MHz	0.06	1005mm (0402inch)	Bias BLM15PD600.c
BLM15PD800SZ1			80ohm@100MHz	0.07	1005mm (0402inch)	BLM15PD800SN1.c
BLM15PD121SN1	120		0.09	1300	1005/0402	General
BLM15PD300SN1	30		0.035	2200	1005/0402	General
BLM15PD600SN1	60		0.06	1700	1005/0402	General
BLM15PD800SN1	80		0.07	1500	1005/0402	General
BLM15PE121SH1			120ohm@100MHz	0.09	1005mm (0402inch)	BLM15PE121SH1.c
BLM15PE181SH1			180ohm@100MHz	0.14	1005mm (0402inch)	BLM15PE181SH1.c
BLM15PE221SH1			220ohm@100MHz	0.17	1005mm (0402inch)	BLM15PE221SH1.c
BLM15PE300SH1			30ohm@100MHz	0.035	1005mm (0402inch)	BLM15PE300SH1.c
BLM15PE331SH1			330ohm@100MHz	0.21	1005mm (0402inch)	BLM15PE331SH1.c
BLM15PE471SH1			470ohm@100MHz	0.35	1005mm (0402inch)	BLM15PE471SH1.c
BLM15PE600SH1			60ohm@100MHz	0.06	1005mm (0402inch)	BLM15PE600SH1.c
BLM15PE601SH1			600ohm@100MHz	0.4	1005mm (0402inch)	BLM15PE601SH1.c
BLM15PE800SH1			80ohm@100MHz	0.07	1005mm (0402inch)	BLM15PE800SH1.c
BLM15PG100SN1	10		0.025	1000	1005/0402	General
BLM15PG100SZ1			10ohm@100MHz	0.025	1005mm (0402inch)	
BLM15PX121BH1			120ohm@100MHz	0.055	1005mm (0402inch)	BLM15PX121SN1.c
BLM15PX121SH1			120ohm@100MHz	0.055	1005mm (0402inch)	BLM15PX121SN1.c
BLM15PX121SZ1			120ohm@100MHz	0.055	1005mm (0402inch)	BLM15PX121SN1.c
BLM15PX181BH1			180ohm@100MHz	0.09	1005mm (0402inch)	BLM15PX181SN1.c
BLM15PX181SH1			180ohm@100MHz	0.09	1005mm (0402inch)	BLM15PX181SN1.c
BLM15PX181SZ1			180ohm@100MHz	0.09	1005mm (0402inch)	BLM15PX181SN1.c
BLM15PX221BH1			220ohm@100MHz	0.1	1005mm (0402inch)	BLM15PX221SN1.c
BLM15PX221SH1			220ohm@100MHz	0.1	1005mm (0402inch)	BLM15PX221SN1.c
BLM15PX221SZ1			220ohm@100MHz	0.1	1005mm (0402inch)	BLM15PX221SN1.c
BLM15PX330BH1			33ohm@100MHz	0.022	1005mm (0402inch)	BLM15PX330SN1.c
BLM15PX330SH1			33ohm@100MHz	0.022	1005mm (0402inch)	BLM15PX330SN1.c
BLM15PX330SZ1			33ohm@100MHz	0.022	1005mm (0402inch)	BLM15PX330SN1.c
BLM15PX331BH1			330ohm@100MHz	0.15	1005mm (0402inch)	BLM15PX331SN1.c
BLM15PX331SH1			330ohm@100MHz	0.15	1005mm (0402inch)	BLM15PX331SN1.c
BLM15PX331SZ1			330ohm@100MHz	0.15	1005mm (0402inch)	BLM15PX331SN1.c
BLM15PX471BH1			470ohm@100MHz	0.2	1005mm (0402inch)	BLM15PX471SN1.c
BLM15PX471SH1			470ohm@100MHz	0.2	1005mm (0402inch)	BLM15PX471SN1.c
BLM15PX471SZ1			470ohm@100MHz	0.2	1005mm (0402inch)	BLM15PX471SN1.c
BLM15PX600BH1			60ohm@100MHz	0.032	1005mm (0402inch)	BLM15PX600SN1.c
BLM15PX600SH1			60ohm@100MHz	0.032	1005mm (0402inch)	BLM15PX600SN1.c
BLM15PX600SZ1			60ohm@100MHz	0.032	1005mm (0402inch)	BLM15PX600SN1.c
BLM15PX601BH1			600ohm@100MHz	0.23	1005mm (0402inch)	BLM15PX601SN1.c
BLM15PX601SH1			600ohm@100MHz	0.23	1005mm (0402inch)	BLM15PX601SN1.c
BLM15PX601SZ1			600ohm@100MHz	0.23	1005mm (0402inch)	BLM15PX601SN1.c
BLM15PX800BH1			80ohm@100MHz	0.038	1005mm (0402inch)	BLM15PX800SN1.c
BLM15PX800SH1			80ohm@100MHz	0.038	1005mm (0402inch)	BLM15PX800SN1.c
BLM15PX800SZ1			80ohm@100MHz	0.038	1005mm (0402inch)	BLM15PX800SN1.c
BLM15PX121SN1	120		0.055	2000	1005/0402	General
BLM15PX181SN1	180		0.09	1500	1005/0402	General
BLM15PX221SN1	220		0.1	1400	1005/0402	General
BLM15PX330SN1	33		0.022	3000	1005/0402	General
BLM15PX331SN1	330		0.15	1200	1005/0402	General
BLM15PX471SN1	470		0.2	1000	1005/0402	General
BLM15PX600SN1	60		0.032	2500	1005/0402	General
BLM15PX601SN1	600		0.23	900	1005/0402	General
BLM15PX800SN1	80		0.038	2300	1005/0402	General
BLM18AG121BH1			120ohm@100MHz	0.18	1608mm (0603inch)	BLM18AG121SN1.c
BLM18AG121SH1			120ohm@100MHz	0.18	1608mm (0603inch)	BLM18AG121SN1.c
BLM18AG121SZ1			120ohm@100MHz	0.18	1608mm (0603inch)	BLM18AG121SN1.c
BLM18AG151BH1			150ohm@100MHz	0.25	1608mm (0603inch)	BLM18AG151SN1.c
BLM18AG151SH1			150ohm@100MHz	0.25	1608mm (0603inch)	BLM18AG151SN1.c
BLM18AG151SZ1			150ohm@100MHz	0.25	1608mm (0603inch)	BLM18AG151SN1.c
BLM18AG221BH1			220ohm@100MHz	0.25	1608mm (0603inch)	BLM18AG221SN1.c
BLM18AG221SH1			220ohm@100MHz	0.25	1608mm (0603inch)	BLM18AG221SN1.c
BLM18AG221SZ1			220ohm@100MHz	0.25	1608mm (0603inch)	BLM18AG221SN1.c
BLM18AG471WH1			470ohm@100MHz	0.35	1608mm (0603inch)	BLM18AG471WH1.c
BLM18AG601BH1			600ohm@100MHz	0.38	1608mm (0603inch)	BLM18AG601SH1.c
BLM18AG601SH1			600ohm@100MHz	0.38	1608mm (0603inch)	BLM18AG601SH1.c
BLM18AG601SZ1			600ohm@100MHz	0.38	1608mm (0603inch)	BLM18AG601SH1.c
BLM18AG102SN1	1000		0.5	450	1608/0603	General
BLM18AG121SN1	120		0.18	800	1608/0603	General
BLM18AG151SN1	150		0.25	700	1608/0603	General
BLM18AG221SN1	220		0.25	700	1608/0603	General
BLM18AG331SN1	330		0.3	600	1608/0603	General
BLM18AG471SN1	470		0.35	550	1608/0603	General
BLM18AG601SN1	600		0.38	500	1608/0603	General
BLM18AG102BH1			1000ohm@100MHz	0.5	1608mm (0603inch)	
BLM18AG102SH1			1000ohm@100MHz	0.5	1608mm (0603inch)	
BLM18AG102SZ1			1000ohm@100MHz	0.5	1608mm (0603inch)	
BLM18AG102WH1			1000ohm@100MHz	0.5	1608mm (0603inch)	
BLM18AG331BH1			330ohm@100MHz	0.3	1608mm (0603inch)	
BLM18AG331SH1			330ohm@100MHz	0.3	1608mm (0603inch)	
BLM18AG331SZ1			330ohm@100MHz	0.3	1608mm (0603inch)	
BLM18AG471BH1			470ohm@100MHz	0.35	1608mm (0603inch)	
BLM18AG471SH1			470ohm@100MHz	0.35	1608mm (0603inch)	
BLM18AG471SZ1			470ohm@100MHz	0.35	1608mm (0603inch)	
BLM18BA050SH1			5ohm@100MHz	0.2	1608mm (0603inch)	BLM18BA050SN1.c
BLM18BA050SZ1			5ohm@100MHz	0.2	1608mm (0603inch)	BLM18BA050SN1.c
BLM18BA100SH1			10ohm@100MHz	0.25	1608mm (0603inch)	BLM18BA100SN1.c
BLM18BA100SZ1			10ohm@100MHz	0.25	1608mm (0603inch)	BLM18BA100SN1.c
BLM18BA121SH1			120ohm@100MHz	0.9	1608mm (0603inch)	BLM18BA121SN1.c
BLM18BA121SZ1			120ohm@100MHz	0.9	1608mm (0603inch)	BLM18BA121SN1.c
BLM18BA220SH1			22ohm@100MHz	0.35	1608mm (0603inch)	BLM18BA220SN1.c
BLM18BA220SZ1			22ohm@100MHz	0.35	1608mm (0603inch)	BLM18BA220SN1.c
BLM18BA470SH1			47ohm@100MHz	0.55	1608mm (0603inch)	BLM18BA470SN1.c
BLM18BA470SZ1			47ohm@100MHz	0.55	1608mm (0603inch)	BLM18BA470SN1.c

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application
BLM18BA050SN1	5		0.2	500	1608/0603	General
BLM18BA100SN1	10		0.25	500	1608/0603	General
BLM18BA121SN1	120		0.9	200	1608/0603	General
BLM18BA220SN1	22		0.35	500	1608/0603	General
BLM18BA470SN1	47		0.55	300	1608/0603	General
BLM18BA750SN1	75		0.7	300	1608/0603	General
BLM18BA750SH1			75ohm@100MHz	0.7	1608mm (0603inch)	
BLM18BA750SZ1			75ohm@100MHz	0.7	1608mm (0603inch)	
BLM18BB050SH1			5ohm@100MHz	0.05	1608mm (0603inch)	BLM18BB050SN1
BLM18BB050SZ1			5ohm@100MHz	0.05	1608mm (0603inch)	BLM18BB050SN1
BLM18BB121SH1			120ohm@100MHz	0.3	1608mm (0603inch)	BLM18BB121SN1
BLM18BB121SZ1			120ohm@100MHz	0.3	1608mm (0603inch)	BLM18BB121SN1
BLM18BB141SH1			140ohm@100MHz	0.35	1608mm (0603inch)	BLM18BB141SN1
BLM18BB141SZ1			140ohm@100MHz	0.35	1608mm (0603inch)	BLM18BB141SN1
BLM18BB151SH1			150ohm@100MHz	0.37	1608mm (0603inch)	BLM18BB151SN1
BLM18BB151SZ1			150ohm@100MHz	0.37	1608mm (0603inch)	BLM18BB151SN1
BLM18BB220SH1			22ohm@100MHz	0.2	1608mm (0603inch)	BLM18BB220SN1
BLM18BB220SZ1			22ohm@100MHz	0.2	1608mm (0603inch)	BLM18BB220SN1
BLM18BB221SH1			220ohm@100MHz	0.45	1608mm (0603inch)	BLM18BB221SN1
BLM18BB221SZ1			220ohm@100MHz	0.45	1608mm (0603inch)	BLM18BB221SN1
BLM18BB331SH1			330ohm@100MHz	0.58	1608mm (0603inch)	BLM18BB331SN1
BLM18BB331SZ1			330ohm@100MHz	0.58	1608mm (0603inch)	BLM18BB331SN1
BLM18BB470SH1			47ohm@100MHz	0.25	1608mm (0603inch)	BLM18BB470SN1
BLM18BB470SZ1			47ohm@100MHz	0.25	1608mm (0603inch)	BLM18BB470SN1
BLM18BB471SH1			470ohm@100MHz	0.85	1608mm (0603inch)	BLM18BB471SN1
BLM18BB471SZ1			470ohm@100MHz	0.85	1608mm (0603inch)	BLM18BB471SN1
BLM18BB600SH1			60ohm@100MHz	0.25	1608mm (0603inch)	BLM18BB600SN1
BLM18BB600SZ1			60ohm@100MHz	0.25	1608mm (0603inch)	BLM18BB600SN1
BLM18BB050SN1	5		0.05	800	1608/0603	General
BLM18BB100SN1	10		0.1	700	1608/0603	General
BLM18BB121SN1	120		0.3	550	1608/0603	General
BLM18BB141SN1	140		0.35	500	1608/0603	General
BLM18BB151SN1	150		0.37	450	1608/0603	General
BLM18BB220SN1	22		0.2	700	1608/0603	General
BLM18BB221SN1	220		0.45	450	1608/0603	General
BLM18BB331SN1	330		0.58	400	1608/0603	General
BLM18BB470SN1	47		0.25	600	1608/0603	General
BLM18BB471SN1	470		0.85	300	1608/0603	General
BLM18BB600SN1	60		0.25	600	1608/0603	General
BLM18BB750SN1	75		0.3	600	1608/0603	General
BLM18BB100SH1			10ohm@100MHz	0.1	1608mm (0603inch)	
BLM18BB100SZ1			10ohm@100MHz	0.1	1608mm (0603inch)	
BLM18BB750SH1			75ohm@100MHz	0.3	1608mm (0603inch)	
BLM18BB750SZ1			75ohm@100MHz	0.3	1608mm (0603inch)	
BLM18BD121BH1			120ohm@100MHz	0.4	1608mm (0603inch)	BLM18BD121SN1
BLM18BD121SH1			120ohm@100MHz	0.4	1608mm (0603inch)	BLM18BD121SN1
BLM18BD121SZ1			120ohm@100MHz	0.4	1608mm (0603inch)	BLM18BD121SN1
BLM18BD151BH1			150ohm@100MHz	0.4	1608mm (0603inch)	BLM18BD151SH1
BLM18BD151SH1			150ohm@100MHz	0.4	1608mm (0603inch)	BLM18BD151SH1
BLM18BD151SZ1			150ohm@100MHz	0.4	1608mm (0603inch)	BLM18BD151SH1
BLM18BD182BH1			180ohm@100MHz	1.5	1608mm (0603inch)	BLM18BD182SN1
BLM18BD182SH1			180ohm@100MHz	1.5	1608mm (0603inch)	BLM18BD182SN1
BLM18BD182SZ1			180ohm@100MHz	1.5	1608mm (0603inch)	BLM18BD182SN1
BLM18BD221BH1			220ohm@100MHz	0.45	1608mm (0603inch)	BLM18BD221SN1
BLM18BD221SH1			220ohm@100MHz	0.45	1608mm (0603inch)	BLM18BD221SN1
BLM18BD221SZ1			220ohm@100MHz	0.45	1608mm (0603inch)	BLM18BD221SN1
BLM18BD222BH1			2200ohm@100MHz	1.5	1608mm (0603inch)	BLM18BD222SN1
BLM18BD222SH1			2200ohm@100MHz	1.5	1608mm (0603inch)	BLM18BD222SN1
BLM18BD222SZ1			2200ohm@100MHz	1.5	1608mm (0603inch)	BLM18BD222SN1
BLM18BD252BH1			2500ohm@100MHz	1.5	1608mm (0603inch)	BLM18BD252SN1
BLM18BD252SH1			2500ohm@100MHz	1.5	1608mm (0603inch)	BLM18BD252SN1
BLM18BD252SZ1			2500ohm@100MHz	1.5	1608mm (0603inch)	BLM18BD252SN1
BLM18BD421BH1			420ohm@100MHz	0.55	1608mm (0603inch)	BLM18BD421SN1
BLM18BD421SH1			420ohm@100MHz	0.55	1608mm (0603inch)	BLM18BD421SN1
BLM18BD421SZ1			420ohm@100MHz	0.55	1608mm (0603inch)	BLM18BD421SN1
BLM18BD470BH1			47ohm@100MHz	0.3	1608mm (0603inch)	BLM18BD470SN1
BLM18BD470SH1			47ohm@100MHz	0.3	1608mm (0603inch)	BLM18BD470SN1
BLM18BD470SZ1			47ohm@100MHz	0.3	1608mm (0603inch)	BLM18BD470SN1
BLM18BD471BH1			470ohm@100MHz	0.55	1608mm (0603inch)	BLM18BD471SN1
BLM18BD471SH1			470ohm@100MHz	0.55	1608mm (0603inch)	BLM18BD471SN1
BLM18BD471SZ1			470ohm@100MHz	0.55	1608mm (0603inch)	BLM18BD471SN1
BLM18BD601BH1			600ohm@100MHz	0.65	1608mm (0603inch)	BLM18BD601SN1
BLM18BD601SH1			600ohm@100MHz	0.65	1608mm (0603inch)	BLM18BD601SN1
BLM18BD601SZ1			600ohm@100MHz	0.65	1608mm (0603inch)	BLM18BD601SN1
BLM18BD102SN1	1000		0.85	200	1608/0603	General
BLM18BD121SN1	120		0.4	300	1608/0603	General
BLM18BD151SN1	150		0.4	300	1608/0603	General
BLM18BD152SN1	1500		1.2	150	1608/0603	General
BLM18BD182SN1	1800		1.5	150	1608/0603	General
BLM18BD221SN1	220		0.45	250	1608/0603	General
BLM18BD222SN1	2200		1.5	150	1608/0603	General
BLM18BD252SN1	2500		1.5	150	1608/0603	General
BLM18BD331SN1	330		0.5	250	1608/0603	General
BLM18BD421SN1	420		0.55	250	1608/0603	General
BLM18BD470SN1	47		0.3	500	1608/0603	General
BLM18BD471SN1	470		0.55	250	1608/0603	General
BLM18BD601SN1	600		0.65	200	1608/0603	General
BLM18BD102BH1			1000ohm@100MHz	0.85	1608mm (0603inch)	
BLM18BD102SH1			1000ohm@100MHz	0.85	1608mm (0603inch)	
BLM18BD102SZ1			1000ohm@100MHz	0.85	1608mm (0603inch)	
BLM18BD152BH1			1500ohm@100MHz	1.2	1608mm (0603inch)	
BLM18BD152SH1			1500ohm@100MHz	1.2	1608mm (0603inch)	
BLM18BD152SZ1			1500ohm@100MHz	1.2	1608mm (0603inch)	
BLM18BD331BH1			330ohm@100MHz	0.5	1608mm (0603inch)	
BLM18BD331SH1			330ohm@100MHz	0.5	1608mm (0603inch)	
BLM18BD331SZ1			330ohm@100MHz	0.5	1608mm (0603inch)	
BLM18DN151SH1			150ohm@100MHz	0.12	1608mm (0603inch)	BLM18DN151SN1
BLM18DN151SZ1			150ohm@100MHz	0.12	1608mm (0603inch)	BLM18DN151SN1

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application
BLM18DN221SH1			220ohm@100MHz	0.21	1608mm (0603inch)	BLM18DN221SN1.c
BLM18DN221SZ1			220ohm@100MHz	0.21	1608mm (0603inch)	BLM18DN221SN1.c
BLM18DN381SH1			380ohm@100MHz	0.325	1608mm (0603inch)	BLM18DN381SN1.c
BLM18DN381SZ1			380ohm@100MHz	0.325	1608mm (0603inch)	BLM18DN381SN1.c
BLM18DN601SH1			600ohm@100MHz	0.435	1608mm (0603inch)	Bias BLM18DN601.c
BLM18DN601SZ1			600ohm@100MHz	0.435	1608mm (0603inch)	Bias BLM18DN601.c
BLM18DN151SN1	150		0.12	1400	1608/0603	General
BLM18DN221SN1	220		0.21	1000	1608/0603	General
BLM18DN381SN1	380		0.325	850	1608/0603	General
BLM18DN601SN1	600		0.435	700	1608/0603	General
BLM18EG101TH1			100ohm@100MHz	0.045	1608mm (0603inch)	BLM18EG101TH1.c
BLM18EG101TZ1			100ohm@100MHz	0.045	1608mm (0603inch)	BLM18EG101TH1.c
BLM18EG121SH1			120ohm@100MHz	0.04	1608mm (0603inch)	BLM18EG121SN1.c
BLM18EG121SZ1			120ohm@100MHz	0.04	1608mm (0603inch)	BLM18EG121SN1.c
BLM18EG181SH1			180ohm@100MHz	0.05	1608mm (0603inch)	BLM18EG181SH1.c
BLM18EG221SZ1			220ohm@100MHz	0.05	1608mm (0603inch)	BLM18EG221SN1.c
BLM18EG221TH1			220ohm@100MHz	0.15	1608mm (0603inch)	BLM18EG221SN1.c
BLM18EG221TZ1			220ohm@100MHz	0.15	1608mm (0603inch)	BLM18EG221SN1.c
BLM18EG331TH1			330ohm@100MHz	0.21	1608mm (0603inch)	BLM18EG331TN1.c
BLM18EG331TZ1			330ohm@100MHz	0.21	1608mm (0603inch)	BLM18EG331TN1.c
BLM18EG391TH1			390ohm@100MHz	0.3	1608mm (0603inch)	BLM18EG391TH1.c
BLM18EG391TZ1			390ohm@100MHz	0.3	1608mm (0603inch)	BLM18EG391TH1.c
BLM18EG471SH1			470ohm@100MHz	0.21	1608mm (0603inch)	BLM18EG471SN1.c
BLM18EG471SZ1			470ohm@100MHz	0.21	1608mm (0603inch)	BLM18EG471SN1.c
BLM18EG601SH1			600ohm@100MHz	0.35	1608mm (0603inch)	BLM18EG601SN1.c
BLM18EG601SZ1			600ohm@100MHz	0.35	1608mm (0603inch)	BLM18EG601SN1.c
BLM18EG101TN1	100	140	0.045	2000	1608/0603	General
BLM18EG121SN1	120	145	0.04	2000	1608/0603	General
BLM18EG221SN1	220	260	0.05	2000	1608/0603	General
BLM18EG221TN1	220	300	0.15	1000	1608/0603	General
BLM18EG331TN1	330	450	0.21	500	1608/0603	General
BLM18EG391TN1	390	520	0.3	500	1608/0603	General
BLM18EG471SN1	470	550	0.21	500	1608/0603	General
BLM18EG601SN1	600	700	0.35	500	1608/0603	General
BLM18GG471SN1	470	1800	1.3	200	1608/0603	General
BLM18GG471SZ1			470ohm@100MHz	1.3	1608mm (0603inch)	
BLM18HB121SZ1			120ohm@100MHz	0.5	1608mm (0603inch)	BLM18HB121SN1.c
BLM18HB221SZ1			220ohm@100MHz	0.8	1608mm (0603inch)	BLM18HB221SN1.c
BLM18HB331SZ1			330ohm@100MHz	1.2	1608mm (0603inch)	BLM18HB331SN1.c
BLM18HB121SN1	120	500	0.5	200	1608/0603	General
BLM18HB221SN1	220	1100	0.8	100	1608/0603	General
BLM18HB331SN1	330	1600	1.2	50	1608/0603	General
BLM18HD102SH1			1000ohm@100MHz	1.8	1608mm (0603inch)	BLM18HD102SN1.c
BLM18HD102SZ1			1000ohm@100MHz	1.8	1608mm (0603inch)	BLM18HD102SN1.c
BLM18HD471SH1			470ohm@100MHz	1.2	1608mm (0603inch)	BLM18HD471SN1.c
BLM18HD471SZ1			470ohm@100MHz	1.2	1608mm (0603inch)	BLM18HD471SN1.c
BLM18HD601SH1			600ohm@100MHz	1.5	1608mm (0603inch)	BLM18HD601SN1.c
BLM18HD601SZ1			600ohm@100MHz	1.5	1608mm (0603inch)	BLM18HD601SN1.c
BLM18HD102SN1	1000	1700	1.8	50	1608/0603	General
BLM18HD471SN1	470	1000	1.2	100	1608/0603	General
BLM18HD601SN1	600	1200	1.5	100	1608/0603	General
BLM18HE102SH1			1000ohm@100MHz	0.35	1608mm (0603inch)	BLM18HE102SN1.c
BLM18HE102SZ1			1000ohm@100MHz	0.35	1608mm (0603inch)	BLM18HE102SN1.c
BLM18HE152SH1			1500ohm@100MHz	0.5	1608mm (0603inch)	BLM18HE152SN1.c
BLM18HE152SZ1			1500ohm@100MHz	0.5	1608mm (0603inch)	BLM18HE152SN1.c
BLM18HE601SH1			600ohm@100MHz	0.25	1608mm (0603inch)	BLM18HE601SN1.c
BLM18HE601SZ1			600ohm@100MHz	0.25	1608mm (0603inch)	BLM18HE601SN1.c
BLM18HE102SN1	1000	1000	0.35	600	1608/0603	General
BLM18HE152SN1	1500	1500	0.5	500	1608/0603	General
BLM18HE601SN1	600	600	0.25	800	1608/0603	General
BLM18HG102SH1			1000ohm@100MHz	1.6	1608mm (0603inch)	BLM18HG102SH1.c
BLM18HG102SZ1			1000ohm@100MHz	1.6	1608mm (0603inch)	BLM18HG102SH1.c
BLM18HG471SH1			470ohm@100MHz	0.85	1608mm (0603inch)	BLM18HG471SN1.c
BLM18HG471SZ1			470ohm@100MHz	0.85	1608mm (0603inch)	BLM18HG471SN1.c
BLM18HG601SH1			600ohm@100MHz	1	1608mm (0603inch)	BLM18HG601SN1.c
BLM18HG601SZ1			600ohm@100MHz	1	1608mm (0603inch)	BLM18HG601SN1.c
BLM18HG102SN1	1000	1000	1.6	100	1608/0603	General
BLM18HG471SN1	470	600	0.85	200	1608/0603	General
BLM18HG601SN1	600	700	1	200	1608/0603	General
BLM18HK102SN1	1000	1200	1.5	50	1608/0603	General
BLM18HK331SN1	330	400	0.5	200	1608/0603	General
BLM18HK471SN1	470	600	0.7	200	1608/0603	General
BLM18HK601SN1	600	700	0.9	100	1608/0603	General
BLM18KG101JH1			100ohm@100MHz	0.03	1608mm (0603inch)	BLM18KG101TN1.c
BLM18KG101TH1			100ohm@100MHz	0.03	1608mm (0603inch)	BLM18KG101TN1.c
BLM18KG101TZ1			100ohm@100MHz	0.03	1608mm (0603inch)	BLM18KG101TN1.c
BLM18KG101WH1			100ohm@100MHz	0.055	1608mm (0603inch)	BLM18KG101TN1.c
BLM18KG102BH1			1000ohm@100MHz	0.2	1608mm (0603inch)	BLM18KG102SN1.c
BLM18KG102SH1			1000ohm@100MHz	0.2	1608mm (0603inch)	BLM18KG102SN1.c
BLM18KG102SZ1			1000ohm@100MHz	0.2	1608mm (0603inch)	BLM18KG102SN1.c
BLM18KG102WH1			1000ohm@100MHz	0.23	1608mm (0603inch)	BLM18KG102SN1.c
BLM18KG121JH1			120ohm@100MHz	0.03	1608mm (0603inch)	BLM18KG121TN1.c
BLM18KG121TH1			120ohm@100MHz	0.03	1608mm (0603inch)	BLM18KG121TN1.c
BLM18KG121TZ1			120ohm@100MHz	0.03	1608mm (0603inch)	BLM18KG121TN1.c
BLM18KG121WH1			120ohm@100MHz	0.055	1608mm (0603inch)	BLM18KG121TN1.c
BLM18KG221BH1			220ohm@100MHz	0.05	1608mm (0603inch)	BLM18KG221SN1.c
BLM18KG221SH1			220ohm@100MHz	0.05	1608mm (0603inch)	BLM18KG221SN1.c
BLM18KG221SZ1			220ohm@100MHz	0.05	1608mm (0603inch)	BLM18KG221SN1.c
BLM18KG221WH1			220ohm@100MHz	0.08	1608mm (0603inch)	BLM18KG221SN1.c
BLM18KG260JH1			260ohm@100MHz	0.007	1608mm (0603inch)	BLM18KG260TN1.c
BLM18KG260TH1			260ohm@100MHz	0.007	1608mm (0603inch)	BLM18KG260TN1.c
BLM18KG260TZ1			260ohm@100MHz	0.007	1608mm (0603inch)	BLM18KG260TN1.c
BLM18KG260WH1			260ohm@100MHz	0.032	1608mm (0603inch)	BLM18KG260TN1.c
BLM18KG300JH1			300ohm@100MHz	0.01	1608mm (0603inch)	BLM18KG300TN1.c
BLM18KG300TH1			300ohm@100MHz	0.01	1608mm (0603inch)	BLM18KG300TN1.c
BLM18KG300TZ1			300ohm@100MHz	0.01	1608mm (0603inch)	BLM18KG300TN1.c
BLM18KG300WH1			300ohm@100MHz	0.035	1608mm (0603inch)	BLM18KG300TN1.c
BLM18KG331BH1			330ohm@100MHz	0.08	1608mm (0603inch)	BLM18KG331SN1.c

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application
BLM18KG331SH1			330ohm@100MHz	0.08	1608mm (0603inch)	BLM18KG331SN1.4
BLM18KG331SZ1			330ohm@100MHz	0.08	1608mm (0603inch)	BLM18KG331SN1.4
BLM18KG331WH1			330ohm@100MHz	0.11	1608mm (0603inch)	BLM18KG331SN1.4
BLM18KG471BH1			470ohm@100MHz	0.13	1608mm (0603inch)	BLM18KG471SN1.4
BLM18KG471SH1			470ohm@100MHz	0.13	1608mm (0603inch)	BLM18KG471SN1.4
BLM18KG471SZ1			470ohm@100MHz	0.13	1608mm (0603inch)	BLM18KG471SN1.4
BLM18KG471WH1			470ohm@100MHz	0.16	1608mm (0603inch)	BLM18KG471SN1.4
BLM18KG601SH1			600ohm@100MHz	0.15	1608mm (0603inch)	BLM18KG601SH1.4
BLM18KG601BH1			600ohm@100MHz	0.15	1608mm (0603inch)	BLM18KG601SN1.4
BLM18KG601SZ1			600ohm@100MHz	0.15	1608mm (0603inch)	BLM18KG601SN1.4
BLM18KG601WH1			600ohm@100MHz	0.18	1608mm (0603inch)	BLM18KG601SN1.4
BLM18KG700JH1			70ohm@100MHz	0.022	1608mm (0603inch)	BLM18KG700TN1.4
BLM18KG700TH1			70ohm@100MHz	0.022	1608mm (0603inch)	BLM18KG700TN1.4
BLM18KG700TZ1			70ohm@100MHz	0.022	1608mm (0603inch)	BLM18KG700TN1.4
BLM18KG700WH1			70ohm@100MHz	0.047	1608mm (0603inch)	BLM18KG700TN1.4
BLM18KG101TN1	100		0.03	3000	1608/0603	General
BLM18KG102SN1	1000		0.2	1000	1608/0603	General
BLM18KG121TN1	120		0.03	3000	1608/0603	General
BLM18KG221SN1	220		0.05	2200	1608/0603	General
BLM18KG260TN1	26		0.007	6000	1608/0603	General
BLM18KG300TN1	30		0.01	5000	1608/0603	General
BLM18KG331SN1	330		0.08	1700	1608/0603	General
BLM18KG471SN1	470		0.13	1500	1608/0603	General
BLM18KG601SN1	600		0.15	1300	1608/0603	General
BLM18KG700TN1	70		0.022	3500	1608/0603	General
BLM18KN102EH1			1000ohm@100MHz	0.2	1608mm (0603inch)	BLM18KN102EH1.4
BLM18KN101EH1			100ohm@100MHz	0.03	1608mm (0603inch)	
BLM18KN121EH1			120ohm@100MHz	0.03	1608mm (0603inch)	
BLM18KN221EH1			220ohm@100MHz	0.05	1608mm (0603inch)	
BLM18KN260EH1			26ohm@100MHz	0.007	1608mm (0603inch)	
BLM18KN300EH1			30ohm@100MHz	0.01	1608mm (0603inch)	
BLM18KN331EH1			330ohm@100MHz	0.08	1608mm (0603inch)	
BLM18KN471EH1			470ohm@100MHz	0.13	1608mm (0603inch)	
BLM18KN601EH1			600ohm@100MHz	0.15	1608mm (0603inch)	
BLM18KN700EH1			70ohm@100MHz	0.022	1608mm (0603inch)	
BLM18PG121SH1			120ohm@100MHz	0.05	1608mm (0603inch)	BLM18PG121SN1.4
BLM18PG121SZ1			120ohm@100MHz	0.05	1608mm (0603inch)	BLM18PG121SN1.4
BLM18PG181SH1			180ohm@100MHz	0.09	1608mm (0603inch)	BLM18PG181SN1.4
BLM18PG181SZ1			180ohm@100MHz	0.09	1608mm (0603inch)	BLM18PG181SN1.4
BLM18PG221SH1			220ohm@100MHz	0.1	1608mm (0603inch)	BLM18PG221SN1.4
BLM18PG221SZ1			220ohm@100MHz	0.1	1608mm (0603inch)	BLM18PG221SN1.4
BLM18PG300SH1			30ohm@100MHz	0.05	1608mm (0603inch)	BLM18PG300SN1.4
BLM18PG300SZ1			30ohm@100MHz	0.05	1608mm (0603inch)	BLM18PG300SN1.4
BLM18PG330SH1			330ohm@100MHz	0.025	1608mm (0603inch)	BLM18PG330SN1.4
BLM18PG330SZ1			330ohm@100MHz	0.025	1608mm (0603inch)	BLM18PG330SN1.4
BLM18PG331SH1			330ohm@100MHz	0.15	1608mm (0603inch)	BLM18PG331SN1.4
BLM18PG331SZ1			330ohm@100MHz	0.15	1608mm (0603inch)	BLM18PG331SN1.4
BLM18PG471SH1			470ohm@100MHz	0.2	1608mm (0603inch)	BLM18PG471SN1.4
BLM18PG471SZ1			470ohm@100MHz	0.2	1608mm (0603inch)	BLM18PG471SN1.4
BLM18PG600SH1			60ohm@100MHz	0.1	1608mm (0603inch)	BLM18PG600SN1.4
BLM18PG600SZ1			60ohm@100MHz	0.1	1608mm (0603inch)	BLM18PG600SN1.4
BLM18PG121SN1	120		0.05	2000	1608/0603	General
BLM18PG181SN1	180		0.09	1500	1608/0603	General
BLM18PG221SN1	220		0.1	1400	1608/0603	General
BLM18PG300SN1	30		0.05	1000	1608/0603	General
BLM18PG330SN1	33		0.025	3000	1608/0603	General
BLM18PG331SN1	330		0.15	1200	1608/0603	General
BLM18PG471SN1	470		0.2	1000	1608/0603	General
BLM18PG600SN1	60		0.1	1000	1608/0603	General
BLM18RK102SN1	1000		0.8	200	1608/0603	General
BLM18RK121SN1	120		0.25	200	1608/0603	General
BLM18RK221SN1	220		0.3	200	1608/0603	General
BLM18RK471SN1	470		0.5	200	1608/0603	General
BLM18RK601SN1	600		0.6	200	1608/0603	General
BLM18SD220SN1	22		0.008	6000	1608/0603	General
BLM18SG121TZ1			120ohm@100MHz	0.025	1608mm (0603inch)	BLM18SG121TN1.4
BLM18SG221TZ1			220ohm@100MHz	0.04	1608mm (0603inch)	BLM18SG221TN1.4
BLM18SG260TZ1			26ohm@100MHz	0.007	1608mm (0603inch)	BLM18SG260TN1.4
BLM18SG331TZ1			330ohm@100MHz	0.07	1608mm (0603inch)	BLM18SG331TN1.4
BLM18SG700TZ1			70ohm@100MHz	0.02	1608mm (0603inch)	BLM18SG700TN1.4
BLM18SG121TN1	120		0.025	3000	1608/0603	General
BLM18SG221TN1	220		0.04	2500	1608/0603	General
BLM18SG260TN1	26		0.007	6000	1608/0603	General
BLM18SG330SN1	33		0.008	6000	1608/0603	General
BLM18SG331TN1	330		0.07	1500	1608/0603	General
BLM18SG700TN1	70		0.02	4000	1608/0603	General
BLM18SN220TH1			22ohm@100MHz	0.004	1608mm (0603inch)	BLM18SN220TN1.4
BLM18SN220TZ1			22ohm@100MHz	0.004	1608mm (0603inch)	BLM18SN220TN1.4
BLM18SN220TN1	22		0.004	8000	1608/0603	General
BLM18SP101SN1	100		0.022	3700	1608/0603	General
BLM18SP102SN1	1000		0.185	1200	1608/0603	General
BLM18SP221SN1	220		0.04	2800	1608/0603	General
BLM18SP300SN1	30		0.008	6000	1608/0603	General
BLM18SP601SN1	600		0.14	1500	1608/0603	General
BLM18SP101SH1			100ohm@100MHz	0.022	1608mm (0603inch)	
BLM18SP101SZ1			100ohm@100MHz	0.022	1608mm (0603inch)	
BLM18SP102SH1			1000ohm@100MHz	0.185	1608mm (0603inch)	
BLM18SP102SZ1			1000ohm@100MHz	0.185	1608mm (0603inch)	
BLM18SP221SH1			220ohm@100MHz	0.04	1608mm (0603inch)	
BLM18SP221SZ1			220ohm@100MHz	0.04	1608mm (0603inch)	
BLM18SP300SH1			30ohm@100MHz	0.008	1608mm (0603inch)	
BLM18SP300SZ1			30ohm@100MHz	0.008	1608mm (0603inch)	
BLM18SP601SH1			600ohm@100MHz	0.14	1608mm (0603inch)	
BLM18SP601SZ1			600ohm@100MHz	0.14	1608mm (0603inch)	
BLM18TG102TN1	1000		0.6	100	1608/0603	General
BLM18TG121TN1	120		0.25	200	1608/0603	General
BLM18TG221TN1	220		0.3	200	1608/0603	General
BLM18TG601TN1	600		0.45	200	1608/0603	General

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application
BLM21AG102BH1			1000ohm@100MHz	0.27	2012mm (0805inch)	BLM21AG102SN1.4
BLM21AG102SH1			1000ohm@100MHz	0.27	2012mm (0805inch)	BLM21AG102SN1.4
BLM21AG102SZ1			1000ohm@100MHz	0.27	2012mm (0805inch)	BLM21AG102SN1.4
BLM21AG121BH1			120ohm@100MHz	0.09	2012mm (0805inch)	BLM21AG121SN1.4
BLM21AG121SH1			120ohm@100MHz	0.09	2012mm (0805inch)	BLM21AG121SN1.4
BLM21AG121SZ1			120ohm@100MHz	0.09	2012mm (0805inch)	BLM21AG121SN1.4
BLM21AG151BH1			150ohm@100MHz	0.09	2012mm (0805inch)	BLM21AG151SN1.4
BLM21AG151SH1			150ohm@100MHz	0.09	2012mm (0805inch)	BLM21AG151SN1.4
BLM21AG151SZ1			150ohm@100MHz	0.09	2012mm (0805inch)	BLM21AG151SN1.4
BLM21AG601BH1			600ohm@100MHz	0.2	2012mm (0805inch)	BLM21AG601SN1.4
BLM21AG601SH1			600ohm@100MHz	0.2	2012mm (0805inch)	BLM21AG601SN1.4
BLM21AG601SZ1			600ohm@100MHz	0.2	2012mm (0805inch)	BLM21AG601SN1.4
BLM21AG102SN1	1000		0.27	600	2012/0805	General
BLM21AG121SN1	120		0.09	1000	2012/0805	General
BLM21AG151SN1	150		0.09	1000	2012/0805	General
BLM21AG221SN1	220		0.12	900	2012/0805	General
BLM21AG331SN1	330		0.15	800	2012/0805	General
BLM21AG471SN1	470		0.18	700	2012/0805	General
BLM21AG601SN1	600		0.2	700	2012/0805	General
BLM21AG221BH1			220ohm@100MHz	0.12	2012mm (0805inch)	
BLM21AG221SH1			220ohm@100MHz	0.12	2012mm (0805inch)	
BLM21AG221SZ1			220ohm@100MHz	0.12	2012mm (0805inch)	
BLM21AG331BH1			330ohm@100MHz	0.15	2012mm (0805inch)	
BLM21AG331SH1			330ohm@100MHz	0.15	2012mm (0805inch)	
BLM21AG331SZ1			330ohm@100MHz	0.15	2012mm (0805inch)	
BLM21AG471BH1			470ohm@100MHz	0.18	2012mm (0805inch)	
BLM21AG471SH1			470ohm@100MHz	0.18	2012mm (0805inch)	
BLM21AG471SZ1			470ohm@100MHz	0.18	2012mm (0805inch)	
BLM21BB050SH1			5ohm@100MHz	0.02	2012mm (0805inch)	BLM21BB050SN1.4
BLM21BB050SZ1			5ohm@100MHz	0.02	2012mm (0805inch)	BLM21BB050SN1.4
BLM21BB121SH1			120ohm@100MHz	0.19	2012mm (0805inch)	BLM21BB121SN1.4
BLM21BB121SZ1			120ohm@100MHz	0.19	2012mm (0805inch)	BLM21BB121SN1.4
BLM21BB201SH1			200ohm@100MHz	0.26	2012mm (0805inch)	BLM21BB201SN1.4
BLM21BB201SZ1			200ohm@100MHz	0.26	2012mm (0805inch)	BLM21BB201SN1.4
BLM21BB221SH1			220ohm@100MHz	0.26	2012mm (0805inch)	BLM21BB221SN1.4
BLM21BB221SZ1			220ohm@100MHz	0.26	2012mm (0805inch)	BLM21BB221SN1.4
BLM21BB331SH1			330ohm@100MHz	0.33	2012mm (0805inch)	BLM21BB331SN1.4
BLM21BB331SZ1			330ohm@100MHz	0.33	2012mm (0805inch)	BLM21BB331SN1.4
BLM21BB471SH1			470ohm@100MHz	0.4	2012mm (0805inch)	BLM21BB471SN1.4
BLM21BB471SZ1			470ohm@100MHz	0.4	2012mm (0805inch)	BLM21BB471SN1.4
BLM21BB600SH1			60ohm@100MHz	0.13	2012mm (0805inch)	BLM21BB600SN1.4
BLM21BB600SZ1			60ohm@100MHz	0.13	2012mm (0805inch)	BLM21BB600SN1.4
BLM21BB750SH1			75ohm@100MHz	0.16	2012mm (0805inch)	BLM21BB750SN1.4
BLM21BB750SZ1			75ohm@100MHz	0.16	2012mm (0805inch)	BLM21BB750SN1.4
BLM21BB050SN1	5		0.02	1000	2012/0805	General
BLM21BB121SN1	120		0.19	600	2012/0805	General
BLM21BB151SN1	150		0.21	600	2012/0805	General
BLM21BB201SN1	200		0.26	500	2012/0805	General
BLM21BB221SN1	220		0.26	500	2012/0805	General
BLM21BB331SN1	330		0.33	400	2012/0805	General
BLM21BB471SN1	470		0.4	400	2012/0805	General
BLM21BB600SN1	60		0.13	800	2012/0805	General
BLM21BB750SN1	75		0.16	700	2012/0805	General
BLM21BB151SH1			150ohm@100MHz	0.21	2012mm (0805inch)	
BLM21BB151SZ1			150ohm@100MHz	0.21	2012mm (0805inch)	
BLM21BD121SH1			120ohm@100MHz	0.25	2012mm (0805inch)	BLM21BD121SN1.4
BLM21BD121SZ1			120ohm@100MHz	0.25	2012mm (0805inch)	BLM21BD121SN1.4
BLM21BD222SH1			2250ohm@100MHz	0.6	2012mm (0805inch)	BLM21BD222TN1.4
BLM21BD222SZ1			2250ohm@100MHz	0.6	2012mm (0805inch)	BLM21BD222TN1.4
BLM21BD222TH1			2200ohm@100MHz	0.6	2012mm (0805inch)	BLM21BD222TN1.4
BLM21BD222TZ1			2200ohm@100MHz	0.6	2012mm (0805inch)	BLM21BD222TN1.4
BLM21BD272SH1			2700ohm@100MHz	0.8	2012mm (0805inch)	BLM21BD272SH1.4
BLM21BD272SZ1			2700ohm@100MHz	0.8	2012mm (0805inch)	BLM21BD272SH1.4
BLM21BD601SH1			600ohm@100MHz	0.35	2012mm (0805inch)	BLM21BD601SN1.4
BLM21BD601SZ1			600ohm@100MHz	0.35	2012mm (0805inch)	BLM21BD601SN1.4
BLM21BD102SN1	1000		0.4	250	2012/0805	General
BLM21BD121SN1	120		0.25	350	2012/0805	General
BLM21BD151SN1	150		0.25	350	2012/0805	General
BLM21BD152SN1	1500		0.45	250	2012/0805	General
BLM21BD182SN1	1800		0.5	250	2012/0805	General
BLM21BD221SN1	220		0.25	350	2012/0805	General
BLM21BD222SN1	2250		0.6	250	2012/0805	General
BLM21BD222TN1	2200		0.6	200	2012/0805	General
BLM21BD272SN1	2700		0.8	200	2012/0805	General
BLM21BD331SN1	330		0.3	300	2012/0805	General
BLM21BD421SN1	420		0.3	300	2012/0805	General
BLM21BD471SN1	470		0.35	300	2012/0805	General
BLM21BD601SN1	600		0.35	300	2012/0805	General
BLM21BD751SN1	750		0.4	250	2012/0805	General
BLM21BD102SH1			1000ohm@100MHz	0.4	2012mm (0805inch)	
BLM21BD102SZ1			1000ohm@100MHz	0.4	2012mm (0805inch)	
BLM21BD151SH1			150ohm@100MHz	0.25	2012mm (0805inch)	
BLM21BD151SZ1			150ohm@100MHz	0.25	2012mm (0805inch)	
BLM21BD152SH1			1500ohm@100MHz	0.45	2012mm (0805inch)	
BLM21BD152SZ1			1500ohm@100MHz	0.45	2012mm (0805inch)	
BLM21BD182SH1			1800ohm@100MHz	0.5	2012mm (0805inch)	
BLM21BD182SZ1			1800ohm@100MHz	0.5	2012mm (0805inch)	
BLM21BD221SH1			220ohm@100MHz	0.25	2012mm (0805inch)	
BLM21BD221SZ1			220ohm@100MHz	0.25	2012mm (0805inch)	
BLM21BD331SH1			330ohm@100MHz	0.3	2012mm (0805inch)	
BLM21BD331SZ1			330ohm@100MHz	0.3	2012mm (0805inch)	
BLM21BD421SH1			420ohm@100MHz	0.3	2012mm (0805inch)	
BLM21BD421SZ1			420ohm@100MHz	0.3	2012mm (0805inch)	
BLM21BD471SH1			470ohm@100MHz	0.35	2012mm (0805inch)	
BLM21BD471SZ1			470ohm@100MHz	0.35	2012mm (0805inch)	
BLM21BD751SH1			750ohm@100MHz	0.4	2012mm (0805inch)	
BLM21BD751SZ1			750ohm@100MHz	0.4	2012mm (0805inch)	
BLM21HE122SN1	1200	450	0.11	1600	2012/0805	General

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application
BLM21HE472SN1	4700	750	0.4	850	2012/0805	General
BLM21HE601SN1	600	450	0.055	2300	2012/0805	General
BLM21HE802SN1	8000	850	0.7	650	2012/0805	General
BLM21HE122BH1			1200ohm@100MHz	0.11	2012mm (0805inch)	
BLM21HE122SH1			1200ohm@100MHz	0.11	2012mm (0805inch)	
BLM21HE472BH1			4700ohm@100MHz	0.4	2012mm (0805inch)	
BLM21HE472SH1			4700ohm@100MHz	0.4	2012mm (0805inch)	
BLM21HE601BH1			600ohm@100MHz	0.055	2012mm (0805inch)	
BLM21HE601SH1			600ohm@100MHz	0.055	2012mm (0805inch)	
BLM21HE802BH1			8000ohm@100MHz	0.7	2012mm (0805inch)	
BLM21HE802SH1			8000ohm@100MHz	0.7	2012mm (0805inch)	
BLM21PG121BH1			120ohm@100MHz	0.03	2012mm (0805inch)	BLM21PG121SN1
BLM21PG121SH1			120ohm@100MHz	0.03	2012mm (0805inch)	BLM21PG121SN1
BLM21PG121SZ1			120ohm@100MHz	0.03	2012mm (0805inch)	BLM21PG121SN1
BLM21PG220BH1			22ohm@100MHz	0.009	2012mm (0805inch)	BLM21PG220SN1
BLM21PG220SH1			22ohm@100MHz	0.009	2012mm (0805inch)	BLM21PG220SN1
BLM21PG220SZ1			22ohm@100MHz	0.009	2012mm (0805inch)	BLM21PG220SZ1
BLM21PG221BH1			220ohm@100MHz	0.045	2012mm (0805inch)	BLM21PG221SN1
BLM21PG221SH1			220ohm@100MHz	0.045	2012mm (0805inch)	BLM21PG221SN1
BLM21PG221SZ1			220ohm@100MHz	0.045	2012mm (0805inch)	BLM21PG221SN1
BLM21PG300BH1			30ohm@100MHz	0.014	2012mm (0805inch)	BLM21PG300SN1
BLM21PG300SH1			30ohm@100MHz	0.014	2012mm (0805inch)	BLM21PG300SN1
BLM21PG300SZ1			30ohm@100MHz	0.014	2012mm (0805inch)	BLM21PG300SN1
BLM21PG331BH1			330ohm@100MHz	0.07	2012mm (0805inch)	BLM21PG331SH1
BLM21PG331SH1			330ohm@100MHz	0.07	2012mm (0805inch)	BLM21PG331SH1
BLM21PG331SZ1			330ohm@100MHz	0.07	2012mm (0805inch)	BLM21PG331SH1
BLM21PG600BH1			60ohm@100MHz	0.02	2012mm (0805inch)	BLM21PG600SN1
BLM21PG600SH1			60ohm@100MHz	0.02	2012mm (0805inch)	BLM21PG600SN1
BLM21PG600SZ1			60ohm@100MHz	0.02	2012mm (0805inch)	BLM21PG600SN1
BLM21PG102SN1	1000		0.2	1150	2012/0805	General
BLM21PG121SN1	120		0.03	3000	2012/0805	General
BLM21PG220SN1	22		0.009	6000	2012/0805	General
BLM21PG221SN1	220		0.045	2000	2012/0805	General
BLM21PG300SN1	30		0.014	4000	2012/0805	General
BLM21PG331SN1	330		0.07	1500	2012/0805	General
BLM21PG600SN1	60		0.02	3500	2012/0805	General
BLM21PG601SN1	600		0.14	1400	2012/0805	General
BLM21PG102BH1			1000ohm@100MHz	0.2	2012mm (0805inch)	
BLM21PG102SH1			1000ohm@100MHz	0.2	2012mm (0805inch)	
BLM21PG601BH1			600ohm@100MHz	0.14	2012mm (0805inch)	
BLM21PG601SH1			600ohm@100MHz	0.14	2012mm (0805inch)	
BLM21RK102SN1	1000		0.5	200	2012/0805	General
BLM21RK121SN1	120		0.15	200	2012/0805	General
BLM21RK221SN1	220		0.2	200	2012/0805	General
BLM21RK471SN1	470		0.25	200	2012/0805	General
BLM21RK601SN1	600		0.3	200	2012/0805	General
BLM21SN300SH1			30ohm@100MHz	0.004	2012mm (0805inch)	BLM21SN300SN1
BLM21SN300SZ1			30ohm@100MHz	0.004	2012mm (0805inch)	BLM21SN300SN1
BLM21SN300SN1	30		0.004	8500	2012/0805	General
BLM21SP102BH1			1000ohm@100MHz	0.12	2012mm (0805inch)	BLM21SP102SH1
BLM21SP102SH1			1000ohm@100MHz	0.12	2012mm (0805inch)	BLM21SP102SH1
BLM21SP102SZ1			1000ohm@100MHz	0.12	2012mm (0805inch)	BLM21SP102SH1
BLM21SP111BH1			110ohm@100MHz	0.013	2012mm (0805inch)	BLM21SP111SH1
BLM21SP111SH1			110ohm@100MHz	0.013	2012mm (0805inch)	BLM21SP111SH1
BLM21SP111SZ1			110ohm@100MHz	0.013	2012mm (0805inch)	BLM21SP111SH1
BLM21SP181BH1			180ohm@100MHz	0.02	2012mm (0805inch)	BLM21SP181SH1
BLM21SP181SH1			180ohm@100MHz	0.02	2012mm (0805inch)	BLM21SP181SH1
BLM21SP181SZ1			180ohm@100MHz	0.02	2012mm (0805inch)	BLM21SP181SH1
BLM21SP331BH1			330ohm@100MHz	0.04	2012mm (0805inch)	BLM21SP331SH1
BLM21SP331SH1			330ohm@100MHz	0.04	2012mm (0805inch)	BLM21SP331SH1
BLM21SP331SZ1			330ohm@100MHz	0.04	2012mm (0805inch)	BLM21SP331SH1
BLM21SP471BH1			470ohm@100MHz	0.05	2012mm (0805inch)	BLM21SP471SH1
BLM21SP471SH1			470ohm@100MHz	0.05	2012mm (0805inch)	BLM21SP471SH1
BLM21SP471SZ1			470ohm@100MHz	0.05	2012mm (0805inch)	BLM21SP471SH1
BLM21SP601BH1			600ohm@100MHz	0.06	2012mm (0805inch)	BLM21SP601SH1
BLM21SP601SH1			600ohm@100MHz	0.06	2012mm (0805inch)	BLM21SP601SH1
BLM21SP601SZ1			600ohm@100MHz	0.06	2012mm (0805inch)	BLM21SP601SH1
BLM21SP700BH1			70ohm@100MHz	0.009	2012mm (0805inch)	BLM21SP700SH1
BLM21SP700SH1			70ohm@100MHz	0.009	2012mm (0805inch)	BLM21SP700SH1
BLM21SP700SZ1			70ohm@100MHz	0.009	2012mm (0805inch)	BLM21SP700SH1
BLM21SP102SN1	1000		0.12	1600	2012/0805	General
BLM21SP111SN1	110		0.013	5000	2012/0805	General
BLM21SP181SN1	180		0.02	4000	2012/0805	General
BLM21SP331SN1	330		0.04	2800	2012/0805	General
BLM21SP471SN1	470		0.05	2500	2012/0805	General
BLM21SP601SN1	600		0.06	2300	2012/0805	General
BLM21SP700SN1	70		0.009	6000	2012/0805	General
BLM31AJ601SH1			600ohm@100MHz	0.9	3216mm (1206inch)	
BLM31KN102BH1			1000ohm@100MHz	0.075	3216mm (1206inch)	BLM31KN102SH1
BLM31KN102SH1			1000ohm@100MHz	0.075	3216mm (1206inch)	BLM31KN102SH1
BLM31KN102SZ1			1000ohm@100MHz	0.075	3216mm (1206inch)	BLM31KN102SH1
BLM31KN121BH1			120ohm@100MHz	0.009	3216mm (1206inch)	BLM31KN121SH1
BLM31KN121SH1			120ohm@100MHz	0.009	3216mm (1206inch)	BLM31KN121SH1
BLM31KN121SZ1			120ohm@100MHz	0.009	3216mm (1206inch)	BLM31KN121SH1
BLM31KN271BH1			270ohm@100MHz	0.016	3216mm (1206inch)	BLM31KN271SH1
BLM31KN271SH1			270ohm@100MHz	0.016	3216mm (1206inch)	BLM31KN271SH1
BLM31KN271SZ1			270ohm@100MHz	0.016	3216mm (1206inch)	BLM31KN271SH1
BLM31KN471BH1			470ohm@100MHz	0.02	3216mm (1206inch)	BLM31KN471SH1
BLM31KN471SH1			470ohm@100MHz	0.02	3216mm (1206inch)	BLM31KN471SH1
BLM31KN471SZ1			470ohm@100MHz	0.02	3216mm (1206inch)	BLM31KN471SH1
BLM31KN601BH1			600ohm@100MHz	0.038	3216mm (1206inch)	BLM31KN601SH1
BLM31KN601SH1			600ohm@100MHz	0.038	3216mm (1206inch)	BLM31KN601SH1
BLM31KN601SZ1			600ohm@100MHz	0.038	3216mm (1206inch)	BLM31KN601SH1
BLM31KN801BH1			800ohm@100MHz	0.05	3216mm (1206inch)	BLM31KN801SH1
BLM31KN801SH1			800ohm@100MHz	0.05	3216mm (1206inch)	BLM31KN801SH1
BLM31KN801SZ1			800ohm@100MHz	0.05	3216mm (1206inch)	BLM31KN801SH1
BLM31KN102SN1	1000		0.075	2000	3216/1206	General
BLM31KN121SN1	120		0.009	6000	3216/1206	General

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application
BLM31KN271SN1	270		0.016	4500	3216/1206	General
BLM31KN471SN1	470		0.02	4000	3216/1206	General
BLM31KN601SN1	600		0.038	2900	3216/1206	General
BLM31KN801SN1	800		0.05	2500	3216/1206	General
BLM31PG121SH1			120ohm@100MHz	0.02	3216mm (1206inch)	BLM31PG121SN1
BLM31PG121SZ1			120ohm@100MHz	0.02	3216mm (1206inch)	BLM31PG121SN1
BLM31PG330SH1			33ohm@100MHz	0.009	3216mm (1206inch)	BLM31PG330SN1
BLM31PG330SZ1			33ohm@100MHz	0.009	3216mm (1206inch)	BLM31PG330SN1
BLM31PG391SH1			390ohm@100MHz	0.05	3216mm (1206inch)	BLM31PG391SN1
BLM31PG391SZ1			390ohm@100MHz	0.05	3216mm (1206inch)	BLM31PG391SN1
BLM31PG500SH1			50ohm@100MHz	0.015	3216mm (1206inch)	BLM31PG500SN1
BLM31PG500SZ1			50ohm@100MHz	0.015	3216mm (1206inch)	BLM31PG500SN1
BLM31PG601SH1			600ohm@100MHz	0.08	3216mm (1206inch)	BLM31PG601SN1
BLM31PG601SZ1			600ohm@100MHz	0.08	3216mm (1206inch)	BLM31PG601SN1
BLM31PG121SN1	120		0.02	3500	3216/1206	General
BLM31PG330SN1	33		0.009	6000	3216/1206	General
BLM31PG391SN1	390		0.05	2000	3216/1206	General
BLM31PG500SN1	50		0.015	3500	3216/1206	General
BLM31PG601SN1	600		0.08	1500	3216/1206	General
BLM31SN500BH1			50ohm@100MHz	0.0016	3216mm (1206inch)	BLM31SN500SH1
BLM31SN500SH1			50ohm@100MHz	0.0016	3216mm (1206inch)	BLM31SN500SH1
BLM31SN500SZ1			50ohm@100MHz	0.0016	3216mm (1206inch)	BLM31SN500SH1
BLM31SN500SN1	50		0.0016	12000	3216/1206	General
BLM41PG102SH1			1000ohm@100MHz	0.09	4516mm (1806inch)	BLM41PG102SN1
BLM41PG102SZ1			1000ohm@100MHz	0.09	4516mm (1806inch)	BLM41PG102SN1
BLM41PG181SH1			180ohm@100MHz	0.02	4516mm (1806inch)	BLM41PG181SN1
BLM41PG181SZ1			180ohm@100MHz	0.02	4516mm (1806inch)	BLM41PG181SN1
BLM41PG471SH1			470ohm@100MHz	0.05	4516mm (1806inch)	BLM41PG471SN1
BLM41PG471SZ1			470ohm@100MHz	0.05	4516mm (1806inch)	BLM41PG471SN1
BLM41PG600SH1			60ohm@100MHz	0.009	4516mm (1806inch)	BLM41PG600SN1
BLM41PG600SZ1			60ohm@100MHz	0.009	4516mm (1806inch)	BLM41PG600SN1
BLM41PG750SH1			75ohm@100MHz	0.015	4516mm (1806inch)	BLM41PG750SN1
BLM41PG750SZ1			75ohm@100MHz	0.015	4516mm (1806inch)	BLM41PG750SN1
BLM41PG102SN1	1000		0.09	1500	4516/1806	General
BLM41PG181SN1	180		0.02	3500	4516/1806	General
BLM41PG471SN1	470		0.05	2000	4516/1806	General
BLM41PG600SN1	60		0.009	6000	4516/1806	General
BLM41PG750SN1	75		0.015	3500	4516/1806	General
BLT5BPT680LN1	68		0.01	11000	5050/2020	General
NFZ03SG102SN10			1.3	210	0603/0201	General
NFZ03SG162SN10			1.7	180	0603/0201	General
NFZ03SG331SN10			0.6	305	0603/0201	General
NFZ03SG501SN10			0.73	275	0603/0201	General
NFZ03SG671SN10			0.88	250	0603/0201	General
NFZ15SF102SN10	1000		1.4	230	1005/0402	General
NFZ15SF102SZ10			1000ohm@100MHz	1.4	1005mm (0402inch)	
NFZ15SG101SN11			0.1	1100	1005/0402	General
NFZ15SG151SN11			0.12	1000	1005/0402	General
NFZ15SG152SN10			0.8	400	1005/0402	General
NFZ15SG262SN10			1	350	1005/0402	General
NFZ15SG331SN11			0.3	650	1005/0402	General
NFZ15SG462SN10			1.65	270	1005/0402	General
NFZ15SG771SN10			0.5	500	1005/0402	General
NFZ15SR152SN10	200		0.7	400	1005/0402	General
NFZ15SR262SN10	400		1.2	300	1005/0402	General
NFZ15SR352SN10	500		1.65	270	1005/0402	General
NFZ18SM121SN10	120		0.14	1250	1608/0603	General
NFZ18SM251SN10	250		0.19	1100	1608/0603	General
NFZ18SM501SN10	500		0.25	950	1608/0603	General
NFZ18SM701SN10	700		0.29	800	1608/0603	General
NFZ18SM121SZ10			120ohm@100MHz	0.14	1608mm (0603inch)	
NFZ18SM251SZ10			250ohm@100MHz	0.19	1608mm (0603inch)	
NFZ18SM501SZ10			500ohm@100MHz	0.25	1608mm (0603inch)	
NFZ18SM701SZ10			700ohm@100MHz	0.29	1608mm (0603inch)	
NFZ2HBM110SN10			0.04	800	2520/1008	General
NFZ2HBM170SN10			0.053	700	2520/1008	General
NFZ2HBM1R5SN10			0.015	1200	2520/1008	General
NFZ2HBM240SN10			0.063	650	2520/1008	General
NFZ2HBM2R9SN10			0.021	1100	2520/1008	General
NFZ2HBM330SN10			0.075	500	2520/1008	General
NFZ2HBM4R4SN10			0.026	1050	2520/1008	General
NFZ2HBM600SN10			0.075	400	2520/1008	General
NFZ2HBM6R1SN10			0.031	1000	2520/1008	General
NFZ2HBM8R4SN10			0.036	900	2520/1008	General
NFZ2MSD100SN10			0.02	5200	2016/0806	General
NFZ2MSD131SN10			0.144	1500	2016/0806	General
NFZ2MSD150SN10			0.023	4400	2016/0806	General
NFZ2MSD200SN10			0.028	3900	2016/0806	General
NFZ2MSD300SN10			0.033	3700	2016/0806	General
NFZ2MSD600SN10			0.054	2700	2016/0806	General
NFZ2MSD900SN10			0.095	2000	2016/0806	General
NFZ2MSD101SZ10			100ohm@100MHz	0.018	2016mm (0806inch)	
NFZ2MSD102SZ10			1000ohm@100MHz	0.046	2016mm (0806inch)	
NFZ2MSD181SZ10			180ohm@100MHz	0.022	2016mm (0806inch)	
NFZ2MSD301SZ10			300ohm@100MHz	0.026	2016mm (0806inch)	
NFZ2MSD501SZ10			500ohm@100MHz	0.032	2016mm (0806inch)	
NFZ2MSM101SN10	100		0.018	4000	2016/0806	General
NFZ2MSM181SN10	180		0.025	3400	2016/0806	General
NFZ2MSM301SN10	300		0.03	3100	2016/0806	General
NFZ2MSM601SN10	600		0.046	2500	2016/0806	General
NFZ32BW101HN11			0.57	900	3225/1210	General
NFZ32BW111HN10			0.684	520	3225/1210	General
NFZ32BW120HN11			0.0768	1850	3225/1210	General
NFZ32BW150HN10			0.0912	1600	3225/1210	General
NFZ32BW151HN10			0.972	450	3225/1210	General
NFZ32BW151HN11			0.822	700	3225/1210	General
NFZ32BW190HN11			0.1068	1800	3225/1210	General
NFZ32BW210HN10			0.144	1200	3225/1210	General

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application
NFZ32BW210HN1			0.12	1550	3225/1210	General
NFZ32BW221HN10			1.38	390	3225/1210	General
NFZ32BW291HN10			2.14	310	3225/1210	General
NFZ32BW310HN1			0.186	1200	3225/1210	General
NFZ32BW320HN10			0.216	1000	3225/1210	General
NFZ32BW3R3HN1			0.0288	2900	3225/1210	General
NFZ32BW3R6HN10			0.036	2550	3225/1210	General
NFZ32BW420HN10			0.288	850	3225/1210	General
NFZ32BW451HN10			2.74	275	3225/1210	General
NFZ32BW520HN1			0.264	1100	3225/1210	General
NFZ32BW621HN10			3.24	250	3225/1210	General
NFZ32BW650HN1			0.354	900	3225/1210	General
NFZ32BW6R8HN1			0.0432	2500	3225/1210	General
NFZ32BW700HN10			0.456	700	3225/1210	General
NFZ32BW7R4HN10			0.054	2050	3225/1210	General
NFZ32BW881HN10			5.26	200	3225/1210	General
NFZ32BW8R4HN1			0.0576	2400	3225/1210	General
NFZ32BW9R0HN10			0.0684	1750	3225/1210	General
NFZ32BW9R8HN1			0.0636	2100	3225/1210	General
NFZ32BW101HZ11	100			0.57	3225mm(1210inch)	
NFZ32BW111HZ10	110			0.684	3225mm(1210inch)	
NFZ32BW120HZ11	12			0.0768	3225mm(1210inch)	
NFZ32BW150HZ10	15			0.0912	3225mm(1210inch)	
NFZ32BW151HZ10	150			0.972	3225mm(1210inch)	
NFZ32BW151HZ11	150			0.822	3225mm(1210inch)	
NFZ32BW190HZ11	19			0.1068	3225mm(1210inch)	
NFZ32BW210HZ10	21			0.144	3225mm(1210inch)	
NFZ32BW210HZ11	21			0.12	3225mm(1210inch)	
NFZ32BW221HZ10	220			1.38	3225mm(1210inch)	
NFZ32BW291HZ10	290			2.14	3225mm(1210inch)	
NFZ32BW310HZ11	31			0.186	3225mm(1210inch)	
NFZ32BW320HZ10	32			0.216	3225mm(1210inch)	
NFZ32BW3R3HZ11	3.3			0.0288	3225mm(1210inch)	
NFZ32BW3R6HZ10	3.6			0.036	3225mm(1210inch)	
NFZ32BW420HZ10	42			0.288	3225mm(1210inch)	
NFZ32BW451HZ10	450			2.74	3225mm(1210inch)	
NFZ32BW520HZ11	52			0.264	3225mm(1210inch)	
NFZ32BW621HZ10	620			3.24	3225mm(1210inch)	
NFZ32BW650HZ11	65			0.354	3225mm(1210inch)	
NFZ32BW6R8HZ11	6.8			0.0432	3225mm(1210inch)	
NFZ32BW700HZ10	70			0.456	3225mm(1210inch)	
NFZ32BW7R4HZ10	7.4			0.054	3225mm(1210inch)	
NFZ32BW881HZ10	880			5.26	3225mm(1210inch)	
NFZ32BW8R4HZ11	8.4			0.0576	3225mm(1210inch)	
NFZ32BW9R0HZ10	9			0.0684	3225mm(1210inch)	
NFZ32BW9R8HZ11	9.8			0.0636	3225mm(1210inch)	
NFZ32SW301HN10	300		0.036	2550	3225/1210	General
NFZ32SW901HN10	900		0.054	2050	3225/1210	General
NFZ5BBW100LN10			0.029	3000	5050/2020	General
NFZ5BBW140LN10			0.036	2600	5050/2020	General
NFZ5BBW141LN10			0.311	1050	5050/2020	General
NFZ5BBW170LN10			0.042	2500	5050/2020	General
NFZ5BBW220LN10			0.053	2300	5050/2020	General
NFZ5BBW2R9LN10			0.014	4000	5050/2020	General
NFZ5BBW310LN10			0.07	2000	5050/2020	General
NFZ5BBW450LN10			0.1	1650	5050/2020	General
NFZ5BBW4R5LN10			0.018	3400	5050/2020	General
NFZ5BBW520LN10			0.12	1610	5050/2020	General
NFZ5BBW610LN10			0.127	1600	5050/2020	General
NFZ5BBW6R7LN10			0.023	3100	5050/2020	General
NFZ5BBW7R6LN10			0.023	3100	5050/2020	General
NFZ5BBW970LN10			0.224	1200	5050/2020	General
NFZ5BBW100LZ10	10			0.029	5050mm(2020inch)	
NFZ5BBW140LZ10	14			0.036	5050mm(2020inch)	
NFZ5BBW141LZ10	140			0.311	5050mm(2020inch)	
NFZ5BBW170LZ10	17			0.042	5050mm(2020inch)	
NFZ5BBW220LZ10	22			0.053	5050mm(2020inch)	
NFZ5BBW2R9LZ10	2.9			0.014	5050mm(2020inch)	
NFZ5BBW310LZ10	31			0.07	5050mm(2020inch)	
NFZ5BBW450LZ10	45			0.1	5050mm(2020inch)	
NFZ5BBW4R5LZ10	4.5			0.018	5050mm(2020inch)	
NFZ5BBW520LZ10	52			0.12	5050mm(2020inch)	
NFZ5BBW610LZ10	61			0.127	5050mm(2020inch)	
NFZ5BBW6R7LZ10	6.7			0.023	5050mm(2020inch)	
NFZ5BBW7R6LZ10	7.6			0.023	5050mm(2020inch)	
NFZ5BBW970LZ10	97			0.224	5050mm(2020inch)	

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLE18PK100SN1	10		0.008	6000	1608/0603	General	1 MHz - 3 GHz
BLE18PK160SN1	16		0.012	5000	1608/0603	General	1 MHz - 3 GHz
BLE18PS080BH1			80hm@100MHz	0.004	1608mm (0603inch)	Bias BLE18PS080.csv	1 MHz - 3 GHz
BLE18PS080SH1			80hm@100MHz	0.004	1608mm (0603inch)	Bias BLE18PS080.csv	1 MHz - 3 GHz
BLE18PS080SZ1			80hm@100MHz	0.004	1608mm (0603inch)	Bias BLE18PS080.csv	1 MHz - 3 GHz
BLE18PS080SN1	8		0.004	8000	1608/0603	General	1 MHz - 3 GHz
BLE32PN260SH1			26ohm@100MHz	0.0016	3225mm(1210inch)	As BLE32PN260SN1.d	1 MHz - 3 GHz
BLE32PN260SZ1			26ohm@100MHz	0.0016	3225mm(1210inch)	As BLE32PN260SN1.d	1 MHz - 3 GHz
BLE32PN300SH1			30ohm@100MHz	0.0016	3225mm(1210inch)	As BLE32PN300SN1.d	1 MHz - 3 GHz
BLE32PN300SZ1			30ohm@100MHz	0.0016	3225mm(1210inch)	As BLE32PN300SN1.d	1 MHz - 3 GHz
BLE32PN260SN1	26		0.0016	10000	3225/1210	General	1 MHz - 3 GHz
BLE32PN300SN1	30		0.0016	10000	3225/1210	General	1 MHz - 3 GHz
BLE32SN120BH1				0.0006	3225mm (1210inch)	Bias BLE32SN120.csv	1 MHz - 3 GHz
BLE32SN120SH1				0.0006	3225mm (1210inch)	Bias BLE32SN120.csv	1 MHz - 3 GHz
BLE32SN120SZ1				0.0006	3225mm (1210inch)	Bias BLE32SN120.csv	1 MHz - 3 GHz
BLE32SN120SN1	12		0.0006	20000	3225/1210	General	1 MHz - 3 GHz
BLE32SN120SN1	12		0.0006	20000	3225/1210	General	1 MHz - 3 GHz
BLF02GD162GNE			3	100	0402/01005	General	1 MHz - 3 GHz
BLF02JD361GNE			0.45	380	0402/01005	General	1 MHz - 3 GHz
BLF02JD471GNE			0.6	330	0402/01005	General	1 MHz - 3 GHz
BLF02RD331GNE			0.6	330	0402/01005	General	1 MHz - 3 GHz
BLF02RD471GNE			0.9	200	0402/01005	General	1 MHz - 3 GHz
BLF03JD421GNE			0.28	480	0603/0201	General	1 MHz - 3 GHz
BLF03JD421GZE				0.28	0603mm (0201inch)		1 MHz - 3 GHz
BLF03RD102GNE			1	220	0603/0201	General	1 MHz - 3 GHz
BLF03RD501GNE			0.36	500	0603/0201	General	1 MHz - 3 GHz
BLF03RD102GZE				1	0603mm (0201inch)		1 MHz - 3 GHz
BLF03RD501GZE				0.36	0603mm (0201inch)		1 MHz - 3 GHz
BLF03VK221SNG			0.155	800	0603/0201	General	1 MHz - 8 GHz
BLF03VK600SNL			0.065	1200	0603/0201	General	1 MHz - 8 GHz
BLM02AX100SN1	10		0.07	750	0402/01005	General	1 MHz - 3 GHz
BLM02AX121SN1	120		0.5	250	0402/01005	General	1 MHz - 3 GHz
BLM02AX241SN1	240		0.9	200	0402/01005	General	1 MHz - 3 GHz
BLM02AX331SN1	330		1.4	150	0402/01005	General	1 MHz - 3 GHz
BLM02AX700SN1	700		0.36	300	0402/01005	General	1 MHz - 3 GHz
BLM02BB101SN1	100		2	125	0402/01005	General	1 MHz - 3 GHz
BLM02BC100SN1	10	95	0.5	250	0402/01005	General	1 MHz - 3 GHz
BLM02BC220SN1	22	240	0.9	200	0402/01005	General	1 MHz - 3 GHz
BLM02BX121SN1	120		0.5	350	0402/01005	General	1 MHz - 3 GHz
BLM02BX151SN1	150		0.7	280	0402/01005	General	1 MHz - 3 GHz
BLM02BX241SN1	240		1.1	240	0402/01005	General	1 MHz - 3 GHz
BLM02KX100SN1	10		0.03	1500	0402/01005	General	1 MHz - 3 GHz
BLM02KX180SN1	18		0.045	1200	0402/01005	General	1 MHz - 3 GHz
BLM02PX100SN1	10		0.05	1100	0402/01005	General	1 MHz - 3 GHz
BLM02PX220SN1	22		0.11	750	0402/01005	General	1 MHz - 3 GHz
BLM02PX330SN1	33		0.2	550	0402/01005	General	1 MHz - 3 GHz
BLM02PX600SN1	60		0.25	500	0402/01005	General	1 MHz - 3 GHz
BLM03AG100SZ1			10ohm@100MHz	0.1	0603mm (0201inch)	As BLM03AG100SN1.d	1 MHz - 3 GHz
BLM03AG102SZ1			1000ohm@100MHz	2.5	0603mm (0201inch)	As BLM03AG102SN1.d	1 MHz - 3 GHz
BLM03AG241SZ1			240ohm@100MHz	0.8	0603mm (0201inch)	As BLM03AG241SN1.d	1 MHz - 3 GHz
BLM03AG700SZ1			70ohm@100MHz	0.4	0603mm (0201inch)	As BLM03AG700SN1.d	1 MHz - 3 GHz
BLM03AG800SZ1			80ohm@100MHz	0.4	0603mm (0201inch)	As BLM03AG800SN1.d	1 MHz - 3 GHz
BLM03AG100SN1	10		0.1	500	0603/0201	General	1 MHz - 3 GHz
BLM03AG102SN1	1000		2.5	100	0603/0201	General	1 MHz - 3 GHz
BLM03AG121SN1	120		0.5	200	0603/0201	General	1 MHz - 3 GHz
BLM03AG241SN1	240		0.8	200	0603/0201	General	1 MHz - 3 GHz
BLM03AG601SN1	600		1.5	100	0603/0201	General	1 MHz - 3 GHz
BLM03AG700SN1	70		0.4	200	0603/0201	General	1 MHz - 3 GHz
BLM03AG800SN1	80		0.4	200	0603/0201	General	1 MHz - 3 GHz
BLM03AG121SZ1			120ohm@100MHz	0.5	0603mm (0201inch)		1 MHz - 3 GHz
BLM03AG601SZ1			600ohm@100MHz	1.5	0603mm (0201inch)		1 MHz - 3 GHz
BLM03AX100SZ1			10ohm@100MHz	0.05	0603mm (0201inch)	As BLM03AX100SN1.d	1 MHz - 3 GHz
BLM03AX102SZ1			1000ohm@100MHz	1.25	0603mm (0201inch)	As BLM03AX102SN1.d	1 MHz - 3 GHz
BLM03AX121SZ1			120ohm@100MHz	0.23	0603mm (0201inch)	As BLM03AX121SN1.d	1 MHz - 3 GHz
BLM03AX241SZ1			240ohm@100MHz	0.38	0603mm (0201inch)	As BLM03AX241SN1.d	1 MHz - 3 GHz
BLM03AX601SZ1			600ohm@100MHz	0.85	0603mm (0201inch)	As BLM03AX601SN1.d	1 MHz - 3 GHz
BLM03AX100SN1	10		0.05	1000	0603/0201	General	1 MHz - 3 GHz
BLM03AX102SN1	1000		1.25	200	0603/0201	General	1 MHz - 3 GHz
BLM03AX121SN1	120		0.23	450	0603/0201	General	1 MHz - 3 GHz
BLM03AX241SN1	240		0.38	350	0603/0201	General	1 MHz - 3 GHz
BLM03AX601SN1	600		0.85	250	0603/0201	General	1 MHz - 3 GHz
BLM03AX800SN1	80		0.18	500	0603/0201	General	1 MHz - 3 GHz
BLM03AX800SZ1			80ohm@100MHz	0.18	0603mm (0201inch)		1 MHz - 3 GHz
BLM03BB100SZ1			10ohm@100MHz	0.4	0603mm (0201inch)	As BLM03BB100SN1.d	1 MHz - 3 GHz
BLM03BB121SZ1			120ohm@100MHz	1.5	0603mm (0201inch)	As BLM03BB121SN1.d	1 MHz - 3 GHz
BLM03BB470SZ1			47ohm@100MHz	0.7	0603mm (0201inch)	As BLM03BB470SN1.d	1 MHz - 3 GHz
BLM03BB750SZ1			75ohm@100MHz	1	0603mm (0201inch)	As BLM03BB750SN1.d	1 MHz - 3 GHz
BLM03BB100SN1	10		0.4	300	0603/0201	General	1 MHz - 3 GHz
BLM03BB121SN1	120		1.5	100	0603/0201	General	1 MHz - 3 GHz
BLM03BB220SN1	22		0.5	200	0603/0201	General	1 MHz - 3 GHz
BLM03BB470SN1	47		0.7	200	0603/0201	General	1 MHz - 3 GHz
BLM03BB750SN1	75		1	200	0603/0201	General	1 MHz - 3 GHz
BLM03BB220SZ1			22ohm@100MHz	0.5	0603mm (0201inch)		1 MHz - 3 GHz
BLM03BC330SZ1			33ohm@100MHz	0.85	0603mm (0201inch)	As BLM03BC330SN1.d	1 MHz - 3 GHz
BLM03BC560SZ1			56ohm@100MHz	1.05	0603mm (0201inch)	As BLM03BC560SN1.d	1 MHz - 3 GHz
BLM03BC800SZ1			80ohm@100MHz	1.4	0603mm (0201inch)	As BLM03BC800SN1.d	1 MHz - 3 GHz
BLM03BC330SN1	33		0.85	150	0603/0201	General	1 MHz - 3 GHz
BLM03BC560SN1	56		1.05	100	0603/0201	General	1 MHz - 3 GHz
BLM03BC800SN1	80		1.4	100	0603/0201	General	1 MHz - 3 GHz
BLM03BD121SZ1			120ohm@100MHz	0.5	0603mm (0201inch)	As BLM03BD121SN1.d	1 MHz - 3 GHz
BLM03BD241SZ1			240ohm@100MHz	0.8	0603mm (0201inch)	As BLM03BD241SN1.d	1 MHz - 3 GHz
BLM03BD471SZ1			470ohm@100MHz	1.5	0603mm (0201inch)	As BLM03BD471SN1.d	1 MHz - 3 GHz
BLM03BD601SZ1			600ohm@100MHz	1.7	0603mm (0201inch)	As BLM03BD601SN1.d	1 MHz - 3 GHz
BLM03BD750SZ1			75ohm@100MHz	0.4	0603mm (0201inch)	As BLM03BD750SN1.d	1 MHz - 3 GHz
BLM03BD121SN1	120		0.5	250	0603/0201	General	1 MHz - 3 GHz
BLM03BD241SN1	240		0.8	200	0603/0201	General	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLM03BD471SN1	470		1.5	215	0603/0201	General	1 MHz - 3 GHz
BLM03BD601SN1	600		1.7	200	0603/0201	General	1 MHz - 3 GHz
BLM03BD750SN1	75		0.4	300	0603/0201	General	1 MHz - 3 GHz
BLM03BX102SN1	1000		1.7	170	0603/0201	General	1 MHz - 3 GHz
BLM03BX182SN1	1800		2.5	140	0603/0201	General	1 MHz - 3 GHz
BLM03EB250SH1			25ohm@100MHz	0.26	0603mm (0201inch)	BLM03EB250SN1.d	1 MHz - 3 GHz
BLM03EB250SZ1			25ohm@100MHz	0.26	0603mm (0201inch)	BLM03EB250SN1.d	1 MHz - 3 GHz
BLM03EB500SH1			50ohm@100MHz	0.58	0603mm (0201inch)	BLM03EB500SN1.d	1 MHz - 3 GHz
BLM03EB500SZ1			50ohm@100MHz	0.58	0603mm (0201inch)	BLM03EB500SN1.d	1 MHz - 3 GHz
BLM03EB250SN1	25	105	0.26	600	0603/0201	General	1 MHz - 3 GHz
BLM03EB500SN1	50	255	0.58	400	0603/0201	General	1 MHz - 3 GHz
BLM03HB191SZ1			190ohm@100MHz	2	0603mm (0201inch)	BLM03HB191SN1.d	1 MHz - 3 GHz
BLM03HB191SN1	190	1150	2	150	0603/0201	General	1 MHz - 3 GHz
BLM03HB401SN1	400	1850	2.8	125	0603/0201	General	1 MHz - 3 GHz
BLM03HB401SZ1			400ohm@100MHz	2.8	0603mm (0201inch)		1 MHz - 3 GHz
BLM03HD331SZ1			330ohm@100MHz	1	0603mm (0201inch)	BLM03HD331SN1.d	1 MHz - 3 GHz
BLM03HD471SZ1			470ohm@100MHz	1.3	0603mm (0201inch)	BLM03HD471SN1.d	1 MHz - 3 GHz
BLM03HD601SZ1			600ohm@100MHz	1.7	0603mm (0201inch)	BLM03HD601SN1.d	1 MHz - 3 GHz
BLM03HD102FN1	1000	2300	2.4	135	0603/0201	General	1 MHz - 3 GHz
BLM03HD102SN1	1000	2300	2.9	120	0603/0201	General	1 MHz - 3 GHz
BLM03HD152FN1	1500	2700	3.1	120	0603/0201	General	1 MHz - 3 GHz
BLM03HD182FN1	1800	3000	3.8	100	0603/0201	General	1 MHz - 3 GHz
BLM03HD331SN1	330	750	1	200	0603/0201	General	1 MHz - 3 GHz
BLM03HD471SN1	470	1000	1.3	175	0603/0201	General	1 MHz - 3 GHz
BLM03HD601SN1	600	1500	1.7	150	0603/0201	General	1 MHz - 3 GHz
BLM03HD102FZ1			1000ohm@100MHz	2.4	0603mm (0201inch)		1 MHz - 3 GHz
BLM03HD102SZ1			1000ohm@100MHz	2.9	0603mm (0201inch)		1 MHz - 3 GHz
BLM03HD152FZ1			1500ohm@100MHz	3.1	0603mm (0201inch)		1 MHz - 3 GHz
BLM03HD182FZ1			1800ohm@100MHz	3.8	0603mm (0201inch)		1 MHz - 3 GHz
BLM03HG102SH1			1000ohm@100MHz	2.6	0603mm (0201inch)	BLM03HG102SN1.d	1 MHz - 3 GHz
BLM03HG102SZ1			1000ohm@100MHz	2.6	0603mm (0201inch)	BLM03HG102SN1.d	1 MHz - 3 GHz
BLM03HG122SH1			1200ohm@100MHz	3.5	0603mm (0201inch)	BLM03HG122SN1.d	1 MHz - 3 GHz
BLM03HG122SZ1			1200ohm@100MHz	3.5	0603mm (0201inch)	BLM03HG122SN1.d	1 MHz - 3 GHz
BLM03HG601SH1			600ohm@100MHz	1.6	0603mm (0201inch)	BLM03HG601SN1.d	1 MHz - 3 GHz
BLM03HG601SZ1			600ohm@100MHz	1.6	0603mm (0201inch)	BLM03HG601SN1.d	1 MHz - 3 GHz
BLM03HG102SN1	1000	1800	2.6	125	0603/0201	General	1 MHz - 3 GHz
BLM03HG122SN1	1200	2000	3.5	100	0603/0201	General	1 MHz - 3 GHz
BLM03HG601SN1	600	1000	1.6	150	0603/0201	General	1 MHz - 3 GHz
BLM03PG220SZ1			22ohm@100MHz	0.065	0603mm (0201inch)	BLM03PG220SN1.d	1 MHz - 3 GHz
BLM03PG330SZ1			33ohm@100MHz	0.09	0603mm (0201inch)	BLM03PG330SN1.d	1 MHz - 3 GHz
BLM03PG220SN1	22		0.065	900	0603/0201	General	1 MHz - 3 GHz
BLM03PG330SN1	33		0.09	750	0603/0201	General	1 MHz - 3 GHz
BLM03PX121SZ1			120ohm@100MHz	0.16	0603mm (0201inch)	BLM03PX121SN1.d	1 MHz - 3 GHz
BLM03PX220SZ1			22ohm@100MHz	0.04	0603mm (0201inch)	BLM03PX220SN1.d	1 MHz - 3 GHz
BLM03PX330SZ1			33ohm@100MHz	0.055	0603mm (0201inch)	BLM03PX330SN1.d	1 MHz - 3 GHz
BLM03PX800SZ1			80ohm@100MHz	0.13	0603mm (0201inch)	BLM03PX800SN1.d	1 MHz - 3 GHz
BLM03PX121SN1	120		0.16	900	0603/0201	General	1 MHz - 3 GHz
BLM03PX220SN1	22		0.04	1800	0603/0201	General	1 MHz - 3 GHz
BLM03PX330SN1	33		0.055	1500	0603/0201	General	1 MHz - 3 GHz
BLM03PX800SN1	80		0.13	1000	0603/0201	General	1 MHz - 3 GHz
BLM15AG100SH1			10ohm@100MHz	0.05	1005mm (0402inch)	BLM15AG100SN1.d	1 MHz - 3 GHz
BLM15AG100SZ1			10ohm@100MHz	0.025	1005mm (0402inch)	BLM15AG100SN1.d	1 MHz - 3 GHz
BLM15AG102SH1			1000ohm@100MHz	1	1005mm (0402inch)	BLM15AG102SN1.d	1 MHz - 3 GHz
BLM15AG102SZ1			1000ohm@100MHz	0.65	1005mm (0402inch)	BLM15AG102SN1.d	1 MHz - 3 GHz
BLM15AG121SH1			120ohm@100MHz	0.25	1005mm (0402inch)	BLM15AG121SN1.d	1 MHz - 3 GHz
BLM15AG121SZ1			120ohm@100MHz	0.19	1005mm (0402inch)	BLM15AG121SN1.d	1 MHz - 3 GHz
BLM15AG221SH1			220ohm@100MHz	0.35	1005mm (0402inch)	BLM15AG221SN1.d	1 MHz - 3 GHz
BLM15AG221SZ1			220ohm@100MHz	0.29	1005mm (0402inch)	BLM15AG221SN1.d	1 MHz - 3 GHz
BLM15AG601SH1			600ohm@100MHz	0.6	1005mm (0402inch)	BLM15AG601SN1.d	1 MHz - 3 GHz
BLM15AG601SZ1			600ohm@100MHz	0.52	1005mm (0402inch)	BLM15AG601SN1.d	1 MHz - 3 GHz
BLM15AG100SN1	10		0.025	1000	1005/0402	General	1 MHz - 3 GHz
BLM15AG102SN1	1000		0.65	300	1005/0402	General	1 MHz - 3 GHz
BLM15AG121SN1	120		0.19	550	1005/0402	General	1 MHz - 3 GHz
BLM15AG221SN1	220		0.29	450	1005/0402	General	1 MHz - 3 GHz
BLM15AG601SN1	600		0.52	300	1005/0402	General	1 MHz - 3 GHz
BLM15AG700SN1	70		0.15	600	1005/0402	General	1 MHz - 3 GHz
BLM15AG700SH1			70ohm@100MHz	0.15	1005mm (0402inch)		1 MHz - 3 GHz
BLM15AG700SZ1			70ohm@100MHz	0.15	1005mm (0402inch)		1 MHz - 3 GHz
BLM15AX100SZ1			10ohm@100MHz	0.015	1005mm (0402inch)	BLM15AX100SN1.d	1 MHz - 3 GHz
BLM15AX102SZ1			1000ohm@100MHz	0.49	1005mm (0402inch)	BLM15AX102SN1.d	1 MHz - 3 GHz
BLM15AX300SZ1			30ohm@100MHz	0.06	1005mm (0402inch)	BLM15AX300SN1.d	1 MHz - 3 GHz
BLM15AX100SN1	10		0.015	1740	1005/0402	General	1 MHz - 3 GHz
BLM15AX102SN1	1000		0.49	350	1005/0402	General	1 MHz - 3 GHz
BLM15AX121SN1	120		0.13	700	1005/0402	General	1 MHz - 3 GHz
BLM15AX221SN1	220		0.18	600	1005/0402	General	1 MHz - 3 GHz
BLM15AX300SN1	30		0.06	1100	1005/0402	General	1 MHz - 3 GHz
BLM15AX601SN1	600		0.34	500	1005/0402	General	1 MHz - 3 GHz
BLM15AX700SN1	70		0.1	780	1005/0402	General	1 MHz - 3 GHz
BLM15AX121SZ1			120ohm@100MHz	0.13	1005mm (0402inch)		1 MHz - 3 GHz
BLM15AX221SZ1			220ohm@100MHz	0.18	1005mm (0402inch)		1 MHz - 3 GHz
BLM15AX601SZ1			600ohm@100MHz	0.34	1005mm (0402inch)		1 MHz - 3 GHz
BLM15AX700SZ1			70ohm@100MHz	0.1	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BA220SZ1			22ohm@100MHz	0.3	1005mm (0402inch)	BLM15BA220SN1.d	1 MHz - 3 GHz
BLM15BA330SZ1			33ohm@100MHz	0.4	1005mm (0402inch)	BLM15BA330SN1.d	1 MHz - 3 GHz
BLM15BA750SZ1			75ohm@100MHz	0.8	1005mm (0402inch)	BLM15BA750SN1.d	1 MHz - 3 GHz
BLM15BA050SN1	5		0.1	300	1005/0402	General	1 MHz - 3 GHz
BLM15BA100SN1	10		0.2	300	1005/0402	General	1 MHz - 3 GHz
BLM15BA220SN1	22		0.3	300	1005/0402	General	1 MHz - 3 GHz
BLM15BA330SN1	33		0.4	300	1005/0402	General	1 MHz - 3 GHz
BLM15BA470SN1	47		0.6	200	1005/0402	General	1 MHz - 3 GHz
BLM15BA750SN1	75		0.8	200	1005/0402	General	1 MHz - 3 GHz
BLM15BA050SZ1			5ohm@100MHz	0.1	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BA100SZ1			10ohm@100MHz	0.2	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BA470SZ1			47ohm@100MHz	0.6	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BB050SN1	5		0.08	500	1005/0402	General	1 MHz - 3 GHz
BLM15BB100SN1	10		0.1	300	1005/0402	General	1 MHz - 3 GHz
BLM15BB121SN1	120		0.55	300	1005/0402	General	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLM15BB220SN1	22		0.2	300	1005/0402	General	1 MHz - 3 GHz
BLM15BB221SN1	220		0.8	200	1005/0402	General	1 MHz - 3 GHz
BLM15BB470SN1	47		0.35	300	1005/0402	General	1 MHz - 3 GHz
BLM15BB750SN1	75		0.4	300	1005/0402	General	1 MHz - 3 GHz
BLM15BB050SH1			5ohm@100MHz	0.08	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BB050SZ1			5ohm@100MHz	0.08	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BB100SH1			10ohm@100MHz	0.1	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BB100SZ1			10ohm@100MHz	0.1	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BB121SH1			120ohm@100MHz	0.55	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BB121SZ1			120ohm@100MHz	0.55	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BB220SH1			22ohm@100MHz	0.2	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BB220SZ1			22ohm@100MHz	0.2	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BB221SH1			220ohm@100MHz	0.8	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BB221SZ1			220ohm@100MHz	0.8	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BB470SH1			47ohm@100MHz	0.35	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BB470SZ1			47ohm@100MHz	0.35	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BB750SH1			75ohm@100MHz	0.4	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BB750SZ1			75ohm@100MHz	0.4	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BC121SN1	120		0.45	350	1005/0402	General	1 MHz - 3 GHz
BLM15BC241SN1	240		0.7	250	1005/0402	General	1 MHz - 3 GHz
BLM15BC121SZ1			120ohm@100MHz	0.45	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BC241SZ1			240ohm@100MHz	0.7	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BD102SH1			1000ohm@100MHz	0.9	1005mm (0402inch)	BLM15BD102SN1	1 MHz - 3 GHz
BLM15BD102SZ1			1000ohm@100MHz	0.9	1005mm (0402inch)	BLM15BD102SN1	1 MHz - 3 GHz
BLM15BD221SZ1			220ohm@100MHz	0.4	1005mm (0402inch)	BLM15BD221SN1	1 MHz - 3 GHz
BLM15BD750SZ1			75ohm@100MHz	0.2	1005mm (0402inch)	BLM15BD750SN1	1 MHz - 3 GHz
BLM15BD102SN1	1000		0.9	200	1005/0402	General	1 MHz - 3 GHz
BLM15BD121SN1	120		0.3	300	1005/0402	General	1 MHz - 3 GHz
BLM15BD152SN1	1500		1	190	1005/0402	General	1 MHz - 3 GHz
BLM15BD182SN1	1800		1.4	100	1005/0402	General	1 MHz - 3 GHz
BLM15BD221SN1	220		0.4	300	1005/0402	General	1 MHz - 3 GHz
BLM15BD471SN1	470		0.6	200	1005/0402	General	1 MHz - 3 GHz
BLM15BD601SN1	600		0.65	200	1005/0402	General	1 MHz - 3 GHz
BLM15BD750SN1	75		0.2	300	1005/0402	General	1 MHz - 3 GHz
BLM15BD121SZ1			120ohm@100MHz	0.3	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BD152SZ1			1500ohm@100MHz	1	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BD182SH1			1800ohm@100MHz	1.4	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BD182SZ1			1800ohm@100MHz	1.4	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BD471SH1			470ohm@100MHz	0.6	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BD471SZ1			470ohm@100MHz	0.6	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BD601SH1			600ohm@100MHz	0.65	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BD601SZ1			600ohm@100MHz	0.65	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BX102SZ1			1000ohm@100MHz	0.65	1005mm (0402inch)	BLM15BX102SN1	1 MHz - 3 GHz
BLM15BX121SZ1			120ohm@100MHz	0.17	1005mm (0402inch)	BLM15BX121SN1	1 MHz - 3 GHz
BLM15BX182SZ1			1800ohm@100MHz	0.9	1005mm (0402inch)	BLM15BX182SN1	1 MHz - 3 GHz
BLM15BX221SZ1			220ohm@100MHz	0.27	1005mm (0402inch)	BLM15BX221SN1	1 MHz - 3 GHz
BLM15BX601SZ1			600ohm@100MHz	0.46	1005mm (0402inch)	BLM15BX601SN1	1 MHz - 3 GHz
BLM15BX102SN1	1000		0.65	300	1005/0402	General	1 MHz - 3 GHz
BLM15BX121SN1	120		0.17	600	1005/0402	General	1 MHz - 3 GHz
BLM15BX182SN1	1800		0.9	250	1005/0402	General	1 MHz - 3 GHz
BLM15BX221SN1	220		0.27	450	1005/0402	General	1 MHz - 3 GHz
BLM15BX471SN1	470		0.41	350	1005/0402	General	1 MHz - 3 GHz
BLM15BX601SN1	600		0.46	350	1005/0402	General	1 MHz - 3 GHz
BLM15BX750SN1	75		0.15	600	1005/0402	General	1 MHz - 3 GHz
BLM15BX471SZ1			470ohm@100MHz	0.41	1005mm (0402inch)		1 MHz - 3 GHz
BLM15BX750SZ1			75ohm@100MHz	0.15	1005mm (0402inch)		1 MHz - 3 GHz
BLM15EG121SH1			120ohm@100MHz	0.095	1005mm (0402inch)	BLM15EG121SN1	1 MHz - 3 GHz
BLM15EG121SZ1			120ohm@100MHz	0.095	1005mm (0402inch)	BLM15EG121SN1	1 MHz - 3 GHz
BLM15EG221SH1			220ohm@100MHz	0.28	1005mm (0402inch)	BLM15EG221SN1	1 MHz - 3 GHz
BLM15EG221SZ1			220ohm@100MHz	0.28	1005mm (0402inch)	BLM15EG221SN1	1 MHz - 3 GHz
BLM15EG121SN1	120	145	0.095	1500	1005/0402	General	1 MHz - 3 GHz
BLM15EG221SN1	220	270	0.28	700	1005/0402	General	1 MHz - 3 GHz
BLM15EX121SN1	120	170	0.075	1800	1005/0402	General	1 MHz - 3 GHz
BLM15EX221SN1	220	300	0.14	1300	1005/0402	General	1 MHz - 3 GHz
BLM15EX331SN1	330	450	0.205	1100	1005/0402	General	1 MHz - 3 GHz
BLM15EX471SN1	470	630	0.28	950	1005/0402	General	1 MHz - 3 GHz
BLM15GA750SZ1			75ohm@100MHz	1.3	1005mm (0402inch)	BLM15GA750SN1	1 MHz - 3 GHz
BLM15GA750SN1	75	1000	1.3	200	1005/0402	General	1 MHz - 3 GHz
BLM15GG221SZ1			220ohm@100MHz	0.7	1005mm (0402inch)	BLM15GG221SN1	1 MHz - 3 GHz
BLM15GG471SZ1			470ohm@100MHz	1.3	1005mm (0402inch)	BLM15GG471SN1	1 MHz - 3 GHz
BLM15GG221SN1	220	600	0.7	300	1005/0402	General	1 MHz - 3 GHz
BLM15GG471SN1	470	1200	1.3	200	1005/0402	General	1 MHz - 3 GHz
BLM15HB121SH1			120ohm@100MHz	0.7	1005mm (0402inch)	BLM15HB121SN1	1 MHz - 3 GHz
BLM15HB121SZ1			120ohm@100MHz	0.7	1005mm (0402inch)	BLM15HB121SN1	1 MHz - 3 GHz
BLM15HB121SN1	120	500	0.7	300	1005/0402	General	1 MHz - 3 GHz
BLM15HB221SN1	220	900	1	250	1005/0402	General	1 MHz - 3 GHz
BLM15HB221SH1			220ohm@100MHz	1	1005mm (0402inch)		1 MHz - 3 GHz
BLM15HB221SZ1			220ohm@100MHz	1	1005mm (0402inch)		1 MHz - 3 GHz
BLM15HD182BH1			1800ohm@100MHz	2.2	1005mm (0402inch)	BLM15HD182SN1	1 MHz - 3 GHz
BLM15HD182SH1			1800ohm@100MHz	2.2	1005mm (0402inch)	BLM15HD182SN1	1 MHz - 3 GHz
BLM15HD182SZ1			1800ohm@100MHz	2.2	1005mm (0402inch)	BLM15HD182SN1	1 MHz - 3 GHz
BLM15HD102SN1	1000	2000	1.25	250	1005/0402	General	1 MHz - 3 GHz
BLM15HD182SN1	1800	2700	2.2	200	1005/0402	General	1 MHz - 3 GHz
BLM15HD601SN1	600	1400	0.85	300	1005/0402	General	1 MHz - 3 GHz
BLM15HD102BH1			1000ohm@100MHz	1.25	1005mm (0402inch)		1 MHz - 3 GHz
BLM15HD102SH1			1000ohm@100MHz	1.25	1005mm (0402inch)		1 MHz - 3 GHz
BLM15HD102SZ1			1000ohm@100MHz	1.25	1005mm (0402inch)		1 MHz - 3 GHz
BLM15HD601BH1			600ohm@100MHz	0.85	1005mm (0402inch)		1 MHz - 3 GHz
BLM15HD601SH1			600ohm@100MHz	0.85	1005mm (0402inch)		1 MHz - 3 GHz
BLM15HD601SZ1			600ohm@100MHz	0.85	1005mm (0402inch)		1 MHz - 3 GHz
BLM15HG102BH1			1000ohm@100MHz	1.1	1005mm (0402inch)	BLM15HG102SN1	1 MHz - 3 GHz
BLM15HG102SH1			1000ohm@100MHz	1.1	1005mm (0402inch)	BLM15HG102SN1	1 MHz - 3 GHz
BLM15HG102SZ1			1000ohm@100MHz	1.1	1005mm (0402inch)	BLM15HG102SN1	1 MHz - 3 GHz
BLM15HG601BH1			600ohm@100MHz	0.7	1005mm (0402inch)	BLM15HG601SN1	1 MHz - 3 GHz
BLM15HG601SH1			600ohm@100MHz	0.7	1005mm (0402inch)	BLM15HG601SN1	1 MHz - 3 GHz
BLM15HG601SZ1			600ohm@100MHz	0.7	1005mm (0402inch)	BLM15HG601SN1	1 MHz - 3 GHz
BLM15HG102SN1	1000	1400	1.1	250	1005/0402	General	1 MHz - 3 GHz
BLM15HG601SN1	600	1000	0.7	300	1005/0402	General	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLM15KD121SN1	120		0.07	1500	1005/0402	General	1 MHz - 3 GHz
BLM15KD200SN1	20		0.011	3800	1005/0402	General	1 MHz - 3 GHz
BLM15KD300SN1	30		0.0125	3100	1005/0402	General	1 MHz - 3 GHz
BLM15PD121SZ1			120ohm@100MHz	0.09	1005mm (0402inch)	Bias BLM15PD121SN1.c	1 MHz - 3 GHz
BLM15PD300SZ1			30ohm@100MHz	0.035	1005mm (0402inch)	Bias BLM15PD300.c	1 MHz - 3 GHz
BLM15PD600SZ1			60ohm@100MHz	0.06	1005mm (0402inch)	Bias BLM15PD600.c	1 MHz - 3 GHz
BLM15PD800SZ1			80ohm@100MHz	0.07	1005mm (0402inch)	Bias BLM15PD800SN1.c	1 MHz - 3 GHz
BLM15PD121SN1	120		0.09	1300	1005/0402	General	1 MHz - 3 GHz
BLM15PD300SN1	30		0.035	2200	1005/0402	General	1 MHz - 3 GHz
BLM15PD600SN1	60		0.06	1700	1005/0402	General	1 MHz - 3 GHz
BLM15PD800SN1	80		0.07	1500	1005/0402	General	1 MHz - 3 GHz
BLM15PE121SH1			120ohm@100MHz	0.09	1005mm (0402inch)	Bias BLM15PE121SH1.c	1 MHz - 3 GHz
BLM15PE181SH1			180ohm@100MHz	0.14	1005mm (0402inch)	Bias BLM15PE181SH1.c	1 MHz - 3 GHz
BLM15PE221SH1			220ohm@100MHz	0.17	1005mm (0402inch)	Bias BLM15PE221SH1.c	1 MHz - 3 GHz
BLM15PE300SH1			30ohm@100MHz	0.035	1005mm (0402inch)	Bias BLM15PE300SH1.c	1 MHz - 3 GHz
BLM15PE331SH1			330ohm@100MHz	0.21	1005mm (0402inch)	Bias BLM15PE331SH1.c	1 MHz - 3 GHz
BLM15PE471SH1			470ohm@100MHz	0.35	1005mm (0402inch)	Bias BLM15PE471SH1.c	1 MHz - 3 GHz
BLM15PE600SH1			60ohm@100MHz	0.06	1005mm (0402inch)	Bias BLM15PE600SH1.c	1 MHz - 3 GHz
BLM15PE601SH1			600ohm@100MHz	0.4	1005mm (0402inch)	Bias BLM15PE601SH1.c	1 MHz - 3 GHz
BLM15PE800SH1			80ohm@100MHz	0.07	1005mm (0402inch)	Bias BLM15PE800SH1.c	1 MHz - 3 GHz
BLM15PG100SN1	10		0.025	1000	1005/0402	General	1 MHz - 3 GHz
BLM15PG100SZ1			10ohm@100MHz	0.025	1005mm (0402inch)		1 MHz - 3 GHz
BLM15PX121BH1			120ohm@100MHz	0.055	1005mm (0402inch)	Bias BLM15PX121SN1.c	1 MHz - 3 GHz
BLM15PX121SH1			120ohm@100MHz	0.055	1005mm (0402inch)	Bias BLM15PX121SN1.c	1 MHz - 3 GHz
BLM15PX121SZ1			120ohm@100MHz	0.055	1005mm (0402inch)	Bias BLM15PX121SN1.c	1 MHz - 3 GHz
BLM15PX181BH1			180ohm@100MHz	0.09	1005mm (0402inch)	Bias BLM15PX181SN1.c	1 MHz - 3 GHz
BLM15PX181SH1			180ohm@100MHz	0.09	1005mm (0402inch)	Bias BLM15PX181SN1.c	1 MHz - 3 GHz
BLM15PX181SZ1			180ohm@100MHz	0.09	1005mm (0402inch)	Bias BLM15PX181SN1.c	1 MHz - 3 GHz
BLM15PX221BH1			220ohm@100MHz	0.1	1005mm (0402inch)	Bias BLM15PX221SN1.c	1 MHz - 3 GHz
BLM15PX221SH1			220ohm@100MHz	0.1	1005mm (0402inch)	Bias BLM15PX221SN1.c	1 MHz - 3 GHz
BLM15PX221SZ1			220ohm@100MHz	0.1	1005mm (0402inch)	Bias BLM15PX221SN1.c	1 MHz - 3 GHz
BLM15PX330BH1			33ohm@100MHz	0.022	1005mm (0402inch)	Bias BLM15PX330SN1.c	1 MHz - 3 GHz
BLM15PX330SH1			33ohm@100MHz	0.022	1005mm (0402inch)	Bias BLM15PX330SN1.c	1 MHz - 3 GHz
BLM15PX330SZ1			33ohm@100MHz	0.022	1005mm (0402inch)	Bias BLM15PX330SN1.c	1 MHz - 3 GHz
BLM15PX331BH1			330ohm@100MHz	0.15	1005mm (0402inch)	Bias BLM15PX331SN1.c	1 MHz - 3 GHz
BLM15PX331SH1			330ohm@100MHz	0.15	1005mm (0402inch)	Bias BLM15PX331SN1.c	1 MHz - 3 GHz
BLM15PX331SZ1			330ohm@100MHz	0.15	1005mm (0402inch)	Bias BLM15PX331SN1.c	1 MHz - 3 GHz
BLM15PX471BH1			470ohm@100MHz	0.2	1005mm (0402inch)	Bias BLM15PX471SN1.c	1 MHz - 3 GHz
BLM15PX471SH1			470ohm@100MHz	0.2	1005mm (0402inch)	Bias BLM15PX471SN1.c	1 MHz - 3 GHz
BLM15PX471SZ1			470ohm@100MHz	0.2	1005mm (0402inch)	Bias BLM15PX471SN1.c	1 MHz - 3 GHz
BLM15PX600BH1			60ohm@100MHz	0.032	1005mm (0402inch)	Bias BLM15PX600SN1.c	1 MHz - 3 GHz
BLM15PX600SH1			60ohm@100MHz	0.032	1005mm (0402inch)	Bias BLM15PX600SN1.c	1 MHz - 3 GHz
BLM15PX601BH1			600ohm@100MHz	0.23	1005mm (0402inch)	Bias BLM15PX601SN1.c	1 MHz - 3 GHz
BLM15PX601SH1			600ohm@100MHz	0.23	1005mm (0402inch)	Bias BLM15PX601SN1.c	1 MHz - 3 GHz
BLM15PX601SZ1			600ohm@100MHz	0.23	1005mm (0402inch)	Bias BLM15PX601SN1.c	1 MHz - 3 GHz
BLM15PX800BH1			80ohm@100MHz	0.038	1005mm (0402inch)	Bias BLM15PX800SN1.c	1 MHz - 3 GHz
BLM15PX800SH1			80ohm@100MHz	0.038	1005mm (0402inch)	Bias BLM15PX800SN1.c	1 MHz - 3 GHz
BLM15PX800SZ1			80ohm@100MHz	0.038	1005mm (0402inch)	Bias BLM15PX800SN1.c	1 MHz - 3 GHz
BLM15PX121SN1	120		0.055	2000	1005/0402	General	1 MHz - 3 GHz
BLM15PX181SN1	180		0.09	1500	1005/0402	General	1 MHz - 3 GHz
BLM15PX221SN1	220		0.1	1400	1005/0402	General	1 MHz - 3 GHz
BLM15PX330SN1	33		0.022	3000	1005/0402	General	1 MHz - 3 GHz
BLM15PX331SN1	330		0.15	1200	1005/0402	General	1 MHz - 3 GHz
BLM15PX471SN1	470		0.2	1000	1005/0402	General	1 MHz - 3 GHz
BLM15PX600SN1	60		0.032	2500	1005/0402	General	1 MHz - 3 GHz
BLM15PX601SN1	600		0.23	900	1005/0402	General	1 MHz - 3 GHz
BLM15PX800SN1	80		0.038	2300	1005/0402	General	1 MHz - 3 GHz
BLM18AG121BH1			120ohm@100MHz	0.18	1608mm (0603inch)	Bias BLM18AG121SN1.c	1 MHz - 3 GHz
BLM18AG121SH1			120ohm@100MHz	0.18	1608mm (0603inch)	Bias BLM18AG121SN1.c	1 MHz - 3 GHz
BLM18AG121SZ1			120ohm@100MHz	0.18	1608mm (0603inch)	Bias BLM18AG121SN1.c	1 MHz - 3 GHz
BLM18AG151BH1			150ohm@100MHz	0.25	1608mm (0603inch)	Bias BLM18AG151SN1.c	1 MHz - 3 GHz
BLM18AG151SH1			150ohm@100MHz	0.25	1608mm (0603inch)	Bias BLM18AG151SN1.c	1 MHz - 3 GHz
BLM18AG151SZ1			150ohm@100MHz	0.25	1608mm (0603inch)	Bias BLM18AG151SN1.c	1 MHz - 3 GHz
BLM18AG221BH1			220ohm@100MHz	0.25	1608mm (0603inch)	Bias BLM18AG221SN1.c	1 MHz - 3 GHz
BLM18AG221SH1			220ohm@100MHz	0.25	1608mm (0603inch)	Bias BLM18AG221SN1.c	1 MHz - 3 GHz
BLM18AG221SZ1			220ohm@100MHz	0.25	1608mm (0603inch)	Bias BLM18AG221SN1.c	1 MHz - 3 GHz
BLM18AG471WH1			470ohm@100MHz	0.35	1608mm (0603inch)	Bias BLM18AG471WH1.c	1 MHz - 3 GHz
BLM18AG601BH1			600ohm@100MHz	0.38	1608mm (0603inch)	Bias BLM18AG601SH1.c	1 MHz - 3 GHz
BLM18AG601SH1			600ohm@100MHz	0.38	1608mm (0603inch)	Bias BLM18AG601SH1.c	1 MHz - 3 GHz
BLM18AG601SZ1			600ohm@100MHz	0.38	1608mm (0603inch)	Bias BLM18AG601SH1.c	1 MHz - 3 GHz
BLM18AG102SN1	1000		0.5	450	1608/0603	General	1 MHz - 3 GHz
BLM18AG121SN1	120		0.18	800	1608/0603	General	1 MHz - 3 GHz
BLM18AG151SN1	150		0.25	700	1608/0603	General	1 MHz - 3 GHz
BLM18AG221SN1	220		0.25	700	1608/0603	General	1 MHz - 3 GHz
BLM18AG331SN1	330		0.3	600	1608/0603	General	1 MHz - 3 GHz
BLM18AG471SN1	470		0.35	550	1608/0603	General	1 MHz - 3 GHz
BLM18AG601SN1	600		0.38	500	1608/0603	General	1 MHz - 3 GHz
BLM18AG102BH1			1000ohm@100MHz	0.5	1608mm (0603inch)		1 MHz - 3 GHz
BLM18AG102SH1			1000ohm@100MHz	0.5	1608mm (0603inch)		1 MHz - 3 GHz
BLM18AG102SZ1			1000ohm@100MHz	0.5	1608mm (0603inch)		1 MHz - 3 GHz
BLM18AG102WH1			1000ohm@100MHz	0.5	1608mm (0603inch)		1 MHz - 3 GHz
BLM18AG331BH1			330ohm@100MHz	0.3	1608mm (0603inch)		1 MHz - 3 GHz
BLM18AG331SH1			330ohm@100MHz	0.3	1608mm (0603inch)		1 MHz - 3 GHz
BLM18AG331SZ1			330ohm@100MHz	0.3	1608mm (0603inch)		1 MHz - 3 GHz
BLM18AG471BH1			470ohm@100MHz	0.35	1608mm (0603inch)		1 MHz - 3 GHz
BLM18AG471SH1			470ohm@100MHz	0.35	1608mm (0603inch)		1 MHz - 3 GHz
BLM18AG471SZ1			470ohm@100MHz	0.35	1608mm (0603inch)		1 MHz - 3 GHz
BLM18BA050SH1			5ohm@100MHz	0.2	1608mm (0603inch)	Bias BLM18BA050SN1.c	1 MHz - 3 GHz
BLM18BA050SZ1			5ohm@100MHz	0.2	1608mm (0603inch)	Bias BLM18BA050SN1.c	1 MHz - 3 GHz
BLM18BA100SH1			10ohm@100MHz	0.25	1608mm (0603inch)	Bias BLM18BA100SN1.c	1 MHz - 3 GHz
BLM18BA100SZ1			10ohm@100MHz	0.25	1608mm (0603inch)	Bias BLM18BA100SN1.c	1 MHz - 3 GHz
BLM18BA121SH1			120ohm@100MHz	0.9	1608mm (0603inch)	Bias BLM18BA121SN1.c	1 MHz - 3 GHz
BLM18BA121SZ1			120ohm@100MHz	0.9	1608mm (0603inch)	Bias BLM18BA121SN1.c	1 MHz - 3 GHz
BLM18BA220SH1			22ohm@100MHz	0.35	1608mm (0603inch)	Bias BLM18BA220SN1.c	1 MHz - 3 GHz
BLM18BA220SZ1			22ohm@100MHz	0.35	1608mm (0603inch)	Bias BLM18BA220SN1.c	1 MHz - 3 GHz
BLM18BA470SH1			47ohm@100MHz	0.55	1608mm (0603inch)	Bias BLM18BA470SN1.c	1 MHz - 3 GHz
BLM18BA470SZ1			47ohm@100MHz	0.55	1608mm (0603inch)	Bias BLM18BA470SN1.c	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLM18BA050SN1	5		0.2	500	1608/0603	General	1 MHz - 3 GHz
BLM18BA100SN1	10		0.25	500	1608/0603	General	1 MHz - 3 GHz
BLM18BA121SN1	120		0.9	200	1608/0603	General	1 MHz - 3 GHz
BLM18BA220SN1	22		0.35	500	1608/0603	General	1 MHz - 3 GHz
BLM18BA470SN1	47		0.55	300	1608/0603	General	1 MHz - 3 GHz
BLM18BA750SN1	75		0.7	300	1608/0603	General	1 MHz - 3 GHz
BLM18BA750SH1			75ohm@100MHz	0.7	1608mm (0603inch)		1 MHz - 3 GHz
BLM18BA750SZ1			75ohm@100MHz	0.7	1608mm (0603inch)		1 MHz - 3 GHz
BLM18BB050SH1			5ohm@100MHz	0.05	1608mm (0603inch)	BLM18BB050SN1	1 MHz - 3 GHz
BLM18BB050SZ1			5ohm@100MHz	0.05	1608mm (0603inch)	BLM18BB050SN1	1 MHz - 3 GHz
BLM18BB121SH1			120ohm@100MHz	0.3	1608mm (0603inch)	BLM18BB121SN1	1 MHz - 3 GHz
BLM18BB121SZ1			120ohm@100MHz	0.3	1608mm (0603inch)	BLM18BB121SN1	1 MHz - 3 GHz
BLM18BB141SH1			140ohm@100MHz	0.35	1608mm (0603inch)	BLM18BB141SN1	1 MHz - 3 GHz
BLM18BB141SZ1			140ohm@100MHz	0.35	1608mm (0603inch)	BLM18BB141SN1	1 MHz - 3 GHz
BLM18BB151SH1			150ohm@100MHz	0.37	1608mm (0603inch)	BLM18BB151SN1	1 MHz - 3 GHz
BLM18BB151SZ1			150ohm@100MHz	0.37	1608mm (0603inch)	BLM18BB151SN1	1 MHz - 3 GHz
BLM18BB220SH1			220ohm@100MHz	0.2	1608mm (0603inch)	BLM18BB220SN1	1 MHz - 3 GHz
BLM18BB220SZ1			220ohm@100MHz	0.2	1608mm (0603inch)	BLM18BB220SN1	1 MHz - 3 GHz
BLM18BB221SH1			220ohm@100MHz	0.45	1608mm (0603inch)	BLM18BB221SN1	1 MHz - 3 GHz
BLM18BB221SZ1			220ohm@100MHz	0.45	1608mm (0603inch)	BLM18BB221SN1	1 MHz - 3 GHz
BLM18BB331SH1			330ohm@100MHz	0.58	1608mm (0603inch)	BLM18BB331SN1	1 MHz - 3 GHz
BLM18BB331SZ1			330ohm@100MHz	0.58	1608mm (0603inch)	BLM18BB331SN1	1 MHz - 3 GHz
BLM18BB470SH1			47ohm@100MHz	0.25	1608mm (0603inch)	BLM18BB470SN1	1 MHz - 3 GHz
BLM18BB470SZ1			47ohm@100MHz	0.25	1608mm (0603inch)	BLM18BB470SN1	1 MHz - 3 GHz
BLM18BB471SH1			470ohm@100MHz	0.85	1608mm (0603inch)	BLM18BB471SN1	1 MHz - 3 GHz
BLM18BB471SZ1			470ohm@100MHz	0.85	1608mm (0603inch)	BLM18BB471SN1	1 MHz - 3 GHz
BLM18BB600SH1			60ohm@100MHz	0.25	1608mm (0603inch)	BLM18BB600SN1	1 MHz - 3 GHz
BLM18BB600SZ1			60ohm@100MHz	0.25	1608mm (0603inch)	BLM18BB600SN1	1 MHz - 3 GHz
BLM18BB050SN1	5		0.05	800	1608/0603	General	1 MHz - 3 GHz
BLM18BB100SN1	10		0.1	700	1608/0603	General	1 MHz - 3 GHz
BLM18BB121SN1	120		0.3	550	1608/0603	General	1 MHz - 3 GHz
BLM18BB141SN1	140		0.35	500	1608/0603	General	1 MHz - 3 GHz
BLM18BB151SN1	150		0.37	450	1608/0603	General	1 MHz - 3 GHz
BLM18BB220SN1	22		0.2	700	1608/0603	General	1 MHz - 3 GHz
BLM18BB221SN1	220		0.45	450	1608/0603	General	1 MHz - 3 GHz
BLM18BB331SN1	330		0.58	400	1608/0603	General	1 MHz - 3 GHz
BLM18BB470SN1	47		0.25	600	1608/0603	General	1 MHz - 3 GHz
BLM18BB471SN1	470		0.85	300	1608/0603	General	1 MHz - 3 GHz
BLM18BB600SN1	60		0.25	600	1608/0603	General	1 MHz - 3 GHz
BLM18BB750SN1	75		0.3	600	1608/0603	General	1 MHz - 3 GHz
BLM18BB100SH1			10ohm@100MHz	0.1	1608mm (0603inch)		1 MHz - 3 GHz
BLM18BB100SZ1			10ohm@100MHz	0.1	1608mm (0603inch)		1 MHz - 3 GHz
BLM18BB750SH1			75ohm@100MHz	0.3	1608mm (0603inch)		1 MHz - 3 GHz
BLM18BB750SZ1			75ohm@100MHz	0.3	1608mm (0603inch)		1 MHz - 3 GHz
BLM18BD121BH1			120ohm@100MHz	0.4	1608mm (0603inch)	BLM18BD121SN1	1 MHz - 3 GHz
BLM18BD121SH1			120ohm@100MHz	0.4	1608mm (0603inch)	BLM18BD121SN1	1 MHz - 3 GHz
BLM18BD121SZ1			120ohm@100MHz	0.4	1608mm (0603inch)	BLM18BD121SN1	1 MHz - 3 GHz
BLM18BD151BH1			150ohm@100MHz	0.4	1608mm (0603inch)	BLM18BD151SH1	1 MHz - 3 GHz
BLM18BD151SH1			150ohm@100MHz	0.4	1608mm (0603inch)	BLM18BD151SH1	1 MHz - 3 GHz
BLM18BD151SZ1			150ohm@100MHz	0.4	1608mm (0603inch)	BLM18BD151SH1	1 MHz - 3 GHz
BLM18BD182BH1			180ohm@100MHz	1.5	1608mm (0603inch)	BLM18BD182SN1	1 MHz - 3 GHz
BLM18BD182SH1			180ohm@100MHz	1.5	1608mm (0603inch)	BLM18BD182SN1	1 MHz - 3 GHz
BLM18BD182SZ1			180ohm@100MHz	1.5	1608mm (0603inch)	BLM18BD182SN1	1 MHz - 3 GHz
BLM18BD221BH1			220ohm@100MHz	0.45	1608mm (0603inch)	BLM18BD221SN1	1 MHz - 3 GHz
BLM18BD221SH1			220ohm@100MHz	0.45	1608mm (0603inch)	BLM18BD221SN1	1 MHz - 3 GHz
BLM18BD221SZ1			220ohm@100MHz	0.45	1608mm (0603inch)	BLM18BD221SN1	1 MHz - 3 GHz
BLM18BD222BH1			220ohm@100MHz	1.5	1608mm (0603inch)	BLM18BD222SN1	1 MHz - 3 GHz
BLM18BD222SH1			220ohm@100MHz	1.5	1608mm (0603inch)	BLM18BD222SN1	1 MHz - 3 GHz
BLM18BD222SZ1			220ohm@100MHz	1.5	1608mm (0603inch)	BLM18BD222SN1	1 MHz - 3 GHz
BLM18BD252BH1			250ohm@100MHz	1.5	1608mm (0603inch)	BLM18BD252SN1	1 MHz - 3 GHz
BLM18BD252SH1			250ohm@100MHz	1.5	1608mm (0603inch)	BLM18BD252SN1	1 MHz - 3 GHz
BLM18BD252SZ1			250ohm@100MHz	1.5	1608mm (0603inch)	BLM18BD252SN1	1 MHz - 3 GHz
BLM18BD421BH1			420ohm@100MHz	0.55	1608mm (0603inch)	BLM18BD421SN1	1 MHz - 3 GHz
BLM18BD421SH1			420ohm@100MHz	0.55	1608mm (0603inch)	BLM18BD421SN1	1 MHz - 3 GHz
BLM18BD421SZ1			420ohm@100MHz	0.55	1608mm (0603inch)	BLM18BD421SN1	1 MHz - 3 GHz
BLM18BD470BH1			47ohm@100MHz	0.3	1608mm (0603inch)	BLM18BD470SN1	1 MHz - 3 GHz
BLM18BD470SH1			47ohm@100MHz	0.3	1608mm (0603inch)	BLM18BD470SN1	1 MHz - 3 GHz
BLM18BD470SZ1			47ohm@100MHz	0.3	1608mm (0603inch)	BLM18BD470SN1	1 MHz - 3 GHz
BLM18BD471BH1			470ohm@100MHz	0.55	1608mm (0603inch)	BLM18BD471SN1	1 MHz - 3 GHz
BLM18BD471SH1			470ohm@100MHz	0.55	1608mm (0603inch)	BLM18BD471SN1	1 MHz - 3 GHz
BLM18BD471SZ1			470ohm@100MHz	0.55	1608mm (0603inch)	BLM18BD471SN1	1 MHz - 3 GHz
BLM18BD601BH1			600ohm@100MHz	0.65	1608mm (0603inch)	BLM18BD601SN1	1 MHz - 3 GHz
BLM18BD601SH1			600ohm@100MHz	0.65	1608mm (0603inch)	BLM18BD601SN1	1 MHz - 3 GHz
BLM18BD601SZ1			600ohm@100MHz	0.65	1608mm (0603inch)	BLM18BD601SN1	1 MHz - 3 GHz
BLM18BD102SN1	1000		0.85	200	1608/0603	General	1 MHz - 3 GHz
BLM18BD121SN1	120		0.4	300	1608/0603	General	1 MHz - 3 GHz
BLM18BD151SN1	150		0.4	300	1608/0603	General	1 MHz - 3 GHz
BLM18BD152SN1	1500		1.2	150	1608/0603	General	1 MHz - 3 GHz
BLM18BD182SN1	1800		1.5	150	1608/0603	General	1 MHz - 3 GHz
BLM18BD221SN1	220		0.45	250	1608/0603	General	1 MHz - 3 GHz
BLM18BD222SN1	2200		1.5	150	1608/0603	General	1 MHz - 3 GHz
BLM18BD252SN1	2500		1.5	150	1608/0603	General	1 MHz - 3 GHz
BLM18BD331SN1	330		0.5	250	1608/0603	General	1 MHz - 3 GHz
BLM18BD421SN1	420		0.55	250	1608/0603	General	1 MHz - 3 GHz
BLM18BD470SN1	47		0.3	500	1608/0603	General	1 MHz - 3 GHz
BLM18BD471SN1	470		0.55	250	1608/0603	General	1 MHz - 3 GHz
BLM18BD601SN1	600		0.65	200	1608/0603	General	1 MHz - 3 GHz
BLM18BD102BH1			1000ohm@100MHz	0.85	1608mm (0603inch)		1 MHz - 3 GHz
BLM18BD102SH1			1000ohm@100MHz	0.85	1608mm (0603inch)		1 MHz - 3 GHz
BLM18BD102SZ1			1000ohm@100MHz	0.85	1608mm (0603inch)		1 MHz - 3 GHz
BLM18BD152BH1			1500ohm@100MHz	1.2	1608mm (0603inch)		1 MHz - 3 GHz
BLM18BD152SH1			1500ohm@100MHz	1.2	1608mm (0603inch)		1 MHz - 3 GHz
BLM18BD152SZ1			1500ohm@100MHz	1.2	1608mm (0603inch)		1 MHz - 3 GHz
BLM18BD331BH1			330ohm@100MHz	0.5	1608mm (0603inch)		1 MHz - 3 GHz
BLM18BD331SH1			330ohm@100MHz	0.5	1608mm (0603inch)		1 MHz - 3 GHz
BLM18BD331SZ1			330ohm@100MHz	0.5	1608mm (0603inch)		1 MHz - 3 GHz
BLM18DN151SH1			150ohm@100MHz	0.12	1608mm (0603inch)	BLM18DN151SN1	1 MHz - 3 GHz
BLM18DN151SZ1			150ohm@100MHz	0.12	1608mm (0603inch)	BLM18DN151SN1	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLM18DN221SH1			220ohm@100MHz	0.21	1608mm (0603inch)	BLM18DN221SN1.d	1 MHz - 3 GHz
BLM18DN221SZ1			220ohm@100MHz	0.21	1608mm (0603inch)	BLM18DN221SN1.d	1 MHz - 3 GHz
BLM18DN381SH1			380ohm@100MHz	0.325	1608mm (0603inch)	BLM18DN381SN1.d	1 MHz - 3 GHz
BLM18DN381SZ1			380ohm@100MHz	0.325	1608mm (0603inch)	BLM18DN381SN1.d	1 MHz - 3 GHz
BLM18DN601SH1			600ohm@100MHz	0.435	1608mm (0603inch)	Bias BLM18DN601.cs	1 MHz - 3 GHz
BLM18DN601SZ1			600ohm@100MHz	0.435	1608mm (0603inch)	Bias BLM18DN601.cs	1 MHz - 3 GHz
BLM18DN151SN1	150		0.12	1400	1608/0603	General	1 MHz - 3 GHz
BLM18DN221SN1	220		0.21	1000	1608/0603	General	1 MHz - 3 GHz
BLM18DN381SN1	380		0.325	850	1608/0603	General	1 MHz - 3 GHz
BLM18DN601SN1	600		0.435	700	1608/0603	General	1 MHz - 3 GHz
BLM18EG101TH1			100ohm@100MHz	0.045	1608mm (0603inch)	BLM18EG101TH1.d	1 MHz - 3 GHz
BLM18EG101TZ1			100ohm@100MHz	0.045	1608mm (0603inch)	BLM18EG101TH1.d	1 MHz - 3 GHz
BLM18EG121SH1			120ohm@100MHz	0.04	1608mm (0603inch)	BLM18EG121SN1.d	1 MHz - 3 GHz
BLM18EG121SZ1			120ohm@100MHz	0.04	1608mm (0603inch)	BLM18EG121SN1.d	1 MHz - 3 GHz
BLM18EG181SH1			180ohm@100MHz	0.05	1608mm (0603inch)	BLM18EG181SN1.d	1 MHz - 3 GHz
BLM18EG221SZ1			220ohm@100MHz	0.05	1608mm (0603inch)	BLM18EG221SN1.d	1 MHz - 3 GHz
BLM18EG221TH1			220ohm@100MHz	0.15	1608mm (0603inch)	BLM18EG221SN1.d	1 MHz - 3 GHz
BLM18EG221TZ1			220ohm@100MHz	0.15	1608mm (0603inch)	BLM18EG221SN1.d	1 MHz - 3 GHz
BLM18EG331TH1			330ohm@100MHz	0.21	1608mm (0603inch)	BLM18EG331TN1.d	1 MHz - 3 GHz
BLM18EG331TZ1			330ohm@100MHz	0.21	1608mm (0603inch)	BLM18EG331TN1.d	1 MHz - 3 GHz
BLM18EG391TH1			390ohm@100MHz	0.3	1608mm (0603inch)	BLM18EG391TH1.d	1 MHz - 3 GHz
BLM18EG391TZ1			390ohm@100MHz	0.3	1608mm (0603inch)	BLM18EG391TH1.d	1 MHz - 3 GHz
BLM18EG471SH1			470ohm@100MHz	0.21	1608mm (0603inch)	BLM18EG471SN1.d	1 MHz - 3 GHz
BLM18EG471SZ1			470ohm@100MHz	0.21	1608mm (0603inch)	BLM18EG471SN1.d	1 MHz - 3 GHz
BLM18EG601SH1			600ohm@100MHz	0.35	1608mm (0603inch)	BLM18EG601SN1.d	1 MHz - 3 GHz
BLM18EG601SZ1			600ohm@100MHz	0.35	1608mm (0603inch)	BLM18EG601SN1.d	1 MHz - 3 GHz
BLM18EG101TN1	100	140	0.045	2000	1608/0603	General	1 MHz - 3 GHz
BLM18EG121SN1	120	145	0.04	2000	1608/0603	General	1 MHz - 3 GHz
BLM18EG221SN1	220	260	0.05	2000	1608/0603	General	1 MHz - 3 GHz
BLM18EG221TN1	220	300	0.15	1000	1608/0603	General	1 MHz - 3 GHz
BLM18EG331TN1	330	450	0.21	500	1608/0603	General	1 MHz - 3 GHz
BLM18EG391TN1	390	520	0.3	500	1608/0603	General	1 MHz - 3 GHz
BLM18EG471SN1	470	550	0.21	500	1608/0603	General	1 MHz - 3 GHz
BLM18EG601SN1	600	700	0.35	500	1608/0603	General	1 MHz - 3 GHz
BLM18GG471SN1	470	1800	1.3	200	1608/0603	General	1 MHz - 3 GHz
BLM18GG471SZ1			470ohm@100MHz	1.3	1608mm (0603inch)		1 MHz - 3 GHz
BLM18HB121SZ1			120ohm@100MHz	0.5	1608mm (0603inch)	BLM18HB121SN1.d	1 MHz - 3 GHz
BLM18HB221SZ1			220ohm@100MHz	0.8	1608mm (0603inch)	BLM18HB221SN1.d	1 MHz - 3 GHz
BLM18HB331SZ1			330ohm@100MHz	1.2	1608mm (0603inch)	BLM18HB331SN1.d	1 MHz - 3 GHz
BLM18HB121SN1	120	500	0.5	200	1608/0603	General	1 MHz - 3 GHz
BLM18HB221SN1	220	1100	0.8	100	1608/0603	General	1 MHz - 3 GHz
BLM18HB331SN1	330	1600	1.2	50	1608/0603	General	1 MHz - 3 GHz
BLM18HD102SH1			1000ohm@100MHz	1.8	1608mm (0603inch)	BLM18HD102SN1.d	1 MHz - 3 GHz
BLM18HD102SZ1			1000ohm@100MHz	1.8	1608mm (0603inch)	BLM18HD102SN1.d	1 MHz - 3 GHz
BLM18HD471SH1			470ohm@100MHz	1.2	1608mm (0603inch)	BLM18HD471SN1.d	1 MHz - 3 GHz
BLM18HD471SZ1			470ohm@100MHz	1.2	1608mm (0603inch)	BLM18HD471SN1.d	1 MHz - 3 GHz
BLM18HD601SH1			600ohm@100MHz	1.5	1608mm (0603inch)	BLM18HD601SN1.d	1 MHz - 3 GHz
BLM18HD601SZ1			600ohm@100MHz	1.5	1608mm (0603inch)	BLM18HD601SN1.d	1 MHz - 3 GHz
BLM18HD102SN1	1000	1700	1.8	50	1608/0603	General	1 MHz - 3 GHz
BLM18HD471SN1	470	1000	1.2	100	1608/0603	General	1 MHz - 3 GHz
BLM18HD601SN1	600	1200	1.5	100	1608/0603	General	1 MHz - 3 GHz
BLM18HE102SH1			1000ohm@100MHz	0.35	1608mm (0603inch)	BLM18HE102SN1.d	1 MHz - 3 GHz
BLM18HE102SZ1			1000ohm@100MHz	0.35	1608mm (0603inch)	BLM18HE102SN1.d	1 MHz - 3 GHz
BLM18HE152SH1			1500ohm@100MHz	0.5	1608mm (0603inch)	BLM18HE152SN1.d	1 MHz - 3 GHz
BLM18HE152SZ1			1500ohm@100MHz	0.5	1608mm (0603inch)	BLM18HE152SN1.d	1 MHz - 3 GHz
BLM18HE601SH1			600ohm@100MHz	0.25	1608mm (0603inch)	BLM18HE601SN1.d	1 MHz - 3 GHz
BLM18HE601SZ1			600ohm@100MHz	0.25	1608mm (0603inch)	BLM18HE601SN1.d	1 MHz - 3 GHz
BLM18HE102SN1	1000	1000	0.35	600	1608/0603	General	1 MHz - 3 GHz
BLM18HE152SN1	1500	1500	0.5	500	1608/0603	General	1 MHz - 3 GHz
BLM18HE601SN1	600	600	0.25	800	1608/0603	General	1 MHz - 3 GHz
BLM18HG102SH1			1000ohm@100MHz	1.6	1608mm (0603inch)	BLM18HG102SH1.d	1 MHz - 3 GHz
BLM18HG102SZ1			1000ohm@100MHz	1.6	1608mm (0603inch)	BLM18HG102SH1.d	1 MHz - 3 GHz
BLM18HG471SH1			470ohm@100MHz	0.85	1608mm (0603inch)	BLM18HG471SN1.d	1 MHz - 3 GHz
BLM18HG471SZ1			470ohm@100MHz	0.85	1608mm (0603inch)	BLM18HG471SN1.d	1 MHz - 3 GHz
BLM18HG601SH1			600ohm@100MHz	1	1608mm (0603inch)	BLM18HG601SN1.d	1 MHz - 3 GHz
BLM18HG601SZ1			600ohm@100MHz	1	1608mm (0603inch)	BLM18HG601SN1.d	1 MHz - 3 GHz
BLM18HG102SN1	1000	1000	1.6	100	1608/0603	General	1 MHz - 3 GHz
BLM18HG471SN1	470	600	0.85	200	1608/0603	General	1 MHz - 3 GHz
BLM18HG601SN1	600	700	1	200	1608/0603	General	1 MHz - 3 GHz
BLM18HK102SN1	1000	1200	1.5	50	1608/0603	General	1 MHz - 3 GHz
BLM18HK331SN1	330	400	0.5	200	1608/0603	General	1 MHz - 3 GHz
BLM18HK471SN1	470	600	0.7	200	1608/0603	General	1 MHz - 3 GHz
BLM18HK601SN1	600	700	0.9	100	1608/0603	General	1 MHz - 3 GHz
BLM18KG101JH1			100ohm@100MHz	0.03	1608mm (0603inch)	BLM18KG101TN1.d	1 MHz - 3 GHz
BLM18KG101TH1			100ohm@100MHz	0.03	1608mm (0603inch)	BLM18KG101TN1.d	1 MHz - 3 GHz
BLM18KG101TZ1			100ohm@100MHz	0.03	1608mm (0603inch)	BLM18KG101TN1.d	1 MHz - 3 GHz
BLM18KG101WH1			100ohm@100MHz	0.055	1608mm (0603inch)	BLM18KG101TN1.d	1 MHz - 3 GHz
BLM18KG102BH1			1000ohm@100MHz	0.2	1608mm (0603inch)	BLM18KG102SN1.d	1 MHz - 3 GHz
BLM18KG102SH1			1000ohm@100MHz	0.2	1608mm (0603inch)	BLM18KG102SN1.d	1 MHz - 3 GHz
BLM18KG102SZ1			1000ohm@100MHz	0.2	1608mm (0603inch)	BLM18KG102SN1.d	1 MHz - 3 GHz
BLM18KG102WH1			1000ohm@100MHz	0.23	1608mm (0603inch)	BLM18KG102SN1.d	1 MHz - 3 GHz
BLM18KG121JH1			120ohm@100MHz	0.03	1608mm (0603inch)	BLM18KG121TN1.d	1 MHz - 3 GHz
BLM18KG121TH1			120ohm@100MHz	0.03	1608mm (0603inch)	BLM18KG121TN1.d	1 MHz - 3 GHz
BLM18KG121TZ1			120ohm@100MHz	0.03	1608mm (0603inch)	BLM18KG121TN1.d	1 MHz - 3 GHz
BLM18KG121WH1			120ohm@100MHz	0.055	1608mm (0603inch)	BLM18KG121TN1.d	1 MHz - 3 GHz
BLM18KG221BH1			220ohm@100MHz	0.05	1608mm (0603inch)	BLM18KG221SN1.d	1 MHz - 3 GHz
BLM18KG221SH1			220ohm@100MHz	0.05	1608mm (0603inch)	BLM18KG221SN1.d	1 MHz - 3 GHz
BLM18KG221SZ1			220ohm@100MHz	0.05	1608mm (0603inch)	BLM18KG221SN1.d	1 MHz - 3 GHz
BLM18KG221WH1			220ohm@100MHz	0.08	1608mm (0603inch)	BLM18KG221SN1.d	1 MHz - 3 GHz
BLM18KG260JH1			260ohm@100MHz	0.007	1608mm (0603inch)	BLM18KG260TN1.d	1 MHz - 3 GHz
BLM18KG260TH1			260ohm@100MHz	0.007	1608mm (0603inch)	BLM18KG260TN1.d	1 MHz - 3 GHz
BLM18KG260TZ1			260ohm@100MHz	0.007	1608mm (0603inch)	BLM18KG260TN1.d	1 MHz - 3 GHz
BLM18KG260WH1			260ohm@100MHz	0.032	1608mm (0603inch)	BLM18KG260TN1.d	1 MHz - 3 GHz
BLM18KG300JH1			300ohm@100MHz	0.01	1608mm (0603inch)	BLM18KG300TN1.d	1 MHz - 3 GHz
BLM18KG300TH1			300ohm@100MHz	0.01	1608mm (0603inch)	BLM18KG300TN1.d	1 MHz - 3 GHz
BLM18KG300TZ1			300ohm@100MHz	0.01	1608mm (0603inch)	BLM18KG300TN1.d	1 MHz - 3 GHz
BLM18KG300WH1			300ohm@100MHz	0.035	1608mm (0603inch)	BLM18KG300TN1.d	1 MHz - 3 GHz
BLM18KG331BH1			330ohm@100MHz	0.08	1608mm (0603inch)	BLM18KG331SN1.d	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLM18KG331SH1			330ohm@100MHz	0.08	1608mm (0603inch)	BLM18KG331SN1.4	1 MHz - 3 GHz
BLM18KG331SZ1			330ohm@100MHz	0.08	1608mm (0603inch)	BLM18KG331SN1.4	1 MHz - 3 GHz
BLM18KG331WH1			330ohm@100MHz	0.11	1608mm (0603inch)	BLM18KG331SN1.4	1 MHz - 3 GHz
BLM18KG471BH1			470ohm@100MHz	0.13	1608mm (0603inch)	BLM18KG471SN1.4	1 MHz - 3 GHz
BLM18KG471SH1			470ohm@100MHz	0.13	1608mm (0603inch)	BLM18KG471SN1.4	1 MHz - 3 GHz
BLM18KG471SZ1			470ohm@100MHz	0.13	1608mm (0603inch)	BLM18KG471SN1.4	1 MHz - 3 GHz
BLM18KG471WH1			470ohm@100MHz	0.16	1608mm (0603inch)	BLM18KG471SN1.4	1 MHz - 3 GHz
BLM18KG601SH1			600ohm@100MHz	0.15	1608mm (0603inch)	BLM18KG601SN1.4	1 MHz - 3 GHz
BLM18KG601BH1			600ohm@100MHz	0.15	1608mm (0603inch)	BLM18KG601SN1.4	1 MHz - 3 GHz
BLM18KG601SZ1			600ohm@100MHz	0.15	1608mm (0603inch)	BLM18KG601SN1.4	1 MHz - 3 GHz
BLM18KG601WH1			600ohm@100MHz	0.18	1608mm (0603inch)	BLM18KG601SN1.4	1 MHz - 3 GHz
BLM18KG700JH1			70ohm@100MHz	0.022	1608mm (0603inch)	BLM18KG700TN1.4	1 MHz - 3 GHz
BLM18KG700TH1			70ohm@100MHz	0.022	1608mm (0603inch)	BLM18KG700TN1.4	1 MHz - 3 GHz
BLM18KG700TZ1			70ohm@100MHz	0.022	1608mm (0603inch)	BLM18KG700TN1.4	1 MHz - 3 GHz
BLM18KG700WH1			70ohm@100MHz	0.047	1608mm (0603inch)	BLM18KG700TN1.4	1 MHz - 3 GHz
BLM18KG101TN1	100		0.03	3000	1608/0603	General	1 MHz - 3 GHz
BLM18KG102SN1	1000		0.2	1000	1608/0603	General	1 MHz - 3 GHz
BLM18KG121TN1	120		0.03	3000	1608/0603	General	1 MHz - 3 GHz
BLM18KG221SN1	220		0.05	2200	1608/0603	General	1 MHz - 3 GHz
BLM18KG260TN1	26		0.007	6000	1608/0603	General	1 MHz - 3 GHz
BLM18KG300TN1	30		0.01	5000	1608/0603	General	1 MHz - 3 GHz
BLM18KG331SN1	330		0.08	1700	1608/0603	General	1 MHz - 3 GHz
BLM18KG471SN1	470		0.13	1500	1608/0603	General	1 MHz - 3 GHz
BLM18KG601SN1	600		0.15	1300	1608/0603	General	1 MHz - 3 GHz
BLM18KG700TN1	70		0.022	3500	1608/0603	General	1 MHz - 3 GHz
BLM18KN102EH1			1000ohm@100MHz	0.2	1608mm (0603inch)	BLM18KN102EH1.4	1 MHz - 3 GHz
BLM18KN101EH1			100ohm@100MHz	0.03	1608mm (0603inch)	BLM18KN101EH1.4	1 MHz - 3 GHz
BLM18KN121EH1			120ohm@100MHz	0.03	1608mm (0603inch)	BLM18KN121EH1.4	1 MHz - 3 GHz
BLM18KN221EH1			220ohm@100MHz	0.05	1608mm (0603inch)	BLM18KN221EH1.4	1 MHz - 3 GHz
BLM18KN260EH1			26ohm@100MHz	0.007	1608mm (0603inch)	BLM18KN260EH1.4	1 MHz - 3 GHz
BLM18KN300EH1			30ohm@100MHz	0.01	1608mm (0603inch)	BLM18KN300EH1.4	1 MHz - 3 GHz
BLM18KN331EH1			330ohm@100MHz	0.08	1608mm (0603inch)	BLM18KN331EH1.4	1 MHz - 3 GHz
BLM18KN471EH1			470ohm@100MHz	0.13	1608mm (0603inch)	BLM18KN471EH1.4	1 MHz - 3 GHz
BLM18KN601EH1			600ohm@100MHz	0.15	1608mm (0603inch)	BLM18KN601EH1.4	1 MHz - 3 GHz
BLM18KN700EH1			70ohm@100MHz	0.022	1608mm (0603inch)	BLM18KN700EH1.4	1 MHz - 3 GHz
BLM18PG121SH1			120ohm@100MHz	0.05	1608mm (0603inch)	BLM18PG121SN1.4	1 MHz - 3 GHz
BLM18PG121SZ1			120ohm@100MHz	0.05	1608mm (0603inch)	BLM18PG121SN1.4	1 MHz - 3 GHz
BLM18PG181SH1			180ohm@100MHz	0.09	1608mm (0603inch)	BLM18PG181SN1.4	1 MHz - 3 GHz
BLM18PG181SZ1			180ohm@100MHz	0.09	1608mm (0603inch)	BLM18PG181SN1.4	1 MHz - 3 GHz
BLM18PG221SH1			220ohm@100MHz	0.1	1608mm (0603inch)	BLM18PG221SN1.4	1 MHz - 3 GHz
BLM18PG221SZ1			220ohm@100MHz	0.1	1608mm (0603inch)	BLM18PG221SN1.4	1 MHz - 3 GHz
BLM18PG300SH1			30ohm@100MHz	0.05	1608mm (0603inch)	BLM18PG300SN1.4	1 MHz - 3 GHz
BLM18PG300SZ1			30ohm@100MHz	0.05	1608mm (0603inch)	BLM18PG300SN1.4	1 MHz - 3 GHz
BLM18PG330SH1			330ohm@100MHz	0.025	1608mm (0603inch)	BLM18PG330SN1.4	1 MHz - 3 GHz
BLM18PG330SZ1			330ohm@100MHz	0.025	1608mm (0603inch)	BLM18PG330SN1.4	1 MHz - 3 GHz
BLM18PG331SH1			330ohm@100MHz	0.15	1608mm (0603inch)	BLM18PG331SN1.4	1 MHz - 3 GHz
BLM18PG331SZ1			330ohm@100MHz	0.15	1608mm (0603inch)	BLM18PG331SN1.4	1 MHz - 3 GHz
BLM18PG471SH1			470ohm@100MHz	0.2	1608mm (0603inch)	BLM18PG471SN1.4	1 MHz - 3 GHz
BLM18PG471SZ1			470ohm@100MHz	0.2	1608mm (0603inch)	BLM18PG471SN1.4	1 MHz - 3 GHz
BLM18PG600SH1			60ohm@100MHz	0.1	1608mm (0603inch)	BLM18PG600SN1.4	1 MHz - 3 GHz
BLM18PG600SZ1			60ohm@100MHz	0.1	1608mm (0603inch)	BLM18PG600SN1.4	1 MHz - 3 GHz
BLM18PG121SN1	120		0.05	2000	1608/0603	General	1 MHz - 3 GHz
BLM18PG181SN1	180		0.09	1500	1608/0603	General	1 MHz - 3 GHz
BLM18PG221SN1	220		0.1	1400	1608/0603	General	1 MHz - 3 GHz
BLM18PG300SN1	30		0.05	1000	1608/0603	General	1 MHz - 3 GHz
BLM18PG330SN1	33		0.025	3000	1608/0603	General	1 MHz - 3 GHz
BLM18PG331SN1	330		0.15	1200	1608/0603	General	1 MHz - 3 GHz
BLM18PG471SN1	470		0.2	1000	1608/0603	General	1 MHz - 3 GHz
BLM18PG600SN1	60		0.1	1000	1608/0603	General	1 MHz - 3 GHz
BLM18RK102SN1	1000		0.8	200	1608/0603	General	1 MHz - 3 GHz
BLM18RK121SN1	120		0.25	200	1608/0603	General	1 MHz - 3 GHz
BLM18RK221SN1	220		0.3	200	1608/0603	General	1 MHz - 3 GHz
BLM18RK471SN1	470		0.5	200	1608/0603	General	1 MHz - 3 GHz
BLM18RK601SN1	600		0.6	200	1608/0603	General	1 MHz - 3 GHz
BLM18SD220SN1	22		0.008	6000	1608/0603	General	1 MHz - 3 GHz
BLM18SG121TZ1			120ohm@100MHz	0.025	1608mm (0603inch)	BLM18SG121TN1.4	1 MHz - 3 GHz
BLM18SG221TZ1			220ohm@100MHz	0.04	1608mm (0603inch)	BLM18SG221TN1.4	1 MHz - 3 GHz
BLM18SG260TZ1			26ohm@100MHz	0.007	1608mm (0603inch)	BLM18SG260TN1.4	1 MHz - 3 GHz
BLM18SG331TZ1			330ohm@100MHz	0.07	1608mm (0603inch)	BLM18SG331TN1.4	1 MHz - 3 GHz
BLM18SG700TZ1			70ohm@100MHz	0.02	1608mm (0603inch)	BLM18SG700TN1.4	1 MHz - 3 GHz
BLM18SG121TN1	120		0.025	3000	1608/0603	General	1 MHz - 3 GHz
BLM18SG221TN1	220		0.04	2500	1608/0603	General	1 MHz - 3 GHz
BLM18SG260TN1	26		0.007	6000	1608/0603	General	1 MHz - 3 GHz
BLM18SG330SN1	33		0.008	6000	1608/0603	General	1 MHz - 3 GHz
BLM18SG331TN1	330		0.07	1500	1608/0603	General	1 MHz - 3 GHz
BLM18SG700TN1	70		0.02	4000	1608/0603	General	1 MHz - 3 GHz
BLM18SN220TH1			22ohm@100MHz	0.004	1608mm (0603inch)	BLM18SN220TN1.4	1 MHz - 3 GHz
BLM18SN220TZ1			22ohm@100MHz	0.004	1608mm (0603inch)	BLM18SN220TN1.4	1 MHz - 3 GHz
BLM18SN220TN1	22		0.004	8000	1608/0603	General	1 MHz - 3 GHz
BLM18SP101SN1	100		0.022	3700	1608/0603	General	1 MHz - 3 GHz
BLM18SP102SN1	1000		0.185	1200	1608/0603	General	1 MHz - 3 GHz
BLM18SP221SN1	220		0.04	2800	1608/0603	General	1 MHz - 3 GHz
BLM18SP300SN1	30		0.008	6000	1608/0603	General	1 MHz - 3 GHz
BLM18SP601SN1	600		0.14	1500	1608/0603	General	1 MHz - 3 GHz
BLM18SP101SH1			100ohm@100MHz	0.022	1608mm (0603inch)	BLM18SP101SH1.4	1 MHz - 3 GHz
BLM18SP101SZ1			100ohm@100MHz	0.022	1608mm (0603inch)	BLM18SP101SH1.4	1 MHz - 3 GHz
BLM18SP102SH1			1000ohm@100MHz	0.185	1608mm (0603inch)	BLM18SP102SH1.4	1 MHz - 3 GHz
BLM18SP102SZ1			1000ohm@100MHz	0.185	1608mm (0603inch)	BLM18SP102SH1.4	1 MHz - 3 GHz
BLM18SP221SH1			220ohm@100MHz	0.04	1608mm (0603inch)	BLM18SP221SH1.4	1 MHz - 3 GHz
BLM18SP221SZ1			220ohm@100MHz	0.04	1608mm (0603inch)	BLM18SP221SH1.4	1 MHz - 3 GHz
BLM18SP300SH1			30ohm@100MHz	0.008	1608mm (0603inch)	BLM18SP300SH1.4	1 MHz - 3 GHz
BLM18SP300SZ1			30ohm@100MHz	0.008	1608mm (0603inch)	BLM18SP300SH1.4	1 MHz - 3 GHz
BLM18SP601SH1			600ohm@100MHz	0.14	1608mm (0603inch)	BLM18SP601SH1.4	1 MHz - 3 GHz
BLM18SP601SZ1			600ohm@100MHz	0.14	1608mm (0603inch)	BLM18SP601SH1.4	1 MHz - 3 GHz
BLM18TG102TN1	1000		0.6	100	1608/0603	General	1 MHz - 3 GHz
BLM18TG121TN1	120		0.25	200	1608/0603	General	1 MHz - 3 GHz
BLM18TG221TN1	220		0.3	200	1608/0603	General	1 MHz - 3 GHz
BLM18TG601TN1	600		0.45	200	1608/0603	General	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLM21AG102BH1			1000ohm@100MHz	0.27	2012mm (0805inch)	BLM21AG102SN1.4	1 MHz - 3 GHz
BLM21AG102SH1			1000ohm@100MHz	0.27	2012mm (0805inch)	BLM21AG102SN1.4	1 MHz - 3 GHz
BLM21AG102SZ1			1000ohm@100MHz	0.27	2012mm (0805inch)	BLM21AG102SN1.4	1 MHz - 3 GHz
BLM21AG121BH1			120ohm@100MHz	0.09	2012mm (0805inch)	BLM21AG121SN1.4	1 MHz - 3 GHz
BLM21AG121SH1			120ohm@100MHz	0.09	2012mm (0805inch)	BLM21AG121SN1.4	1 MHz - 3 GHz
BLM21AG121SZ1			120ohm@100MHz	0.09	2012mm (0805inch)	BLM21AG121SN1.4	1 MHz - 3 GHz
BLM21AG151BH1			150ohm@100MHz	0.09	2012mm (0805inch)	BLM21AG151SN1.4	1 MHz - 3 GHz
BLM21AG151SH1			150ohm@100MHz	0.09	2012mm (0805inch)	BLM21AG151SN1.4	1 MHz - 3 GHz
BLM21AG151SZ1			150ohm@100MHz	0.09	2012mm (0805inch)	BLM21AG151SN1.4	1 MHz - 3 GHz
BLM21AG601BH1			600ohm@100MHz	0.2	2012mm (0805inch)	BLM21AG601SN1.4	1 MHz - 3 GHz
BLM21AG601SH1			600ohm@100MHz	0.2	2012mm (0805inch)	BLM21AG601SN1.4	1 MHz - 3 GHz
BLM21AG601SZ1			600ohm@100MHz	0.2	2012mm (0805inch)	BLM21AG601SN1.4	1 MHz - 3 GHz
BLM21AG102SN1	1000		0.27	600	2012/0805	General	1 MHz - 3 GHz
BLM21AG121SN1	120		0.09	1000	2012/0805	General	1 MHz - 3 GHz
BLM21AG151SN1	150		0.09	1000	2012/0805	General	1 MHz - 3 GHz
BLM21AG221SN1	220		0.12	900	2012/0805	General	1 MHz - 3 GHz
BLM21AG331SN1	330		0.15	800	2012/0805	General	1 MHz - 3 GHz
BLM21AG471SN1	470		0.18	700	2012/0805	General	1 MHz - 3 GHz
BLM21AG601SN1	600		0.2	700	2012/0805	General	1 MHz - 3 GHz
BLM21AG221BH1			220ohm@100MHz	0.12	2012mm (0805inch)		1 MHz - 3 GHz
BLM21AG221SH1			220ohm@100MHz	0.12	2012mm (0805inch)		1 MHz - 3 GHz
BLM21AG221SZ1			220ohm@100MHz	0.12	2012mm (0805inch)		1 MHz - 3 GHz
BLM21AG331BH1			330ohm@100MHz	0.15	2012mm (0805inch)		1 MHz - 3 GHz
BLM21AG331SH1			330ohm@100MHz	0.15	2012mm (0805inch)		1 MHz - 3 GHz
BLM21AG331SZ1			330ohm@100MHz	0.15	2012mm (0805inch)		1 MHz - 3 GHz
BLM21AG471BH1			470ohm@100MHz	0.18	2012mm (0805inch)		1 MHz - 3 GHz
BLM21AG471SH1			470ohm@100MHz	0.18	2012mm (0805inch)		1 MHz - 3 GHz
BLM21AG471SZ1			470ohm@100MHz	0.18	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BB050SH1			5ohm@100MHz	0.02	2012mm (0805inch)	BLM21BB050SN1.4	1 MHz - 3 GHz
BLM21BB050SZ1			5ohm@100MHz	0.02	2012mm (0805inch)	BLM21BB050SN1.4	1 MHz - 3 GHz
BLM21BB121SH1			120ohm@100MHz	0.19	2012mm (0805inch)	BLM21BB121SN1.4	1 MHz - 3 GHz
BLM21BB121SZ1			120ohm@100MHz	0.19	2012mm (0805inch)	BLM21BB121SN1.4	1 MHz - 3 GHz
BLM21BB201SH1			200ohm@100MHz	0.26	2012mm (0805inch)	BLM21BB201SN1.4	1 MHz - 3 GHz
BLM21BB201SZ1			200ohm@100MHz	0.26	2012mm (0805inch)	BLM21BB201SN1.4	1 MHz - 3 GHz
BLM21BB221SH1			220ohm@100MHz	0.26	2012mm (0805inch)	BLM21BB221SN1.4	1 MHz - 3 GHz
BLM21BB221SZ1			220ohm@100MHz	0.26	2012mm (0805inch)	BLM21BB221SN1.4	1 MHz - 3 GHz
BLM21BB331SH1			330ohm@100MHz	0.33	2012mm (0805inch)	BLM21BB331SN1.4	1 MHz - 3 GHz
BLM21BB331SZ1			330ohm@100MHz	0.33	2012mm (0805inch)	BLM21BB331SN1.4	1 MHz - 3 GHz
BLM21BB471SH1			470ohm@100MHz	0.4	2012mm (0805inch)	BLM21BB471SN1.4	1 MHz - 3 GHz
BLM21BB471SZ1			470ohm@100MHz	0.4	2012mm (0805inch)	BLM21BB471SN1.4	1 MHz - 3 GHz
BLM21BB600SH1			60ohm@100MHz	0.13	2012mm (0805inch)	BLM21BB600SN1.4	1 MHz - 3 GHz
BLM21BB600SZ1			60ohm@100MHz	0.13	2012mm (0805inch)	BLM21BB600SN1.4	1 MHz - 3 GHz
BLM21BB750SH1			75ohm@100MHz	0.16	2012mm (0805inch)	BLM21BB750SN1.4	1 MHz - 3 GHz
BLM21BB750SZ1			75ohm@100MHz	0.16	2012mm (0805inch)	BLM21BB750SN1.4	1 MHz - 3 GHz
BLM21BB050SN1	5		0.02	1000	2012/0805	General	1 MHz - 3 GHz
BLM21BB121SN1	120		0.19	600	2012/0805	General	1 MHz - 3 GHz
BLM21BB151SN1	150		0.21	600	2012/0805	General	1 MHz - 3 GHz
BLM21BB201SN1	200		0.26	500	2012/0805	General	1 MHz - 3 GHz
BLM21BB221SN1	220		0.26	500	2012/0805	General	1 MHz - 3 GHz
BLM21BB331SN1	330		0.33	400	2012/0805	General	1 MHz - 3 GHz
BLM21BB471SN1	470		0.4	400	2012/0805	General	1 MHz - 3 GHz
BLM21BB600SN1	60		0.13	800	2012/0805	General	1 MHz - 3 GHz
BLM21BB750SN1	75		0.16	700	2012/0805	General	1 MHz - 3 GHz
BLM21BB151SH1			150ohm@100MHz	0.21	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BB151SZ1			150ohm@100MHz	0.21	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BD121SH1			120ohm@100MHz	0.25	2012mm (0805inch)	BLM21BD121SN1.4	1 MHz - 3 GHz
BLM21BD121SZ1			120ohm@100MHz	0.25	2012mm (0805inch)	BLM21BD121SN1.4	1 MHz - 3 GHz
BLM21BD222SH1			2250ohm@100MHz	0.6	2012mm (0805inch)	BLM21BD222TN1.4	1 MHz - 3 GHz
BLM21BD222SZ1			2250ohm@100MHz	0.6	2012mm (0805inch)	BLM21BD222TN1.4	1 MHz - 3 GHz
BLM21BD222TH1			2200ohm@100MHz	0.6	2012mm (0805inch)	BLM21BD222TN1.4	1 MHz - 3 GHz
BLM21BD222TZ1			2200ohm@100MHz	0.6	2012mm (0805inch)	BLM21BD222TN1.4	1 MHz - 3 GHz
BLM21BD272SH1			2700ohm@100MHz	0.8	2012mm (0805inch)	BLM21BD272SH1.4	1 MHz - 3 GHz
BLM21BD272SZ1			2700ohm@100MHz	0.8	2012mm (0805inch)	BLM21BD272SH1.4	1 MHz - 3 GHz
BLM21BD601SH1			600ohm@100MHz	0.35	2012mm (0805inch)	BLM21BD601SN1.4	1 MHz - 3 GHz
BLM21BD601SZ1			600ohm@100MHz	0.35	2012mm (0805inch)	BLM21BD601SN1.4	1 MHz - 3 GHz
BLM21BD102SN1	1000		0.4	250	2012/0805	General	1 MHz - 3 GHz
BLM21BD121SN1	120		0.25	350	2012/0805	General	1 MHz - 3 GHz
BLM21BD151SN1	150		0.25	350	2012/0805	General	1 MHz - 3 GHz
BLM21BD152SN1	1500		0.45	250	2012/0805	General	1 MHz - 3 GHz
BLM21BD182SN1	1800		0.5	250	2012/0805	General	1 MHz - 3 GHz
BLM21BD221SN1	220		0.25	350	2012/0805	General	1 MHz - 3 GHz
BLM21BD222SN1	2250		0.6	250	2012/0805	General	1 MHz - 3 GHz
BLM21BD222TN1	2200		0.6	200	2012/0805	General	1 MHz - 3 GHz
BLM21BD272SN1	2700		0.8	200	2012/0805	General	1 MHz - 3 GHz
BLM21BD331SN1	330		0.3	300	2012/0805	General	1 MHz - 3 GHz
BLM21BD421SN1	420		0.3	300	2012/0805	General	1 MHz - 3 GHz
BLM21BD471SN1	470		0.35	300	2012/0805	General	1 MHz - 3 GHz
BLM21BD601SN1	600		0.35	300	2012/0805	General	1 MHz - 3 GHz
BLM21BD751SN1	750		0.4	250	2012/0805	General	1 MHz - 3 GHz
BLM21BD102SH1			1000ohm@100MHz	0.4	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BD102SZ1			1000ohm@100MHz	0.4	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BD151SH1			150ohm@100MHz	0.25	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BD151SZ1			150ohm@100MHz	0.25	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BD152SH1			1500ohm@100MHz	0.45	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BD152SZ1			1500ohm@100MHz	0.45	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BD182SH1			1800ohm@100MHz	0.5	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BD182SZ1			1800ohm@100MHz	0.5	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BD221SH1			220ohm@100MHz	0.25	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BD221SZ1			220ohm@100MHz	0.25	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BD331SH1			330ohm@100MHz	0.3	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BD331SZ1			330ohm@100MHz	0.3	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BD421SH1			420ohm@100MHz	0.3	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BD421SZ1			420ohm@100MHz	0.3	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BD471SH1			470ohm@100MHz	0.35	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BD471SZ1			470ohm@100MHz	0.35	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BD751SH1			750ohm@100MHz	0.4	2012mm (0805inch)		1 MHz - 3 GHz
BLM21BD751SZ1			750ohm@100MHz	0.4	2012mm (0805inch)		1 MHz - 3 GHz
BLM21HE122SN1	1200	450	0.11	1600	2012/0805	General	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLM21HE472SN1	4700	750	0.4	850	2012/0805	General	1 MHz - 3 GHz
BLM21HE601SN1	600	450	0.055	2300	2012/0805	General	1 MHz - 3 GHz
BLM21HE802SN1	8000	850	0.7	650	2012/0805	General	1 MHz - 3 GHz
BLM21HE122BH1			1200ohm@100MHz	0.11	2012mm (0805inch)		1 MHz - 3 GHz
BLM21HE122SH1			1200ohm@100MHz	0.11	2012mm (0805inch)		1 MHz - 3 GHz
BLM21HE472BH1			4700ohm@100MHz	0.4	2012mm (0805inch)		1 MHz - 3 GHz
BLM21HE472SH1			4700ohm@100MHz	0.4	2012mm (0805inch)		1 MHz - 3 GHz
BLM21HE601BH1			600ohm@100MHz	0.055	2012mm (0805inch)		1 MHz - 3 GHz
BLM21HE601SH1			600ohm@100MHz	0.055	2012mm (0805inch)		1 MHz - 3 GHz
BLM21HE802BH1			8000ohm@100MHz	0.7	2012mm (0805inch)		1 MHz - 3 GHz
BLM21HE802SH1			8000ohm@100MHz	0.7	2012mm (0805inch)		1 MHz - 3 GHz
BLM21PG121BH1			120ohm@100MHz	0.03	2012mm (0805inch)	BLM21PG121SN1	1 MHz - 3 GHz
BLM21PG121SH1			120ohm@100MHz	0.03	2012mm (0805inch)	BLM21PG121SN1	1 MHz - 3 GHz
BLM21PG121SZ1			120ohm@100MHz	0.03	2012mm (0805inch)	BLM21PG121SN1	1 MHz - 3 GHz
BLM21PG220BH1			220ohm@100MHz	0.009	2012mm (0805inch)	BLM21PG220SN1	1 MHz - 3 GHz
BLM21PG220SH1			220ohm@100MHz	0.009	2012mm (0805inch)	BLM21PG220SN1	1 MHz - 3 GHz
BLM21PG220SZ1			220ohm@100MHz	0.009	2012mm (0805inch)	BLM21PG220SN1	1 MHz - 3 GHz
BLM21PG221BH1			220ohm@100MHz	0.045	2012mm (0805inch)	BLM21PG221SN1	1 MHz - 3 GHz
BLM21PG221SH1			220ohm@100MHz	0.045	2012mm (0805inch)	BLM21PG221SN1	1 MHz - 3 GHz
BLM21PG221SZ1			220ohm@100MHz	0.045	2012mm (0805inch)	BLM21PG221SN1	1 MHz - 3 GHz
BLM21PG300BH1			300ohm@100MHz	0.014	2012mm (0805inch)	BLM21PG300SN1	1 MHz - 3 GHz
BLM21PG300SH1			300ohm@100MHz	0.014	2012mm (0805inch)	BLM21PG300SN1	1 MHz - 3 GHz
BLM21PG300SZ1			300ohm@100MHz	0.014	2012mm (0805inch)	BLM21PG300SN1	1 MHz - 3 GHz
BLM21PG331BH1			330ohm@100MHz	0.07	2012mm (0805inch)	BLM21PG331SH1	1 MHz - 3 GHz
BLM21PG331SH1			330ohm@100MHz	0.07	2012mm (0805inch)	BLM21PG331SH1	1 MHz - 3 GHz
BLM21PG331SZ1			330ohm@100MHz	0.07	2012mm (0805inch)	BLM21PG331SH1	1 MHz - 3 GHz
BLM21PG600BH1			60ohm@100MHz	0.02	2012mm (0805inch)	BLM21PG600SN1	1 MHz - 3 GHz
BLM21PG600SH1			60ohm@100MHz	0.02	2012mm (0805inch)	BLM21PG600SN1	1 MHz - 3 GHz
BLM21PG600SZ1			60ohm@100MHz	0.02	2012mm (0805inch)	BLM21PG600SN1	1 MHz - 3 GHz
BLM21PG102SN1	1000	0.2	1150	2000	2012/0805	General	1 MHz - 3 GHz
BLM21PG121SN1	120	0.03	3000	2000	2012/0805	General	1 MHz - 3 GHz
BLM21PG220SN1	22	0.009	6000	2000	2012/0805	General	1 MHz - 3 GHz
BLM21PG221SN1	220	0.045	2000	2000	2012/0805	General	1 MHz - 3 GHz
BLM21PG300SN1	30	0.014	4000	2000	2012/0805	General	1 MHz - 3 GHz
BLM21PG331SN1	330	0.07	1500	2000	2012/0805	General	1 MHz - 3 GHz
BLM21PG600SN1	60	0.02	3500	2000	2012/0805	General	1 MHz - 3 GHz
BLM21PG601SN1	600	0.14	1400	2000	2012/0805	General	1 MHz - 3 GHz
BLM21PG102BH1			1000ohm@100MHz	0.2	2012mm (0805inch)		1 MHz - 3 GHz
BLM21PG102SH1			1000ohm@100MHz	0.2	2012mm (0805inch)		1 MHz - 3 GHz
BLM21PG601BH1			600ohm@100MHz	0.14	2012mm (0805inch)		1 MHz - 3 GHz
BLM21PG601SH1			600ohm@100MHz	0.14	2012mm (0805inch)		1 MHz - 3 GHz
BLM21RK102SN1	1000	0.5	200	2000	2012/0805	General	1 MHz - 3 GHz
BLM21RK121SN1	120	0.15	200	2000	2012/0805	General	1 MHz - 3 GHz
BLM21RK221SN1	220	0.2	200	2000	2012/0805	General	1 MHz - 3 GHz
BLM21RK471SN1	470	0.25	200	2000	2012/0805	General	1 MHz - 3 GHz
BLM21RK601SN1	600	0.3	200	2000	2012/0805	General	1 MHz - 3 GHz
BLM21SN300SH1			30ohm@100MHz	0.004	2012mm (0805inch)	BLM21SN300SN1	1 MHz - 3 GHz
BLM21SN300SZ1			30ohm@100MHz	0.004	2012mm (0805inch)	BLM21SN300SN1	1 MHz - 3 GHz
BLM21SN300SN1	30	0.004	8500	2000	2012/0805	General	1 MHz - 3 GHz
BLM21SP102BH1			1000ohm@100MHz	0.12	2012mm (0805inch)	BLM21SP102SH1	1 MHz - 3 GHz
BLM21SP102SH1			1000ohm@100MHz	0.12	2012mm (0805inch)	BLM21SP102SH1	1 MHz - 3 GHz
BLM21SP102SZ1			1000ohm@100MHz	0.12	2012mm (0805inch)	BLM21SP102SH1	1 MHz - 3 GHz
BLM21SP111BH1			110ohm@100MHz	0.013	2012mm (0805inch)	BLM21SP111SH1	1 MHz - 3 GHz
BLM21SP111SH1			110ohm@100MHz	0.013	2012mm (0805inch)	BLM21SP111SH1	1 MHz - 3 GHz
BLM21SP111SZ1			110ohm@100MHz	0.013	2012mm (0805inch)	BLM21SP111SH1	1 MHz - 3 GHz
BLM21SP181BH1			180ohm@100MHz	0.02	2012mm (0805inch)	BLM21SP181SH1	1 MHz - 3 GHz
BLM21SP181SH1			180ohm@100MHz	0.02	2012mm (0805inch)	BLM21SP181SH1	1 MHz - 3 GHz
BLM21SP181SZ1			180ohm@100MHz	0.02	2012mm (0805inch)	BLM21SP181SH1	1 MHz - 3 GHz
BLM21SP331BH1			330ohm@100MHz	0.04	2012mm (0805inch)	BLM21SP331SH1	1 MHz - 3 GHz
BLM21SP331SH1			330ohm@100MHz	0.04	2012mm (0805inch)	BLM21SP331SH1	1 MHz - 3 GHz
BLM21SP331SZ1			330ohm@100MHz	0.04	2012mm (0805inch)	BLM21SP331SH1	1 MHz - 3 GHz
BLM21SP471BH1			470ohm@100MHz	0.05	2012mm (0805inch)	BLM21SP471SH1	1 MHz - 3 GHz
BLM21SP471SH1			470ohm@100MHz	0.05	2012mm (0805inch)	BLM21SP471SH1	1 MHz - 3 GHz
BLM21SP471SZ1			470ohm@100MHz	0.05	2012mm (0805inch)	BLM21SP471SH1	1 MHz - 3 GHz
BLM21SP601BH1			600ohm@100MHz	0.06	2012mm (0805inch)	BLM21SP601SH1	1 MHz - 3 GHz
BLM21SP601SH1			600ohm@100MHz	0.06	2012mm (0805inch)	BLM21SP601SH1	1 MHz - 3 GHz
BLM21SP601SZ1			600ohm@100MHz	0.06	2012mm (0805inch)	BLM21SP601SH1	1 MHz - 3 GHz
BLM21SP700BH1			70ohm@100MHz	0.009	2012mm (0805inch)	BLM21SP700SH1	1 MHz - 3 GHz
BLM21SP700SH1			70ohm@100MHz	0.009	2012mm (0805inch)	BLM21SP700SH1	1 MHz - 3 GHz
BLM21SP700SZ1			70ohm@100MHz	0.009	2012mm (0805inch)	BLM21SP700SH1	1 MHz - 3 GHz
BLM21SP102SN1	1000	0.12	1600	2000	2012/0805	General	1 MHz - 3 GHz
BLM21SP111SN1	110	0.013	5000	2000	2012/0805	General	1 MHz - 3 GHz
BLM21SP181SN1	180	0.02	4000	2000	2012/0805	General	1 MHz - 3 GHz
BLM21SP331SN1	330	0.04	2800	2000	2012/0805	General	1 MHz - 3 GHz
BLM21SP471SN1	470	0.05	2500	2000	2012/0805	General	1 MHz - 3 GHz
BLM21SP601SN1	600	0.06	2300	2000	2012/0805	General	1 MHz - 3 GHz
BLM21SP700SN1	70	0.009	6000	2000	2012/0805	General	1 MHz - 3 GHz
BLM31AJ601SH1			600ohm@100MHz	0.9	3216mm (1206inch)		1 MHz - 3 GHz
BLM31KN102BH1			1000ohm@100MHz	0.075	3216mm (1206inch)	BLM31KN102SH1	1 MHz - 3 GHz
BLM31KN102SH1			1000ohm@100MHz	0.075	3216mm (1206inch)	BLM31KN102SH1	1 MHz - 3 GHz
BLM31KN102SZ1			1000ohm@100MHz	0.075	3216mm (1206inch)	BLM31KN102SH1	1 MHz - 3 GHz
BLM31KN121BH1			120ohm@100MHz	0.009	3216mm (1206inch)	BLM31KN121SH1	1 MHz - 3 GHz
BLM31KN121SH1			120ohm@100MHz	0.009	3216mm (1206inch)	BLM31KN121SH1	1 MHz - 3 GHz
BLM31KN121SZ1			120ohm@100MHz	0.009	3216mm (1206inch)	BLM31KN121SH1	1 MHz - 3 GHz
BLM31KN271BH1			270ohm@100MHz	0.016	3216mm (1206inch)	BLM31KN271SH1	1 MHz - 3 GHz
BLM31KN271SH1			270ohm@100MHz	0.016	3216mm (1206inch)	BLM31KN271SH1	1 MHz - 3 GHz
BLM31KN271SZ1			270ohm@100MHz	0.016	3216mm (1206inch)	BLM31KN271SH1	1 MHz - 3 GHz
BLM31KN471BH1			470ohm@100MHz	0.02	3216mm (1206inch)	BLM31KN471SH1	1 MHz - 3 GHz
BLM31KN471SH1			470ohm@100MHz	0.02	3216mm (1206inch)	BLM31KN471SH1	1 MHz - 3 GHz
BLM31KN471SZ1			470ohm@100MHz	0.02	3216mm (1206inch)	BLM31KN471SH1	1 MHz - 3 GHz
BLM31KN601BH1			600ohm@100MHz	0.038	3216mm (1206inch)	BLM31KN601SH1	1 MHz - 3 GHz
BLM31KN601SH1			600ohm@100MHz	0.038	3216mm (1206inch)	BLM31KN601SH1	1 MHz - 3 GHz
BLM31KN601SZ1			600ohm@100MHz	0.038	3216mm (1206inch)	BLM31KN601SH1	1 MHz - 3 GHz
BLM31KN801BH1			800ohm@100MHz	0.05	3216mm (1206inch)	BLM31KN801SH1	1 MHz - 3 GHz
BLM31KN801SH1			800ohm@100MHz	0.05	3216mm (1206inch)	BLM31KN801SH1	1 MHz - 3 GHz
BLM31KN801SZ1			800ohm@100MHz	0.05	3216mm (1206inch)	BLM31KN801SH1	1 MHz - 3 GHz
BLM31KN102SN1	1000	0.075	2000	2000	3216/1206	General	1 MHz - 3 GHz
BLM31KN121SN1	120	0.009	6000	2000	3216/1206	General	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLM31KN271SN1	270		0.016	4500	3216/1206	General	1 MHz - 3 GHz
BLM31KN471SN1	470		0.02	4000	3216/1206	General	1 MHz - 3 GHz
BLM31KN601SN1	600		0.038	2900	3216/1206	General	1 MHz - 3 GHz
BLM31KN801SN1	800		0.05	2500	3216/1206	General	1 MHz - 3 GHz
BLM31PG121SH1			120ohm@100MHz	0.02	3216mm (1206inch)	BLM31PG121SN1.4	1 MHz - 3 GHz
BLM31PG121SZ1			120ohm@100MHz	0.02	3216mm (1206inch)	BLM31PG121SN1.4	1 MHz - 3 GHz
BLM31PG330SH1			33ohm@100MHz	0.009	3216mm (1206inch)	BLM31PG330SN1.4	1 MHz - 3 GHz
BLM31PG330SZ1			33ohm@100MHz	0.009	3216mm (1206inch)	BLM31PG330SN1.4	1 MHz - 3 GHz
BLM31PG391SH1			390ohm@100MHz	0.05	3216mm (1206inch)	BLM31PG391SH1.4	1 MHz - 3 GHz
BLM31PG391SZ1			390ohm@100MHz	0.05	3216mm (1206inch)	BLM31PG391SH1.4	1 MHz - 3 GHz
BLM31PG500SH1			50ohm@100MHz	0.015	3216mm (1206inch)	BLM31PG500SN1.4	1 MHz - 3 GHz
BLM31PG500SZ1			50ohm@100MHz	0.015	3216mm (1206inch)	BLM31PG500SN1.4	1 MHz - 3 GHz
BLM31PG601SH1			600ohm@100MHz	0.08	3216mm (1206inch)	BLM31PG601SH1.4	1 MHz - 3 GHz
BLM31PG601SZ1			600ohm@100MHz	0.08	3216mm (1206inch)	BLM31PG601SH1.4	1 MHz - 3 GHz
BLM31PG121SN1	120		0.02	3500	3216/1206	General	1 MHz - 3 GHz
BLM31PG330SN1	33		0.009	6000	3216/1206	General	1 MHz - 3 GHz
BLM31PG391SN1	390		0.05	2000	3216/1206	General	1 MHz - 3 GHz
BLM31PG500SN1	50		0.015	3500	3216/1206	General	1 MHz - 3 GHz
BLM31PG601SN1	600		0.08	1500	3216/1206	General	1 MHz - 3 GHz
BLM31SN500BH1			50ohm@100MHz	0.0016	3216mm (1206inch)	BLM31SN500SH1.4	1 MHz - 3 GHz
BLM31SN500SH1			50ohm@100MHz	0.0016	3216mm (1206inch)	BLM31SN500SH1.4	1 MHz - 3 GHz
BLM31SN500SZ1			50ohm@100MHz	0.0016	3216mm (1206inch)	BLM31SN500SH1.4	1 MHz - 3 GHz
BLM31SN500SN1	50		0.0016	12000	3216/1206	General	1 MHz - 3 GHz
BLM41PG102SH1			1000ohm@100MHz	0.09	4516mm (1806inch)	BLM41PG102SN1.4	1 MHz - 3 GHz
BLM41PG102SZ1			1000ohm@100MHz	0.09	4516mm (1806inch)	BLM41PG102SN1.4	1 MHz - 3 GHz
BLM41PG181SH1			180ohm@100MHz	0.02	4516mm (1806inch)	BLM41PG181SN1.4	1 MHz - 3 GHz
BLM41PG181SZ1			180ohm@100MHz	0.02	4516mm (1806inch)	BLM41PG181SN1.4	1 MHz - 3 GHz
BLM41PG471SH1			470ohm@100MHz	0.05	4516mm (1806inch)	BLM41PG471SN1.4	1 MHz - 3 GHz
BLM41PG471SZ1			470ohm@100MHz	0.05	4516mm (1806inch)	BLM41PG471SN1.4	1 MHz - 3 GHz
BLM41PG600SH1			60ohm@100MHz	0.009	4516mm (1806inch)	BLM41PG600SN1.4	1 MHz - 3 GHz
BLM41PG600SZ1			60ohm@100MHz	0.009	4516mm (1806inch)	BLM41PG600SN1.4	1 MHz - 3 GHz
BLM41PG750SH1			75ohm@100MHz	0.015	4516mm (1806inch)	BLM41PG750SN1.4	1 MHz - 3 GHz
BLM41PG750SZ1			75ohm@100MHz	0.015	4516mm (1806inch)	BLM41PG750SN1.4	1 MHz - 3 GHz
BLM41PG102SN1	1000		0.09	1500	4516/1806	General	1 MHz - 3 GHz
BLM41PG181SN1	180		0.02	3500	4516/1806	General	1 MHz - 3 GHz
BLM41PG471SN1	470		0.05	2000	4516/1806	General	1 MHz - 3 GHz
BLM41PG600SN1	60		0.009	6000	4516/1806	General	1 MHz - 3 GHz
BLM41PG750SN1	75		0.015	3500	4516/1806	General	1 MHz - 3 GHz
BLT5BPT680LN1	68		0.01	11000	5050/2020	General	1 MHz - 3 GHz
NFZ03SG102SN10			1.3	210	0603/0201	General	1 MHz - 3 GHz
NFZ03SG162SN10			1.7	180	0603/0201	General	1 MHz - 3 GHz
NFZ03SG331SN10			0.6	305	0603/0201	General	1 MHz - 3 GHz
NFZ03SG501SN10			0.73	275	0603/0201	General	1 MHz - 3 GHz
NFZ03SG671SN10			0.88	250	0603/0201	General	1 MHz - 3 GHz
NFZ15SF102SN10	1000		1.4	230	1005/0402	General	1 MHz - 3 GHz
NFZ15SF102SZ10			1000ohm@100MHz	1.4	1005mm (0402inch)		1 MHz - 3 GHz
NFZ15SG101SN11			0.1	1100	1005/0402	General	1 MHz - 3 GHz
NFZ15SG151SN11			0.12	1000	1005/0402	General	1 MHz - 3 GHz
NFZ15SG152SN10			0.8	400	1005/0402	General	1 MHz - 3 GHz
NFZ15SG262SN10			1	350	1005/0402	General	1 MHz - 3 GHz
NFZ15SG331SN11			0.3	650	1005/0402	General	1 MHz - 3 GHz
NFZ15SG462SN10			1.65	270	1005/0402	General	1 MHz - 3 GHz
NFZ15SG771SN10			0.5	500	1005/0402	General	1 MHz - 3 GHz
NFZ15SR152SN10	200		0.7	400	1005/0402	General	1 MHz - 3 GHz
NFZ15SR262SN10	400		1.2	300	1005/0402	General	1 MHz - 3 GHz
NFZ15SR352SN10	500		1.65	270	1005/0402	General	1 MHz - 3 GHz
NFZ18SM121SN10	120		0.14	1250	1608/0603	General	1 MHz - 3 GHz
NFZ18SM251SN10	250		0.19	1100	1608/0603	General	1 MHz - 3 GHz
NFZ18SM501SN10	500		0.25	950	1608/0603	General	1 MHz - 3 GHz
NFZ18SM701SN10	700		0.29	800	1608/0603	General	1 MHz - 3 GHz
NFZ18SM121SZ10			120ohm@100MHz	0.14	1608mm (0603inch)		1 MHz - 3 GHz
NFZ18SM251SZ10			250ohm@100MHz	0.19	1608mm (0603inch)		1 MHz - 3 GHz
NFZ18SM501SZ10			500ohm@100MHz	0.25	1608mm (0603inch)		1 MHz - 3 GHz
NFZ18SM701SZ10			700ohm@100MHz	0.29	1608mm (0603inch)		1 MHz - 3 GHz
NFZ2HBM110SN10			0.04	800	2520/1008	General	1 MHz - 3 GHz
NFZ2HBM170SN10			0.053	700	2520/1008	General	1 MHz - 3 GHz
NFZ2HBM1R5SN10			0.015	1200	2520/1008	General	1 MHz - 3 GHz
NFZ2HBM240SN10			0.063	650	2520/1008	General	1 MHz - 3 GHz
NFZ2HBM2R9SN10			0.021	1100	2520/1008	General	1 MHz - 3 GHz
NFZ2HBM330SN10			0.075	500	2520/1008	General	1 MHz - 3 GHz
NFZ2HBM4R4SN10			0.026	1050	2520/1008	General	1 MHz - 3 GHz
NFZ2HBM600SN10			0.075	400	2520/1008	General	1 MHz - 3 GHz
NFZ2HBM6R1SN10			0.031	1000	2520/1008	General	1 MHz - 3 GHz
NFZ2HBM8R4SN10			0.036	900	2520/1008	General	1 MHz - 3 GHz
NFZ2MSD100SN10			0.02	5200	2016/0806	General	1 MHz - 3 GHz
NFZ2MSD131SN10			0.144	1500	2016/0806	General	1 MHz - 3 GHz
NFZ2MSD150SN10			0.023	4400	2016/0806	General	1 MHz - 3 GHz
NFZ2MSD200SN10			0.028	3900	2016/0806	General	1 MHz - 3 GHz
NFZ2MSD300SN10			0.033	3700	2016/0806	General	1 MHz - 3 GHz
NFZ2MSD600SN10			0.054	2700	2016/0806	General	1 MHz - 3 GHz
NFZ2MSD900SN10			0.095	2000	2016/0806	General	1 MHz - 3 GHz
NFZ2MSD101SZ10			100ohm@100MHz	0.018	2016mm (0806inch)		1 MHz - 3 GHz
NFZ2MSD102SZ10			1000ohm@100MHz	0.046	2016mm (0806inch)		1 MHz - 3 GHz
NFZ2MSD181SZ10			180ohm@100MHz	0.022	2016mm (0806inch)		1 MHz - 3 GHz
NFZ2MSD301SZ10			300ohm@100MHz	0.026	2016mm (0806inch)		1 MHz - 3 GHz
NFZ2MSD501SZ10			500ohm@100MHz	0.032	2016mm (0806inch)		1 MHz - 3 GHz
NFZ2MSM101SN10	100		0.018	4000	2016/0806	General	1 MHz - 3 GHz
NFZ2MSM181SN10	180		0.025	3400	2016/0806	General	1 MHz - 3 GHz
NFZ2MSM301SN10	300		0.03	3100	2016/0806	General	1 MHz - 3 GHz
NFZ2MSM601SN10	600		0.046	2500	2016/0806	General	1 MHz - 3 GHz
NFZ32BW101HN11			0.57	900	3225/1210	General	1 MHz - 3 GHz
NFZ32BW111HN10			0.684	520	3225/1210	General	1 MHz - 3 GHz
NFZ32BW120HN11			0.0768	1850	3225/1210	General	1 MHz - 3 GHz
NFZ32BW150HN10			0.0912	1600	3225/1210	General	1 MHz - 3 GHz
NFZ32BW151HN10			0.972	450	3225/1210	General	1 MHz - 3 GHz
NFZ32BW151HN11			0.822	700	3225/1210	General	1 MHz - 3 GHz
NFZ32BW190HN11			0.1068	1800	3225/1210	General	1 MHz - 3 GHz
NFZ32BW210HN10			0.144	1200	3225/1210	General	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
NFZ32BW210HN11			0.12	1550	3225/1210	General	1 MHz - 3 GHz
NFZ32BW221HN10			1.38	390	3225/1210	General	1 MHz - 3 GHz
NFZ32BW291HN10			2.14	310	3225/1210	General	1 MHz - 3 GHz
NFZ32BW310HN11			0.186	1200	3225/1210	General	1 MHz - 3 GHz
NFZ32BW320HN10			0.216	1000	3225/1210	General	1 MHz - 3 GHz
NFZ32BW3R3HN11			0.0288	2900	3225/1210	General	1 MHz - 3 GHz
NFZ32BW3R6HN10			0.036	2550	3225/1210	General	1 MHz - 3 GHz
NFZ32BW420HN10			0.288	850	3225/1210	General	1 MHz - 3 GHz
NFZ32BW451HN10			2.74	275	3225/1210	General	1 MHz - 3 GHz
NFZ32BW520HN11			0.264	1100	3225/1210	General	1 MHz - 3 GHz
NFZ32BW621HN10			3.24	250	3225/1210	General	1 MHz - 3 GHz
NFZ32BW650HN11			0.354	900	3225/1210	General	1 MHz - 3 GHz
NFZ32BW6R8HN11			0.0432	2500	3225/1210	General	1 MHz - 3 GHz
NFZ32BW700HN10			0.456	700	3225/1210	General	1 MHz - 3 GHz
NFZ32BW7R4HN10			0.054	2050	3225/1210	General	1 MHz - 3 GHz
NFZ32BW881HN10			5.26	200	3225/1210	General	1 MHz - 3 GHz
NFZ32BW8R4HN11			0.0576	2400	3225/1210	General	1 MHz - 3 GHz
NFZ32BW9R0HN10			0.0684	1750	3225/1210	General	1 MHz - 3 GHz
NFZ32BW9R8HN11			0.0636	2100	3225/1210	General	1 MHz - 3 GHz
NFZ32BW101HZ11	100			0.57	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW111HZ10	110			0.684	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW120HZ11	12			0.0768	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW150HZ10	15			0.0912	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW151HZ10	150			0.972	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW151HZ11	150			0.822	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW190HZ11	19			0.1068	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW210HZ10	21			0.144	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW210HZ11	21			0.12	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW221HZ10	220			1.38	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW291HZ10	290			2.14	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW310HZ11	31			0.186	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW320HZ10	32			0.216	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW3R3HZ11	3.3			0.0288	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW3R6HZ10	3.6			0.036	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW420HZ10	42			0.288	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW451HZ10	450			2.74	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW520HZ11	52			0.264	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW621HZ10	620			3.24	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW650HZ11	65			0.354	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW6R8HZ11	6.8			0.0432	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW700HZ10	70			0.456	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW7R4HZ10	7.4			0.054	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW881HZ10	880			5.26	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW8R4HZ11	8.4			0.0576	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW9R0HZ10	9			0.0684	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32BW9R8HZ11	9.8			0.0636	3225mm(1210inch)		1 MHz - 3 GHz
NFZ32SW301HN10	300		0.036	2550	3225/1210	General	1 MHz - 3 GHz
NFZ32SW901HN10	900		0.054	2050	3225/1210	General	1 MHz - 3 GHz
NFZ5BBW100LN10			0.029	3000	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW140LN10			0.036	2600	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW141LN10			0.311	1050	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW170LN10			0.042	2500	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW220LN10			0.053	2300	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW2R9LN10			0.014	4000	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW310LN10			0.07	2000	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW450LN10			0.1	1650	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW4R5LN10			0.018	3400	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW520LN10			0.12	1610	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW610LN10			0.127	1600	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW6R7LN10			0.023	3100	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW7R6LN10			0.023	3100	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW970LN10			0.224	1200	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW100LZ10	10			0.029	5050mm(2020inch)		1 MHz - 3 GHz
NFZ5BBW140LZ10	14			0.036	5050mm(2020inch)		1 MHz - 3 GHz
NFZ5BBW141LZ10	140			0.311	5050mm(2020inch)		1 MHz - 3 GHz
NFZ5BBW170LZ10	17			0.042	5050mm(2020inch)		1 MHz - 3 GHz
NFZ5BBW220LZ10	22			0.053	5050mm(2020inch)		1 MHz - 3 GHz
NFZ5BBW2R9LZ10	2.9			0.014	5050mm(2020inch)		1 MHz - 3 GHz
NFZ5BBW310LZ10	31			0.07	5050mm(2020inch)		1 MHz - 3 GHz
NFZ5BBW450LZ10	45			0.1	5050mm(2020inch)		1 MHz - 3 GHz
NFZ5BBW4R5LZ10	4.5			0.018	5050mm(2020inch)		1 MHz - 3 GHz
NFZ5BBW520LZ10	52			0.12	5050mm(2020inch)		1 MHz - 3 GHz
NFZ5BBW610LZ10	61			0.127	5050mm(2020inch)		1 MHz - 3 GHz
NFZ5BBW6R7LZ10	6.7			0.023	5050mm(2020inch)		1 MHz - 3 GHz
NFZ5BBW7R6LZ10	7.6			0.023	5050mm(2020inch)		1 MHz - 3 GHz
NFZ5BBW970LZ10	97			0.224	5050mm(2020inch)		1 MHz - 3 GHz