

CLB1C6U120K1000TC1

In Production

RoHS

REACH

Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Consumer equipment, Industrial Equipment, Mobile Electronics Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.
Recommended Applications	Consumer equipment, Router, Wi-Fi Router, Optical Backbone network, Optical Module, Mobile Electronics, Base Station, RF Power Amplifier, Industrial Equipment

Features

1. Fine grained high-density ceramic dielectric, pure gold electrode and simple single layer structure provide very reliable performance and excellent frequency characteristics.
2. A wide selection of sizes from very miniature 0.25mm square is suited to high-density mounting.
3. For compatibility with the gold electrodes, die bonding with Au-Sn is possible and wire bonding with gold wire is possible.
4. To improve handling of bonding, Au-Sn coating is available on one side or both sides.
5. Custom made type (dimensions, cap. values, etc.) are also available upon request.

Applications

1. Microwave Integrated Circuits
2. Microwave Devices
3. Optical Devices
4. Measuring Equipments

Appearance & Shape



Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

CLB1C6U120K1000TC1



Specifications

Shape	SMD
Operating Temperature Range	-55°C to 125°C
L x W (size)	L 1.27 X W 1.27mm
Thickness	0.14mm
Rated Voltage	100Vdc
Capacitance (25°C)	12pF
Capacitance Tolerance	±10%
Temperature Characteristics (-25 to 85°C)	-750±120ppm/°C
Withstanding Voltage	250Vdc
Resistance	25°C: 100000MΩmin.

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.