

MHR0417SA306D70

Note: This datasheet may be out of date.

Please download the latest datasheet of MHR0417SA306D70 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-gb/products/productdetail?partno=MHR0417SA306D70









Applications

Unsuitable	Please he sure to read and comply with
	Please be sure to read and comply with
Applications	these "Precautions for use."
	Consumer equipment,Industrial
	Equipment,Medical equipment [GHTF
	A/B]
	Please refer to Our Website and
Specific Applications	specifications, etc. for information about
	the performance, functions, quality,
	management, and safety required for
	the above applications, and use
	Products after confirming the
	performance and reliability of the actual
	Product.
	Copier,Printer,High-Voltage-Handling
December	Equipment,Healthcare [Medical
Recommended	equipment[GHTF Class A/B]],White
Applications	Goods,Air Purifier,Air Conditioner,Hair
	Dryer,High-Voltage Power Supply



Packaging Information

Packaging		Standard Packing Quantity
-	Bulk(Bag)	500



Appearance & Shape



(in mm)

1 of 2

Attentior

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

 $2. This \ data{sheet has only typical specifications because there is no \ space for \ detailed \ specifications.}$

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





MHR0417SA306D70

Note: This datasheet may be out of date.

Please download the latest datasheet of MHR0417SA306D70 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-gb/products/productdetail?partno=MHR0417SA306D70



Specifications

Power Rating	1.1W
Shape	Lead
Maximum Working Voltage	5.7kVdc
Resistance	30.0ΜΩ
Resistance Deviation	±0.5%
Single Use/Mold Use	Single use
Length	17.6mm
Height H	6.5mm
Lead Pitch P	15.24mm

2 of 2

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

