


# SCA620-EF1V1B



## Appearance & Shape



## Packaging Information

Packaging	Specifications	Standard Packing Quantity
-1	330mm Embossed Tape	100

### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# SCA620-EF1V1B



## Specifications

Output Type	Analog
Axis	1(Z)
Maximum Range	0 to +2.0g
Supply Voltage	5V
Offset Temp. Characteristic	±125mg
Sensitivity	2V/G
Amplitude Response	50Hz
Mass	0.73g

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.