

# LQH43NH1R2K03#

“#” at the end indicates the package specification code.

It can be used in 125 °C environment.




## < List of part numbers with package codes >

LQH43NH1R2K03K      LQH43NH1R2K03L

## Applications

|                          |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
|--------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Unsuitable Applications  | Please be sure to read and comply with these "Precautions for use."                                                                                                                                                                                                                                                                                                                                                                                                              |
| Specific Applications    | Consumer equipment, Automotive infotainment/comfort equipment, Automotive powertrain/safety equipment, Medical equipment [GHTF A/B/C] except for implant & surgery & auto injector, Industrial Equipment<br>Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product. |
| Recommended Applications | Automotive powertrain/safety equipment                                                                                                                                                                                                                                                                                                                                                                                                                                           |

## Appearance & Shape



## Notices

When rated current is applied to the products, self-temperature rise shall be limited to 20°C max and inductance will be within ±10% of nominal value.

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2. This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# LQH43NH1R2K03#

“#”at the end indicates the package specification code.



## References

| Packaging | Specifications   | Standard Packing Quantity |
|-----------|------------------|---------------------------|
| K         | 330Embossed Tape | 2500                      |
| L         | 180Embossed Tape | 500                       |

| Mass (typ.) |       |
|-------------|-------|
| 1 piece     | 0.13g |

### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# LQH43NH1R2K03#

“#” at the end indicates the package specification code.



## Specifications

|                                                      |                |
|------------------------------------------------------|----------------|
| L size                                               | 4.5±0.3mm      |
| W size                                               | 3.2±0.2mm      |
| T size                                               | 2.6±0.2mm      |
| Size code inch (mm)                                  | 1812 (4532)    |
| Inductance                                           | 1.2μH±10%      |
| Inductance Test Frequency                            | 1MHz           |
| Rated current (Itemp)<br>(Based on Temperature rise) | 1100mA         |
| Max. of DC resistance                                | 0.0516Ω        |
| DC resistance                                        | 0.043Ω±20%     |
| Class of magnetic shield                             | Non-Shielded   |
| Q(min.)                                              | 20             |
| Q Test Frequency                                     | 1MHz           |
| Self resonance frequency<br>(min.)                   | 100MHz         |
| Brand                                                | Murata         |
| Operating Temperature<br>Range                       | -40°C to 125°C |
| Series                                               | LQH43NH_03     |

### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.




# LQH43NH1R2K03#

“#” at the end indicates the package specification code.



## Characteristic Data

The charts below may show another part number which shares its characteristics.



### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.