

# DMR30-PM1-1-DC4-R-C

In Production

Recommended

RoHS

## Appearance & Shape



## Features

Red LED, 4.5 digit Precision DC Process Meter, Measures 0-5V, 0-10V, 0-20mA & 4-20mA process signals

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# DMR30-PM1-1-DC4-R-C



## Specifications

Productseries	DMR30-PM1
Product Series Features	DMR30-PM1
Measuring Range(Vdc)	0Vdc to 10Vdc
Measuring Range(mA)	4mA to 20mA
Display Type	LED
Color	Red
Number of Digits	4.5
Digit Height (mm)	11.4mm
Power Supply Type	DC Powered
Operatingtemperature(degC)	0°C to 50°C
Humidity	0% to 85%
Measurement Type	Precision process signals, 0-5V, 0-10V, 0-20mA & 4-20mA process signals
Mounting Type	Panel Mount
Accuracy	0.2% F.S Max
Case Material	Polycarbonate
Configurable DPM	Yes
Daylight Readable	Yes
Digit Height (inch)	0.45inch
Input Protection	±30V
Resolution (V)	4.5V
Update Rate (samples /sec)	2.5
Weight (g)	64g
Weight (oz)	2.23

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.