

# PRF15BF102RB6RC

To be discontinued


RoHS

REACH

## Applications

|                         |                                                                                                                                                                                                                                                                                                                                                                    |
|-------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Unsuitable Applications | Please be sure to read and comply with these "Precautions for use."                                                                                                                                                                                                                                                                                                |
| Specific Applications   | Mobile Electronics, Consumer equipment, Industrial Equipment, Medical equipment [GHTF A/B]<br>Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product. |

## Appearance & Shape



| Part Number | Dimensions (mm) |          |          |            |          |
|-------------|-----------------|----------|----------|------------|----------|
|             | L               | W        | T        | e          | g        |
| PRF03_RL    | 0.6±0.05        | 0.3±0.05 | 0.3±0.05 | 0.1 to 0.2 | -        |
| PRF15_RC    | 1.0±0.05        | 0.5±0.05 | 0.5±0.05 | 0.1 to 0.4 | 0.3 min. |
| PRF18_RB    | 1.6±0.15        | 0.8±0.15 | 0.8±0.15 | 0.1 to 0.6 | -        |
| PRF21_RA    | 2.0±0.2         | 1.25±0.2 | 0.9±0.2  | 0.2 min.   | 0.5 min. |

## Packaging Information

| Packaging | Specifications   | Standard Packing Quantity |
|-----------|------------------|---------------------------|
| RC        | 180mm Paper Tape | 10000                     |

## Features

1. SMD type is helpful for miniaturizing circuits because of its small size and light weight.
2. Excellent thermal response due to small size
3. Solid-state construction provides excellent resistance to mechanical vibration and impact resistance.
4. Contactless operation provides noiseless operation.
5. UL/cULcertified product. (UL1434, File No. E137188)

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# PRF15BF102RB6RC



## Specifications

|                                             |                |
|---------------------------------------------|----------------|
| Max. Voltage                                | 32V            |
| Sensing Temperature                         | 75°C           |
| Sensing Temperature Tolerance               | ±5°C           |
| Measure Condition of Sensing Temperature    | at 10k ohm     |
| Sensing Temperature(2)                      | 90°C           |
| Sensing Temperature (2) Tolerance           | ±3°C           |
| Measure Condition of Sensing Temperature(2) | at 100k ohm    |
| Resistance (25°C)                           | 1kΩ            |
| Resistance Value Tolerance (at 25°C)        | ±50%           |
| Operating Temperature Range                 | -40°C to 100°C |
| Size Code (in mm)                           | 1.0x0.5mm      |
| Size Code (in inch)                         | 0.4x0.2inch    |
| Shape                                       | SMD            |
| Mass                                        | 0.001g         |
| MSL                                         | 1              |

### Attention


1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# PRF15BF102RB6RC

## Product Data



Resistance-Temperature Charac.



Resistance-Temperature Charac. Range

**Attention**

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.