

XRCJK20M000F1QB3P0

Discontinued



RoHS

REACH

Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Consumer equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.

Appearance & Shape



Packaging Information

Packaging	Specifications	Standard Packing Quantity
P0	180mm Plastic Tape	3000

Features

Standard package size (3225) product with seam sealing technology.

Robust package gives high reliability and high impact resistance. They are suitable for various types of digital communication equipment requiring high reliability.

Attention

XRCJK20M000F1QB3P0



Specifications

Product Type	Crystal Unit
Series	XRCJK
Type	TSS-3225J
Frequency	20.0000MHz
Frequency Tolerance	+/-10ppm max. (25+/-3°C)
Operating Temperature Range	-30°C~85°C
Frequency Shift by Temperature	+/-15ppm max.
Frequency Aging	+/-3ppm max./year
Equivalent Series Resistance (ESR)	80ohm max.
Drive Level (DL)	30μW
Load Capacitance (Cs)	8pF
Shape	SMD
Wash	Not available
L x W (size)	3.2x2.5mm
Mass	17.73mg

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.