

MHR0312SA805G20



Packaging Information

Packaging	Specifications	Minimum Order Quantity
-	Bulk(Bag)	1000

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

MHR0312SA805G20

Specifications

Power Rating	0.6W
Shape	Lead
Maximum Working Voltage	2.1kVdc
Resistance	8.0MΩ
Resistance Deviation	±2%
Single Use/Mold Use	Molded use
Length	12.6mm
Height H	5.0mm
Lead Pitch P	10.16mm

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.