

## ● Part Numbering

### Crystal Oscillator

(Part Number)

XN	C	HH	19M200	T	J	E	A5	E2
①	②	③	④	⑤	⑥	⑦	⑧	⑨

#### ① Product ID

Product ID	
XT	VC-TCXO
XN	TCXO

#### ② Lead Style

Code	Lead Style
C	SMD

#### ③ Size · Structure

Code	Size · Structure
HH	2520 Metal Sealing
JH	3225 Metal Sealing
LH	5032 Metal Sealing

#### ④ Nominal Center Frequency

Expressed by six-digit alphanumeric. The unit is in hertz (Hz).  
Decimal point is expressed by capital letter "M".

#### ⑤ Output Wave

Code	Output Wave
T	Clipped Sign Wave

#### ⑥ Frequency Tolerance

Code	Frequency Tolerance
J	±1.0 to ±1.4ppm

#### ⑦ Frequency Shift by Temperature

Code	Frequency Shift by Temperature
E	±0.5ppm max.
J	Less than ±0.3ppm

#### ⑧ Individual Specification

Code	
**	Two-digit alphanumeric express Individual Specification.

#### ⑨ Packaging (Packging quantity is expressed by one-digit number in "\*\*")

Code	Packaging
L*	Plastic Taping ø180mm
G*	Plastic Taping ø254mm