

MHR0412SA157K70



Packaging Information

| Packaging | Specifications | Minimum Order Quantity |
|-----------|----------------|------------------------|
| - | Bulk(Bag) | 1000 |

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

MHR0412SA157K70

Specifications

| | |
|-------------------------|------------|
| Power Rating | 0.8W |
| Shape | Lead |
| Maximum Working Voltage | 5kVdc |
| Resistance | 150.0MΩ |
| Resistance Deviation | ±10% |
| Single Use/Mold Use | Single use |
| Length | 12.6mm |
| Height H | 6.5mm |
| Lead Pitch P | 10.16mm |

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.