


SCA3300-D01

In Production RoHS REACH

Appearance & Shape



Packaging Information

Packaging	Specifications	Minimum Order Quantity
-1	330mm Embossed Tape	100

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

SCA3300-D01

Specifications

Output Type	SPI
Axis	3
Maximum Range	$\pm 1.5\text{g}/\pm 3\text{g}/\pm 6\text{g}/$
Supply Voltage	3.3V
Offset Temp. Characteristic	X,Y $\pm 10\text{mg}$ Z $\pm 15\text{mg}$
Amplitude Response	88/10Hz
Mass	0.31g

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.