

GCM033D70E105ME36#

“#” indicates a package specification code.




< List of part numbers with package codes >

GCM033D70E105ME36D

GCM033D70E105ME36W

GCM033D70E105ME36J

Appearance & Shape



References

Packaging	Specifications	Standard Packing Quantity
D	180mm Paper Tape	15000
W	180mm Paper Tape (W8P1)	30000
J	330mm Paper Tape	50000

Mass (typ.)	
1 piece	0.33mg
φ180mm Reel	118g

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

GCM033D70E105ME36#

“#” indicates a package specification code.

Specifications

Length	0.6±0.09mm
Width	0.3±0.09mm
Thickness	0.3±0.09mm
Capacitance	1.0μF ±20%
Distance between external terminals g	0.2mm min.
External terminal size e	0.1 to 0.25mm
Operating Temperature Range	-55°C to 125°C
Rated Voltage	2.5Vdc
Size code in inch(mm)	0201 (0603M)
Capacitance change rate	+22.0/-33.0%
Temperature characteristics (complied standard)	X7T(EIA)
Temperature range of temperature characteristics	-55°C to 125°C

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.