

# MHM305-01

In Production

RoHS

REACH


## Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Consumer equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.
Recommended Applications	Air Purifier,Air Conditioner,Fan

## Packaging Information

Packaging	Specifications	Standard Packing Quantity
-	Carton Box	200

## Appearance & Shape



### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# MHM305-01



## Specifications

Input Voltage	12.0Vdc
Consumption Electricity	0.4W
Operating Temperature Range	-10°C to 50°C
Operating Humidity Range	20%RH to 80%RH
Ion Type	negative ion
Ion Amount	5,000,000pcs/cc
Ozone Amount	0.15mg/H max
state monitoring(Vmon)	✓
Lead Length	290mm

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.