


ZPA2326-0311A-R

Discontinued

RoHS

REACH

Appearance & Shape



Packaging Information

Packaging	Specifications	Standard Packing Quantity
-R	330mm Embossed Tape	5000

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

ZPA2326-0311A-R



Specifications

Output Type	Digital
Current Consumption	6.3uA Typ./Conversion time 1/6s
Puressure RMS Noise	1.1parms Typ./Conversion time 1/6s
Absolute accuracy	+/-0.8 hPa/T= -10 to 65degC, P range= 800 to1100hPa
Supply Voltage Range	1.71 to 2.0 V
Interface	SPI / I2 C

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.