

MHM305-05

In Production

RoHS

REACH

Applications

| | |
|--------------------------|--|
| Unsuitable Applications | Please be sure to read and comply with these "Precautions for use." |
| Specific Applications | Consumer equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product. |
| Recommended Applications | Air Purifier,Air Conditioner,Fan |

Packaging Information

| Packaging | Specifications | Standard Packing Quantity |
|-----------|----------------|---------------------------|
| - | Carton Box | 200 |

Appearance & Shape



Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

MHM305-05



Specifications

| | |
|-----------------------------|-----------------|
| Input Voltage | 12.0Vdc |
| Consumption Electricity | 0.4W |
| Operating Temperature Range | -10°C to 50°C |
| Operating Humidity Range | 20%RH to 80%RH |
| Ion Type | negative ion |
| Ion Amount | 5,000,000pcs/cc |
| Ozone Amount | 0.15mg/H max |
| state monitoring(Vmon) | ✓ |
| Lead Length | 115mm |

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.