


# MRSS27H

Discontinued

RoHS

REACH

## Appearance & Shape



## Packaging Information

Packaging	Specifications	Standard Packing Quantity
-	180mm Embossed Tape	3000

**Attention**  
1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.  
2.This datasheet has only typical specifications because there is no space for detailed specifications.  
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# MRSS27H



## Specifications

Operating Temperature Range	-40°C to 100°C
Supply Voltage Range	3.5V to 30.0V
Low Level Output Voltage	0.3V
High Level Output Voltage	11.4V
Current Consumption(typ.)	1.0mA
Measure Condition of Current Consumption	Typ.Vcc12V
Operating Magnetic Field (Hon)	Max 2.2mT
Operating Magnetic Field (Hoff)	Min 0.8mT
Storage Temperature Range	-40.0°C to 125.0°C

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.