

● Part Numbering

Crystal Oscillator

(Part Number)

XN	C	LH	19M200	T	H	J	A1	P0
①	②	③	④	⑤	⑥	⑦	⑧	⑨

① Product ID

Product ID	
XT	VC-TCXO
XN	TCXO

② Lead Style

Code	Lead Style
C	SMD

③ Size · Structure

Code	Size · Structure
LH	5032 Metal Sealing

④ Nominal Center Frequency

Expressed by six-digit alphanumeric. The unit is in hertz (Hz).
Decimal point is expressed by capital letter "M".

⑤ Output Wave

Code	Output Wave
T	Clipped Sign Wave
C	CMOS

⑥ Frequency Tolerance

Code	Frequency Tolerance
J	±1.0 to ±1.4ppm
H	±0.5 to ±0.9ppm

⑦ Frequency Shift by Temperature

Code	Frequency Shift by Temperature
J	±0.20 to ±0.29ppm
K	±0.10 to ±0.19ppm

⑧ Individual Specification

Code	
**	Two-digit alphanumerics express Individual Specification.

⑨ Packaging (Packaging quantity is expressed by one-digit number in "**")

Code	Packaging
P*	Plastic Taping ø254mm