Part Numbering

Frequency Specified Filters

(Part Number) BLF 03 J D 421 G N E D

1 2 3 4 5 6 7 8 9

1Product ID

Code	
BLF	Frequency Specified Filters

2Dimensions (LxW)

Code	Dimensions (LxW)	Size Code (inch)
02	0.4×0.2mm	01005
03	0.6×0.3mm	0201

3Target Frequency

Code	Target Frequency
J	700MHz
G	700MHz (Wide Frequency)
R	2.4GHz
V	5GHz

Characteristics Classification

6 Impedance at Target Frequency

Expressed by three figures. The unit is in ohm (Ω) . The first and second figures are significant digits, and the third figure expresses the number of zeros that follow the two figures.

6Chip Shape/Electrode

Expressed by a letter.

Code	Chip Shape/Electrode
G	High Profile (Sn Plating/5 Surface Electrode)
S	Standard (Sn Plating/5 Surface Electrode)

Category

Code	Category
N	For General-Purpose

8 Rated Current

Code	Rated Current
E	500mA max.
G	1A max.
L	2A max.

Packaging

Code	Packaging
В	Bulk
D	Paper Taping (ø180mm Reel)