


酸化銀電池
Silver oxide batteries

SR927R

■外形寸法 Dimensions(mm)



■刻印 Monogram




■定格 Specifications

公称電圧 Nominal Voltage	1.55 V
公称容量 (終止電圧 1.2V) Nominal Capacity (1.2V cutoff)	45 mAh
標準放電負荷 Standard Discharge Load ※公称電圧/抵抗 Nominal Voltage/Standard Load	15 k Ω ($\approx 0.1 \text{ mA}$)
最大放電電流 Maximum Discharge Current ※23°C、DOD 0%、0.1sにて 1.2V以上を維持できる放電電流 ※Keep higher than 1.2V, discharge at 23°C, DOD 0%, 0.1s	75mA
標準質量 Weight	0.70 g
使用温度範囲 Operating Temperature	-10 ~ +60°C
水銀使用率 0% No mercury added	


■放電特性 Discharge Characteristics

load : 15k Ω temperature: 23°C




■ 放電負荷特性

Discharge Characteristics on Load




■ 放電温度特性

Discharge Characteristics by Temperature




■ 放電負荷と放電容量

Discharge Load vs. Discharge Capacity



■ 標準モデルと大電流モデルの比較

Standard Model vs. High Drain Model



*記載のデータ及び数値は、参考値であり保証値ではありません。

*Data is not guaranteed, and is provided for reference purposes only.