

# PVA2A222A01B00

已经停产

RoHS

REACH

## 外观&形状



## 特点

1. Ultra-small and thin external dimensions of 2.2(W)x2.75(L)x0.90 max.(T)mm.
2. For the terminal attachment method of construction that uses neither solder nor adhesives, good solderability and terminal attachment intensity are realized.
3. Because of multi-contact wiper structure, PVA2 has a stable characteristics (low noise).
4. PVA2 series does not use a solder, flux or cleaning solvent, so they are environmentally friendly products.
5. Heat resistance performance enables high temperature peak reflow soldering.

## 包装信息

| 包装  | 规格  | 标准包装数量 |
|-----|-----|--------|
| B00 | 散装袋 | 1000   |

注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，谨请核准其规格或者办理产品规格表。

# PVA2A222A01B00

规格

|              |                                           |
|--------------|-------------------------------------------|
| 额定功率         | 0.1W                                      |
| 形状           | SMD                                       |
| 最大工作电压       | 50Vdc                                     |
| 调整方向         | 上方                                        |
| 尺寸           | 2mm                                       |
| 自动调整         | Yes                                       |
| 调节转数(有效旋转角度) | 1(260°±10°)                               |
| 机械旋转角度       | Endless                                   |
| 总电阻值         | 2.2kΩ                                     |
| 总电阻值公差       | ±25%                                      |
| 电阻温度系数       | ±250ppm/°C                                |
| 电阻变化特性       | B (Linear)                                |
| 接触电阻变化       | 3% max. of nominal total resistance value |
| 剩余电阻         | 4% max. of nominal total resistance value |
| 力矩           | 0.5 to 9.8mN · m                          |
| 额定功率测量条件     | 70°C                                      |
| 工作温度范围       | -55°C to 125°C                            |
| 质量           | 0.01g                                     |

注意

1.

本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。


2.

本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前， 谨请核准其规格或者办理产品规格表。

# PVA2A222A01B00



## 产品数据



### 结构

在3 / 3页

#### 注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，谨请核准其规格或者办理产品规格表。