


TZV2Z100A110R00

已经停产

RoHS

REACH

外观&形状



特点

1. Small size with external dimensions of $2.3(\text{W}) \times 3.2(\text{L}) \times 1.45 \text{ max.}(\text{H}) \text{ mm}$.
2. Unique construction with no plastic material provides superior soldering heat resistance to maintain excellent characteristic performance after reflow soldering.
3. Designed for automatic placement in surface mount applications.
4. Funnel shaped metal case enables in-process automatic adjustment.

包装信息

包装	规格	标准包装数量
R00	180mm压纹带	2000

注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。

2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，谨请核准其规格或者办理产品规格表。

TZV2Z100A110R00

规格

形状	SMD
工作温度范围	-25°C to 85°C
厚度	1.45mm
厚度公差	max.
额定电压	25Vdc
静电容量最小值(max.)	3pF
静电容量最大值	10pF
静电容量最大值公差	+100/-0%
调整方向	上方
温度特性	NP0±300ppm/°C
Q	500min. at 1MHz, Cmax.
耐电压	55Vdc
绝缘电阻(min.)	10000MΩ
力矩	1.0 to 9.8mNm
质量	0.04g

注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。

2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，谨请核准其规格或者办理产品规格表。


TZV2Z100A110R00

注：这张数据表有可能不是很新的。


请从村田制作所的官方网站下载TZV2Z100A110R00的很新数据表。

<http://www.murata.com/zh-cn/products/productdetail?partno=TZV2Z100A110R00>


产品数据



结构



频率特性



温度特性

注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，请核准其规格或者办理产品规格表。