

782100/53VC

NRND

RoHS

用途

不能使用的用途	请务必确认并遵守“操作要求”。
可以使用的用途	民用设备,工业设备 针对上述用途所要求的性能、功能、质量、管理、安全性,请参照本网站及规格说明书等,并在确认实机性能与信赖性之后使用。

外观&形状



在1 / 2页

注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更,或若其中产品停产,请在订购时确认,恕不另行通知。
2. 本目录因没有足够的空间说明详细规格,仅载明标准规格。因此,在订购产品之前,谨请核准其规格或者办理产品规格表。

782100/53VC

规格

Target IC	PE22100
Type	Converter Transformer
Height (inch)	0.25inch
Height (mm)	6.35mm
Width (mm)	9.77mm
Depth (mm)	9.14mm
Mounting Option	Through Hole
Turns Ratio (Pri)	1.14CT
Turns Ratio (Sec)	1CT
Turns Ratio	1.14CT to 1CT
Isolation Voltage (V)	4000Vrms
Packaging style	Tube
Package weight (g)	1.1g
Package Qty.	50
Short Description	The 782100 series of converter transformers are specifically designed for use with the pSemi PE22100 chip set to provide isolated power supplies for transceivers in isolated interface applications.

Description	The 782100 series of converter transformers are specifically designed for use with the pSemi PE22100 chip set to provide isolated power supplies for transceivers in isolated interface applications.
Series	782100
Series Headline	PE22100 Compatible Converter Transformers
Series Description	The 782100 series of converter transformers are specifically designed for use with the Peregrine Semiconductor PE22100 chip set to provide isolated power supplies for transceivers in isolated interface applications.

注意

1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。

2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前， 谨请核准其规格或者办理产品规格表。