

56050C

目前生产

RoHS

用途

不能使用的用途	请务必确认并遵守“操作要求”。
可以使用的用途	民用设备,工业设备 针对上述用途所要求的性能、功能、质量、管理、安全性，请参照本网站及规格说明书等，并在确认实机性能与信赖性之后使用。

外观&形状



注意
1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，谨请核准其规格或者办理产品规格表。

56050C

规格

Height (inch)	0.795inch
Height (mm)	20.19mm
Width (mm)	16.79mm
Depth (mm)	8.89mm
Mounting Option	Through Hole
Turns Ratio	N to 50
Primary Current Rating (A)	10A
Secondary DC Resistance Min. (Ω)	0.133Ω
Secondary DC Resistance Max. (Ω)	0.199Ω
Terminating Resistance (Ω)	50Ω
Package weight (g)	5.7g
Short Description	The 5600 series of current sense transformers are designed to monitor AC currents. They can be used for high frequency current sensing, for example in switched-mode power supplies, motor control and electronic lighting ballasts.

Description	The 5600 series of current sense transformers are designed to monitor AC currents. They can be used for high frequency current sensing, for example in switched-mode power supplies, motor control and electronic lighting ballasts.
Series	5600
Series Headline	10A Current Sensing Transformers
Series Description	The 5600 series of current sense transformers are designed to monitor AC currents. They can be used for high frequency current sensing, for example in switched-mode power supplies, motor control and electronic lighting ballasts.

注意
1. 本目录是从株式会社村田制作所网站中下载的。规格若有变更，或若其中产品停产，请在订购时确认，恕不另行通知。
2. 本目录因没有足够的空间说明详细规格，仅载明标准规格。因此，在订购产品之前，谨请核准其规格或者办理产品规格表。