



# **Ceramic Trimmer Capacitors**





# **Contents**

Product specifications are as of September 2017.

Bluetooth  $^{\otimes}$  is a registered trademark or trademark of Bluetooth SIG, Inc. in the United States and other countries.

Part Numbering ·····	p2
Selection Guide of Ceramic Trimmer Capacitors ···	p3
1 TZR1 Series ·····	p4
2 TZY2 Series ·····	p8
3 TZC3 Series	p13
4 TZW4 Series ·····	p18
5 TZB4 Series	p21
Packaging ·····	p26
Recommended Adjustment Tools ······	p28
Qualified Standards ·····	p29

Please check the MURATA website (http://www.murata.com/) if you cannot find a part number in this catalog.



#### Part Numbering

#### **Ceramic Trimmer Capacitors**

(Part Number) TZ Y2 R 200 A C01 R00

#### ①Product ID

Product ID	
TZ	Trimmer Capacitors

#### 2Series/Terminal

Code	Series/Terminal
B4	4mm Size SMD Type
W4	4mm Size SMD Type
С3	3mm Size SMD Type
Y2	2mm Size SMD Type
R1	1mm Size SMD Type

#### **3**Temperature Characteristics

Code	Temperature Characteristics
Z	NP0ppm/°C
R	N750ppm/°C
К	N1000ppm/°C
Р	N1200ppm/°C

Please refer to ratings for tolerance of temperature characteristics.

#### Maximum Capacitance

Expressed by three-digit alphanumerics. The unit is pico-farad (pF). The first and second figures are significant digits, and the third figure expresses the number of zeros that follow the two numbers. If there is a decimal point, it is expressed by the capital letter "R". In this case, all figures are significant digits.

#### **5**Terminal Shape

Code	Terminal Shape		
Α	Top Adjustment: TZR1, TZY2, TZC3, TZW4, TZB4		
В	Top Adjustment: <b>TZB4</b>		

Please refer to dimensions for terminal details.

#### **6**Individual Specifications


Code	Individual Specifications
001	TZR1, TZW4 Standard Type
C01	TZY2 Standard Type
A01	TZC3 Standard Type
A10	TZB4 No-cover Film Standard Type
B10	TZB4 with Cover Film Standard Type

#### Packaging

Code	Packaging
В00	Bulk
R00	Reel (Taping ø180mm)
R01*	Reel (Taping ø330mm)

<sup>\*</sup> TZB4 only.

## **Selection Guide**



All Ceramic Trimmer Capacitor products comply with RoHS and ELV.


# Ceramic Trimmer Capacitors

## **■ TZR1 Series**

#### **Features**

- Ultra-small and thin with external dimensions of 1.5(W)x1.7(L)x0.85(H)mm (80% less in volume than the current product).
- Unique construction with no plastic material provides superior soldering heat resistance to maintain excellent characteristic performance after reflow soldering.
- 3. Suitable for high frequency circuit due to high self-resonant frequency (6.2GHz of TZR1Z010 at 1.0pF setting).






#### **Applications**

- 1. Bluetooth®
- 2. Crystal oscillators
- 3. Crystal filters
- 4. Miniature tuner packs (FM Radio, TV)
- 5. Remote keyless entry systems


Part Number	C min. (max.) (pF)	C max. (pF)	тс	Q	Rated Voltage	Withstanding Voltage
TZR1Z010A001	0.55	1.0 +100/-0%	NP0±300ppm/°C	200min. at 200MHz, Cmax.	25Vdc	55Vdc
TZR1Z1R5A001	0.7	1.5 +100/-0%	NP0±300ppm/°C	200min. at 200MHz, Cmax.	25Vdc	55Vdc
TZR1Z040A001	1.5	4.0 +100/-0%	NP0±500ppm/°C	300min. at 1MHz, Cmax.	25Vdc	55Vdc
TZR1R080A001	3.0	8.0 +100/-0%	N750±500ppm/°C	300min. at 1MHz, Cmax.	25Vdc	55Vdc

Insulation Resistance: 10000M ohm Torque: 0.1 to 1.0mNm Operating Temperature Range: -25 to +85°C


#### Construction




## Temperature Characteristics



#### **Frequency Characteristics**



#### **Land Pattern**




(Tolerance: ±0.1

#### **Temperature Profile**

#### Reflow Soldering Profile


①Soldering profile for Lead-free solder (96.5Sn/3Ag/0.5Cu)



Standard Profile						
Pre-heating						Cycle
Temp. (T1)	Time (t1)	Temp. (T2)	Time (t2)	temperature (T3)	of reflow	
150 to 180°C	60 to 120sec.	220°C	30 to 60sec.	245±3°C	2 times	

Limit Profile							
Pre-heating					Heating		Cycle
Temp. (T1)	Time (t1)	Temp. (T4)		temperature (T5)	of reflow		
150 to 180°C	60 to 120sec.	230°C	30 to 50sec.	260 +5/-0°C	2 times		

# ②Soldering profile for Eutectic solder (63Sn/37Pb) (Limit profile: refer to ①)



Standard Profile					
Pre-heating Heating Peak Cycle				Cycle	
Temp. (T1)	Time (t1)	Temp. (T2)	Time (t2)	temperature (T3)	of reflow
150°C	60 to 120sec.	183°C	30sec.	230 +5/-0°C	1 time

#### Soldering Iron

Standard Profile						
Temperature of soldering iron tip	Temperature of soldering iron tip Soldering time Soldering iron power output Cycle of soldering iron					
350±10°C	3sec. max.	30W max.	1 time			

#### Notice (Storage and Operating Conditions)

- Do not use the trimmer capacitor under atmosphere of RTV silicone rubber (Room Temperature Vulcanizing Silicone Rubber) except Acetone liberating silicone sealant.
- Before using trimmer capacitors, please store under the conditions of -10 to +40°C and 30 to 85%RH.
- 3. Do not store in or near corrosive gasses.
- 4. Use within 6 months of delivery.
- 5. Do not store under direct sunlight.

- 6. Do not use the trimmer capacitor under the conditions listed below.
- (1) Corrosive gasses atmosphere

   (ex. Chlorine gas, Hydrogen sulfide gas,
   Ammonia gas, Sulfuric acid gas, Nitric oxide gas, etc.)
- (2) In liquid (ex. water, oil, medical liquid, organic solvent, etc.)
- (3) Dusty / dirty atmosphere
- (4) Direct sunlight
- (5) Static voltage or electric/magnetic fields
- (6) Direct sea breeze
- (7) Other variations of the above

#### Notice (Soldering and Mounting)

- 1. Soldering
- TZR1 series can be soldered by reflow soldering method and soldering iron. Do not use flow soldering method (dipping).
- (2) Soldering conditions Refer to the temperature profile. If the soldering conditions are not suitable, e.g., excessive time and/or excessive temperature, the trimmer capacitor may deviate from the specified characteristics.
- (3) The amount of solder is critical.
- (4) The thickness of solder paste should be printed from 100 micro m to 150 micro m and the dimension of land pattern should be Murata's standard land pattern used at reflow soldering. Insufficient amounts of solder can lead to insufficient soldering strength on PCB. Excessive amounts of solder may cause bridging between the terminals or contact failure due to flux wicking up.
- (5) When using soldering iron, the diameter of the string solder shall be less than 0.5mm. The string solder shall be applied to the lower part of the terminal only. Do not apply flux except to the terminals. Excessive amounts of solder and/or applying solder to the upper part of the terminal may cause fixed metal rotor or contact failure due to flux invasion into the movable part and/or the contact point. The soldering iron should not come in contact with the monolithic stator of the trimmer capacitor. If such contact does occur, the trimmer capacitor may be damaged.

- (6) Our recommended chlorine content of solder is as follows.
  - (a) Solder paste: 0.2wt% max.
  - (b) String solder: 0.5wt% max.
- (7) Do not use water-soluble flux (for water cleaning). To prevent the deterioration of trimmer capacitor characteristics, apply flux only to terminals.
- 2. Mounting
  - (1) Do not apply excessive force (preferably 5.0 N [Ref: 500gf] max.), when the trimmer capacitor is mounted on the PCB.
  - (2) Do not warp and/or bend PCB to protect trimmer capacitor from breaking.
- (3) Use a pick-up nozzle of a suitable dimension. (1.6mm external diameter and 0.8mm bore diameter.)
- Cleaning
   This product cannot be cleaned because of open construction.
- Other
   Note the polarity of the trimmer capacitor to minimize influence by stray capacitance.
   (Refer to the dimensions concerning the polarity.)

#### Notice (Handling)

- 1. Use suitable screwdrivers that fit comfortably in driver slot.
  - \*Recommended screwdriver for manual adjustment MURATA: KMDR160
- When adjusting with a screwdriver, do not apply excessive force (preferably 0.5 N [Ref: 50gf] max.) to minimize capacitance drift. Excessive force applied to the screwdriver slot may cause deformation of the products.
- Do not apply adhesive, lock paints, or any other substances to the trimmer capacitor to secure the rotor position. They may cause corrosion or electrical contact problems.

#### Notice (Other)

Before using trimmer capacitors, please test after assembly in your particular mass production system.

# Ceramic Trimmer Capacitors

## **■ TZY2 Series**

#### **Features**

- 1. Small and thin size with external dimensions of 2.5(W)x3.2(L)x1.25max.(H)mm.
- 2. New shape of cover can improve the flux invasion compared with current products.
- 3. Improvement of the adhesion between rotor and stator leads to superior stability.
- Unique construction with no plastic material provides superior soldering heat resistance to maintain excellent characteristic performance after reflow soldering.
- Suitable for high frequency circuit due to high self-resonant frequency (4.8GHz of TZY2Z010 at 1.0pF setting).




1. Crystal oscillators 7. W-LAN

Crystal filters
 Radar detectors
 Stylus pen
 Compact radios
 Hand radios
 Burglarproof devices
 Watches
 Headphone stereos

6. Remote keyless entry systems







Part Number	C min. (max.) (pF)	C max. (pF)	тс	Q	Rated Voltage	Withstanding Voltage
TZY2Z010AC01	0.6	1.0 +100/-0%	NP0±300ppm/°C	200min. at 200MHz, Cmax.	25Vdc	55Vdc
TZY2Z2R5AC01	1.0	2.5 +100/-0%	NP0±300ppm/°C	200min. at 200MHz, Cmax.	25Vdc	55Vdc
TZY2Z030AC01	1.5	3.0 +100/-0%	NP0±300ppm/°C	300min. at 1MHz, Cmax.	25Vdc	55Vdc
TZY2Z060AC01	2.5	6.0 +100/-0%	NP0±300ppm/°C	500min. at 1MHz, Cmax.	25Vdc	55Vdc
TZY2Z100AC01	3.0	10.0 +100/-0%	NP0±300ppm/°C	500min. at 1MHz, Cmax.	25Vdc	55Vdc
TZY2R200AC01	4.5	20.0 +100/-0%	N750±500ppm/°C	500min. at 1MHz, Cmax.	25Vdc	55Vdc
TZY2R250AC01	5.5	25.0 +100/-0%	N750±500ppm/°C	300min. at 1MHz, Cmax.	25Vdc	55Vdc
TZY2K450AC01	8.0	45.0 +100/-0%	N1000±500ppm/°C	300min. at 1MHz, Cmax.	25Vdc	55Vdc

 $Insulation \ Resistance: 10000 Mohm \qquad Torque: 0.7 \ to \ 4.9 mNm \qquad Operating \ Temperature \ Range: -25 \ to \ +85 ^{\circ}C$ 


#### Construction





#### **Temperature Characteristics**




# Frequency Characteristics










#### **Land Pattern**




/Tolerance: ±0.1

#### **Temperature Profile**

#### Reflow Soldering Profile


①Soldering profile for Lead-free solder (96.5Sn/3Ag/0.5Cu)



Standard Profile								
Pre-heating		Hea	Heating		Cycle			
Temp. (T1)	Time (t1)	Temp. (T2)	Time (t2)	temperature (T3)	of reflow			
150 to 180°C	60 to 120sec.	220°C	30 to 60sec.	245±3°C	2 times			

Limit Profile								
Pre-h	eating	Heating		Peak temperature	Cycle			
Temp. (T1)	Time (t1)	Temp. (T4)	Time (t3)	(T5)	of reflow			
150 to 180°C	60 to 120sec.	230°C	30 to 50sec.	260 +5/-0°C	2 times			

#### ②Soldering profile for Eutectic solder (63Sn/37Pb) (Limit profile: refer to ①)



Standard Profile							
Pre-heating Heatin		ting	Peak	Cycle			
Temp. (T1)	Time (t1)	Temp. (T2)	Time (t2)	temperature (T3)	of reflow		
150°C	60 to 120sec.	183°C	30sec.	230 +5/-0°C	1 time		

#### Soldering Iron

Standard Profile								
Temperature of soldering iron tip	Soldering time	Soldering iron power output	Cycle of soldering iron					
350±10°C	3sec. max.	30W max.	1 time					

#### Notice (Storage and Operating Conditions)

- Do not use the trimmer capacitor under atmosphere of RTV silicone rubber (Room Temperature Vulcanizing Silicone Rubber) except Acetone liberating silicone sealant.
- Before using trimmer capacitors, please store under the conditions of -10 to +40°C and 30 to 85%RH.
- 3. Do not store in or near corrosive gasses.
- 4. Use within 6 months of delivery.
- 5. Do not store under direct sunlight.

- 6. Do not use the trimmer capacitor under the conditions listed below.
- Corrosive gasses atmosphere

   (ex. Chlorine gas, Hydrogen sulfide gas,
   Ammonia gas, Sulfuric acid gas, Nitric oxide gas, etc.)
- (2) In liquid (ex. water, oil, medical liquid, organic solvent, etc.)
- (3) Dusty / dirty atmosphere
- (4) Direct sunlight
- (5) Static voltage or electric/magnetic fields
- (6) Direct sea breeze
- (7) Other variations of the above

#### Notice (Soldering and Mounting)

- 1. Soldering
- TZY2 series can be soldered by reflow soldering method and soldering iron. Do not use flow soldering method (dipping).
- (2) Soldering conditions Refer to the temperature profile. If the soldering conditions are not suitable, e.g., excessive time and/or excessive temperature, the trimmer capacitor may deviate from the specified characteristics.
- (3) The amount of solder is critical.
- (4) The thickness of solder paste should be printed from 120 micro m to 170 micro m and the dimension of land pattern should be Murata's standard land pattern used at reflow soldering. Insufficient amounts of solder can lead to insufficient soldering strength on PCB. Excessive amounts of solder may cause bridging between the terminals or contact failure due to flux wicking up.
- (5) When using soldering iron, the diameter of the string solder shall be less than 0.5mm. The string solder shall be applied to the lower part of the terminal only. Do not apply flux except to the terminals. Excessive amounts of solder and/or applying solder to the upper part of the terminal may cause fixed metal rotor or contact failure due to flux invasion into the movable part and/or the contact point. The soldering iron should not come in contact with the monolithic stator of the trimmer capacitor. If such contact does occur, the trimmer capacitor may be damaged.

- (6) Our recommended chlorine content of solder is as follows.
  - (a) Solder paste: 0.2wt% max.
  - (b) String solder: 0.5wt% max.
- (7) Do not use water-soluble flux (for water cleaning). To prevent the deterioration of trimmer capacitor characteristics, apply flux only to terminals.
- 2. Mounting
- (1) Do not apply excessive force (preferably 5.0 N [Ref: 500gf] max.), when the trimmer capacitor is mounted on the PCB.
- (2) Do not warp and/or bend PCB to protect trimmer capacitor from breakage.
- (3) Use a pick-up nozzle of a suitable dimension. (2.5mm external diameter and 1.2mm bore diameter.)
- Cleaning
   This product cannot be cleaned because of open construction.
- Other
   Note the polarity of the trimmer capacitor to minimize influence by stray capacitance.
   (Refer to the dimensions concerning the polarity.)

#### Notice (Handling)

- 1. Use suitable screwdrivers that fit comfortably in driver slot.
- (1) Recommended screwdriver for manual adjustment MURATA: KMDR020
- (2) Recommended screwdriver bit for automatic adjustment
  - MURATA: KMBT020

- When adjusting with a screwdriver, do not apply excessive force (preferably 1.0 N [Ref: 100gf] max.) to minimize capacitance drift. Excessive force applied to the screwdriver slot may cause deformation of the products.
- Do not apply adhesive, lock paints, or any other substances to the trimmer capacitor to secure the rotor position. They may cause corrosion or electrical contact problems.

#### Notice (Other)

12


Before using trimmer capacitor, please test after assembly in your particular mass production system.

# Ceramic Trimmer Capacitors

# **● TZC3 Series**

#### **Features**

- 1. Small size with external dimension of 3.2(W)x4.5(L)x1.6(H)mm.
- 2. Can be adjusted with conventional adjustment tools having a thickness of 0.5mm.
- 3. Designed for automatic placement in surface mount applications.
- 4. Heat resistant resin withstands reflow soldering temperatures.




#### **Applications**


- 1. Compact radios
- 2. Stylus pen
- 3. Portable radio equipment
- 4. Hybrid ICs
- 5. Remote keyless entry systems


Part Number	C min. (max.) (pF)	C max. (pF)	тс	Q	Rated Voltage	Withstanding Voltage
TZC3Z030AA01	1.4	3.0 +50/-0%	NP0±300ppm/°C	300min. at 1MHz, Cmax.	100Vdc	220Vdc
TZC3Z060AA01	2.0	6.0 +50/-0%	NP0±300ppm/°C	500min. at 1MHz, Cmax.	100Vdc	220Vdc
TZC3R100AA01	3.0	10.0 +50/-0%	N750±300ppm/°C	500min. at 1MHz, Cmax.	100Vdc	220Vdc
TZC3P200AA01	5.0	20.0 +50/-0%	N1200±500ppm/°C	300min. at 1MHz, Cmax.	100Vdc	220Vdc
TZC3P300AA01	6.5	30.0 +50/-0%	N1200±500ppm/°C	300min. at 1MHz, Cmax.	100Vdc	220Vdc


#### Construction





# Temperature Characteristics















# Frequency Characteristics










#### **Land Pattern**




(Tolerance: ±0.1) in mm)

#### **Temperature Profile**

#### Reflow Soldering Profile


①Soldering profile for Lead-free solder (96.5Sn/3Ag/0.5Cu)



Standard Profile							
Pre-h	Pre-heating Heating		Peak temperature	Cycle			
Temp. (T1)	Time (t1)	Temp. (T2)	Time (t2)	(T3)	of reflow		
150 to 180°C	60 to 120sec.	220°C	30 to 60sec.	245±3°C	2 times		

Limit Profile								
Pre-heating Heating		ting	Peak	Cycle				
Temp. (T1)	Time (t1)	Temp. (T4)	Time (t3)	temperature (T5)	of reflow			
150 to 180°C	60 to 120sec.	230°C	30 to 50sec.	260 +5/-0°C	2 times			

# ②Soldering profile for Eutectic solder (63Sn/37Pb) (Limit profile: refer to ①)



Standard Profile								
Pre-heating		Heating		Peak	Cycle			
Temp. (T1)	Time (t1)	Temp. (T2)	Time (t2)	temperature (T3)	of reflow			
150°C	60 to 120sec.	183°C	30sec.	230 +5/-0°C	1 time			

#### Soldering Iron

Standard Profile								
Temperature of soldering iron tip	Soldering time	Soldering iron power output	Cycle of soldering iron					
350±10°C	3sec. max.	30W max.	1 time					

#### Notice (Storage and Operating Conditions)

- Do not use the trimmer capacitor under atmosphere of RTV silicone rubber (Room Temperature Vulcanizing Silicone Rubber) except Acetone liberating silicone sealant.
- Before using trimmer capacitors, please store under the conditions of -10 to +40°C and 30 to 85%RH.
- 3. Do not store in or near corrosive gasses.
- 4. Use within 6 months of delivery.
- 5. Do not store under direct sunlight.

- 6. Do not use the trimmer capacitor under the conditions listed below.
- Corrosive gasses atmosphere

   (ex. Chlorine gas, Hydrogen sulfide gas,
   Ammonia gas, Sulfuric acid gas, Nitric oxide gas, etc.)
- (2) In liquid (ex. water, oil, medical liquid, organic solvent, etc.)
- (3) Dusty / dirty atmosphere
- (4) Direct sunlight
- (5) Static voltage or electric/magnetic fields
- (6) Direct sea breeze
- (7) Other variations of the above

#### Notice (Soldering and Mounting)

- 1. Soldering
- TZC3 series can be soldered by reflow soldering method and soldering iron. Do not use flow soldering method (dipping).
- (2) Soldering conditions Refer to the temperature profile. If the soldering conditions are not suitable, e.g., excessive time and/or excessive temperature, the trimmer capacitor may deviate from the specified characteristics.
- (3) The amount of solder is critical.
- (4) The thickness of solder paste should be printed from 150 micro m to 200 micro m and the dimension of land pattern should be Murata's standard land pattern used at reflow soldering. Insufficient amounts of solder can lead to insufficient soldering strength on PCB. Excessive amounts of solder may cause bridging between the terminals or contact failure due to flux wicking up.
- (5) When using soldering iron, the diameter of the string solder shall be less than 0.5mm. The string solder shall be applied to the lower part of the terminal only. Do not apply flux except to the terminals. Excessive amounts of solder and/or applying solder to the upper part of the terminal may cause fixed metal rotor or contact failure due to flux invasion into the movable part and/or the contact point. The soldering iron should not come in contact with the stator of the trimmer capacitor. If such contact does occur, the trimmer capacitor may be damaged.

- (6) Our recommended chlorine content of solder is
  - (a) Solder paste: 0.2wt% max.
  - (b) String solder: 0.5wt% max.
- (7) Do not use water-soluble flux (for water cleaning). To prevent the deterioration of trimmer capacitor characteristics, apply flux only to terminals.
- (8) When soldering the TZC3 series, the solder should not flow into the staking part of the substrate. If such flow does occur, driver slot rotation will be damaged.
- 2. Mounting
  - (1) Do not apply excessive force (preferably 5.0 N [Ref: 500gf] max.), when the trimmer capacitor is mounted on the PCB.
  - (2) Do not warp and/or bend PCB to protect trimmer capacitor from breakage.
  - (3) Use a pick-up nozzle of a suitable dimension. (2.5mm external diameter and 1.5mm bore diameter.)
- Cleaning
   This product cannot be cleaned because of open construction.
- 4. Other

Note the polarity of the trimmer capacitor to minimize influence by stray capacitance. (Refer to the dimensions concerning the polarity.)

#### Notice (Handling)

- 1. Use suitable screwdrivers that fit comfortably in driver slot.
  - Recommended screwdriver for manual adjustment Standard type --> MURATA: KMDR080
- When adjusting with a screwdriver, do not apply excessive force (preferably 1.0 N [Ref: 100gf] max.) to minimize capacitance drift. Excessive force applied to the screwdriver slot may cause deformation of the products.
- Do not apply adhesive, lock paints, or any other substances to the trimmer capacitor to secure the rotor position. They may cause corrosion or electrical contact problems.

#### Notice (Other)

Before using trimmer capacitors, please test after assembly in your particular mass production system.

# Ceramic Trimmer Capacitors

## **■ TZW4 Series**

#### **Features**

- 1. To meet high power application due to withstanding voltage 550Vdc.
- 2. Extremely high self-resonant frequency. (More than 3GHz at rated C max.)
- 3. Typical application: Impedance matching for Cellular Base Station.
- 4. High Q value in more than VHF, UHF and Microwave bands.


(More than 200 in 500MHz, C max.)

- 5. Available for pick and place machine. Possible thinner design due to 2.6mm low profile.
- Non-electrical contact construction (rotor as middle electrode) provides high reliability.
- 7. Compact size: 4.2(W)x5.2(L)x2.6max.(H)mm.

#### **Applications**

- 1. Transmitting power amplifier for Cellular base station
- 2. Transmitting amplifier for PHS base station
- 3. High frequency electric circuit
- 4. High power radio transmission
- 5. Transponder amplifier for cable TV







Part Number	C min. (max.) (pF)	C max. (pF)	тс	Q	Rated Voltage	Withstanding Voltage
TZW4Z010A001	0.4	1.0 +50/-0%	NP0±150ppm/°C	200min. at 500MHz, Cmax.	250Vdc	550Vdc
TZW4Z1R5A001	0.4	1.5 +100/-0%	NP0±150ppm/°C	200min. at 500MHz, Cmax.	250Vdc	550Vdc


 $Insulation \ Resistance: 10000M \ ohm \qquad Torque: 1.5 \ to \ 10.0mNm \qquad Operating \ Temperature \ Range: -55 \ to \ +125 ^{\circ}C$ 

#### Construction




#### **Temperature Characteristics**






#### **Frequency Characteristics**



#### **Land Pattern**




(Tolerance: ±0.1 in mm)

#### **Temperature Profile**

#### Reflow Soldering Profile


 $@Soldering\ profile\ for\ Lead-free\ solder\ (96.5Sn/3Ag/0.5Cu) \\$ 



Standard Profile								
Pre-heating Heating		ting	Peak temperature	Cycle				
Temp. (T1)	Time (t1)	Temp. (T2)	Time (t2)	(T3)	of reflow			
150 to 180°C	60 to 120sec.	220°C	30 to 60sec.	245±3°C	2 times			

Limit Profile					
Pre-h	eating	Heating		Peak temperature	Cycle
Temp. (T1)	Time (t1)	Temp. (T4)		(T5)	of reflow
150 to 180°C	60 to 120sec.	230°C	30 to 50sec.	260 +5/-0°C	2 times

# ②Soldering profile for Eutectic solder (63Sn/37Pb) (Limit profile: refer to ①)



Standard Profile					
Pre-h	eating	Heating		Peak	Cycle
Temp. (T1)	Time (t1)	Temp. (T2)		temperature (T3)	of reflow
150°C	60 to 120sec.	183°C	30sec.	230 +5/-0°C	1 time

#### Soldering Iron

Standard Profile				
Temperature of soldering iron tip	Soldering time	Soldering iron power output	Cycle of soldering iron	
350±10°C	3sec. max.	30W max.	1 time	

#### Notice (Storage and Operating Conditions)

- Do not use the trimmer capacitor under atmosphere of RTV silicone rubber (Room Temperature Vulcanizing Silicone Rubber) except Acetone liberating silicone sealant.
- Before using trimmer capacitors, please store under the conditions of -10 to +40°C and 30 to 85%RH.
- 3. Do not store in or near corrosive gasses.
- 4. Use within 6 months of delivery.
- 5. Do not store under direct sunlight.

- 6. Do not use the trimmer capacitor under the conditions listed below.
- Corrosive gasses atmosphere
   (Ex. Chlorine gas, Hydrogen sulfide gas,
   Ammonia gas, Sulfuric acid gas, Nitric oxide gas, etc.)
- (2) In liquid (Ex. water, oil, medical liquid, organic solvent, etc.)
- (3) Dusty/dirty atmosphere
- (4) Direct sunlight
- (5) Static voltage or electric/magnetic fields
- (6) Direct sea breeze
- (7) Other variations of the above

#### Notice (Soldering and Mounting)

- 1. Soldering
- TZW4 series can be soldered by reflow soldering method and soldering iron. Do not use flow soldering method (dipping).
- (2) Soldering conditions Refer to the temperature profile. If the soldering conditions are not suitable, e.g., excessive time and/or excessive temperature, the trimmer capacitor may deviate from the specified characteristics.
- (3) The amount of solder is critical.
- (4) The thickness of solder paste should be printed from 150 micro m to 200 micro m and the dimension of land pattern should be Murata's standard land pattern used at reflow soldering. Insufficient amounts of solder can lead to insufficient soldering strength on PCB. Excessive amounts of solder may cause bridging between the terminals or contact failure due to flux wicking up.
- (5) When using soldering iron, the diameter of the string solder shall be less than 0.5mm. The string solder shall be applied to the lower part of the terminal only. Do not apply flux except to the terminals. Excessive amounts of solder and/or applying solder to the upper part of the terminal may cause fixed metal rotor or

- the contact failure due to flux invasion into the movable part and/or the contact point. The soldering iron should not come in contact with the monolithic stator of the trimmer capacitor. If such contact does occur, the trimmer capacitor may be damaged.
- (6) Our recommended chlorine content of solder is as follows.
  - (a) Solder paste: 0.2wt% max.
  - (b) String solder: 0.5wt% max.
- (7) Do not use water-soluble flux (for water cleaning). To prevent the deterioration of trimmer capacitor characteristics, apply flux only to terminals.
- 2. Mounting
- (1) Do not apply excessive force (preferably 5.0 N [Ref: 500gf] max.), when the trimmer capacitor is mounted on the PCB.
- (2) Do not warp and/or bend PCB to protect trimmer capacitor from breaking.
- (3) Use a pick-up nozzle of a suitable dimension. (4.0mm external diameter and 1.2mm bore diameter.)
- 3. Cleaning

This product cannot be cleaned because of open construction.

#### Notice (Handling)

- 1. Use suitable screwdrivers that fit comfortably in driver slot.
- -Recommended screwdriver for manual adjustment VESSEL : No.9000 -1.3x30 (Murata P/N is KMDR130)
- When adjusting with a screwdriver, do not apply excessive force (preferably 1.0 N [Ref: 100gf] max.) to minimize capacitance drift. Excessive force applied to the screwdriver slot may cause deformation of the products.
- Do not apply adhesive, lock paints, or any other substances to the trimmer capacitor to secure the rotor position. They may cause corrosion or electrical contact problems.

#### Notice (Other)

Before using trimmer capacitors, please test after assembly in your particular mass production system.



# Ceramic Trimmer Capacitors

## **■ TZB4 Series**

#### **Features**


- 1. Miniature rectangular shape: 4.0(W)x4.5(L)x3.0(H)mm.
- 2. Color coded case facilitates identification of capacitance range.
- 3. Designed for automatic placement in surface mount applications.
- 4. Designed to withstand flux baths and solder baths (with cover film type).
- 5. Can be temporarily attached to PCB with adhesives (Terminal style A and B).
- 6. Can be reflow and flow (with cover film type) soldering method.
- 7. Stable characteristics over a wide frequency range. (Resonant frequency: 1000MHz min. / 6pF)

#### **Applications**

- 1. Car audio systems
- 2. Hybrid ICs
- 3. Remote keyless entry systems
- 4. Surveillance cameras
- 5. Burglarproof devices
- 6. Entry phone















Part Number	C min. (max.) (pF)	C max. (pF)	тс	Q	Rated Voltage	Withstanding Voltage	Stator/Case Color
TZB4Z030□□10	1.4	3.0 +50/-0%	NP0±200ppm/°C	300min. at 1MHz, Cmax	100Vdc	220Vdc	Brown
TZB4Z060□□10	2.0	6.0 +50/-0%	NP0±200ppm/°C	500min. at 1MHz, Cmax.	100Vdc	220Vdc	Blue
TZB4Z100□□10	3.0	10.0 +50/-0%	NP0±300ppm/°C	500min. at 1MHz, Cmax.	100Vdc	220Vdc	White
TZB4R200□□10	4.5	20.0 +50/-0%	N750±400ppm/°C	500min. at 1MHz, Cmax	100Vdc	220Vdc	Red
TZB4P300□□10	6.5	30.0 +50/-0%	N1200±500ppm/°C	300min. at 1MHz, Cmax	100Vdc	220Vdc	Green
TZB4P400□□10	8.5	40.0 +50/-0%	N1200±500ppm/°C	300min. at 1MHz, Cmax	100Vdc	220Vdc	Yellow
TZB4Z250□□10	4.0	25.0 +100/-0%	NP0±300ppm/°C	300min. at 1MHz, Cmax.	50Vdc	110Vdc	Black+Marking
TZB4R500□□10	7.0	50.0 +100/-0%	N750±300ppm/°C	300min. at 1MHz, Cmax	50Vdc	110Vdc	Black+Marking

Insulation Resistance: 10000M ohm Torque: 1.5 to 9.8mNm Operating Temperature Range: -25 to +85°C First blank: Terminal Type Second blank: Cover film codes (A: not provided, B: provided)


rex. TZB4Z100 $\underline{AB}$ 10: Terminal Type is A, and Cover film is provided.


#### Construction



#### Land Pattern/Mounting Holes


A Type B Type








(in mm) (in mm)


### **Temperature Characteristics**


















Continued on the following page.  $\nearrow$ 




#### **Frequency Characteristics**










#### **Temperature Profile**

#### •Flow Soldering Profile

Soldering profile for Lead-free solder (96.5Sn/3Ag/0.5Cu), Eutectic solder (63Sn/37Pb)




<sup>•</sup> Immerse the body in solder bath, available for cover film type.

Standard Profile					
Pre-heating		Hea	Cycle		
Temp. (T1)	Time (t1)	Temp. (T2)	Time (t2)	of reflow	
150°C	60 to 120sec.	250°C	5sec. max.	1 time	

Limit Profile				
Pre-heating		Hea	Cycle	
Temp. (T1)	Time (t1)	Temp. (T3)	Time (t2)	of reflow
150°C	60 to 120sec.	265±3°C	5sec. max.	2 times

#### Reflow Soldering Profile

@Soldering profile for Lead-free solder (96.5Sn/3Ag/0.5Cu)




Standard Profile					
Pre-h	eating	Heating		Peak temperature	Cycle
Temp. (T1)	Time (t1)	Temp. (T2)	Time (t2)	(T3)	of reflow
150 to 180°C	60 to 120sec.	220°C	30 to 60sec.	245±3°C	2 times

Limit Profile					
Pre-h	eating	Heating		Peak temperature	Cycle
Temp. (T1)	Time (t1)	Temp. (T4)	Time (t3)	(T5)	of reflow
150 to 180°C	60 to 120sec.	230°C	30 to 50sec.	260 +5/-0°C	2 times

<sup>•</sup> Available for terminal shape A, B, and E.

②Soldering profile for Eutectic solder (63Sn/37Pb) (Limit profile: refer to ①)



Standard Profile					
Pre-h	eating	Heating		Peak	Cycle
Temp. (T1)	Time (t1)	Temp. (T2)	Time (t2)	temperature (T3)	of reflow
150°C	60 to 120sec.	183°C	30sec.	230 +5/-0°C	1 time

#### Soldering Iron

Standard Profile				
Temperature of soldering iron tip	Soldering time	Soldering iron power output	Cycle of soldering iron	
350±10°C	3sec. max.	30W max.	1 time	

#### Notice (Storage and Operating Conditions)

- Do not use the trimmer capacitor under atmosphere of RTV silicone rubber (Room Temperature Vulcanizing Silicone Rubber) except Acetone liberating silicone sealant.
- 2. Before using trimmer capacitors, please store under the conditions of -10 to +40°C and 30 to 85%RH.
- 3. Do not store in or near corrosive gasses.
- 4. Use within 6 months of delivery.
- 5. Do not store under direct sunlight.

- 6. Do not use the trimmer capacitor under the conditions listed below.
- (1) Corrosive gasses atmosphere
   (ex. Chlorine gas, Hydrogen sulfide gas, Ammonia gas, Sulfuric acid gas, Nitric oxide gas, etc.)
- (2) In liquid (ex. water, oil, medical liquid, organic solvent, etc.)
- (3) Dusty / dirty atmosphere
- (4) Direct sunlight
- (5) Static voltage or electric/magnetic fields
- (6) Direct sea breeze
- (7) Other variations of the above

#### Notice (Soldering and Mounting)

- 1. Soldering
- (1) Can be soldered by reflow soldering method, flow soldering method, and soldering iron.
- (2) Soldering conditions Refer to the temperature profile. If the soldering conditions are not suitable, e.g., excessive time and/or excessive temperature, the trimmer capacitor may deviate from the specified characteristics.
- (3) The amount of solder is critical.
- (4) The thickness of solder paste should be printed from 150 micro m to 200 micro m and the dimension of land pattern should be Murata's standard land pattern used at reflow soldering. Insufficient amounts of solder can lead to insufficient soldering strength on PCB. Excessive amounts of solder may cause bridging between the terminals or contact failure due to flux wicking up.
- (5) When using soldering iron, the string solder shall be applied to the lower part of the terminal only. Do not apply flux except to the terminals. Excessive amounts of solder and/or applying solder to the upper part of the terminal may cause fixed rotor or contact failure due to flux invasion into the movable part and/or the contact point. The soldering iron should not come in contact with the plastic case of the trimmer capacitor. If such contact does occur, the trimmer capacitor may be damaged.
- (6) Our recommended chlorine content of solder is as follows.
  - (a) Solder paste: 0.2wt% max.
  - (b) String solder: 0.5wt% max.
- (7) Do not use water-soluble flux (for water cleaning). To prevent the deterioration of trimmer capacitor characteristics, apply flux only to terminals.

- 2. Mounting
- (1) Do not apply excessive force (preferably 5.0N [Ref: 500gf] max.), when the trimmer capacitor is mounted on the PCB.
- (2) Do not warp and/or bend PCB to protect trimmer capacitor from breakage.
- (3) When bending the terminals, do not apply excessive force to the body of the product to protect the terminal fixing part from damage.
- (4) Use a pick-up nozzle of a suitable dimension.
  - > Without cover film type
    - External dimensions of 4.5x4.0mm and 2.5mm bore diameter.
  - > With cover film type
    - 4.0mm external diameter and 2.0mm bore diameter.
- 3. Cleaning [with cover film type] Isopropyl alcohol and ethyl alcohol are available material for cleaning. If you use any other type of solvent, please evaluate performance in your application. Moreover, please confirm that no damage has occurred to the trimmer capacitor after cleaning in your conditions.
- 4. Other

Note the polarity of the trimmer capacitor to minimize influence by stray capacitance.
(Refer to the dimensions concerning the polarity.)

#### Notice (Handling)

- 1. Use suitable screwdrivers that fit comfortably in driver slot.
- (1) Recommended screwdriver for manual adjustment MURATA: KMDR010
- (2) Recommended screwdriver bit for automatic adjustment
  MURATA: KMBT010
- When adjusting with a screwdriver, do not apply excessive force (preferably 1.0 N [Ref: 100gf] max.) to minimize capacitance drift. Excessive force applied to the screwdriver slot may cause deformation of the products.
- Do not apply adhesive, lock paints, or any other substances to the trimmer capacitor to secure the rotor position. They may cause corrosion or electrical contact problems.
- 4. Do not break the cover film before the completion of PCB mounting, soldering, and cleaning.
- Do not clean the trimmer capacitor after the cover film has been broken.
- To break the cover film, first turn the screwdriver more than 360°, and set the capacitance value. (Inserting the screwdriver only will not break the cover film.)

#### Notice (Other)

Before using trimmer capacitors, please test after assembly in your particular mass production system.


## **Packaging**

#### **Minimum Quantity**

Part Number		Minimum Quantity (pcs.)		
Part Number	ø180mm Reel	ø330mm Reel	Bulk	
TZR1	3000	-	500	
TZY2	2000	-	500	
TZC3	1000	-	500	
TZW4	500	-	100	
TZB4	500	2500	500	


#### **Tape Dimensions**

#### TZR1 Series




(in mm)

#### TZY2 Series




TZC3 Series




(Tolerance: ±0.1 in mm)

#### TZW4 Series



(Tolerance: ±0.1)

#### TZB4 Series



(Tolerance: ±0.1)

Continued on the following page.  ${\cal J}$ 

## Packaging


Continued from the preceding page.

#### Reel Dimensions (180mm diameter)

# TZR1/TZY2 Series TZC3/TZW4/TZB4 Series 13.0±0.5 dia 2.0±0.5 dia 2.0±0.8 dia 9.0±1.0 13.0±1.0 178±2 dia. (in mm) (in mm)

#### Reel Dimensions (330mm diameter)

#### **TZB4** Series





(in mm)

## **Recommended Adjustment Tools**

Please use the following recommended screwdrivers.

You can order these drivers using the part numbers below.

Although you can also adjust the capacitance value using commercial products, please use one with the same head size as the driver listed below.

For Manual Adjustment

For Maridat Adjustifierit			
Series	MURATA Model Number	Manufacturer's Model Number	Shape
TZR1	KMDR160	MURATA MFG. KMDR160	80  1.5  Bit shape: ⊖Minus (0.3x0.13) (in mm)
TZY2	KMDR020	VESSEL MFG. NO.9000 -0.9x30	125  15  VESSEL 9000 0,9-30  Bit shape: ⊝Minus (0.9x30)  (in mm)
тzсз	KMDR080	VESSEL MFG. NO.9000 +1.7x30	125  15  CERAMIC BLADE PAT. PRODUCT OF JAPAN  Bit shape: ⊕Plus (1.7x30)  (in mm)
TZB4	KMDR010	MURATA MFG. KMDR010	122 20 50 muRata  Bit shape: ⊝Minus (2.2x0.4) (in mm)
TZW4	KMDR130	VESSEL MFG. NO.9000 -1.3x30	125  15  9000  1.3-30  Bit shape: ⊝Minus (1.3x30)  (in mm)

#### For Automatic Adjustment

Series	MURATA Model Number	Manufacturer's Model Number	Shape
TZY2	КМВТО20	MURATA MFG. KMBT020	0.9±0.05 0.9±0.05 0.9±0.05 0.0±0.05 0.0±0.05 0.0±0.05 0.0±0.05
TZB4	КМВТО10	MURATA MFG. KMBT010	Bit shape: ⊝Minus (2.2x0.4)  (in mm)

# Qualified Standards

The products listed herein have been produced by a ISO9001 certified factory.

#### MURATA FACTORY

Sabae Murata Mfg. Co., Ltd.

29

<sup>\*</sup> No ODCs (Ozone Depleting Chemicals) are used on any Murata trimmer capacitors.

# Global Locations

For details please visit www.murata.com



#### **Note**

#### 1 Export Control

#### For customers outside Japan:

No Murata products should be used or sold, through any channels, for use in the design, development, production, utilization, maintenance or operation of, or otherwise contribution to (1) any weapons (Weapons of Mass Destruction [nuclear, chemical or biological weapons or missiles] or conventional weapons) or (2) goods or systems specially designed or intended for military end-use or utilization by military end-users.

#### For customers in Japan:

For products which are controlled items subject to the "Foreign Exchange and Foreign Trade Law" of Japan, the export license specified by the law is required for export.

- Please contact our sales representatives or product engineers before using the products in this catalog for the applications listed below, which require especially high reliability for the prevention of defects which might directly damage a third party's life, body or property, or when one of our products is intended for use in applications other than those specified in this catalog.
  - Aircraft equipment
  - Aerospace equipment
  - 3 Undersea equipment
  - Power plant equipment
  - Medical equipment
  - (6) Transportation equipment (vehicles, trains, ships, etc.)
  - 7 Traffic signal equipment
  - 8 Disaster prevention / crime prevention equipment
  - Data-processing equipment
  - Application of similar complexity and/or reliability requirements to the applications listed above

- 3 Product specifications in this catalog are as of September 2017. They are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. If there are any questions, please contact our sales representatives or product engineers.
- 4 Please read rating and &CAUTION (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
- 5 This catalog has only typical specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.
- Please note that unless otherwise specified, we shall assume no responsibility whatsoever for any conflict or dispute that may occur in connection with the effect of our and/or a third party's intellectual property rights and other related rights in consideration of your use of our products and/or information described or contained in our catalogs. In this connection, no representation shall be made to the effect that any third parties are authorized to use the rights mentioned above under licenses without our consent.
- No ozone depleting substances (ODS) under the Montreal Protocol are used in our manufacturing process.

Murata Manufacturing Co., Ltd.

www.murata.com

