

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLE18PK100SN1	10		0.008	6000	1608/0603	General	1 MHz - 3 GHz
BLE18PK160SN1	16		0.012	5000	1608/0603	General	1 MHz - 3 GHz
BLE18PS080SN1	8		0.004	8000	1608/0603	General	1 MHz - 3 GHz
BLE18PS080SZ1	8		0.004	8000	1608/0603	Infotainment	1 MHz - 3 GHz
BLE18PS080BH1	8		0.004	5000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLE18PS080SH1	8		0.004	8000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLE32PN260SN1	26		0.0016	10000	3225/1210	General	1 MHz - 3 GHz
BLE32PN300SN1	30		0.0016	10000	3225/1210	General	1 MHz - 3 GHz
BLE32PN260SZ1	26		0.0016	10000	3225/1210	Infotainment	1 MHz - 3 GHz
BLE32PN300SZ1	30		0.0016	10000	3225/1210	Infotainment	1 MHz - 3 GHz
BLE32PN260SH1	26		0.0016	10000	3225/1210	Powertrain/Safety	1 MHz - 3 GHz
BLE32PN300SH1	30		0.0016	10000	3225/1210	Powertrain/Safety	1 MHz - 3 GHz
BLE32SN120BN1	12		0.0006	20000	3225/1210	General	1 MHz - 3 GHz
BLE32SN120SN1	12		0.0006	20000	3225/1210	General	1 MHz - 3 GHz
BLE32SN120SZ1	12		0.0006	20000	3225/1210	Infotainment	1 MHz - 3 GHz
BLE32SN120BH1	12		0.0006	20000	3225/1210	Powertrain/Safety	1 MHz - 3 GHz
BLE32SN120SH1	12		0.0006	20000	3225/1210	Powertrain/Safety	1 MHz - 3 GHz
BLF02GD162GNE			3	100	0402/01005	General	1 MHz - 3 GHz
BLF02JD361GNE			0.45	380	0402/01005	General	1 MHz - 3 GHz
BLF02JD471GNE			0.6	330	0402/01005	General	1 MHz - 3 GHz
BLF02RD331GNE			0.6	330	0402/01005	General	1 MHz - 3 GHz
BLF02RD471GNE			0.9	200	0402/01005	General	1 MHz - 3 GHz
BLF03JD421GNE			0.28	480	0603/0201	General	1 MHz - 3 GHz
BLF03RD102GNE			1	220	0603/0201	General	1 MHz - 3 GHz
BLF03RD501GNE			0.36	500	0603/0201	General	1 MHz - 3 GHz
BLF03RD102GZE			1	220	0603/0201	Infotainment	1 MHz - 3 GHz
BLF03RD501GZE			0.36	500	0603/0201	Infotainment	1 MHz - 3 GHz
BLF03VK221SNG			0.155	800	0603/0201	General	1 MHz - 8 GHz
BLF03VK600SNL			0.065	1200	0603/0201	General	1 MHz - 8 GHz
BLM02AX100SN1	10		0.07	750	0402/01005	General	1 MHz - 3 GHz
BLM02AX121SN1	120		0.5	250	0402/01005	General	1 MHz - 3 GHz
BLM02AX241SN1	240		0.9	200	0402/01005	General	1 MHz - 3 GHz
BLM02AX331SN1	330		1.4	150	0402/01005	General	1 MHz - 3 GHz
BLM02AX700SN1	70		0.36	300	0402/01005	General	1 MHz - 3 GHz
BLM02BB101SN1	100		2	125	0402/01005	General	1 MHz - 3 GHz
BLM02BC100SN1	10	95	0.5	250	0402/01005	General	1 MHz - 3 GHz
BLM02BC220SN1	22	240	0.9	200	0402/01005	General	1 MHz - 3 GHz
BLM02BX121SN1	120		0.5	350	0402/01005	General	1 MHz - 3 GHz
BLM02BX151SN1	150		0.7	280	0402/01005	General	1 MHz - 3 GHz
BLM02BX241SN1	240		1.1	240	0402/01005	General	1 MHz - 3 GHz
BLM02KX100SN1	10		0.03	1500	0402/01005	General	1 MHz - 3 GHz
BLM02KX180SN1	18		0.045	1200	0402/01005	General	1 MHz - 3 GHz
BLM02PX100SN1	10		0.05	1100	0402/01005	General	1 MHz - 3 GHz
BLM02PX220SN1	22		0.11	750	0402/01005	General	1 MHz - 3 GHz
BLM02PX330SN1	33		0.2	550	0402/01005	General	1 MHz - 3 GHz
BLM02PX600SN1	60		0.25	500	0402/01005	General	1 MHz - 3 GHz
BLM03AG100SN1	10		0.1	500	0603/0201	General	1 MHz - 3 GHz
BLM03AG102SN1	1000		2.5	100	0603/0201	General	1 MHz - 3 GHz
BLM03AG121SN1	120		0.5	200	0603/0201	General	1 MHz - 3 GHz
BLM03AG241SN1	240		0.8	200	0603/0201	General	1 MHz - 3 GHz
BLM03AG601SN1	600		1.5	100	0603/0201	General	1 MHz - 3 GHz
BLM03AG700SN1	70		0.4	200	0603/0201	General	1 MHz - 3 GHz
BLM03AG800SN1	80		0.4	200	0603/0201	General	1 MHz - 3 GHz
BLM03AG100SZ1	10		0.1	500	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03AG102SZ1	1000		2.5	100	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03AG121SZ1	120		0.5	200	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03AG241SZ1	240		0.8	200	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03AG601SZ1	600		1.5	100	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03AG700SZ1	70		0.4	200	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03AG800SZ1	80		0.4	200	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03AX100SN1	10		0.05	1000	0603/0201	General	1 MHz - 3 GHz
BLM03AX102SN1	1000		1.25	200	0603/0201	General	1 MHz - 3 GHz
BLM03AX121SN1	120		0.23	450	0603/0201	General	1 MHz - 3 GHz
BLM03AX241SN1	240		0.38	350	0603/0201	General	1 MHz - 3 GHz
BLM03AX601SN1	600		0.85	250	0603/0201	General	1 MHz - 3 GHz
BLM03AX800SN1	80		0.18	500	0603/0201	General	1 MHz - 3 GHz
BLM03AX100SZ1	10		0.05	1000	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03AX102SZ1	1000		1.25	200	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03AX121SZ1	120		0.23	450	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03AX241SZ1	240		0.38	350	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03AX601SZ1	600		0.85	250	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03AX800SZ1	80		0.18	500	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03BB100SN1	10		0.4	300	0603/0201	General	1 MHz - 3 GHz
BLM03BB121SN1	120		1.5	100	0603/0201	General	1 MHz - 3 GHz
BLM03BB220SN1	22		0.5	200	0603/0201	General	1 MHz - 3 GHz
BLM03BB470SN1	47		0.7	200	0603/0201	General	1 MHz - 3 GHz
BLM03BB750SN1	75		1	200	0603/0201	General	1 MHz - 3 GHz
BLM03BB100SZ1	10		0.4	300	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03BB121SZ1	120		1.5	100	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03BB220SZ1	22		0.5	200	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03BB470SZ1	47		0.7	200	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03BB750SZ1	75		1	200	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03BC330SN1	33		0.85	150	0603/0201	General	1 MHz - 3 GHz
BLM03BC560SN1	56		1.05	100	0603/0201	General	1 MHz - 3 GHz
BLM03BC800SN1	80		1.4	100	0603/0201	General	1 MHz - 3 GHz
BLM03BC330SZ1	33		0.85	150	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03BC560SZ1	56		1.05	100	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03BC800SZ1	80		1.4	100	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03BD121SN1	120		0.5	250	0603/0201	General	1 MHz - 3 GHz
BLM03BD241SN1	240		0.8	200	0603/0201	General	1 MHz - 3 GHz
BLM03BD471SN1	470		1.5	215	0603/0201	General	1 MHz - 3 GHz
BLM03BD601SN1	600		1.7	200	0603/0201	General	1 MHz - 3 GHz
BLM03BD750SN1	75		0.4	300	0603/0201	General	1 MHz - 3 GHz
BLM03BD121SZ1	120		0.5	250	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03BD241SZ1	240		0.8	200	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03BD471SZ1	470		1.5	215	0603/0201	Infotainment	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLM03BD601SZ1	600		1.7	200	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03BD750SZ1	75		0.4	300	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03BX102SN1	1000		1.7	170	0603/0201	General	1 MHz - 3 GHz
BLM03BX182SN1	1800		2.5	140	0603/0201	General	1 MHz - 3 GHz
BLM03EB250SN1	25	105	0.26	600	0603/0201	General	1 MHz - 3 GHz
BLM03EB500SN1	50	255	0.58	400	0603/0201	General	1 MHz - 3 GHz
BLM03EB250SZ1	25	105	0.26	600	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03EB500SZ1	50	255	0.58	400	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03EB250SH1	25	105	0.26	600	0603/0201	Powertrain/Safety	1 MHz - 3 GHz
BLM03EB500SH1	50	255	0.58	400	0603/0201	Powertrain/Safety	1 MHz - 3 GHz
BLM03HB191SN1	190	1150	2	150	0603/0201	General	1 MHz - 3 GHz
BLM03HB401SN1	400	1850	2.8	125	0603/0201	General	1 MHz - 3 GHz
BLM03HB191SZ1	190	1150	2	150	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03HB401SZ1	400	1850	2.8	125	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03HD102FN1	1000	2300	2.4	135	0603/0201	General	1 MHz - 3 GHz
BLM03HD102SN1	1000	2300	2.9	120	0603/0201	General	1 MHz - 3 GHz
BLM03HD152FN1	1500	2700	3.1	120	0603/0201	General	1 MHz - 3 GHz
BLM03HD182FN1	1800	3000	3.8	100	0603/0201	General	1 MHz - 3 GHz
BLM03HD331SN1	330	750	1	200	0603/0201	General	1 MHz - 3 GHz
BLM03HD471SN1	470	1000	1.3	175	0603/0201	General	1 MHz - 3 GHz
BLM03HD601SN1	600	1500	1.7	150	0603/0201	General	1 MHz - 3 GHz
BLM03HD102FZ1	1000	2300	2.4	135	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03HD102SZ1	1000	2300	2.9	120	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03HD152FZ1	1500	2700	3.1	120	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03HD182FZ1	1800	3000	3.8	100	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03HD331SZ1	330	750	1	200	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03HD471SZ1	470	1000	1.3	175	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03HD601SZ1	600	1500	1.7	150	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03HG102SN1	1000	1800	2.6	125	0603/0201	General	1 MHz - 3 GHz
BLM03HG122SN1	1200	2000	3.5	100	0603/0201	General	1 MHz - 3 GHz
BLM03HG601SN1	600	1000	1.6	150	0603/0201	General	1 MHz - 3 GHz
BLM03HG102SZ1	1000	1800	2.6	125	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03HG122SZ1	1200	2000	3.5	100	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03HG601SZ1	600	1000	1.6	150	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03HG102SH1	1000	1800	2.6	125	0603/0201	Powertrain/Safety	1 MHz - 3 GHz
BLM03HG122SH1	1200	2000	3.5	100	0603/0201	Powertrain/Safety	1 MHz - 3 GHz
BLM03HG601SH1	600	1000	1.6	150	0603/0201	Powertrain/Safety	1 MHz - 3 GHz
BLM03PG220SN1	22		0.065	900	0603/0201	General	1 MHz - 3 GHz
BLM03PG330SN1	33		0.09	750	0603/0201	General	1 MHz - 3 GHz
BLM03PG220SZ1	22		0.065	900	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03PG330SZ1	33		0.09	750	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03PX121SN1	120		0.16	900	0603/0201	General	1 MHz - 3 GHz
BLM03PX220SN1	22		0.04	1800	0603/0201	General	1 MHz - 3 GHz
BLM03PX330SN1	33		0.055	1500	0603/0201	General	1 MHz - 3 GHz
BLM03PX800SN1	80		0.13	1000	0603/0201	General	1 MHz - 3 GHz
BLM03PX121SZ1	120		0.16	900	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03PX220SZ1	22		0.04	1800	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03PX330SZ1	33		0.055	1500	0603/0201	Infotainment	1 MHz - 3 GHz
BLM03PX800SZ1	80		0.13	1000	0603/0201	Infotainment	1 MHz - 3 GHz
BLM15AG100SN1	10		0.025	1000	1005/0402	General	1 MHz - 3 GHz
BLM15AG102SN1	1000		0.65	300	1005/0402	General	1 MHz - 3 GHz
BLM15AG121SN1	120		0.19	550	1005/0402	General	1 MHz - 3 GHz
BLM15AG221SN1	220		0.29	450	1005/0402	General	1 MHz - 3 GHz
BLM15AG601SN1	600		0.52	300	1005/0402	General	1 MHz - 3 GHz
BLM15AG700SN1	70		0.15	600	1005/0402	General	1 MHz - 3 GHz
BLM15AG100SZ1	10		0.025	1000	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15AG102SZ1	1000		0.65	300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15AG121SZ1	120		0.19	550	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15AG221SZ1	220		0.29	450	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15AG601SZ1	600		0.52	300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15AG700SZ1	70		0.15	600	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15AG100SH1	10		0.05	1000	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15AG102SH1	1000		1	200	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15AG121SH1	120		0.25	500	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15AG221SH1	220		0.35	300	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15AG601SH1	600		0.6	300	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15AG700SH1	70		0.15	500	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15AX100SN1	10		0.015	1740	1005/0402	General	1 MHz - 3 GHz
BLM15AX102SN1	1000		0.49	350	1005/0402	General	1 MHz - 3 GHz
BLM15AX121SN1	120		0.13	700	1005/0402	General	1 MHz - 3 GHz
BLM15AX221SN1	220		0.18	600	1005/0402	General	1 MHz - 3 GHz
BLM15AX300SN1	30		0.06	1100	1005/0402	General	1 MHz - 3 GHz
BLM15AX601SN1	600		0.34	500	1005/0402	General	1 MHz - 3 GHz
BLM15AX700SN1	70		0.1	780	1005/0402	General	1 MHz - 3 GHz
BLM15AX100SZ1	10		0.015	1740	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15AX102SZ1	1000		0.49	350	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15AX121SZ1	120		0.13	700	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15AX221SZ1	220		0.18	600	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15AX300SZ1	30		0.06	1100	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15AX601SZ1	600		0.34	500	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15AX700SZ1	70		0.1	780	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BA050SN1	5		0.1	300	1005/0402	General	1 MHz - 3 GHz
BLM15BA100SN1	10		0.2	300	1005/0402	General	1 MHz - 3 GHz
BLM15BA220SN1	22		0.3	300	1005/0402	General	1 MHz - 3 GHz
BLM15BA330SN1	33		0.4	300	1005/0402	General	1 MHz - 3 GHz
BLM15BA470SN1	47		0.6	200	1005/0402	General	1 MHz - 3 GHz
BLM15BA750SN1	75		0.8	200	1005/0402	General	1 MHz - 3 GHz
BLM15BA050SZ1	5		0.1	300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BA100SZ1	10		0.2	300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BA220SZ1	22		0.3	300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BA330SZ1	33		0.4	300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BA470SZ1	47		0.6	200	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BA750SZ1	75		0.8	200	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BB050SN1	5		0.08	500	1005/0402	General	1 MHz - 3 GHz
BLM15BB100SN1	10		0.1	300	1005/0402	General	1 MHz - 3 GHz
BLM15BB121SN1	120		0.55	300	1005/0402	General	1 MHz - 3 GHz
BLM15BB220SN1	22		0.2	300	1005/0402	General	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLM15BB221SN1	220		0.8	200	1005/0402	General	1 MHz - 3 GHz
BLM15BB470SN1	47		0.35	300	1005/0402	General	1 MHz - 3 GHz
BLM15BB750SN1	75		0.4	300	1005/0402	General	1 MHz - 3 GHz
BLM15BB050SZ1	5		0.08	500	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BB100SZ1	10		0.1	300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BB121SZ1	120		0.55	300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BB220SZ1	22		0.2	300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BB221SZ1	220		0.8	200	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BB470SZ1	47		0.35	300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BB750SZ1	75		0.4	300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BB050SH1	5		0.08	500	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15BB100SH1	10		0.1	300	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15BB121SH1	120		0.55	300	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15BB220SH1	22		0.2	300	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15BB221SH1	220		0.8	200	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15BB470SH1	47		0.35	300	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15BB750SH1	75		0.4	300	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15BC121SN1	120		0.45	350	1005/0402	General	1 MHz - 3 GHz
BLM15BC241SN1	240		0.7	250	1005/0402	General	1 MHz - 3 GHz
BLM15BC121SZ1	120		0.45	350	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BC241SZ1	240		0.7	250	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BD102SN1	1000		0.9	200	1005/0402	General	1 MHz - 3 GHz
BLM15BD121SN1	120		0.3	300	1005/0402	General	1 MHz - 3 GHz
BLM15BD152SN1	1500		1	190	1005/0402	General	1 MHz - 3 GHz
BLM15BD182SN1	1800		1.4	100	1005/0402	General	1 MHz - 3 GHz
BLM15BD221SN1	220		0.4	300	1005/0402	General	1 MHz - 3 GHz
BLM15BD471SN1	470		0.6	200	1005/0402	General	1 MHz - 3 GHz
BLM15BD601SN1	600		0.65	200	1005/0402	General	1 MHz - 3 GHz
BLM15BD750SN1	75		0.2	300	1005/0402	General	1 MHz - 3 GHz
BLM15BD102SZ1	1000		0.9	200	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BD121SZ1	120		0.3	300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BD152SZ1	1500		1	190	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BD182SZ1	1800		1.4	100	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BD221SZ1	220		0.4	300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BD471SZ1	470		0.6	200	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BD601SZ1	600		0.65	200	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BD750SZ1	75		0.2	300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BD102SH1	1000		0.9	200	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15BD182SH1	1800		1.4	200	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15BD471SH1	470		0.6	200	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15BD601SH1	600		0.65	200	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15BX102SN1	1000		0.65	300	1005/0402	General	1 MHz - 3 GHz
BLM15BX121SN1	120		0.17	600	1005/0402	General	1 MHz - 3 GHz
BLM15BX182SN1	1800		0.9	250	1005/0402	General	1 MHz - 3 GHz
BLM15BX221SN1	220		0.27	450	1005/0402	General	1 MHz - 3 GHz
BLM15BX471SN1	470		0.41	350	1005/0402	General	1 MHz - 3 GHz
BLM15BX601SN1	600		0.46	350	1005/0402	General	1 MHz - 3 GHz
BLM15BX750SN1	75		0.15	600	1005/0402	General	1 MHz - 3 GHz
BLM15BX102SZ1	1000		0.65	300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BX121SZ1	120		0.17	600	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BX182SZ1	1800		0.9	250	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BX221SZ1	220		0.27	450	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BX471SZ1	470		0.41	350	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BX601SZ1	600		0.46	350	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15BX750SZ1	75		0.15	600	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15EG121SN1	120	145	0.095	1500	1005/0402	General	1 MHz - 3 GHz
BLM15EG221SN1	220	270	0.28	700	1005/0402	General	1 MHz - 3 GHz
BLM15EG121SZ1	120	145	0.095	1500	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15EG221SZ1	220	270	0.28	700	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15EG121SH1	120	145	0.095	1500	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15EG221SH1	220	270	0.28	700	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15EX121SN1	120	170	0.075	1800	1005/0402	General	1 MHz - 3 GHz
BLM15EX221SN1	220	300	0.14	1300	1005/0402	General	1 MHz - 3 GHz
BLM15EX331SN1	330	450	0.205	1100	1005/0402	General	1 MHz - 3 GHz
BLM15EX471SN1	470	630	0.28	950	1005/0402	General	1 MHz - 3 GHz
BLM15GA750SN1	75	1000	1.3	200	1005/0402	General	1 MHz - 3 GHz
BLM15GA750SZ1	75	1000	1.3	200	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15GG221SN1	220	600	0.7	300	1005/0402	General	1 MHz - 3 GHz
BLM15GG471SN1	470	1200	1.3	200	1005/0402	General	1 MHz - 3 GHz
BLM15GG221SZ1	220	600	0.7	300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15GG471SZ1	470	1200	1.3	200	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15HB121SN1	120	500	0.7	300	1005/0402	General	1 MHz - 3 GHz
BLM15HB221SN1	220	900	1	250	1005/0402	General	1 MHz - 3 GHz
BLM15HB121SZ1	120	500	0.7	300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15HB221SZ1	220	900	1	250	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15HB121SH1	120	500	0.7	300	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15HB221SH1	220	900	1	250	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15HD102SN1	1000	2000	1.25	250	1005/0402	General	1 MHz - 3 GHz
BLM15HD182SN1	1800	2700	2.2	200	1005/0402	General	1 MHz - 3 GHz
BLM15HD601SN1	600	1400	0.85	300	1005/0402	General	1 MHz - 3 GHz
BLM15HD102SZ1	1000	2000	1.25	250	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15HD182SZ1	1800	2700	2.2	200	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15HD601SZ1	600	1400	0.85	300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15HD102BH1	1000	2000	1.25	250	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15HD102SH1	1000	2000	1.25	250	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15HD182BH1	1800	2700	2.2	200	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15HD182SH1	1800	2700	2.2	200	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15HD601BH1	600	1400	0.85	300	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15HD601SH1	600	1400	0.85	300	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15HG102SN1	1000	1400	1.1	250	1005/0402	General	1 MHz - 3 GHz
BLM15HG601SN1	600	1000	0.7	300	1005/0402	General	1 MHz - 3 GHz
BLM15HG102SZ1	1000	1400	1.1	250	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15HG601SZ1	600	1000	0.7	300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15HG102BH1	1000	1400	1.1	250	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15HG102SH1	1000	1400	1.1	250	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15HG601BH1	600	1000	0.7	300	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15HG601SH1	600	1000	0.7	300	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15KD121SN1	120		0.07	1500	1005/0402	General	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLM15KD200SN1	20		0.011	3800	1005/0402	General	1 MHz - 3 GHz
BLM15KD300SN1	30		0.0125	3100	1005/0402	General	1 MHz - 3 GHz
BLM15PD121SN1	120		0.09	1300	1005/0402	General	1 MHz - 3 GHz
BLM15PD300SN1	30		0.035	2200	1005/0402	General	1 MHz - 3 GHz
BLM15PD600SN1	60		0.06	1700	1005/0402	General	1 MHz - 3 GHz
BLM15PD800SN1	80		0.07	1500	1005/0402	General	1 MHz - 3 GHz
BLM15PD121SZ1	120		0.09	1300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15PD300SZ1	30		0.035	2200	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15PD600SZ1	60		0.06	1700	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15PD800SZ1	80		0.07	1500	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15PE121SH1	120		0.09	1500	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PE181SH1	180		0.14	1200	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PE221SH1	220		0.17	1100	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PE300SH1	30		0.035	2300	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PE331SH1	330		0.21	1000	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PE471SH1	470		0.35	750	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PE600SH1	60		0.06	1800	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PE601SH1	600		0.4	700	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PE800SH1	80		0.07	1700	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PG100SN1	10		0.025	1000	1005/0402	General	1 MHz - 3 GHz
BLM15PG100SZ1	10		0.025	1000	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15PX121SN1	120		0.055	2000	1005/0402	General	1 MHz - 3 GHz
BLM15PX181SN1	180		0.09	1500	1005/0402	General	1 MHz - 3 GHz
BLM15PX221SN1	220		0.1	1400	1005/0402	General	1 MHz - 3 GHz
BLM15PX330SN1	33		0.022	3000	1005/0402	General	1 MHz - 3 GHz
BLM15PX331SN1	330		0.15	1200	1005/0402	General	1 MHz - 3 GHz
BLM15PX471SN1	470		0.2	1000	1005/0402	General	1 MHz - 3 GHz
BLM15PX600SN1	60		0.032	2500	1005/0402	General	1 MHz - 3 GHz
BLM15PX601SN1	600		0.23	900	1005/0402	General	1 MHz - 3 GHz
BLM15PX800SN1	80		0.038	2300	1005/0402	General	1 MHz - 3 GHz
BLM15PX121SZ1	120		0.055	2000	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15PX181SZ1	180		0.09	1500	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15PX221SZ1	220		0.1	1400	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15PX330SZ1	33		0.022	3000	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15PX331SZ1	330		0.15	1200	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15PX471SZ1	470		0.2	1000	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15PX600SZ1	60		0.032	2500	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15PX601SZ1	600		0.23	900	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15PX800SZ1	80		0.038	2300	1005/0402	Infotainment	1 MHz - 3 GHz
BLM15PX121BH1	120		0.055	2000	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PX121SH1	120		0.055	2000	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PX181BH1	180		0.09	1500	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PX181SH1	180		0.09	1500	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PX221BH1	220		0.1	1400	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PX221SH1	220		0.1	1400	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PX330BH1	33		0.022	3000	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PX330SH1	33		0.022	3000	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PX331BH1	330		0.15	1200	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PX331SH1	330		0.15	1200	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PX471BH1	470		0.2	1000	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PX471SH1	470		0.2	1000	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PX600BH1	60		0.032	2500	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PX600SH1	60		0.032	2500	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PX601BH1	600		0.23	900	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PX601SH1	600		0.23	900	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PX800BH1	80		0.038	2300	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15PX800SH1	80		0.038	2300	1005/0402	Powertrain/Safety	1 MHz - 3 GHz
BLM15VM150BH1	15		0.245	900	1005/0402	Powertrain/Safety	1 MHz - 10 GHz
BLM18AG102SN1	1000		0.5	450	1608/0603	General	1 MHz - 3 GHz
BLM18AG121SN1	120		0.18	800	1608/0603	General	1 MHz - 3 GHz
BLM18AG151SN1	150		0.25	700	1608/0603	General	1 MHz - 3 GHz
BLM18AG221SN1	220		0.25	700	1608/0603	General	1 MHz - 3 GHz
BLM18AG331SN1	330		0.3	600	1608/0603	General	1 MHz - 3 GHz
BLM18AG471SN1	470		0.35	550	1608/0603	General	1 MHz - 3 GHz
BLM18AG601SN1	600		0.38	500	1608/0603	General	1 MHz - 3 GHz
BLM18AG102SZ1	1000		0.5	450	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18AG121SZ1	120		0.18	800	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18AG151SZ1	150		0.25	700	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18AG221SZ1	220		0.25	700	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18AG331SZ1	330		0.3	600	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18AG471SZ1	470		0.35	550	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18AG601SZ1	600		0.38	500	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18AG102BH1	1000		0.5	450	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18AG102SH1	1000		0.5	450	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18AG102WH1	1000		0.5	200	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18AG121BH1	120		0.18	800	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18AG121SH1	120		0.18	800	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18AG151BH1	150		0.25	700	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18AG151SH1	150		0.25	700	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18AG221BH1	220		0.25	700	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18AG221SH1	220		0.25	700	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18AG331BH1	330		0.3	600	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18AG331SH1	330		0.3	600	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18AG471BH1	470		0.35	550	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18AG471SH1	470		0.35	550	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18AG471WH1	470		0.35	1000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18AG601BH1	600		0.38	500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18AG601SH1	600		0.38	500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BA050SN1	5		0.2	500	1608/0603	General	1 MHz - 3 GHz
BLM18BA100SN1	10		0.25	500	1608/0603	General	1 MHz - 3 GHz
BLM18BA121SN1	120		0.9	200	1608/0603	General	1 MHz - 3 GHz
BLM18BA220SN1	22		0.35	500	1608/0603	General	1 MHz - 3 GHz
BLM18BA470SN1	47		0.55	300	1608/0603	General	1 MHz - 3 GHz
BLM18BA750SN1	75		0.7	300	1608/0603	General	1 MHz - 3 GHz
BLM18BA050SZ1	5		0.2	500	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BA100SZ1	10		0.25	500	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BA121SZ1	120		0.9	200	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BA220SZ1	22		0.35	500	1608/0603	Infotainment	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLM18BA470SZ1	47		0.55	300	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BA750SZ1	75		0.7	300	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BA050SH1	5		0.2	500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BA100SH1	10		0.25	500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BA121SH1	120		0.9	200	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BA220SH1	22		0.35	500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BA470SH1	47		0.55	300	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BA750SH1	75		0.7	300	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BB050SN1	5		0.05	800	1608/0603	General	1 MHz - 3 GHz
BLM18BB100SN1	10		0.1	700	1608/0603	General	1 MHz - 3 GHz
BLM18BB121SN1	120		0.3	550	1608/0603	General	1 MHz - 3 GHz
BLM18BB141SN1	140		0.35	500	1608/0603	General	1 MHz - 3 GHz
BLM18BB151SN1	150		0.37	450	1608/0603	General	1 MHz - 3 GHz
BLM18BB220SN1	22		0.2	700	1608/0603	General	1 MHz - 3 GHz
BLM18BB221SN1	220		0.45	450	1608/0603	General	1 MHz - 3 GHz
BLM18BB331SN1	330		0.58	400	1608/0603	General	1 MHz - 3 GHz
BLM18BB470SN1	47		0.25	600	1608/0603	General	1 MHz - 3 GHz
BLM18BB471SN1	470		0.85	300	1608/0603	General	1 MHz - 3 GHz
BLM18BB600SN1	60		0.25	600	1608/0603	General	1 MHz - 3 GHz
BLM18BB750SN1	75		0.3	600	1608/0603	General	1 MHz - 3 GHz
BLM18BB050SZ1	5		0.05	800	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BB100SZ1	10		0.1	700	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BB121SZ1	120		0.3	550	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BB141SZ1	140		0.35	500	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BB151SZ1	150		0.37	450	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BB220SZ1	22		0.2	700	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BB221SZ1	220		0.45	450	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BB331SZ1	330		0.58	400	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BB470SZ1	47		0.25	600	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BB471SZ1	470		0.85	300	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BB600SZ1	60		0.25	600	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BB750SZ1	75		0.3	600	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BB050SH1	5		0.05	800	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BB100SH1	10		0.1	700	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BB121SH1	120		0.3	550	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BB141SH1	140		0.35	500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BB151SH1	150		0.37	450	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BB220SH1	22		0.2	700	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BB221SH1	220		0.45	450	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BB331SH1	330		0.58	400	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BB470SH1	47		0.25	600	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BB471SH1	470		0.85	300	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BB600SH1	60		0.25	600	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BB750SH1	75		0.3	600	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD102SN1	1000		0.85	200	1608/0603	General	1 MHz - 3 GHz
BLM18BD121SN1	120		0.4	300	1608/0603	General	1 MHz - 3 GHz
BLM18BD151SN1	150		0.4	300	1608/0603	General	1 MHz - 3 GHz
BLM18BD152SN1	1500		1.2	150	1608/0603	General	1 MHz - 3 GHz
BLM18BD182SN1	1800		1.5	150	1608/0603	General	1 MHz - 3 GHz
BLM18BD221SN1	220		0.45	250	1608/0603	General	1 MHz - 3 GHz
BLM18BD222SN1	2200		1.5	150	1608/0603	General	1 MHz - 3 GHz
BLM18BD252SN1	2500		1.5	150	1608/0603	General	1 MHz - 3 GHz
BLM18BD331SN1	330		0.5	250	1608/0603	General	1 MHz - 3 GHz
BLM18BD421SN1	420		0.55	250	1608/0603	General	1 MHz - 3 GHz
BLM18BD470SN1	47		0.3	500	1608/0603	General	1 MHz - 3 GHz
BLM18BD471SN1	470		0.55	250	1608/0603	General	1 MHz - 3 GHz
BLM18BD601SN1	600		0.65	200	1608/0603	General	1 MHz - 3 GHz
BLM18BD102SZ1	1000		0.85	200	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BD121SZ1	120		0.4	300	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BD151SZ1	150		0.4	300	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BD152SZ1	1500		1.2	150	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BD182SZ1	1800		1.5	150	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BD221SZ1	220		0.45	250	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BD222SZ1	2200		1.5	150	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BD252SZ1	2500		1.5	150	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BD331SZ1	330		0.5	250	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BD421SZ1	420		0.55	250	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BD470SZ1	47		0.3	500	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BD471SZ1	470		0.55	250	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BD601SZ1	600		0.65	200	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18BD102BH1	1000		0.85	200	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD102SH1	1000		0.85	200	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD121BH1	120		0.4	300	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD121SH1	120		0.4	300	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD151BH1	150		0.4	300	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD151SH1	150		0.4	300	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD152BH1	1500		1.2	150	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD152SH1	1500		1.2	150	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD182BH1	1800		1.5	150	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD182SH1	1800		1.5	150	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD221BH1	220		0.45	250	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD221SH1	220		0.45	250	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD222BH1	2200		1.5	150	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD222SH1	2200		1.5	150	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD252BH1	2500		1.5	150	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD252SH1	2500		1.5	150	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD331BH1	330		0.5	250	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD331SH1	330		0.5	250	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD421BH1	420		0.55	250	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD421SH1	420		0.55	250	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD470BH1	47		0.3	500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD470SH1	47		0.3	500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD471BH1	470		0.55	250	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD471SH1	470		0.55	250	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD601BH1	600		0.65	200	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18BD601SH1	600		0.65	200	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18DN151SN1	150		0.12	1400	1608/0603	General	1 MHz - 3 GHz
BLM18DN221SN1	220		0.21	1000	1608/0603	General	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLM18DN381SN1	380		0.325	850	1608/0603	General	1 MHz - 3 GHz
BLM18DN601SN1	600		0.435	700	1608/0603	General	1 MHz - 3 GHz
BLM18DN151SZ1	150		0.12	1400	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18DN221SZ1	220		0.21	1000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18DN381SZ1	380		0.325	850	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18DN601SZ1	600		0.435	700	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18DN151SH1	150		0.12	1400	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18DN221SH1	220		0.21	1000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18DN381SH1	380		0.325	850	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18DN601SH1	600		0.435	700	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18EG101TN1	100	140	0.045	2000	1608/0603	General	1 MHz - 3 GHz
BLM18EG121SN1	120	145	0.04	2000	1608/0603	General	1 MHz - 3 GHz
BLM18EG221SN1	220	260	0.05	2000	1608/0603	General	1 MHz - 3 GHz
BLM18EG221TN1	220	300	0.15	1000	1608/0603	General	1 MHz - 3 GHz
BLM18EG331TN1	330	450	0.21	500	1608/0603	General	1 MHz - 3 GHz
BLM18EG391TN1	390	520	0.3	500	1608/0603	General	1 MHz - 3 GHz
BLM18EG471SN1	470	550	0.21	500	1608/0603	General	1 MHz - 3 GHz
BLM18EG601SN1	600	700	0.35	500	1608/0603	General	1 MHz - 3 GHz
BLM18EG101TZ1	100	140	0.045	2000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18EG121SZ1	120	145	0.04	2000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18EG221SZ1	220	260	0.05	2000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18EG221TZ1	220	300	0.15	1000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18EG331TZ1	330	450	0.21	500	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18EG391TZ1	390	520	0.3	500	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18EG471SZ1	470	550	0.21	500	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18EG601SZ1	600	700	0.35	500	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18EG101TH1	100	140	0.045	2000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18EG121SH1	120	145	0.04	2000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18EG181SH1	180	240	0.05	2000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18EG221TH1	220	300	0.15	1000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18EG331TH1	330	450	0.21	500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18EG391TH1	390	520	0.3	500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18EG471SH1	470	550	0.21	500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18EG601SH1	600	700	0.35	500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18GG471SN1	470	1800	1.3	200	1608/0603	General	1 MHz - 3 GHz
BLM18GG471SZ1	470	1800	1.3	200	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18HB121SN1	120	500	0.5	200	1608/0603	General	1 MHz - 3 GHz
BLM18HB221SN1	220	1100	0.8	100	1608/0603	General	1 MHz - 3 GHz
BLM18HB331SN1	330	1600	1.2	50	1608/0603	General	1 MHz - 3 GHz
BLM18HB121SZ1	120	500	0.5	200	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18HB221SZ1	220	1100	0.8	100	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18HB331SZ1	330	1600	1.2	50	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18HD102SN1	1000	1700	1.8	50	1608/0603	General	1 MHz - 3 GHz
BLM18HD471SN1	470	1000	1.2	100	1608/0603	General	1 MHz - 3 GHz
BLM18HD601SN1	600	1200	1.5	100	1608/0603	General	1 MHz - 3 GHz
BLM18HD102SZ1	1000	1700	1.8	50	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18HD471SZ1	470	1000	1.2	100	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18HD601SZ1	600	1200	1.5	100	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18HD102SH1	1000	1700	1.8	50	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18HD471SH1	470	1000	1.2	100	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18HD601SH1	600	1200	1.5	100	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18HE102SN1	1000	1000	0.35	600	1608/0603	General	1 MHz - 3 GHz
BLM18HE152SN1	1500	1500	0.5	500	1608/0603	General	1 MHz - 3 GHz
BLM18HE601SN1	600	600	0.25	800	1608/0603	General	1 MHz - 3 GHz
BLM18HE102SZ1	1000	1000	0.35	600	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18HE152SZ1	1500	1500	0.5	500	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18HE601SZ1	600	600	0.25	800	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18HE102SH1	1000	1000	0.35	600	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18HE152SH1	1500	1500	0.5	500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18HE601SH1	600	600	0.25	800	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18HG102SN1	1000	1000	1.6	100	1608/0603	General	1 MHz - 3 GHz
BLM18HG471SN1	470	600	0.85	200	1608/0603	General	1 MHz - 3 GHz
BLM18HG601SN1	600	700	1	200	1608/0603	General	1 MHz - 3 GHz
BLM18HG102SZ1	1000	1000	1.6	100	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18HG471SZ1	470	600	0.85	200	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18HG601SZ1	600	700	1	200	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18HG102SH1	1000	1000	1.6	100	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18HG471SH1	470	600	0.85	200	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18HG601SH1	600	700	1	200	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18HK102SN1	1000	1200	1.5	50	1608/0603	General	1 MHz - 3 GHz
BLM18HK331SN1	330	400	0.5	200	1608/0603	General	1 MHz - 3 GHz
BLM18HK471SN1	470	600	0.7	200	1608/0603	General	1 MHz - 3 GHz
BLM18HK601SN1	600	700	0.9	100	1608/0603	General	1 MHz - 3 GHz
BLM18KG101TN1	100		0.03	3000	1608/0603	General	1 MHz - 3 GHz
BLM18KG102SN1	1000		0.2	1000	1608/0603	General	1 MHz - 3 GHz
BLM18KG121TN1	120		0.03	3000	1608/0603	General	1 MHz - 3 GHz
BLM18KG221SN1	220		0.05	2200	1608/0603	General	1 MHz - 3 GHz
BLM18KG260TN1	26		0.007	6000	1608/0603	General	1 MHz - 3 GHz
BLM18KG300TN1	30		0.01	5000	1608/0603	General	1 MHz - 3 GHz
BLM18KG331SN1	330		0.08	1700	1608/0603	General	1 MHz - 3 GHz
BLM18KG471SN1	470		0.13	1500	1608/0603	General	1 MHz - 3 GHz
BLM18KG601SN1	600		0.15	1300	1608/0603	General	1 MHz - 3 GHz
BLM18KG700TN1	70		0.022	3500	1608/0603	General	1 MHz - 3 GHz
BLM18KG101TZ1	100		0.03	3000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18KG102SZ1	1000		0.2	1000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18KG121TZ1	120		0.03	3000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18KG221SZ1	220		0.05	2200	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18KG260TZ1	26		0.007	6000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18KG300TZ1	30		0.01	5000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18KG331SZ1	330		0.08	1700	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18KG471SZ1	470		0.13	1500	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18KG601SZ1	600		0.15	1300	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18KG700TZ1	70		0.022	3500	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18KG101JH1	100		0.03	1900	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG101TH1	100		0.03	3000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG101WH1	100		0.055	1500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG102BH1	1000		0.2	800	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG102SH1	1000		0.2	1000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLM18KG102WH1	1000		0.23	800	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG121JH1	120		0.03	1900	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG121TH1	120		0.03	3000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG121WH1	120		0.055	1500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG221BH1	220		0.05	1500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG221SH1	220		0.05	2200	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG221WH1	220		0.08	1400	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG260JH1	26		0.007	4000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG260TH1	26		0.007	6000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG260WH1	26		0.032	2000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG300JH1	30		0.01	3300	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG300TH1	30		0.01	5000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG300WH1	30		0.035	1850	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG331BH1	330		0.08	1200	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG331SH1	330		0.08	1700	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG331WH1	330		0.11	1250	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG471BH1	470		0.13	1000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG471SH1	470		0.13	1500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG471WH1	470		0.16	1100	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG601BH1	600		0.15	1000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG601SH1	600		0.15	1300	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG601WH1	600		0.18	1000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG700JH1	70		0.022	2200	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG700TH1	70		0.022	3500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KG700WH1	70		0.047	1650	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KN101EH1	100		0.03	1900	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KN102EH1	1000		0.2	740	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KN121EH1	120		0.03	1900	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KN221EH1	220		0.05	1400	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KN260EH1	26		0.007	4000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KN300EH1	30		0.01	2600	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KN331EH1	330		0.08	1100	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KN471EH1	470		0.13	920	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KN601EH1	600		0.15	860	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18KN700EH1	70		0.022	2200	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18PG121SN1	120		0.05	2000	1608/0603	General	1 MHz - 3 GHz
BLM18PG181SN1	180		0.09	1500	1608/0603	General	1 MHz - 3 GHz
BLM18PG221SN1	220		0.1	1400	1608/0603	General	1 MHz - 3 GHz
BLM18PG300SN1	30		0.05	1000	1608/0603	General	1 MHz - 3 GHz
BLM18PG330SN1	33		0.025	3000	1608/0603	General	1 MHz - 3 GHz
BLM18PG331SN1	330		0.15	1200	1608/0603	General	1 MHz - 3 GHz
BLM18PG471SN1	470		0.2	1000	1608/0603	General	1 MHz - 3 GHz
BLM18PG600SN1	60		0.1	1000	1608/0603	General	1 MHz - 3 GHz
BLM18PG121SZ1	120		0.05	2000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18PG181SZ1	180		0.09	1500	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18PG221SZ1	220		0.1	1400	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18PG300SZ1	30		0.05	1000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18PG330SZ1	33		0.025	3000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18PG331SZ1	330		0.15	1200	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18PG471SZ1	470		0.2	1000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18PG600SZ1	60		0.1	1000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18PG121SH1	120		0.05	2000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18PG181SH1	180		0.09	1500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18PG221SH1	220		0.1	1400	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18PG300SH1	30		0.05	1000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18PG330SH1	33		0.025	3000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18PG331SH1	330		0.15	1200	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18PG471SH1	470		0.2	1000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18PG600SH1	60		0.1	1000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18RK102SN1	1000		0.8	200	1608/0603	General	1 MHz - 3 GHz
BLM18RK121SN1	120		0.25	200	1608/0603	General	1 MHz - 3 GHz
BLM18RK221SN1	220		0.3	200	1608/0603	General	1 MHz - 3 GHz
BLM18RK471SN1	470		0.5	200	1608/0603	General	1 MHz - 3 GHz
BLM18RK601SN1	600		0.6	200	1608/0603	General	1 MHz - 3 GHz
BLM18SD220SN1	22		0.008	6000	1608/0603	General	1 MHz - 3 GHz
BLM18SG121TN1	120		0.025	3000	1608/0603	General	1 MHz - 3 GHz
BLM18SG221TN1	220		0.04	2500	1608/0603	General	1 MHz - 3 GHz
BLM18SG260TN1	26		0.007	6000	1608/0603	General	1 MHz - 3 GHz
BLM18SG330SN1	33		0.008	6000	1608/0603	General	1 MHz - 3 GHz
BLM18SG331TN1	330		0.07	1500	1608/0603	General	1 MHz - 3 GHz
BLM18SG700TN1	70		0.02	4000	1608/0603	General	1 MHz - 3 GHz
BLM18SG121TZ1	120		0.025	3000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18SG221TZ1	220		0.04	2500	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18SG260TZ1	26		0.007	6000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18SG331TZ1	330		0.07	1500	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18SG700TZ1	70		0.02	4000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18SN220TN1	22		0.004	8000	1608/0603	General	1 MHz - 3 GHz
BLM18SN220TZ1	22		0.004	8000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18SN220TH1	22		0.004	8000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18SP101SN1	100		0.022	3700	1608/0603	General	1 MHz - 3 GHz
BLM18SP102SN1	1000		0.185	1200	1608/0603	General	1 MHz - 3 GHz
BLM18SP221SN1	220		0.04	2800	1608/0603	General	1 MHz - 3 GHz
BLM18SP300SN1	30		0.008	6000	1608/0603	General	1 MHz - 3 GHz
BLM18SP601SN1	600		0.14	1500	1608/0603	General	1 MHz - 3 GHz
BLM18SP101SZ1	100		0.022	3700	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18SP102SZ1	1000		0.185	1200	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18SP221SZ1	220		0.04	2800	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18SP300SZ1	30		0.008	6000	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18SP601SZ1	600		0.14	1500	1608/0603	Infotainment	1 MHz - 3 GHz
BLM18SP101SH1	100		0.022	3700	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18SP102SH1	1000		0.185	1200	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18SP221SH1	220		0.04	2800	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18SP300SH1	30		0.008	6000	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18SP601SH1	600		0.14	1500	1608/0603	Powertrain/Safety	1 MHz - 3 GHz
BLM18TG102TN1	1000		0.6	100	1608/0603	General	1 MHz - 3 GHz
BLM18TG121TN1	120		0.25	200	1608/0603	General	1 MHz - 3 GHz
BLM18TG221TN1	220		0.3	200	1608/0603	General	1 MHz - 3 GHz
BLM18TG601TN1	600		0.45	200	1608/0603	General	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLM21AG102SN1	1000		0.27	600	2012/0805	General	1 MHz - 3 GHz
BLM21AG121SN1	120		0.09	1000	2012/0805	General	1 MHz - 3 GHz
BLM21AG151SN1	150		0.09	1000	2012/0805	General	1 MHz - 3 GHz
BLM21AG221SN1	220		0.12	900	2012/0805	General	1 MHz - 3 GHz
BLM21AG331SN1	330		0.15	800	2012/0805	General	1 MHz - 3 GHz
BLM21AG471SN1	470		0.18	700	2012/0805	General	1 MHz - 3 GHz
BLM21AG601SN1	600		0.2	700	2012/0805	General	1 MHz - 3 GHz
BLM21AG102SZ1	1000		0.27	600	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21AG121SZ1	120		0.09	1000	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21AG151SZ1	150		0.09	1000	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21AG221SZ1	220		0.12	900	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21AG331SZ1	330		0.15	800	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21AG471SZ1	470		0.18	700	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21AG601SZ1	600		0.2	700	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21AG102BH1	1000		0.27	600	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21AG102SH1	1000		0.27	600	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21AG121BH1	120		0.09	1000	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21AG121SH1	120		0.09	1000	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21AG151BH1	150		0.09	1000	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21AG151SH1	150		0.09	1000	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21AG221BH1	220		0.12	900	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21AG221SH1	220		0.12	900	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21AG331BH1	330		0.15	800	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21AG331SH1	330		0.15	800	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21AG471BH1	470		0.18	700	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21AG471SH1	470		0.18	700	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21AG601BH1	600		0.2	700	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21AG601SH1	600		0.2	700	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BB050SN1	5		0.02	1000	2012/0805	General	1 MHz - 3 GHz
BLM21BB121SN1	120		0.19	600	2012/0805	General	1 MHz - 3 GHz
BLM21BB151SN1	150		0.21	600	2012/0805	General	1 MHz - 3 GHz
BLM21BB201SN1	200		0.26	500	2012/0805	General	1 MHz - 3 GHz
BLM21BB221SN1	220		0.26	500	2012/0805	General	1 MHz - 3 GHz
BLM21BB331SN1	330		0.33	400	2012/0805	General	1 MHz - 3 GHz
BLM21BB471SN1	470		0.4	400	2012/0805	General	1 MHz - 3 GHz
BLM21BB600SN1	60		0.13	800	2012/0805	General	1 MHz - 3 GHz
BLM21BB750SN1	75		0.16	700	2012/0805	General	1 MHz - 3 GHz
BLM21BB050SZ1	5		0.02	1000	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BB121SZ1	120		0.19	600	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BB151SZ1	150		0.21	600	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BB201SZ1	200		0.26	500	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BB221SZ1	220		0.26	500	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BB331SZ1	330		0.33	400	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BB471SZ1	470		0.4	400	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BB600SZ1	60		0.13	800	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BB750SZ1	75		0.16	700	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BB050SH1	5		0.02	1000	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BB121SH1	120		0.19	600	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BB151SH1	150		0.21	600	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BB201SH1	200		0.26	500	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BB221SH1	220		0.26	500	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BB331SH1	330		0.33	400	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BB471SH1	470		0.4	400	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BB600SH1	60		0.13	800	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BB750SH1	75		0.16	700	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BD102SN1	1000		0.4	250	2012/0805	General	1 MHz - 3 GHz
BLM21BD121SN1	120		0.25	350	2012/0805	General	1 MHz - 3 GHz
BLM21BD151SN1	150		0.25	350	2012/0805	General	1 MHz - 3 GHz
BLM21BD152SN1	1500		0.45	250	2012/0805	General	1 MHz - 3 GHz
BLM21BD182SN1	1800		0.5	250	2012/0805	General	1 MHz - 3 GHz
BLM21BD221SN1	220		0.25	350	2012/0805	General	1 MHz - 3 GHz
BLM21BD222SN1	2250		0.6	250	2012/0805	General	1 MHz - 3 GHz
BLM21BD222TN1	2200		0.6	200	2012/0805	General	1 MHz - 3 GHz
BLM21BD272SN1	2700		0.8	200	2012/0805	General	1 MHz - 3 GHz
BLM21BD331SN1	330		0.3	300	2012/0805	General	1 MHz - 3 GHz
BLM21BD421SN1	420		0.3	300	2012/0805	General	1 MHz - 3 GHz
BLM21BD471SN1	470		0.35	300	2012/0805	General	1 MHz - 3 GHz
BLM21BD601SN1	600		0.35	300	2012/0805	General	1 MHz - 3 GHz
BLM21BD751SN1	750		0.4	250	2012/0805	General	1 MHz - 3 GHz
BLM21BD102SZ1	1000		0.4	250	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BD121SZ1	120		0.25	350	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BD151SZ1	150		0.25	350	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BD152SZ1	1500		0.45	250	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BD182SZ1	1800		0.5	250	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BD221SZ1	220		0.25	350	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BD222SZ1	2250		0.6	250	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BD222TZ1	2200		0.6	200	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BD272SZ1	2700		0.8	200	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BD331SZ1	330		0.3	300	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BD421SZ1	420		0.3	300	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BD471SZ1	470		0.35	300	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BD601SZ1	600		0.35	300	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BD751SZ1	750		0.4	250	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21BD102SH1	1000		0.4	250	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BD121SH1	120		0.25	350	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BD151SH1	150		0.25	350	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BD152SH1	1500		0.45	250	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BD182SH1	1800		0.5	250	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BD221SH1	220		0.25	350	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BD222SH1	2250		0.6	250	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BD222TH1	2200		0.6	200	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BD272SH1	2700		0.8	200	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BD331SH1	330		0.3	300	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BD421SH1	420		0.3	300	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BD471SH1	470		0.35	300	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BD601SH1	600		0.35	300	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21BD751SH1	750		0.4	250	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21HE122SN1	1200	450	0.11	1600	2012/0805	General	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLM21HE472SN1	4700	750	0.4	850	2012/0805	General	1 MHz - 3 GHz
BLM21HE601SN1	600	450	0.055	2300	2012/0805	General	1 MHz - 3 GHz
BLM21HE802SN1	8000	850	0.7	650	2012/0805	General	1 MHz - 3 GHz
BLM21HE122BH1	1200	450	0.11	1600	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21HE122SH1	1200	450	0.11	1600	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21HE472BH1	4700	750	0.4	850	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21HE472SH1	4700	750	0.4	850	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21HE601BH1	600	450	0.055	2300	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21HE601SH1	600	450	0.055	2300	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21HE802BH1	8000	850	0.7	650	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21HE802SH1	8000	850	0.7	650	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21PG102SN1	1000		0.2	1150	2012/0805	General	1 MHz - 3 GHz
BLM21PG121SN1	120		0.03	3000	2012/0805	General	1 MHz - 3 GHz
BLM21PG220SN1	22		0.009	6000	2012/0805	General	1 MHz - 3 GHz
BLM21PG221SN1	220		0.045	2000	2012/0805	General	1 MHz - 3 GHz
BLM21PG300SN1	30		0.014	4000	2012/0805	General	1 MHz - 3 GHz
BLM21PG331SN1	330		0.07	1500	2012/0805	General	1 MHz - 3 GHz
BLM21PG600SN1	60		0.02	3500	2012/0805	General	1 MHz - 3 GHz
BLM21PG601SN1	600		0.14	1400	2012/0805	General	1 MHz - 3 GHz
BLM21PG121SZ1	120		0.03	3000	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21PG220SZ1	22		0.009	6000	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21PG221SZ1	220		0.045	2000	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21PG300SZ1	30		0.014	4000	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21PG331SZ1	330		0.07	1500	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21PG600SZ1	60		0.02	3500	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21PG102BH1	1000		0.2	1150	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21PG102SH1	1000		0.2	1150	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21PG121BH1	120		0.03	1550	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21PG121SH1	120		0.03	3000	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21PG220BH1	22		0.009	3300	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21PG220SH1	22		0.009	6000	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21PG221BH1	220		0.045	1250	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21PG221SH1	220		0.045	2000	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21PG300BH1	30		0.014	2300	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21PG300SH1	30		0.014	4000	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21PG331BH1	330		0.07	1000	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21PG331SH1	330		0.07	1500	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21PG600BH1	60		0.02	1900	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21PG600SH1	60		0.02	3500	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21PG601BH1	600		0.14	1400	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21PG601SH1	600		0.14	1400	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21RK102SN1	1000		0.5	200	2012/0805	General	1 MHz - 3 GHz
BLM21RK121SN1	120		0.15	200	2012/0805	General	1 MHz - 3 GHz
BLM21RK221SN1	220		0.2	200	2012/0805	General	1 MHz - 3 GHz
BLM21RK471SN1	470		0.25	200	2012/0805	General	1 MHz - 3 GHz
BLM21RK601SN1	600		0.3	200	2012/0805	General	1 MHz - 3 GHz
BLM21SN300SN1	30		0.004	8500	2012/0805	General	1 MHz - 3 GHz
BLM21SN300SZ1	30		0.004	8500	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21SN300SH1	30		0.004	8500	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21SP102SN1	1000		0.12	1600	2012/0805	General	1 MHz - 3 GHz
BLM21SP111SN1	110		0.013	5000	2012/0805	General	1 MHz - 3 GHz
BLM21SP181SN1	180		0.02	4000	2012/0805	General	1 MHz - 3 GHz
BLM21SP331SN1	330		0.04	2800	2012/0805	General	1 MHz - 3 GHz
BLM21SP471SN1	470		0.05	2500	2012/0805	General	1 MHz - 3 GHz
BLM21SP601SN1	600		0.06	2300	2012/0805	General	1 MHz - 3 GHz
BLM21SP700SN1	70		0.009	6000	2012/0805	General	1 MHz - 3 GHz
BLM21SP102SZ1	1000		0.12	1600	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21SP111SZ1	110		0.013	5000	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21SP181SZ1	180		0.02	4000	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21SP331SZ1	330		0.04	2800	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21SP471SZ1	470		0.05	2500	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21SP601SZ1	600		0.06	2300	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21SP700SZ1	70		0.009	6000	2012/0805	Infotainment	1 MHz - 3 GHz
BLM21SP102BH1	1000		0.12	1600	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21SP102SH1	1000		0.12	1600	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21SP111BH1	110		0.013	5000	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21SP111SH1	110		0.013	5000	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21SP181BH1	180		0.02	4000	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21SP181SH1	180		0.02	4000	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21SP331BH1	330		0.04	2800	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21SP331SH1	330		0.04	2800	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21SP471BH1	470		0.05	2500	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21SP471SH1	470		0.05	2500	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21SP601BH1	600		0.06	2300	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21SP601SH1	600		0.06	2300	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21SP700BH1	70		0.009	6000	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM21SP700SH1	70		0.009	6000	2012/0805	Powertrain/Safety	1 MHz - 3 GHz
BLM31AJ601SH1	600		0.9	200	3216/1206	Powertrain/Safety	1 MHz - 3 GHz
BLM31KN102SN1	1000		0.075	2000	3216/1206	General	1 MHz - 3 GHz
BLM31KN121SN1	120		0.009	6000	3216/1206	General	1 MHz - 3 GHz
BLM31KN271SN1	270		0.016	4500	3216/1206	General	1 MHz - 3 GHz
BLM31KN471SN1	470		0.02	4000	3216/1206	General	1 MHz - 3 GHz
BLM31KN601SN1	600		0.038	2900	3216/1206	General	1 MHz - 3 GHz
BLM31KN801SN1	800		0.05	2500	3216/1206	General	1 MHz - 3 GHz
BLM31KN102SZ1	1000		0.075	2000	3216/1206	Infotainment	1 MHz - 3 GHz
BLM31KN121SZ1	120		0.009	6000	3216/1206	Infotainment	1 MHz - 3 GHz
BLM31KN271SZ1	270		0.016	4500	3216/1206	Infotainment	1 MHz - 3 GHz
BLM31KN471SZ1	470		0.02	4000	3216/1206	Infotainment	1 MHz - 3 GHz
BLM31KN601SZ1	600		0.038	2900	3216/1206	Infotainment	1 MHz - 3 GHz
BLM31KN801SZ1	800		0.05	2500	3216/1206	Infotainment	1 MHz - 3 GHz
BLM31KN102BH1	1000		0.075	1400	3216/1206	Powertrain/Safety	1 MHz - 3 GHz
BLM31KN102SH1	1000		0.075	2000	3216/1206	Powertrain/Safety	1 MHz - 3 GHz
BLM31KN121BH1	120		0.009	4000	3216/1206	Powertrain/Safety	1 MHz - 3 GHz
BLM31KN121SH1	120		0.009	6000	3216/1206	Powertrain/Safety	1 MHz - 3 GHz
BLM31KN271BH1	270		0.016	3000	3216/1206	Powertrain/Safety	1 MHz - 3 GHz
BLM31KN271SH1	270		0.016	4500	3216/1206	Powertrain/Safety	1 MHz - 3 GHz
BLM31KN471BH1	470		0.02	2700	3216/1206	Powertrain/Safety	1 MHz - 3 GHz
BLM31KN471SH1	470		0.02	4000	3216/1206	Powertrain/Safety	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
BLM31KN601BH1	600		0.038	2000	3216/1206	Powertrain/Safety	1 MHz - 3 GHz
BLM31KN601SH1	600		0.038	2900	3216/1206	Powertrain/Safety	1 MHz - 3 GHz
BLM31KN801BH1	800		0.05	1700	3216/1206	Powertrain/Safety	1 MHz - 3 GHz
BLM31KN801SH1	800		0.05	2500	3216/1206	Powertrain/Safety	1 MHz - 3 GHz
BLM31PG121SN1	120		0.02	3500	3216/1206	General	1 MHz - 3 GHz
BLM31PG330SN1	33		0.009	6000	3216/1206	General	1 MHz - 3 GHz
BLM31PG391SN1	390		0.05	2000	3216/1206	General	1 MHz - 3 GHz
BLM31PG500SN1	50		0.015	3500	3216/1206	General	1 MHz - 3 GHz
BLM31PG601SN1	600		0.08	1500	3216/1206	General	1 MHz - 3 GHz
BLM31PG121SZ1	120		0.02	3500	3216/1206	Infotainment	1 MHz - 3 GHz
BLM31PG330SZ1	33		0.009	6000	3216/1206	Infotainment	1 MHz - 3 GHz
BLM31PG391SZ1	390		0.05	2000	3216/1206	Infotainment	1 MHz - 3 GHz
BLM31PG500SZ1	50		0.015	3500	3216/1206	Infotainment	1 MHz - 3 GHz
BLM31PG601SZ1	600		0.08	1500	3216/1206	Infotainment	1 MHz - 3 GHz
BLM31PG121SH1	120		0.02	3500	3216/1206	Powertrain/Safety	1 MHz - 3 GHz
BLM31PG330SH1	33		0.009	6000	3216/1206	Powertrain/Safety	1 MHz - 3 GHz
BLM31PG391SH1	390		0.05	2000	3216/1206	Powertrain/Safety	1 MHz - 3 GHz
BLM31PG500SH1	50		0.015	3500	3216/1206	Powertrain/Safety	1 MHz - 3 GHz
BLM31PG601SH1	600		0.08	1500	3216/1206	Powertrain/Safety	1 MHz - 3 GHz
BLM31SN500SN1	50		0.0016	12000	3216/1206	General	1 MHz - 3 GHz
BLM31SN500SZ1	50		0.0016	12000	3216/1206	Infotainment	1 MHz - 3 GHz
BLM31SN500BH1	50		0.0016	12000	3216/1206	Powertrain/Safety	1 MHz - 3 GHz
BLM31SN500SH1	50		0.0016	12000	3216/1206	Powertrain/Safety	1 MHz - 3 GHz
BLM41PG102SN1	1000		0.09	1500	4516/1806	General	1 MHz - 3 GHz
BLM41PG181SN1	180		0.02	3500	4516/1806	General	1 MHz - 3 GHz
BLM41PG471SN1	470		0.05	2000	4516/1806	General	1 MHz - 3 GHz
BLM41PG600SN1	60		0.009	6000	4516/1806	General	1 MHz - 3 GHz
BLM41PG750SN1	75		0.015	3500	4516/1806	General	1 MHz - 3 GHz
BLM41PG102SZ1	1000		0.09	1500	4516/1806	Infotainment	1 MHz - 3 GHz
BLM41PG181SZ1	180		0.02	3500	4516/1806	Infotainment	1 MHz - 3 GHz
BLM41PG471SZ1	470		0.05	2000	4516/1806	Infotainment	1 MHz - 3 GHz
BLM41PG600SZ1	60		0.009	6000	4516/1806	Infotainment	1 MHz - 3 GHz
BLM41PG750SZ1	75		0.015	3500	4516/1806	Infotainment	1 MHz - 3 GHz
BLM41PG102SH1	1000		0.09	1500	4516/1806	Powertrain/Safety	1 MHz - 3 GHz
BLM41PG181SH1	180		0.02	3500	4516/1806	Powertrain/Safety	1 MHz - 3 GHz
BLM41PG471SH1	470		0.05	2000	4516/1806	Powertrain/Safety	1 MHz - 3 GHz
BLM41PG600SH1	60		0.009	6000	4516/1806	Powertrain/Safety	1 MHz - 3 GHz
BLM41PG750SH1	75		0.015	3500	4516/1806	Powertrain/Safety	1 MHz - 3 GHz
BLT5BPT680LN1	68		0.01	11000	5050/2020	General	1 MHz - 3 GHz
NFZ03SG102SN10			1.3	210	0603/0201	General	1 MHz - 3 GHz
NFZ03SG162SN10			1.7	180	0603/0201	General	1 MHz - 3 GHz
NFZ03SG331SN10			0.6	305	0603/0201	General	1 MHz - 3 GHz
NFZ03SG501SN10			0.73	275	0603/0201	General	1 MHz - 3 GHz
NFZ03SG671SN10			0.88	250	0603/0201	General	1 MHz - 3 GHz
NFZ15SF102SN10	1000		1.4	230	1005/0402	General	1 MHz - 3 GHz
NFZ15SF102SZ10	1000		1.4	230	1005/0402	Infotainment	1 MHz - 3 GHz
NFZ15SG101SN11			0.1	1100	1005/0402	General	1 MHz - 3 GHz
NFZ15SG151SN11			0.12	1000	1005/0402	General	1 MHz - 3 GHz
NFZ15SG152SN10			0.8	400	1005/0402	General	1 MHz - 3 GHz
NFZ15SG262SN10			1	350	1005/0402	General	1 MHz - 3 GHz
NFZ15SG331SN11			0.3	650	1005/0402	General	1 MHz - 3 GHz
NFZ15SG462SN10			1.65	270	1005/0402	General	1 MHz - 3 GHz
NFZ15SG771SN10			0.5	500	1005/0402	General	1 MHz - 3 GHz
NFZ18SM121SN10	120		0.14	1250	1608/0603	General	1 MHz - 3 GHz
NFZ18SM251SN10	250		0.19	1100	1608/0603	General	1 MHz - 3 GHz
NFZ18SM501SN10	500		0.25	950	1608/0603	General	1 MHz - 3 GHz
NFZ18SM701SN10	700		0.29	800	1608/0603	General	1 MHz - 3 GHz
NFZ18SM121SZ10	120		0.14	1250	1608/0603	Infotainment	1 MHz - 3 GHz
NFZ18SM251SZ10	250		0.19	1100	1608/0603	Infotainment	1 MHz - 3 GHz
NFZ18SM501SZ10	500		0.25	950	1608/0603	Infotainment	1 MHz - 3 GHz
NFZ18SM701SZ10	700		0.29	800	1608/0603	Infotainment	1 MHz - 3 GHz
NFZ2HBM110SN10			0.04	800	2520/1008	General	1 MHz - 3 GHz
NFZ2HBM170SN10			0.053	700	2520/1008	General	1 MHz - 3 GHz
NFZ2HBM1R5SN10			0.015	1200	2520/1008	General	1 MHz - 3 GHz
NFZ2HBM240SN10			0.063	650	2520/1008	General	1 MHz - 3 GHz
NFZ2HBM2R9SN10			0.021	1100	2520/1008	General	1 MHz - 3 GHz
NFZ2HBM330SN10			0.075	500	2520/1008	General	1 MHz - 3 GHz
NFZ2HBM4R4SN10			0.026	1050	2520/1008	General	1 MHz - 3 GHz
NFZ2HBM600SN10			0.075	400	2520/1008	General	1 MHz - 3 GHz
NFZ2HBM6R1SN10			0.031	1000	2520/1008	General	1 MHz - 3 GHz
NFZ2HBM8R4SN10			0.036	900	2520/1008	General	1 MHz - 3 GHz
NFZ2MSD100SN10			0.02	5200	2016/0806	General	1 MHz - 3 GHz
NFZ2MSD131SN10			0.144	1500	2016/0806	General	1 MHz - 3 GHz
NFZ2MSD150SN10			0.023	4400	2016/0806	General	1 MHz - 3 GHz
NFZ2MSD200SN10			0.028	3900	2016/0806	General	1 MHz - 3 GHz
NFZ2MSD300SN10			0.033	3700	2016/0806	General	1 MHz - 3 GHz
NFZ2MSD600SN10			0.054	2700	2016/0806	General	1 MHz - 3 GHz
NFZ2MSD900SN10			0.095	2000	2016/0806	General	1 MHz - 3 GHz
NFZ2MSD101SZ10	100		0.018	5.2	2016/0806	Infotainment	1 MHz - 3 GHz
NFZ2MSD102SZ10	1000		0.046	2.5	2016/0806	Infotainment	1 MHz - 3 GHz
NFZ2MSD181SZ10	180		0.022	4	2016/0806	Infotainment	1 MHz - 3 GHz
NFZ2MSD301SZ10	300		0.026	3.8	2016/0806	Infotainment	1 MHz - 3 GHz
NFZ2MSD501SZ10	500		0.032	3.2	2016/0806	Infotainment	1 MHz - 3 GHz
NFZ2MSM101SN10	100		0.018	4000	2016/0806	General	1 MHz - 3 GHz
NFZ2MSM181SN10	180		0.025	3400	2016/0806	General	1 MHz - 3 GHz
NFZ2MSM301SN10	300		0.03	3100	2016/0806	General	1 MHz - 3 GHz
NFZ2MSM601SN10	600		0.046	2500	2016/0806	General	1 MHz - 3 GHz
NFZ32BW101HN11			0.57	900	3225/1210	General	1 MHz - 3 GHz
NFZ32BW111HN10			0.684	520	3225/1210	General	1 MHz - 3 GHz
NFZ32BW120HN11			0.0768	1850	3225/1210	General	1 MHz - 3 GHz
NFZ32BW150HN10			0.0912	1600	3225/1210	General	1 MHz - 3 GHz
NFZ32BW151HN10			0.972	450	3225/1210	General	1 MHz - 3 GHz
NFZ32BW151HN11			0.822	700	3225/1210	General	1 MHz - 3 GHz
NFZ32BW190HN11			0.1068	1800	3225/1210	General	1 MHz - 3 GHz
NFZ32BW210HN10			0.144	1200	3225/1210	General	1 MHz - 3 GHz
NFZ32BW210HN11			0.12	1550	3225/1210	General	1 MHz - 3 GHz
NFZ32BW221HN10			1.38	390	3225/1210	General	1 MHz - 3 GHz
NFZ32BW291HN10			2.14	310	3225/1210	General	1 MHz - 3 GHz

Part Number	Impedance @100MHz (ohm)	Impedance @1GHz (ohm)	DC Resistance max. (ohm)	Rated Current (mA)	Size Code (mm/inch)	Application	Frequency Range (simulation model)
NFZ32BW310HN11			0.186	1200	3225/1210	General	1 MHz - 3 GHz
NFZ32BW320HN10			0.216	1000	3225/1210	General	1 MHz - 3 GHz
NFZ32BW3R3HN11			0.0288	2900	3225/1210	General	1 MHz - 3 GHz
NFZ32BW3R6HN10			0.036	2550	3225/1210	General	1 MHz - 3 GHz
NFZ32BW420HN10			0.288	850	3225/1210	General	1 MHz - 3 GHz
NFZ32BW451HN10			2.74	275	3225/1210	General	1 MHz - 3 GHz
NFZ32BW520HN11			0.264	1100	3225/1210	General	1 MHz - 3 GHz
NFZ32BW621HN10			3.24	250	3225/1210	General	1 MHz - 3 GHz
NFZ32BW650HN11			0.354	900	3225/1210	General	1 MHz - 3 GHz
NFZ32BW6R8HN11			0.0432	2500	3225/1210	General	1 MHz - 3 GHz
NFZ32BW700HN10			0.456	700	3225/1210	General	1 MHz - 3 GHz
NFZ32BW7R4HN10			0.054	2050	3225/1210	General	1 MHz - 3 GHz
NFZ32BW881HN10			5.26	200	3225/1210	General	1 MHz - 3 GHz
NFZ32BW8R4HN11			0.0576	2400	3225/1210	General	1 MHz - 3 GHz
NFZ32BW9R0HN10			0.0684	1750	3225/1210	General	1 MHz - 3 GHz
NFZ32BW9R8HN11			0.0636	2100	3225/1210	General	1 MHz - 3 GHz
NFZ32BW101HZ11			0.57	900	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW111HZ10			0.684	520	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW120HZ11			0.0768	1850	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW150HZ10			0.0912	1600	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW151HZ10			0.972	450	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW151HZ11			0.822	700	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW190HZ11			0.1068	1800	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW210HZ10			0.144	1200	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW210HZ11			0.12	1550	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW221HZ10			1.38	390	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW291HZ10			2.14	310	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW310HZ11			0.186	1200	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW320HZ10			0.216	1000	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW3R3HZ11			0.0288	2900	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW3R6HZ10			0.036	2550	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW420HZ10			0.288	850	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW451HZ10			2.74	275	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW520HZ11			0.264	1100	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW621HZ10			3.24	250	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW650HZ11			0.354	900	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW6R8HZ11			0.0432	2500	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW700HZ10			0.456	700	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW7R4HZ10			0.054	2050	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW881HZ10			5.26	200	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW8R4HZ11			0.0576	2400	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW9R0HZ10			0.0684	1750	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32BW9R8HZ11			0.0636	2100	3225/1210	Infotainment	1 MHz - 3 GHz
NFZ32SW301HN10	300		0.036	2550	3225/1210	General	1 MHz - 3 GHz
NFZ32SW901HN10	900		0.054	2050	3225/1210	General	1 MHz - 3 GHz
NFZ5BBW100LN10			0.029	3000	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW140LN10			0.036	2600	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW141LN10			0.311	1050	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW170LN10			0.042	2500	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW220LN10			0.053	2300	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW2R9LN10			0.014	4000	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW310LN10			0.07	2000	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW450LN10			0.1	1650	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW4R5LN10			0.018	3400	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW520LN10			0.12	1610	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW610LN10			0.127	1600	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW6R7LN10			0.023	3100	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW7R6LN10			0.023	3100	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW970LN10			0.224	1200	5050/2020	General	1 MHz - 3 GHz
NFZ5BBW100LZ10			0.029	3000	5050/2020	Infotainment	1 MHz - 3 GHz
NFZ5BBW140LZ10			0.036	2600	5050/2020	Infotainment	1 MHz - 3 GHz
NFZ5BBW141LZ10			0.311	1050	5050/2020	Infotainment	1 MHz - 3 GHz
NFZ5BBW170LZ10			0.042	2500	5050/2020	Infotainment	1 MHz - 3 GHz
NFZ5BBW220LZ10			0.053	2300	5050/2020	Infotainment	1 MHz - 3 GHz
NFZ5BBW2R9LZ10			0.014	4000	5050/2020	Infotainment	1 MHz - 3 GHz
NFZ5BBW310LZ10			0.07	2000	5050/2020	Infotainment	1 MHz - 3 GHz
NFZ5BBW450LZ10			0.1	1650	5050/2020	Infotainment	1 MHz - 3 GHz
NFZ5BBW4R5LZ10			0.018	3400	5050/2020	Infotainment	1 MHz - 3 GHz
NFZ5BBW520LZ10			0.12	1610	5050/2020	Infotainment	1 MHz - 3 GHz
NFZ5BBW610LZ10			0.127	1600	5050/2020	Infotainment	1 MHz - 3 GHz
NFZ5BBW6R7LZ10			0.023	3100	5050/2020	Infotainment	1 MHz - 3 GHz
NFZ5BBW7R6LZ10			0.023	3100	5050/2020	Infotainment	1 MHz - 3 GHz
NFZ5BBW970LZ10			0.224	1200	5050/2020	Infotainment	1 MHz - 3 GHz