

Product Search Data Sheet

MHR0312SA205G70

In Production RoHS REACH

Applications

Unsuitable	Please be sure to read and comply with	
Applications	these "Precautions for use."	
	Consumer equipment, Industrial	
	Equipment,Medical equipment [GHTF	
	A/B]	
	Please refer to Our Website and	
Creatific	specifications, etc. for information about	
Specific	the performance, functions, quality,	
Applications	management, and safety required for	
	the above applications, and use	
	Products after confirming the	
	performance and reliability of the actual	
	Product.	
	Copier,Printer,High-Voltage-Handling	
Recommended	Equipment,Healthcare [Medical	
	equipment[GHTF Class A/B]],White	
Applications	Goods,Air Purifier,Air Conditioner,Hair	
	Dryer,High-Voltage Power Supply	

Note: This datasheet may be out of date. Please download the latest datasheet of MHR0312SA205G70 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=MHR0312SA205G70

Packaging Information

Packaging	Specifications	Standard Packing Quantity
-	Bulk(Bag)	500

Appearance & Shape



(in mm)

1 of 2

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





MHR0312SA205G70

Note: This datasheet may be out of date. Please download the latest datasheet of MHR0312SA205G70 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=MHR0312SA205G70

Specifications

Power Rating	0.6W
Shape	Lead
Maximum Working Voltage	1kVdc
Resistance	2.0ΜΩ
Resistance Deviation	±2%
Single Use/Mold Use	Single use
Length	12.6mm
Height H	5.0mm
Lead Pitch P	10.16mm

2 of 2

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

