

# GJM0335C1E1R5CB01#

Note: This datasheet may be out of date.

Please download the latest datasheet of GJM0335C1E1R5CB01# from the official website of Murata

http://www.murata.com/en/products/productdetail?partno=G.IM0335C1E1R5CB01%23

"#"at the end indicates the package specification code.











< List of part numbers with package codes > GJM0335C1E1R5CB01D GJM0335C1E1R5CB01W GJM0335C1E1R5CB01V

GJM0335C1E1R5CB01J



### **Applications**

Unsuitable	Please be sure to read and comply with	
Applications	these "Precautions for use."	
Specific Applications	Consumer equipment,Industrial Equipment,Mobile Electronics,Medical equipment [GHTF A/B/C] except for implant equipment,Automotive infotainment/comfort equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.	



Manufacturing Co., Ltd.

### References

Packaging	Specifications	Standard Packing Quantity
D	φ180mm Reel Paper Tape	15000
W	φ180mm Reel W8P1 Paper Tape	30000
J	φ330mm Reel Paper Tape	50000
V	φ330mm Reel W8P1 Paper Tape	150000

Mass (typ.)	
1 piece	0.33mg



### Appearance & Shape





1 of 4

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

 $2. This \ data{sheet has only typical specifications because there is no \ space for \ detailed \ specifications.}$ 

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





# GJM0335C1E1R5CB01#

Note: This datasheet may be out of date.

Please download the latest datasheet of GJM0335C1E1R5CB01# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=GJM0335C1E1R5CB01%23

"#"at the end indicates the package specification code.



## **Specifications**

Length	0.6±0.03mm
Width	0.3±0.03mm
Thickness	0.3±0.03mm
Capacitance	1.5pF ±0.25pF
Distance between external terminals g	0.2mm min.
External terminal size e	0.1 to 0.2mm
Operating Temperature Range	-55°C to 125°C
Rated Voltage	25Vdc
Size code in inch(mm)	0201 (0603M)
TC	0±30ppm/°C
Temperature characteristics (complied standard)	C0G(EIA)
Temperature range of temperature characteristics	25°C to 125°C

2 of 4

#### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



### **Product Search Data Sheet**

Note: This datasheet may be out of date. Please download the latest datasheet of GJM0335C1E1R5CB01# from the official website of Murata Manufacturing Co., Ltd.


"#"at the end indicates the package specification code.


# GJM0335C1E1R5CB01#





### Characteristic Data

The charts below may show another part number which shares its characteristics.









3 of 4

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering






# GJM0335C1E1R5CB01#

Note: This datasheet may be out of date.


Please download the latest datasheet of GJM0335C1E1R5CB01# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=GJM0335C1E1R5CB01%2

"#"at the end indicates the package specification code.



GJM0335C1E1R5CB01 C-Temp. capchange, DCOV, 1



4 of 4

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

