

NFM41PC155B1E3#

“#” at the end indicates the package specification code.



< List of part numbers with package codes >
NFM41PC155B1E3L

Applications


Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Consumer equipment, Industrial Equipment, Mobile Electronics, Medical equipment [GHTE A/B/C] except for implant equipment, Automotive infotainment/comfort equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.

References

Packaging	Specifications	Standard Packing Quantity
L	180 Embossed Tape	4000

Mass (typ.)	
1 piece	38.7mg

Appearance & Shape



Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

NFM41PC155B1E3#

“#” at the end indicates the package specification code.



Specifications

Length	4.5±0.3mm
Width	1.6±0.3mm
Thickness	1.0±0.2mm
Capacitance	1.5μF ±20%
Distance between external terminals g	0.7mm min.
DC Resistance(max.)	9mΩ
External terminal size e	0.4±0.3mm
External terminal size i	1.5±0.3mm
External terminal size J	0.3+0.3/-0.2mm
Operating Temperature Range	-55°C to 85°C
Rated Current	6A
Rated Voltage	25Vdc
Size code in inch(mm)	1806 (4516M)

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


NFM41PC155B1E3#

“#” at the end indicates the package specification code.



Characteristic Data

The charts below may show another part number which shares its characteristics.



Frequency [Hz]

NFM41PC155B1E3 S21 DCOV, 25degC, Feedthrough

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.