

# MHR0622SA507F70

Note: This datasheet may be out of date. Please download the latest datasheet of MHR0622SA507F70 from the official website of Murata  $\,$ Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=MHR0622SA507F70









### **Applications**

Unsuitable	Please he sure to read and comply with	
	Please be sure to read and comply with	
Applications	these "Precautions for use."	
	Consumer equipment,Industrial	
	Equipment,Medical equipment [GHTF	
	A/B]	
	Please refer to Our Website and	
Charifia	specifications, etc. for information about	
Specific	the performance, functions, quality,	
Applications	management, and safety required for	
	the above applications, and use	
	Products after confirming the	
	performance and reliability of the actual	
	Product.	
	Copier,Printer,High-Voltage-Handling	
December	Equipment,Healthcare [Medical	
Recommended	equipment[GHTF Class A/B]],White	
Applications	Goods,Air Purifier,Air Conditioner,Hair	
	Dryer,High-Voltage Power Supply	



### **Packaging Information**

	Packaging		Standard Packing Quantity
	-	Bulk(Bag)	250



### Appearance & Shape



(in mm)

1 of 2

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





# MHR0622SA507F70

Note: This datasheet may be out of date.

Please download the latest datasheet of MHR0622SA507F70 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=MHR0622SA507F70



## **Specifications**

Power Rating	1.5W
Shape	Lead
Maximum Working Voltage	9kVdc
Resistance	500.0ΜΩ
Resistance Deviation	±1%
Single Use/Mold Use	Single use
Length	22.7mm
Height H	9.0mm
Lead Pitch P	20.32mm

2 of 2

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

