

1226AS-H-R47N#



“#” indicates a package specification code.



< List of part numbers with package codes >

1226AS-H-R47N=P2

Appearance & Shape



References

Packaging	Specifications	Minimum Order Quantity
=P2	180Embossed Tape	2000

Mass (typ.)	
1 piece	0.0524g

Notices

Rated current (I_{sat}) is specified when the decrease of the initial inductance value at 30%. Rated current (I_{temp}) is specified when temperature of the inductor is raised 40°C by DC current.

Attention

- This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

1226AS-H-R47N#

“#” indicates a package specification code.

Specifications

L size	3.0±0.2mm
W size	2.8±0.2mm
T size	1.5mm
Size code inch (mm)	1211 (3028)
Inductance	0.47μH±30%
Inductance Test Frequency	0.1MHz
Rated current (I _{sat}) (Based on Inductance change)	2900mA
Rated current (I _{temp}) (Based on Temperature rise)	3900mA
Max. of DC resistance	0.024Ω
Operating Temperature Range (Self-temperature rise is included)	-40°C to 85°C
Class of magnetic shield	Ferrite Core
DC Resistance Intermediate Values	0.020Ω+20%/-30%
Series	DEM2815C

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

1226AS-H-R47N#


"#" indicates a package specification code.

Characteristic Data


The charts below may show another part number which shares its characteristics.



■ 1226AS-H-R47N L



■ 1226AS-H-R47N Q



■ 1226AS-H-R47N |Z|

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
 - 2.This datasheet has only typical specifications because there is no space for detailed specifications.
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.