

DE2E3KY222MN2AM01F



Applications

| | |
|-------------------------|--|
| Unsuitable Applications | Please be sure to read and comply with these "Precautions for use." |
| Specific Applications | Consumer equipment, Industrial Equipment, Mobile Electronics, Medical equipment [GHTF A/B/C] except for implant equipment, Automotive infotainment/comfort equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product. |

Notices


Please use replacements or Recommended. X1/Y2 Class Certified Products, Halogen-free Products

References

| Packaging | Specifications | Standard Packing Quantity |
|-----------|----------------|---------------------------|
| A | Ammo Pack | 1000 |

Appearance & Shape

| Mass (typ.) | |
|-------------|-------|
| 1 piece | 0.41g |



Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

DE2E3KY222MN2AM01F



Specifications

| | |
|--|------------------------|
| L size or Outer diameter D | 8.0mm max. |
| T size | 5.0mm max. |
| Lead spacing F | 5.0+0.8/-0.2mm |
| Lead diameter d | 0.6±0.05mm |
| Paint dripping e | Up to the end of crimp |
| Capacitance | 2200pF ±20% |
| Rated voltage | 250Vac(r.m.s.) |
| Temperature characteristics | E(JIS) |
| Capacitance change rate | +20/-55% |
| Temperature range of temperature characteristics | -25°C to 85°C |
| Operating Temperature Range | -40°C to 125°C |

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.


Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

DE2E3KY222MN2AM01F




Characteristic Data


The charts below may show another part number which shares its characteristics.




DE2E3KY222MN2AM01F |Z| DCOV, 20degC



DE2E3KY222MN2AM01F R DCOV, 20degC



DE2E3KY222MN2AM01F C-DC bias capchange, 20.0



DE2E3KY222MN2AM01F C-AC Voltage capchange, I


Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.


2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

DE2E3KY222MN2AM01F



DE2E3KY222MN2AM01F C-Temp. capchange, DCOV,



DE2E3KY222MN2AM01F S21 DCOV, 20degC

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.