

Product Search Data Sheet

# MHR0422SA257K20

In Production RoHS REACH

### Applications

Unsuitable	Please be sure to read and comply with
Applications	these "Precautions for use."
	Consumer equipment, Industrial
	Equipment,Medical equipment [GHTF
	A/B]
	Please refer to Our Website and
Creatific	specifications, etc. for information about
Specific	the performance, functions, quality,
Applications	management, and safety required for
	the above applications, and use
	Products after confirming the
	performance and reliability of the actual
	Product.
	Copier,Printer,High-Voltage-Handling
Recommended	Equipment,Healthcare [Medical
	equipment[GHTF Class A/B]],White
Applications	Goods,Air Purifier,Air Conditioner,Hair
	Dryer,High-Voltage Power Supply

Note: This datasheet may be out of date. Please download the latest datasheet of MHR0422SA257K20 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=MHR0422SA257K20

## Packaging Information

Packaging	Specifications	Standard Packing Quantity
-	Bulk(Bag)	250

## Appearance & Shape



(in mm)

### 1 of 2

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





# MHR0422SA257K20

Note: This datasheet may be out of date. Please download the latest datasheet of MHR0422SA257K20 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=MHR0422SA257K20

## Specifications

Power Rating	1.3W
Shape	Lead
Maximum Working Voltage	16kVdc
Resistance	250.0ΜΩ
Resistance Deviation	±10%
Single Use/Mold Use	Molded use
Length	22.7mm
Height H	6.5mm
Lead Pitch P	20.32mm

2 of 2

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

