



PVZ2A474C04B00

Discontinued

RoHS

REACH

Appearance & Shape



Features

1. Ultra-small and thin external dimensions of 2.1(W)x2.7(L)x0.85 max. (T)mm.
(Top adjustment type: PVZ2A_C04 Series)
2. Au plated termination achieves a high-density PCB mounting.
3. Cross-shaped driver slot allows for in-process automatic adjustment and it provides superior adjustability.
4. Two-piece parts construction achieves low cost and excellent quality.

Packaging Information

Packaging	Specifications	Standard Packing Quantity
B00	Bulk(Bag)	1000

Attention
1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

PVZ2A474C04B00



Specifications

Power Rating	0.05W
Shape	SMD
Maximum Working Voltage	50Vdc
Adjustment Direction	Top
Size	2mm
Auto Adjustment	Yes
Number of Turns (Effective Rotation Angle)	1(240°±10°)
Mechanical Rotation Angle	Endless
Total Resistance Value	470kΩ
Total Resistance Value Tolerance	±30%
Temperature Coefficient of Resistance	±500ppm/°C
Resistance Taper	B (Linear)
Contact Resistance Variation	5% max. of nominal total resistance value
Residual Resistance	2% max. of nominal total resistance value
Torque	1.0 to 9.8mN · m
Measure Condition of RatedPower	50°C
Operating Temperature Range	-25°C to 85°C
Mass	0.01g

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.


2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

PVZ2A474C04B00



Product Data



Constructions

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.