

Product Search Data Sheet

# MHR0622SA807G20

In Production RoHS REACH

## Applications

Unsuitable	Please be sure to read and comply with	
Applications	these "Precautions for use."	
	Consumer equipment, Industrial	
	Equipment,Medical equipment [GHTF	
	A/B]	
	Please refer to Our Website and	
Onesifie	specifications, etc. for information about	
Specific	the performance, functions, quality,	
Applications	management, and safety required for	
	the above applications, and use	
	Products after confirming the	
	performance and reliability of the actual	
	Product.	
	Copier,Printer,High-Voltage-Handling	
Recommended	Equipment,Healthcare [Medical	
	equipment[GHTF Class A/B]],White	
Applications	Goods,Air Purifier,Air Conditioner,Hair	
	Dryer,High-Voltage Power Supply	

Note: This datasheet may be out of date. Please download the latest datasheet of MHR0622SA807G20 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=MHR0622SA807G20

# Packaging Information

Packaging	Specifications	Standard Packing Quantity
-	Bulk(Bag)	250



### Appearance & Shape



(in mm)



#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





# MHR0622SA807G20

Note: This datasheet may be out of date. Please download the latest datasheet of MHR0622SA807G20 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=MHR0622SA807G20

## Specifications

Power Rating	1.5W
Shape	Lead
Maximum Working Voltage	18kVdc
Resistance	800.0MΩ
Resistance Deviation	±2%
Single Use/Mold Use	Molded use
Length	22.7mm
Height H	9.0mm
Lead Pitch P	20.32mm

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



2 of 2