




CSTCE16M0V13C99-R0	CSTNE16M0VH3C000R0																								
電気特性 Electrical Characteristics <table> <tr> <td>公称発振周波数 Nominal Oscillating Frequency</td><td>16.000MHz</td></tr> <tr> <td>共振抵抗 Resonant Impedance</td><td>40Ωmax.</td></tr> <tr> <td>発振周波数初期公差 Initial Tolerance</td><td>±0.1%max.</td></tr> <tr> <td>発振周波数温度依存性 Frequency Shift by Temperature(-40 to 125[° C])</td><td>±0.13%max. (from initial value)</td></tr> <tr> <td>発振周波数エージング Oscillating Frequency Aging</td><td>±0.07%max. (from initial value)</td></tr> <tr> <td>内蔵容量 Built-in Load Capacitance</td><td>15pF±20%max.</td></tr> </table>	公称発振周波数 Nominal Oscillating Frequency	16.000MHz	共振抵抗 Resonant Impedance	40Ωmax.	発振周波数初期公差 Initial Tolerance	±0.1%max.	発振周波数温度依存性 Frequency Shift by Temperature(-40 to 125[° C])	±0.13%max. (from initial value)	発振周波数エージング Oscillating Frequency Aging	±0.07%max. (from initial value)	内蔵容量 Built-in Load Capacitance	15pF±20%max.	電気特性 Electrical Characteristics <table> <tr> <td>公称発振周波数 Nominal Oscillating Frequency</td><td>16.000MHz</td></tr> <tr> <td>共振抵抗 Resonant Impedance</td><td>40Ωmax.</td></tr> <tr> <td>発振周波数初期公差 Initial Tolerance</td><td>±0.07%max.</td></tr> <tr> <td>発振周波数温度依存性 Frequency Shift by Temperature(-40 to 125[° C])</td><td>±0.13%max. (from initial value)</td></tr> <tr> <td>発振周波数エージング Oscillating Frequency Aging</td><td>±0.07%max. (from initial value)</td></tr> <tr> <td>内蔵容量 Built-in Load Capacitance</td><td>15pF±20%max.</td></tr> </table>	公称発振周波数 Nominal Oscillating Frequency	16.000MHz	共振抵抗 Resonant Impedance	40Ωmax.	発振周波数初期公差 Initial Tolerance	±0.07%max.	発振周波数温度依存性 Frequency Shift by Temperature(-40 to 125[° C])	±0.13%max. (from initial value)	発振周波数エージング Oscillating Frequency Aging	±0.07%max. (from initial value)	内蔵容量 Built-in Load Capacitance	15pF±20%max.
公称発振周波数 Nominal Oscillating Frequency	16.000MHz																								
共振抵抗 Resonant Impedance	40Ωmax.																								
発振周波数初期公差 Initial Tolerance	±0.1%max.																								
発振周波数温度依存性 Frequency Shift by Temperature(-40 to 125[° C])	±0.13%max. (from initial value)																								
発振周波数エージング Oscillating Frequency Aging	±0.07%max. (from initial value)																								
内蔵容量 Built-in Load Capacitance	15pF±20%max.																								
公称発振周波数 Nominal Oscillating Frequency	16.000MHz																								
共振抵抗 Resonant Impedance	40Ωmax.																								
発振周波数初期公差 Initial Tolerance	±0.07%max.																								
発振周波数温度依存性 Frequency Shift by Temperature(-40 to 125[° C])	±0.13%max. (from initial value)																								
発振周波数エージング Oscillating Frequency Aging	±0.07%max. (from initial value)																								
内蔵容量 Built-in Load Capacitance	15pF±20%max.																								
外形寸法図 Dimensions W : 3.20±0.15 □ : A L : 1.30±0.15 * : 製造年月度 T : 0.90±0.10 (EIAJ Monthly Code) unit : [mm] 	外形寸法図 Dimensions W : 3.20±0.15 □ : A L : 1.30±0.15 * : 製造年月度 T : 0.90±0.10 (EIAJ Monthly Code) unit : [mm] 																								
推奨ランド寸法 Recommendable Land Pattern (推奨ランド寸法) (Recommendable Land Pattern) 	推奨ランド寸法 Recommendable Land Pattern (推奨ランド寸法) (Recommendable Land Pattern) 