

LFB215G78SG8A170

In Production

Recommended

RoHS

REACH

Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Consumer equipment, Industrial Equipment, Medical equipment [GHTF A/B], Mobile Electronics Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.
Recommended Applications	Consumer equipment, Industrial Equipment, Medical equipment [GHTF A/B], Mobile Electronics

Packaging Information

Packaging	Specifications	Standard Packing Quantity
-	180mm Embossed Tape	4000

Features

Ultra-small, low-profiled, lightweight chip filters based on ceramic multilayer technology.
Extremely ultra-small band-pass filters.

1. Ultra-small, low-profiled, lightweight band-pass filters.
2. Absolutely no adjustment required.
3. Reflow solderable.
4. Available in tape and reel packagings for automatic mounting.

Appearance & Shape



Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

LFB215G78SG8A170



Specifications

Applications	WiFi
Nominal Center Frequency (fo)	5787.50MHz
Bandwidth(BW)	fo±62.50MHz
Insertion Loss in BW I)	2.20dB max. (at 25°C)
Insertion Loss in BW II)	2.50dB max. (-40 to +85°C)
Attenuation(Absolute Value) I)	35.0dB min. at 3275.00 to 3400.00MHz
Attenuation(Absolute Value) II)	37.0dB min. at 2x(fo±62.5)MHz
Attenuation(Absolute Value) III)	25.0dB min. at 3x(fo±62.5)MHz
Attenuation(Absolute Value) IV)	10.0dB min. at 6800.00MHz
Ripple(max.)	1.2dB
VSWR(max.)	2.0
Characteristic Impedance (Nom.)	50Ω
Power Capacity	1W
Operating Temperature Range	-40°C to 85°C
L x W (size)	2.00x1.25mm
Thickness(max.)	1.05mm

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.