

Product Search Data Sheet

PTGL7SARR47M1B51A0

Discontinued

RoHS REACH


Applications

Unsuitable	Please be sure to read and comply with
Applications	these "Precautions for use."
	Automotive powertrain/safety equipment
	Please refer to Our Website and
	specifications, etc. for information about
Onesifie	the performance, functions, quality,
Specific	management, and safety required for
Applications	the above applications, and use
	Products after confirming the
	performance and reliability of the actual
	Product.




Appearance & Shape





D max



(in mm)

Note: This datasheet may be out of date. Please download the latest datasheet of PTGL7SARR47M1B51A0 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-gb/products/productdetail?partno=PTGL7SARR47M1B51A0

Packaging Information

Packaging		Standard Packing Quantity
A0	Ammo Pack	2000



 Best suited to meet the requirements for power supply and motor protection. Error-free operation is assured by rush current.
Circuit is protected until current is turned off.

3. Restores the original low resistance value automatically once the overload is removed.

4. Non-contact design leads to long life and no noise.

Durable and strong against mechanical vibration and shock because it is a solid element.

5. Lead (Pb) is not contained in the terminations.

1 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering





PTGL7SARR47M1B51A0

Note: This datasheet may be out of date. Please download the latest datasheet of PTGL7SARR47M1B51A0 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-gb/products/productdetail?partno=PTGL7SARR47M1B51A0

Specifications

Max. Voltage	16V
Hold Current(25°C)	705mA
Hold Current (2)	376mA
Measure Condition of Hold Current (2)	(at +85°C)
Trip Current(25°C)	1310mA
Trip Current(2)	1634mA
Measure Condition of Trip Current(2)	(at -30°C)
Max. Current	5A
Resistance (25°C)	0.47Ω
Resistance Value Tolerance (at 25°C)	±20%
Curie Point(typ.)	120℃
Power Consumption(typ)	1.5W
Operating Temperature Range	-30°C to 85°C
D- Outer Dimension	7.5mm
Thickness	3.5mm
H- Height	12mm
F- Lead Space	5mm
d- Lead Diameter	0.6mm
Shape	Lead
Mass	0.46g
MSL	Ν

2 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





PTGL7SARR47M1B51A0

Note: This datasheet may be out of date. Please download the latest datasheet of PTGL7SARR47M1B51A0 from the official website of Murata Manufacturing Co., Ltd.


http://www.murata.com/en-gb/products/productdetail?partno=PTGL7SARR47M1B51A0







Resistance-Temperature Charac.



1

Operating Time (Typical Curve)

Protective Threshold Current Range

3 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

