

# MHR0309SA406F70

In Production

RoHS

REACH

## Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Consumer equipment, Industrial Equipment, Medical equipment [GHTF A/B] Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.
Recommended Applications	Copier, Printer, High-Voltage-Handling Equipment, Healthcare [Medical equipment[GHTF Class A/B]], White Goods, Air Purifier, Air Conditioner, Hair Dryer, High-Voltage Power Supply

## Packaging Information

Packaging	Specifications	Standard Packing Quantity
-	Bulk(Bag)	1000

## Appearance & Shape



### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# MHR0309SA406F70



## Specifications

Power Rating	0.5W
Shape	Lead
Maximum Working Voltage	3.5kVdc
Resistance	40.0MΩ
Resistance Deviation	±1%
Single Use/Mold Use	Single use
Length	10.1mm
Height H	5.0mm
Lead Pitch P	7.62mm

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.