Note: This datasheet may be out of date.
Please download the latest datasheet of NTSA0WB203EE1B0 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-sg/products/productdetail?partno=NTSA0WB203EE1B0

NTSA0WB203EE1B0


Discontinued RoHS REACH

Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Industrial Equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.

Appearance & Shape





Packaging Information

Packaging	Specifications	Standard Packing Quantity
B0	Bulk(Bag)	500

Features

1. +/-1% of resistance and B-Constant tolerance is realized due to uniform thickness by the precise sheet forming method.
2. This product provides faster response time due to its smaller size.
3. Taping type is available.
4. Original lead-wiring technique assures reliable connection. It can be formed and bent flexibly according to the mounting conditions.

Attention
1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

Note: This datasheet may be out of date.
Please download the latest datasheet of NTSA0WB203EE1B0 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-sg/products/productdetail?partno=NTSA0WB203EE1B0

NTSA0WB203EE1B0

Specifications

Resistance (25℃)	20kΩ
Resistance Value Tolerance (at 25℃)	±3%
B-Constant (25/50℃)	4050K
B-Constant (25/50℃) Tolerance	±1%
B-Constant(25/80℃) (Reference Value)	4078K
B-Constant(25/85℃) (Reference Value)	4080K
B-Constant(25/100℃) (Reference Value)	4096K
Maximum Operating Current (25℃)	0.1mA
Rated Electric Power (25℃)	21.0mW
Typical Dissipation Constant (25℃)	2.1mW/℃
Operating Temperature Range	-40℃ to 125℃
Thermal Time Constant	7s
Lead Shape	Lead Wire type
Shape	Lead
Mass	0.08g
MSL	N


Attention
1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

Note: This datasheet may be out of date.
Please download the latest datasheet of NTSA0WB203EE1B0 from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-sg/products/productdetail?partno=NTSA0WB203EE1B0

NTSA0WB203EE1B0

Product Data



Temperature Tolenrance-Temperature Characteristics

Attention
1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
2.This datasheet has only typical specifications because there is no space for detailed specifications.
Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.