



PVZ2A471C04R00

Discontinued

RoHS

REACH

Appearance & Shape



Features

1. Ultra-small and thin external dimensions of 2.1(W)x2.7(L)x0.85 max. (T)mm. (Top adjustment type: PVZ2A_C04 Series)
2. Au plated termination achieves a high-density PCB mounting.
3. Cross-shaped driver slot allows for in-process automatic adjustment and it provides superior adjustability.
4. Two-piece parts construction achieves low cost and excellent quality.


Packaging Information

| Packaging | Specifications | Standard Packing Quantity |
|-----------|---------------------|---------------------------|
| R00 | 180mm Embossed Tape | 3000 |

Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

PVZ2A471C04R00



Specifications

| | |
|--|---|
| Power Rating | 0.05W |
| Shape | SMD |
| Maximum Working Voltage | 50Vdc |
| Adjustment Direction | Top |
| Size | 2mm |
| Auto Adjustment | Yes |
| Number of Turns (Effective Rotation Angle) | 1(240°±10°) |
| Mechanical Rotation Angle | Endless |
| Total Resistance Value | 470Ω |
| Total Resistance Value Tolerance | ±30% |
| Temperature Coefficient of Resistance | ±500ppm/°C |
| Resistance Taper | B (Linear) |
| Contact Resistance Variation | 5% max. of nominal total resistance value |
| Residual Resistance | 2% max. of nominal total resistance value |
| Torque | 1.0 to 9.8mN · m |
| Measure Condition of RatedPower | 50°C |
| Operating Temperature Range | -25°C to 85°C |
| Mass | 0.01g |

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.


2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

PVZ2A471C04R00



Product Data



Constructions

Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.